

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026730

Luminaire Tested: S125DIP-B1090D610UB2750-4F0-XX-W2A-D_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026730
REPORT IS A COMBINATION OF REPORTS P1001414 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B1090D610UB2750-4F0-XX-W2A-D_3000K
Description: Define 5 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6610.0 lumens
Efficiency: N/A
Efficacy: 106.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.21 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 62.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026730

CATALOG NUMBER: S125DIP-B1090D610UB2750-4F0-XX-W2A-D_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1026730

CATALOG NUMBER: S125DIP-B1090D610UB2750-4F0-XX-W2A-D_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	66	66	66
1	99	94	90	86	92	88	85	81	77	74	71	66	64	62	57	55	54
2	90	82	75	70	84	77	71	66	67	62	58	58	54	51	49	47	44
3	82	72	64	58	76	67	60	55	59	53	49	51	47	43	43	40	37
4	75	63	55	49	69	59	52	46	52	46	41	45	40	37	39	35	32
5	69	56	48	42	64	53	45	40	46	40	36	40	35	32	35	31	28
6	63	51	42	36	59	48	40	34	42	36	31	36	31	28	31	27	24
7	58	46	37	32	54	43	35	30	38	32	27	33	28	24	29	25	22
8	54	41	33	28	51	39	32	27	35	29	24	30	25	22	26	22	19
9	51	38	30	25	47	36	29	24	32	26	22	28	23	20	24	20	17
10	47	35	27	22	44	33	26	21	29	23	20	26	21	18	23	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8769	8769	8769
5°	8784	8585	8606
10°	8718	8411	8387
15°	8612	8207	8116
20°	8468	7961	7847
25°	8299	7699	7522
30°	8093	7414	7227
35°	7902	7150	6954
40°	7705	6873	6679
45°	7485	6633	6432
50°	7273	6372	6210
55°	7019	6122	5951
60°	6741	5839	5686
65°	6449	5541	5386
70°	6116	5140	5076
75°	5590	4744	4697
80°	4899	4264	4276
85°	4220	3880	4055

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7485 cd/sqm

TEST NUMBER: P1026730

CATALOG NUMBER: S125DIP-B1090D610UB2750-4F0-XX-W2A-D_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	129.5	2.0
10°-20°	367.7	5.6
20°-30°	546.7	8.3
30°-40°	647.5	9.8
40°-50°	669.4	10.1
50°-60°	616.7	9.3
60°-70°	498.5	7.5
70°-80°	333.6	5.0
80°-90°	173.5	2.6
90°-100°	123.3	1.9
100°-110°	245.6	3.7
110°-120°	361.3	5.5
120°-130°	429.4	6.5
130°-140°	444.5	6.7
140°-150°	408.4	6.2
150°-160°	328.5	5.0
160°-170°	212.4	3.2
170°-180°	73.3	1.1
0°-30°	1043.9	15.8
0°-40°	1691.5	25.6
0°-60°	2977.5	45.0
0°-90°	3983.1	60.3
90°-120°	730.3	11.0
90°-150°	2012.7	30.4
90°-180°	2627.0	39.7
0°-180°	6610.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1369	1369	1369	1369	1369	
5°	1369	1366	1357	1367	1366	130
15°	1307	1308	1299	1307	1302	368
25°	1188	1192	1184	1189	1182	547
35°	1028	1037	1033	1037	1037	643
45°	847	862	868	878	879	653
55°	651	672	694	708	714	582
65°	448	479	511	531	537	445
75°	247	282	325	352	358	262
85°	74	118	165	195	205	77
90°	22	70	119	153	164	17
95°	50	83	107	140	149	54
105°	180	204	244	271	280	191
115°	324	336	371	393	398	321
125°	454	457	484	503	508	405
135°	562	564	573	589	592	434
145°	650	650	650	657	659	406
155°	715	711	712	714	709	329
165°	754	751	751	755	750	213
175°	771	768	768	773	768	73
180°	771	771	771	771	771	

TEST NUMBER: P1026730

CATALOG NUMBER: S125DIP-B1090D610UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1368.7	1368.7	1368.7	1368.7	1368.7
2.5°	1372.7	1370.0	1360.7	1370.0	1368.7
5°	1368.7	1366.0	1356.6	1367.4	1366.0
7.5°	1359.3	1358.0	1348.6	1358.0	1356.6
10°	1345.9	1345.9	1335.2	1344.5	1343.2
12.5°	1327.1	1328.4	1320.4	1327.1	1323.1
15°	1307.0	1308.3	1298.9	1307.0	1301.6
17.5°	1281.5	1284.2	1274.8	1281.5	1277.5
20°	1253.3	1256.0	1246.6	1250.6	1250.6
22.5°	1221.1	1226.5	1215.7	1221.1	1217.1
25°	1187.6	1191.6	1183.5	1188.9	1182.2
27.5°	1151.3	1156.7	1147.3	1151.3	1148.6
30°	1109.7	1117.8	1109.7	1112.4	1111.1
32.5°	1072.2	1078.9	1073.5	1076.2	1074.8
35°	1027.9	1037.3	1033.2	1037.3	1037.3
37.5°	984.9	993.0	991.6	997.0	995.7
40°	940.6	951.4	950.0	955.4	958.1
42.5°	892.3	907.1	911.1	917.8	917.8
45°	846.7	861.5	868.2	877.6	878.9
47.5°	799.8	813.2	823.9	837.3	840.0
50°	751.4	766.2	781.0	795.7	799.8
52.5°	700.5	719.2	738.0	754.1	756.8
55°	650.8	672.3	693.7	708.5	713.9
57.5°	599.8	625.3	649.5	665.6	669.6
60°	548.8	575.7	602.5	622.6	626.7
62.5°	499.2	526.0	555.5	578.3	583.7
65°	448.2	479.0	511.3	531.4	536.7
67.5°	401.2	430.7	462.9	487.1	493.8
70°	348.9	379.7	414.6	440.1	448.2
72.5°	297.9	330.1	369.0	397.2	402.6
75°	246.9	281.8	324.7	351.6	358.3
77.5°	197.3	237.5	277.8	307.3	312.7
80°	151.6	191.9	237.5	267.0	272.4
82.5°	110.0	153.0	199.9	228.1	238.9
85°	73.8	118.1	165.0	194.6	205.3
87.5°	47.0	89.9	135.5	166.4	175.8
90°	22.1	69.5	119.1	152.9	164.0
92.5°	29.7	63.4	113.8	146.2	156.2
95°	50.0	83.2	107.1	139.5	148.9
97.5°	77.3	112.9	102.9	132.2	142.2
100°	110.3	140.1	185.4	128.4	134.1
102.5°	143.7	171.5	214.3	242.2	202.3
105°	180.2	203.9	244.2	271.0	279.8
107.5°	217.6	236.4	276.5	304.0	309.7
110°	254.1	270.2	308.9	332.7	342.7



TEST NUMBER: P1026730

CATALOG NUMBER: S125DIP-B1090D610UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	289.5	303.3	340.1	362.0	370.2
115°	323.7	335.8	371.3	393.2	397.8
117.5°	359.4	366.1	402.0	421.4	429.6
120°	393.7	397.1	429.8	451.4	456.7
122.5°	422.7	426.9	456.9	477.3	482.0
125°	454.2	456.8	483.7	502.8	507.8
127.5°	483.0	484.6	506.8	525.8	529.3
130°	510.5	512.0	531.4	548.5	552.3
132.5°	536.6	540.1	551.7	570.5	573.1
135°	562.4	564.4	572.6	589.0	592.3
137.5°	586.4	588.4	592.6	608.7	611.3
140°	608.4	609.5	610.4	626.2	628.2
142.5°	629.6	628.8	630.0	642.1	643.9
145°	650.1	650.0	650.0	657.2	659.2
147.5°	667.1	667.1	667.7	671.0	669.7
150°	684.3	683.1	684.3	685.4	682.1
152.5°	700.9	698.0	699.1	700.3	696.3
155°	714.6	711.1	712.3	714.0	709.4
157.5°	725.4	723.7	723.7	725.4	720.9
160°	736.9	733.4	734.0	736.3	731.7
162.5°	746.0	742.6	743.2	746.6	741.4
165°	754.0	750.6	751.2	754.6	750.0
167.5°	760.3	756.9	757.4	761.4	756.3
170°	765.4	761.4	762.0	766.6	761.4
172.5°	768.9	764.9	766.0	770.0	764.9
175°	771.2	767.7	768.3	772.9	767.7
177.5°	772.9	769.5	770.0	774.0	769.5
180°	771.2	771.2	771.2	771.2	771.2

(END OF REPORT)