

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027007

Luminaire Tested: S125DIP-B850D1270UB2750-4F0-XX-W2A-F_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027007
REPORT IS A COMBINATION OF REPORTS P1002501 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B850D1270UB2750-4F0-XX-W2A-F_4000K
Description: Define 5 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8203.0 lumens
Efficiency: N/A
Efficacy: 115.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 70.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027007

CATALOG NUMBER: S125DIP-B850D1270UB2750-4F0-XX-W2A-F_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1027007

CATALOG NUMBER: S125DIP-B850D1270UB2750-4F0-XX-W2A-F_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	48	48	48
1	96	92	88	84	87	84	80	77	69	67	64	55	54	52	43	42	41
2	87	80	74	69	79	73	68	63	60	57	53	48	46	44	38	36	34
3	80	70	63	57	72	64	58	53	53	49	45	43	40	37	33	31	29
4	73	62	54	48	66	57	50	45	47	42	38	38	34	31	30	27	25
5	67	55	47	41	61	51	44	38	42	37	33	34	30	27	27	24	22
6	61	49	41	36	56	45	38	33	38	33	29	31	27	24	24	21	19
7	57	45	37	31	52	41	34	29	34	29	25	28	24	21	22	19	17
8	53	40	33	28	48	37	30	26	31	26	22	26	22	19	20	17	15
9	49	37	29	24	45	34	27	23	29	23	20	24	20	17	19	16	14
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8407	8407	8407
5°	8407	8211	8227
10°	8338	8023	7998
15°	8228	7798	7728
20°	8080	7537	7418
25°	7921	7252	7087
30°	7729	6955	6738
35°	7525	6645	6347
40°	7313	6316	5999
45°	7084	5996	5629
50°	6833	5632	5198
55°	6583	5231	4802
60°	6285	4809	4341
65°	5930	4320	3865
70°	5567	3757	3315
75°	4959	3095	2681
80°	4227	2311	1972
85°	3265	1366	1086

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7084 cd/sqm

TEST NUMBER: P1027007

CATALOG NUMBER: S125DIP-B850D1270UB2750-4F0-XX-W2A-F_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	123.8	1.5
10°-20°	349.7	4.3
20°-30°	516.3	6.3
30°-40°	602.4	7.3
40°-50°	605.0	7.4
50°-60°	531.1	6.5
60°-70°	395.6	4.8
70°-80°	225.9	2.8
80°-90°	67.5	0.8
90°-100°	52.9	0.6
100°-110°	351.6	4.3
110°-120°	633.2	7.7
120°-130°	812.7	9.9
130°-140°	874.1	10.7
140°-150°	820.4	10.0
150°-160°	663.6	8.1
160°-170°	429.2	5.2
170°-180°	148.0	1.8
0°-30°	989.8	12.1
0°-40°	1592.2	19.4
0°-60°	2728.3	33.3
0°-90°	3417.3	41.7
90°-120°	1037.7	12.7
90°-150°	3544.9	43.2
90°-180°	4786.0	58.3
0°-180°	8203.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1312	1312	1312	1312	1312	
5°	1310	1308	1298	1307	1306	124
15°	1249	1246	1234	1239	1239	352
25°	1134	1128	1115	1117	1114	522
35°	979	975	960	955	947	612
45°	801	797	785	772	769	617
55°	610	607	593	583	576	545
65°	412	410	399	389	385	409
75°	219	217	212	209	204	233
85°	57	58	58	57	55	63
90°	1	10	18	24	28	7
95°	66	62	18	24	24	81
105°	340	344	344	344	343	360
115°	638	643	644	640	633	632
125°	907	915	915	910	907	810
135°	1131	1138	1135	1133	1126	872
145°	1311	1313	1313	1314	1307	820
155°	1444	1437	1439	1442	1433	665
165°	1523	1516	1518	1524	1515	430
175°	1558	1551	1552	1561	1551	148
180°	1558	1558	1558	1558	1558	

TEST NUMBER: P1027007

CATALOG NUMBER: S125DIP-B850D1270UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1312.1	1312.1	1312.1	1312.1	1312.1
2.5°	1316.2	1313.1	1302.7	1313.1	1312.1
5°	1310.0	1307.9	1297.5	1306.9	1305.8
7.5°	1300.7	1298.6	1287.2	1296.5	1295.5
10°	1287.2	1285.1	1273.7	1282.0	1280.9
12.5°	1270.6	1266.4	1256.0	1262.2	1262.2
15°	1248.8	1245.6	1234.2	1239.4	1239.4
17.5°	1225.9	1220.7	1209.3	1215.5	1210.3
20°	1195.8	1193.7	1180.2	1187.5	1182.3
22.5°	1165.7	1161.6	1149.1	1153.3	1150.1
25°	1133.5	1128.3	1114.8	1116.9	1113.8
27.5°	1096.2	1093.0	1079.6	1080.6	1077.5
30°	1059.8	1056.7	1041.1	1039.1	1036.0
32.5°	1020.4	1015.2	1001.7	997.5	991.3
35°	978.9	974.7	960.2	955.0	946.7
37.5°	936.3	931.1	917.6	910.4	905.2
40°	892.7	887.5	873.0	863.6	860.5
42.5°	846.0	841.8	827.3	819.0	813.8
45°	801.4	797.2	784.8	772.3	769.2
47.5°	752.6	753.6	738.0	725.6	718.3
50°	705.9	702.7	690.3	676.8	669.5
52.5°	658.1	656.0	642.5	631.1	622.8
55°	610.4	607.2	592.7	583.4	576.1
57.5°	559.5	558.5	546.0	533.5	530.4
60°	511.7	507.6	496.2	485.8	478.5
62.5°	461.9	458.8	449.5	438.0	432.9
65°	412.1	410.0	398.6	389.3	385.1
67.5°	363.3	359.2	350.9	342.6	340.5
70°	317.6	312.4	303.1	296.9	292.7
72.5°	267.8	264.7	259.5	252.2	248.1
75°	219.0	216.9	211.8	208.6	204.5
77.5°	173.4	172.3	169.2	167.1	164.0
80°	130.8	130.8	128.7	127.7	125.6
82.5°	93.4	91.3	91.3	89.3	89.3
85°	57.1	58.1	58.1	57.1	55.0
87.5°	28.0	28.0	27.0	27.0	24.9
90°	1.2	10.4	18.5	24.3	27.7
92.5°	21.9	11.5	18.5	24.3	25.4
95°	65.8	62.4	18.5	24.3	24.3
97.5°	123.6	130.5	20.8	23.1	24.3
100°	192.9	196.3	201.0	28.9	24.3
102.5°	263.3	267.9	270.2	272.6	175.5
105°	339.5	344.2	344.2	344.2	343.0
107.5°	418.1	418.1	420.4	421.5	416.9
110°	494.3	494.3	496.6	493.1	494.3

TEST NUMBER: P1027007

CATALOG NUMBER: S125DIP-B850D1270UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	565.9	569.4	570.5	565.9	563.6
115°	637.5	643.3	644.4	639.8	632.9
117.5°	712.6	712.6	717.2	710.3	707.9
120°	781.9	780.7	784.2	781.9	776.1
122.5°	843.1	848.8	850.0	847.7	840.8
125°	906.6	914.7	914.7	910.1	906.6
127.5°	967.8	973.6	972.4	970.1	960.9
130°	1023.2	1029.0	1030.2	1026.7	1020.9
132.5°	1078.7	1085.6	1082.1	1082.1	1076.4
135°	1130.6	1137.6	1135.3	1132.9	1126.0
137.5°	1179.1	1186.1	1183.8	1183.8	1178.0
140°	1226.5	1228.8	1227.6	1230.0	1223.0
142.5°	1269.2	1270.4	1272.7	1272.7	1265.8
145°	1310.8	1313.1	1313.1	1314.3	1307.3
147.5°	1347.8	1347.8	1348.9	1350.1	1342.0
150°	1382.4	1380.1	1382.4	1384.7	1375.5
152.5°	1415.9	1410.1	1412.4	1414.7	1406.7
155°	1443.6	1436.7	1439.0	1442.5	1433.2
157.5°	1465.6	1462.1	1462.1	1465.6	1456.3
160°	1488.7	1481.7	1482.9	1487.5	1478.3
162.5°	1507.1	1500.2	1501.4	1508.3	1497.9
165°	1523.3	1516.4	1517.5	1524.5	1515.2
167.5°	1536.0	1529.1	1530.2	1538.3	1527.9
170°	1546.4	1538.3	1539.5	1548.7	1538.3
172.5°	1553.3	1545.2	1547.6	1555.6	1545.2
175°	1557.9	1551.0	1552.2	1561.4	1551.0
177.5°	1561.4	1554.5	1555.6	1563.7	1554.5
180°	1557.9	1557.9	1557.9	1557.9	1557.9

(END OF REPORT)