

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026732

Luminaire Tested: S125DIP-B1090D610UB2750-4F0-XX-W2A-D_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026732
REPORT IS A COMBINATION OF REPORTS P1001416 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B1090D610UB2750-4F0-XX-W2A-D_4000K
Description: Define 5 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6573.0 lumens
Efficiency: N/A
Efficacy: 105.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.21 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 62.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026732

CATALOG NUMBER: S125DIP-B1090D610UB2750-4F0-XX-W2A-D_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1026732

CATALOG NUMBER: S125DIP-B1090D610UB2750-4F0-XX-W2A-D_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	66	66	66
1	99	94	90	86	92	88	85	81	77	74	71	66	64	62	57	55	54
2	90	82	75	70	84	77	71	66	67	62	58	58	54	51	49	47	44
3	82	72	64	58	76	67	60	55	59	53	49	51	47	43	43	40	37
4	75	63	55	49	69	59	52	46	52	46	41	45	40	37	39	35	32
5	69	56	48	42	64	53	45	40	46	40	36	40	35	32	35	31	28
6	63	51	42	36	59	48	40	34	42	36	31	36	31	28	31	27	24
7	58	46	37	32	54	43	35	30	38	32	27	33	28	24	29	25	22
8	54	41	33	28	51	39	32	27	35	29	24	30	25	22	26	22	19
9	51	38	30	25	47	36	29	24	32	26	22	28	23	20	24	20	17
10	47	35	27	22	44	33	26	21	29	23	20	26	21	18	23	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8720	8720	8720
5°	8734	8537	8558
10°	8669	8363	8339
15°	8563	8161	8070
20°	8420	7915	7802
25°	8251	7655	7480
30°	8047	7371	7186
35°	7857	7110	6914
40°	7662	6834	6641
45°	7442	6595	6396
50°	7232	6335	6174
55°	6979	6088	5917
60°	6702	5806	5653
65°	6412	5510	5356
70°	6081	5111	5046
75°	5559	4718	4669
80°	4873	4241	4253
85°	4197	3859	4032

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7442 cd/sqm

TEST NUMBER: P1026732

CATALOG NUMBER: S125DIP-B1090D610UB2750-4F0-XX-W2A-D_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	128.8	2.0
10°-20°	365.6	5.6
20°-30°	543.6	8.3
30°-40°	643.8	9.8
40°-50°	665.6	10.1
50°-60°	613.2	9.3
60°-70°	495.7	7.5
70°-80°	331.7	5.0
80°-90°	172.6	2.6
90°-100°	122.6	1.9
100°-110°	244.3	3.7
110°-120°	359.3	5.5
120°-130°	427.1	6.5
130°-140°	442.1	6.7
140°-150°	406.2	6.2
150°-160°	326.7	5.0
160°-170°	211.3	3.2
170°-180°	72.9	1.1
0°-30°	1038.0	15.8
0°-40°	1681.9	25.6
0°-60°	2960.7	45.0
0°-90°	3960.6	60.3
90°-120°	726.2	11.0
90°-150°	2001.6	30.5
90°-180°	2612.0	39.7
0°-180°	6573.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1361	1361	1361	1361	1361	
5°	1361	1358	1349	1360	1358	129
15°	1300	1301	1292	1300	1294	366
25°	1181	1185	1177	1182	1176	544
35°	1022	1031	1027	1031	1031	640
45°	842	857	863	873	874	650
55°	647	668	690	704	710	578
65°	446	476	508	528	534	442
75°	246	280	323	350	356	260
85°	73	117	164	194	204	77
90°	22	69	118	152	163	16
95°	50	83	106	139	148	53
105°	179	203	243	270	278	190
115°	322	334	369	391	396	319
125°	452	454	481	500	505	403
135°	559	561	570	586	589	431
145°	647	646	646	654	656	404
155°	711	707	708	710	706	327
165°	750	746	747	750	746	212
175°	767	764	764	769	764	73
180°	767	767	767	767	767	

TEST NUMBER: P1026732

CATALOG NUMBER: S125DIP-B1090D610UB2750-4F0-XX-W2A-D_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1361.0	1361.0	1361.0	1361.0	1361.0
2.5°	1365.0	1362.3	1352.9	1362.3	1361.0
5°	1361.0	1358.3	1348.9	1359.6	1358.3
7.5°	1351.6	1350.3	1340.9	1350.3	1348.9
10°	1338.3	1338.3	1327.6	1336.9	1335.6
12.5°	1319.6	1320.9	1312.9	1319.6	1315.6
15°	1299.6	1300.9	1291.6	1299.6	1294.2
17.5°	1274.2	1276.9	1267.6	1274.2	1270.2
20°	1246.2	1248.9	1239.5	1243.5	1243.5
22.5°	1214.2	1219.5	1208.8	1214.2	1210.2
25°	1180.8	1184.8	1176.8	1182.2	1175.5
27.5°	1144.8	1150.1	1140.8	1144.8	1142.1
30°	1103.4	1111.4	1103.4	1106.1	1104.8
32.5°	1066.1	1072.8	1067.4	1070.1	1068.7
35°	1022.1	1031.4	1027.4	1031.4	1031.4
37.5°	979.4	987.4	986.0	991.4	990.0
40°	935.3	946.0	944.7	950.0	952.7
42.5°	887.3	902.0	906.0	912.6	912.6
45°	841.9	856.6	863.3	872.6	873.9
47.5°	795.2	808.6	819.2	832.6	835.3
50°	747.2	761.9	776.5	791.2	795.2
52.5°	696.5	715.2	733.8	749.9	752.5
55°	647.1	668.5	689.8	704.5	709.8
57.5°	596.4	621.8	645.8	661.8	665.8
60°	545.7	572.4	599.1	619.1	623.1
62.5°	496.3	523.0	552.4	575.1	580.4
65°	445.6	476.3	508.4	528.4	533.7
67.5°	398.9	428.3	460.3	484.3	491.0
70°	346.9	377.6	412.3	437.6	445.6
72.5°	296.2	328.2	366.9	394.9	400.3
75°	245.5	280.2	322.9	349.6	356.2
77.5°	196.1	236.2	276.2	305.5	310.9
80°	150.8	190.8	236.2	265.5	270.9
82.5°	109.4	152.1	198.8	226.8	237.5
85°	73.4	117.4	164.1	193.5	204.1
87.5°	46.7	89.4	134.8	165.4	174.8
90°	21.9	69.1	118.5	152.0	163.0
92.5°	29.5	63.1	113.2	145.3	155.3
95°	49.7	82.7	106.5	138.7	148.0
97.5°	76.8	112.2	102.3	131.5	141.3
100°	109.6	139.3	184.3	127.6	133.3
102.5°	142.9	170.6	213.1	240.9	201.1
105°	179.1	202.8	242.8	269.5	278.3
107.5°	216.5	235.2	274.9	302.2	307.9
110°	252.6	268.7	307.2	330.9	340.7



TEST NUMBER: P1026732

CATALOG NUMBER: S125DIP-B1090D610UB2750-4F0-XX-W2A-D_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	287.9	301.6	338.2	360.0	368.1
115°	321.8	334.0	369.2	391.1	395.6
117.5°	357.5	364.1	399.8	419.0	427.2
120°	391.6	395.0	427.4	448.9	454.1
122.5°	420.3	424.6	454.4	474.7	479.3
125°	451.6	454.3	481.0	500.0	505.0
127.5°	480.4	482.0	504.1	523.0	526.4
130°	507.7	509.3	528.4	545.4	549.3
132.5°	533.7	537.1	548.7	567.4	569.9
135°	559.3	561.3	569.6	585.7	589.0
137.5°	583.2	585.2	589.4	605.4	607.9
140°	605.1	606.2	607.0	622.8	624.8
142.5°	626.1	625.4	626.5	638.5	640.4
145°	646.6	646.4	646.4	653.7	655.6
147.5°	663.5	663.5	664.0	667.3	665.9
150°	680.5	679.4	680.5	681.7	678.4
152.5°	697.0	694.2	695.3	696.4	692.5
155°	710.7	707.2	708.4	710.1	705.5
157.5°	721.5	719.7	719.7	721.5	716.9
160°	732.8	729.4	730.0	732.3	727.7
162.5°	741.9	738.5	739.1	742.5	737.4
165°	749.9	746.5	747.0	750.4	745.9
167.5°	756.1	752.7	753.3	757.3	752.2
170°	761.2	757.3	757.8	762.4	757.3
172.5°	764.7	760.7	761.8	765.8	760.7
175°	766.9	763.5	764.1	768.6	763.5
177.5°	768.6	765.2	765.8	769.8	765.2
180°	766.9	766.9	766.9	766.9	766.9

(END OF REPORT)