

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026734

Luminaire Tested: S125DIP-B1090D610UB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026734
REPORT IS A COMBINATION OF REPORTS P1001418 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B1090D610UB2750-4F0-XX-W2A-F_2700K
Description: Define 5 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6727.0 lumens
Efficiency: N/A
Efficacy: 108.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 62.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026734

CATALOG NUMBER: S125DIP-B1090D610UB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1026734

CATALOG NUMBER: S125DIP-B1090D610UB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	104	104	104	104	92	92	92	80	80	80	70	70	70
1	101	97	93	89	95	91	87	84	80	78	75	71	69	67	62	60	59
2	92	84	78	73	86	80	74	69	70	66	62	62	59	56	54	52	50
3	84	74	67	61	79	70	63	58	62	57	52	55	51	47	48	45	42
4	77	66	58	51	72	62	55	49	55	49	45	49	44	40	43	39	36
5	71	59	50	44	66	55	48	42	49	43	39	44	39	35	39	35	32
6	65	53	44	38	61	50	42	37	45	38	34	40	35	31	35	31	28
7	60	48	39	34	57	45	38	32	41	34	30	36	31	27	32	28	25
8	56	43	35	30	53	41	34	29	37	31	27	33	28	24	30	25	22
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	27	23	20
10	49	36	29	24	46	35	28	23	31	26	22	28	23	20	25	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10775	10775	10775
5°	10775	10525	10545
10°	10686	10284	10251
15°	10546	9995	9905
20°	10356	9660	9508
25°	10152	9295	9084
30°	9907	8915	8636
35°	9644	8517	8135
40°	9373	8095	7688
45°	9080	7684	7215
50°	8757	7218	6663
55°	8437	6705	6155
60°	8056	6164	5564
65°	7600	5537	4954
70°	7136	4816	4249
75°	6356	3965	3436
80°	5416	2962	2528
85°	4185	1752	1393

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9080 cd/sqm

TEST NUMBER: P1026734

CATALOG NUMBER: S125DIP-B1090D610UB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	158.7	2.4
10°-20°	448.2	6.7
20°-30°	661.7	9.8
30°-40°	772.1	11.5
40°-50°	775.4	11.5
50°-60°	680.7	10.1
60°-70°	507.0	7.5
70°-80°	289.6	4.3
80°-90°	84.7	1.3
90°-100°	26.0	0.4
100°-110°	172.6	2.6
110°-120°	310.8	4.6
120°-130°	398.9	5.9
130°-140°	429.0	6.4
140°-150°	402.7	6.0
150°-160°	325.7	4.8
160°-170°	210.6	3.1
170°-180°	72.6	1.1
0°-30°	1268.7	18.9
0°-40°	2040.7	30.3
0°-60°	3496.8	52.0
0°-90°	4378.1	65.1
90°-120°	509.3	7.6
90°-150°	1739.8	25.9
90°-180°	2349.0	34.9
0°-180°	6727.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1682	1682	1682	1682	1682	
5°	1679	1676	1663	1675	1674	159
15°	1600	1596	1582	1588	1588	451
25°	1453	1446	1429	1432	1428	668
35°	1255	1249	1231	1224	1213	785
45°	1027	1022	1006	990	986	791
55°	782	778	760	748	738	698
65°	528	526	511	499	494	524
75°	281	278	271	267	262	299
85°	73	74	74	73	70	80
90°	1	5	9	12	14	7
95°	32	31	9	12	12	40
105°	167	169	169	169	168	177
115°	313	316	316	314	311	310
125°	445	449	449	447	445	397
135°	555	558	557	556	553	428
145°	643	644	644	645	642	402
155°	708	705	706	708	703	326
165°	748	744	745	748	744	211
175°	765	761	762	766	761	73
180°	765	765	765	765	765	

TEST NUMBER: P1026734

CATALOG NUMBER: S125DIP-B1090D610UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1681.7	1681.7	1681.7	1681.7	1681.7
2.5°	1687.0	1683.0	1669.7	1683.0	1681.7
5°	1679.0	1676.4	1663.1	1675.0	1673.7
7.5°	1667.0	1664.4	1649.7	1661.7	1660.4
10°	1649.7	1647.1	1632.5	1643.1	1641.8
12.5°	1628.5	1623.1	1609.8	1617.8	1617.8
15°	1600.5	1596.5	1581.9	1588.5	1588.5
17.5°	1571.3	1564.6	1550.0	1557.9	1551.3
20°	1532.7	1530.0	1512.7	1522.0	1515.4
22.5°	1494.1	1488.8	1472.8	1478.1	1474.1
25°	1452.8	1446.2	1428.9	1431.6	1427.6
27.5°	1404.9	1401.0	1383.7	1385.0	1381.0
30°	1358.4	1354.4	1334.4	1331.8	1327.8
32.5°	1307.8	1301.2	1283.9	1278.6	1270.6
35°	1254.6	1249.3	1230.7	1224.0	1213.4
37.5°	1200.1	1193.4	1176.1	1166.8	1160.1
40°	1144.2	1137.5	1118.9	1106.9	1102.9
42.5°	1084.3	1079.0	1060.4	1049.7	1043.1
45°	1027.1	1021.8	1005.8	989.8	985.9
47.5°	964.6	965.9	945.9	930.0	920.7
50°	904.7	900.7	884.7	867.4	858.1
52.5°	843.5	840.8	823.5	808.9	798.3
55°	782.3	778.3	759.7	747.7	738.4
57.5°	717.1	715.8	699.8	683.8	679.9
60°	655.9	650.6	636.0	622.6	613.3
62.5°	592.0	588.1	576.1	561.4	554.8
65°	528.2	525.5	510.9	498.9	493.6
67.5°	465.7	460.3	449.7	439.0	436.4
70°	407.1	400.5	388.5	380.5	375.2
72.5°	343.3	339.3	332.6	323.3	318.0
75°	280.7	278.1	271.4	267.4	262.1
77.5°	222.2	220.9	216.9	214.2	210.2
80°	167.6	167.6	165.0	163.6	161.0
82.5°	119.7	117.1	117.1	114.4	114.4
85°	73.2	74.5	74.5	73.2	70.5
87.5°	35.9	35.9	34.6	34.6	31.9
90°	0.6	5.1	9.1	11.9	13.6
92.5°	10.8	5.7	9.1	11.9	12.5
95°	32.3	30.6	9.1	11.9	11.9
97.5°	60.7	64.1	10.2	11.3	11.9
100°	94.7	96.4	98.6	14.2	11.9
102.5°	129.2	131.5	132.6	133.8	86.2
105°	166.6	168.9	168.9	168.9	168.3
107.5°	205.2	205.2	206.3	206.9	204.6
110°	242.6	242.6	243.7	242.0	242.6



TEST NUMBER: P1026734

CATALOG NUMBER: S125DIP-B1090D610UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	277.7	279.4	280.0	277.7	276.6
115°	312.9	315.7	316.3	314.0	310.6
117.5°	349.7	349.7	352.0	348.6	347.5
120°	383.7	383.2	384.9	383.7	380.9
122.5°	413.8	416.6	417.2	416.1	412.7
125°	445.0	448.9	448.9	446.7	445.0
127.5°	475.0	477.8	477.3	476.1	471.6
130°	502.2	505.0	505.6	503.9	501.1
132.5°	529.4	532.8	531.1	531.1	528.3
135°	554.9	558.3	557.2	556.1	552.7
137.5°	578.7	582.1	581.0	581.0	578.2
140°	602.0	603.1	602.5	603.7	600.3
142.5°	622.9	623.5	624.6	624.6	621.2
145°	643.4	644.5	644.5	645.1	641.7
147.5°	661.5	661.5	662.1	662.6	658.7
150°	678.5	677.4	678.5	679.6	675.1
152.5°	694.9	692.1	693.2	694.4	690.4
155°	708.5	705.1	706.3	708.0	703.4
157.5°	719.3	717.6	717.6	719.3	714.8
160°	730.6	727.2	727.8	730.1	725.5
162.5°	739.7	736.3	736.9	740.3	735.2
165°	747.7	744.3	744.8	748.2	743.7
167.5°	753.9	750.5	751.1	755.0	749.9
170°	759.0	755.0	755.6	760.1	755.0
172.5°	762.4	758.4	759.6	763.5	758.4
175°	764.7	761.3	761.8	766.4	761.3
177.5°	766.4	763.0	763.5	767.5	763.0
180°	764.7	764.7	764.7	764.7	764.7

(END OF REPORT)