

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027012

Luminaire Tested: S125DIP-B850D375UB2750-4F0-XX-W2A-A_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027012
REPORT IS A COMBINATION OF REPORTS P1002551 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B850D375UB2750-4F0-XX-W2A-A_4000K
Description: Define 5 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4917.0 lumens
Efficiency: N/A
Efficacy: 108.8 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.43 / 1.52
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 45.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027012

CATALOG NUMBER: S125DIP-B850D375UB2750-4F0-XX-W2A-A_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1027012

CATALOG NUMBER: S125DIP-B850D375UB2750-4F0-XX-W2A-A_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	112	112	112	112	106	106	106	106	95	95	95	84	84	84	75	75	75	75	75	75
1	103	98	94	91	97	93	90	87	84	81	79	75	73	71	67	65	64	64	64	60
2	94	86	80	75	88	82	76	72	74	69	66	66	63	60	59	56	54	54	54	51
3	86	76	69	63	81	72	66	60	65	60	55	59	54	51	52	49	46	46	46	43
4	79	68	60	53	74	64	57	51	58	52	48	52	48	44	47	43	40	40	40	37
5	72	60	52	46	68	58	50	44	52	46	41	47	42	38	42	38	35	35	35	32
6	67	54	46	40	63	52	44	39	47	41	36	43	38	34	39	34	31	31	31	28
7	62	49	41	35	58	47	40	34	43	37	32	39	34	30	35	31	28	28	28	25
8	57	45	37	31	54	43	36	30	39	33	29	36	30	27	32	28	25	25	25	23
9	54	41	33	28	51	39	32	27	36	30	26	33	28	24	30	26	22	22	22	20
10	50	38	30	25	47	36	29	25	33	27	23	30	25	22	28	23	20	20	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	7836	7836	7836	7836
5°	7842	8889	7849	6743
10°	7794	10131	7781	5789
15°	7737	10985	7689	5230
20°	7639	12038	7569	4775
25°	7552	13793	7414	4505
30°	7427	14551	7299	4261
35°	7230	11665	7078	4065
40°	6923	8062	6821	3857
45°	6535	6002	6461	3685
50°	6089	4941	5989	3547
55°	5609	4215	5565	3427
60°	5139	3607	5049	3334
65°	4630	3115	4556	3198
70°	4095	2587	4040	2963
75°	3525	2000	3478	2572
80°	2786	1353	2685	1890
85°	1778	678	1721	964

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 135°

Vertical Angle: 45°

Luminance: 11968 cd/sqm

TEST NUMBER: P1027012

CATALOG NUMBER: S125DIP-B850D375UB2750-4F0-XX-W2A-A_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	117.7	2.4
10°-20°	350.6	7.1
20°-30°	569.5	11.6
30°-40°	696.0	14.2
40°-50°	631.3	12.8
50°-60°	502.8	10.2
60°-70°	350.2	7.1
70°-80°	186.6	3.8
80°-90°	47.0	1.0
90°-100°	16.2	0.3
100°-110°	107.7	2.2
110°-120°	193.9	3.9
120°-130°	248.8	5.1
130°-140°	267.6	5.4
140°-150°	251.2	5.1
150°-160°	203.2	4.1
160°-170°	131.4	2.7
170°-180°	45.3	0.9
0°-30°	1037.8	21.1
0°-40°	1733.8	35.3
0°-60°	2867.9	58.3
0°-90°	3451.7	70.2
90°-120°	317.7	6.5
90°-150°	1085.4	22.1
90°-180°	1465.0	29.8
0°-180°	4917.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1223	1223	1223	1223	1223	
5°	1222	1411	1223	1070	1222	116
15°	1174	1762	1167	839	1174	331
25°	1081	2168	1061	708	1081	498
35°	941	1740	921	606	941	587
45°	739	820	731	504	739	569
55°	520	506	516	411	520	465
65°	322	310	317	319	322	319
75°	156	153	154	196	156	166
85°	31	34	30	49	31	37
90°	0	8	0	8	0	3
95°	20	7	20	7	20	25
105°	104	105	104	105	104	110
115°	195	194	195	194	195	194
125°	278	278	278	278	278	248
135°	346	345	346	345	346	267
145°	401	400	401	400	401	251
155°	442	439	442	439	442	204
165°	466	464	466	464	466	132
175°	477	475	477	475	477	45
180°	477	477	477	477	477	

TEST NUMBER: P1027012

CATALOG NUMBER: S125DIP-B850D375UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0
2.5°	1225.0	1232.3	1240.6	1246.8	1257.2	1260.3	1265.5	1268.6	1271.7	1274.9	1276.9
5°	1221.9	1239.6	1255.1	1266.6	1286.3	1293.5	1302.9	1314.3	1327.8	1339.2	1346.5
7.5°	1213.6	1241.6	1262.4	1285.2	1312.2	1329.9	1339.2	1363.1	1384.9	1401.5	1423.3
10°	1203.2	1236.5	1268.6	1302.9	1341.3	1361.0	1379.7	1412.9	1443.0	1470.0	1491.8
12.5°	1191.8	1232.3	1270.7	1315.4	1367.3	1391.1	1403.6	1460.7	1498.1	1512.6	1555.2
15°	1174.2	1221.9	1276.9	1332.0	1375.6	1403.6	1437.9	1483.5	1520.9	1553.1	1587.3
17.5°	1157.6	1209.5	1265.5	1326.8	1390.1	1426.4	1452.4	1492.9	1533.4	1574.9	1607.1
20°	1130.6	1198.0	1255.1	1320.5	1395.3	1421.2	1448.2	1496.0	1539.6	1584.2	1624.7
22.5°	1108.8	1173.1	1251.0	1313.3	1376.6	1402.6	1435.8	1485.6	1537.5	1588.4	1647.6
25°	1080.7	1152.4	1219.8	1286.3	1351.7	1379.7	1409.8	1474.2	1528.2	1593.6	1659.0
27.5°	1050.6	1124.3	1191.8	1252.0	1313.3	1351.7	1383.9	1451.3	1523.0	1594.6	1679.7
30°	1018.4	1088.0	1152.4	1211.5	1279.0	1318.5	1350.6	1429.5	1509.5	1600.8	1702.6
32.5°	984.2	1049.6	1104.6	1164.8	1236.5	1272.8	1316.4	1402.6	1497.0	1606.0	1733.7
35°	940.6	1002.9	1051.7	1112.9	1184.5	1231.3	1276.9	1373.5	1483.5	1605.0	1751.4
37.5°	897.0	945.8	992.5	1057.9	1140.9	1183.5	1231.3	1337.2	1462.8	1601.9	1758.6
40°	845.1	892.8	933.3	999.7	1087.0	1135.7	1185.6	1296.7	1438.9	1590.5	1732.7
42.5°	793.2	833.6	878.3	947.8	1031.9	1083.8	1136.8	1260.3	1407.7	1557.2	1661.1
45°	739.2	770.3	819.1	882.4	971.7	1021.6	1081.8	1215.7	1364.1	1497.0	1548.9
47.5°	683.1	714.3	759.9	821.2	909.4	968.6	1025.7	1159.6	1309.1	1411.9	1411.9
50°	629.1	654.0	698.7	759.9	849.2	903.2	961.3	1103.6	1224.0	1299.8	1232.3
52.5°	571.0	599.0	636.4	700.8	789.0	837.8	901.1	1022.6	1136.8	1167.9	1064.1
55°	520.1	543.0	578.3	639.5	721.5	772.4	826.4	942.7	1039.2	1037.1	926.0
57.5°	467.2	485.9	523.2	579.3	655.1	700.8	754.7	855.4	934.3	906.3	801.5
60°	418.4	431.9	468.2	513.9	586.6	629.1	681.0	763.0	823.3	783.8	677.9
62.5°	367.5	383.1	412.2	456.8	521.2	555.4	593.8	676.9	715.3	680.0	572.0
65°	321.8	334.3	360.2	397.6	455.8	486.9	520.1	588.6	625.0	574.1	484.8
67.5°	276.2	290.7	309.4	342.6	388.3	417.3	446.4	505.6	522.2	476.5	401.8
70°	233.6	246.0	263.7	287.6	326.0	351.9	373.7	422.5	434.0	391.4	332.2
72.5°	192.1	200.4	214.9	234.6	269.9	284.5	307.3	340.5	355.1	316.6	274.1
75°	155.7	162.0	171.3	185.8	209.7	225.3	244.0	275.1	274.1	247.1	217.0
77.5°	120.4	121.5	131.8	145.3	159.9	173.4	182.7	204.5	206.6	190.0	165.1
80°	86.2	89.3	93.4	103.8	116.3	121.5	132.9	146.4	148.5	136.0	119.4
82.5°	55.0	57.1	60.2	66.4	74.7	81.0	87.2	92.4	97.6	90.3	76.8
85°	31.1	32.2	35.3	37.4	41.5	44.6	49.8	55.0	54.0	48.8	44.6
87.5°	15.6	15.6	15.6	17.6	19.7	19.7	21.8	22.8	23.9	21.8	19.7
90°	0.4	1.0	1.6	2.3	2.9	3.2	3.5	4.0	4.6	5.1	5.7
92.5°	6.7	6.0	5.3	4.6	3.9	3.5	3.7	4.2	4.7	5.2	5.7
95°	20.2	20.0	19.7	19.5	19.2	19.1	17.6	14.6	11.7	8.7	5.7
97.5°	37.8	38.3	38.8	39.3	39.8	40.0	36.3	28.8	21.3	13.9	6.4
100°	59.1	59.3	59.5	59.8	60.0	60.1	60.3	60.6	60.9	61.2	61.5
102.5°	80.6	80.9	81.2	81.5	81.8	82.0	82.1	82.2	82.4	82.5	82.7
105°	104.0	104.3	104.6	104.9	105.2	105.4	105.4	105.4	105.4	105.4	105.4
107.5°	128.0	128.0	128.0	128.0	128.0	128.0	128.1	128.2	128.4	128.5	128.7
110°	151.3	151.3	151.3	151.3	151.3	151.3	151.4	151.6	151.7	151.9	152.1

TEST NUMBER: P1027012

CATALOG NUMBER: S125DIP-B850D375UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	173.3	173.5	173.7	174.0	174.2	174.3	174.3	174.4	174.5	174.6	174.7
115°	195.2	195.6	196.0	196.4	196.8	197.0	197.0	197.1	197.2	197.2	197.3
117.5°	218.2	218.2	218.2	218.2	218.2	218.2	218.4	218.7	219.0	219.3	219.6
120°	239.4	239.3	239.2	239.1	239.0	239.0	239.1	239.4	239.6	239.9	240.1
122.5°	258.1	258.5	258.9	259.3	259.7	259.9	259.9	260.0	260.1	260.2	260.3
125°	277.6	278.2	278.7	279.3	279.8	280.1	280.1	280.1	280.1	280.1	280.1
127.5°	296.3	296.7	297.1	297.5	297.9	298.1	298.1	298.0	297.9	297.8	297.7
130°	313.3	313.7	314.1	314.5	314.9	315.1	315.1	315.2	315.3	315.3	315.4
132.5°	330.3	330.8	331.2	331.7	332.2	332.4	332.3	332.0	331.8	331.5	331.3
135°	346.2	346.7	347.1	347.6	348.1	348.3	348.2	348.1	347.9	347.8	347.6
137.5°	361.0	361.5	362.0	362.5	363.0	363.2	363.1	362.9	362.8	362.6	362.4
140°	375.5	375.7	375.8	376.0	376.1	376.2	376.2	376.1	376.0	376.0	375.9
142.5°	388.6	388.7	388.8	388.9	389.0	389.0	389.1	389.2	389.4	389.5	389.7
145°	401.3	401.5	401.7	401.8	402.0	402.1	402.1	402.1	402.1	402.1	402.1
147.5°	412.7	412.7	412.7	412.7	412.7	412.7	412.7	412.8	412.9	412.9	413.0
150°	423.3	423.1	423.0	422.8	422.7	422.6	422.7	422.8	423.0	423.1	423.3
152.5°	433.5	433.1	432.7	432.4	432.0	431.8	431.9	432.0	432.2	432.3	432.5
155°	442.0	441.5	441.1	440.6	440.1	439.9	440.0	440.1	440.3	440.4	440.6
157.5°	448.7	448.5	448.3	448.0	447.8	447.7	447.7	447.7	447.7	447.7	447.7
160°	455.8	455.3	454.9	454.4	453.9	453.7	453.7	453.8	453.9	453.9	454.0
162.5°	461.5	461.0	460.5	460.0	459.5	459.3	459.3	459.4	459.5	459.6	459.7
165°	466.4	465.9	465.5	465.0	464.5	464.3	464.3	464.4	464.5	464.5	464.6
167.5°	470.3	469.8	469.4	468.9	468.4	468.2	468.2	468.3	468.4	468.4	468.5
170°	473.5	472.9	472.4	471.8	471.3	471.0	471.0	471.1	471.2	471.3	471.4
172.5°	475.6	475.0	474.5	473.9	473.4	473.1	473.2	473.3	473.5	473.6	473.8
175°	477.0	476.5	476.1	475.6	475.1	474.9	474.9	475.0	475.1	475.1	475.2
177.5°	478.1	477.6	477.2	476.7	476.2	476.0	476.0	476.1	476.2	476.2	476.3
180°	477.0	477.0	477.0	477.0	477.0	477.0	477.0	477.0	477.0	477.0	477.0

TEST NUMBER: P1027012

CATALOG NUMBER: S125DIP-B850D375UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0
2.5°	1279.0	1286.3	1292.5	1297.7	1301.9	1308.1	1303.9	1305.0	1307.0	1311.2	1311.2
5°	1362.1	1373.5	1379.7	1400.5	1405.7	1404.6	1401.5	1418.1	1417.1	1410.9	1409.8
7.5°	1443.0	1462.8	1480.4	1497.0	1502.2	1515.7	1518.8	1526.1	1524.0	1534.4	1529.2
10°	1516.8	1547.9	1564.5	1589.4	1595.7	1601.9	1610.2	1614.3	1623.7	1622.6	1622.6
12.5°	1573.9	1611.2	1633.0	1639.3	1663.1	1670.4	1677.7	1691.2	1688.1	1689.1	1695.3
15°	1618.5	1654.8	1673.5	1702.6	1719.2	1727.5	1740.0	1754.5	1752.4	1761.8	1759.7
17.5°	1651.7	1686.0	1720.2	1763.8	1764.9	1786.7	1815.7	1822.0	1835.5	1826.1	1826.1
20°	1678.7	1724.4	1773.2	1829.2	1835.5	1849.0	1884.3	1908.1	1923.7	1918.5	1921.6
22.5°	1707.8	1773.2	1830.3	1886.3	1916.4	1940.3	1974.6	2012.0	2025.5	2033.8	2031.7
25°	1745.1	1813.7	1897.8	1975.6	2006.8	2052.4	2098.1	2134.5	2144.8	2167.7	2146.9
27.5°	1783.6	1880.1	1985.0	2076.3	2115.8	2153.1	2208.2	2235.2	2248.7	2259.0	2251.8
30°	1815.7	1948.6	2062.8	2146.9	2174.9	2196.7	2227.9	2234.1	2228.9	2237.2	2247.6
32.5°	1865.6	1995.3	2091.9	2132.4	2129.3	2128.2	2104.4	2071.1	2063.9	2044.1	2071.1
35°	1892.6	1996.4	2033.8	1979.8	1958.0	1918.5	1842.7	1792.9	1749.3	1740.0	1742.0
37.5°	1877.0	1917.5	1872.8	1730.6	1695.3	1635.1	1534.4	1463.8	1431.6	1406.7	1438.9
40°	1792.9	1748.3	1625.8	1452.4	1401.5	1344.4	1249.9	1211.5	1165.9	1156.5	1199.1
42.5°	1653.8	1517.8	1344.4	1210.5	1157.6	1125.4	1046.5	1010.1	977.9	963.4	987.3
45°	1464.8	1299.8	1125.4	1015.3	970.7	932.3	885.6	847.1	826.4	820.1	839.9
47.5°	1269.7	1095.3	956.1	874.1	827.4	798.3	754.7	732.9	716.3	718.4	721.5
50°	1082.8	924.0	817.0	735.0	712.2	689.3	660.3	641.6	633.3	636.4	634.3
52.5°	921.9	793.2	702.8	639.5	629.1	607.3	583.4	567.9	564.8	565.8	568.9
55°	780.7	680.0	608.4	562.7	551.3	535.7	521.2	510.8	502.5	505.6	504.5
57.5°	673.8	585.5	530.5	493.1	484.8	475.5	462.0	456.8	453.7	447.4	452.6
60°	579.3	507.7	459.9	437.1	429.8	423.6	409.0	402.8	400.7	397.6	405.9
62.5°	490.0	439.1	402.8	382.0	374.8	368.5	361.3	356.1	357.1	353.0	357.1
65°	419.4	377.9	351.9	333.2	323.9	319.8	318.7	310.4	309.4	310.4	311.4
67.5°	354.0	318.7	299.0	287.6	280.3	276.2	273.0	267.8	272.0	268.9	271.0
70°	294.8	271.0	250.2	238.8	235.7	236.7	231.5	229.4	230.5	228.4	230.5
72.5°	237.7	218.0	209.7	201.4	197.3	196.2	193.1	190.0	193.1	192.1	192.1
75°	190.0	175.4	166.1	160.9	160.9	158.8	153.6	153.6	153.6	152.6	153.6
77.5°	146.4	133.9	129.8	124.6	124.6	121.5	120.4	120.4	118.4	121.5	119.4
80°	109.0	99.7	93.4	90.3	90.3	89.3	87.2	86.2	87.2	86.2	86.2
82.5°	70.6	66.4	63.3	60.2	59.2	60.2	59.2	57.1	58.1	57.1	59.2
85°	40.5	36.3	36.3	34.3	35.3	33.2	34.3	32.2	31.1	34.3	32.2
87.5°	17.6	16.6	16.6	14.5	14.5	14.5	13.5	14.5	13.5	12.5	13.5
90°	6.1	6.5	6.8	7.2	7.4	7.5	7.8	8.0	8.3	8.5	8.3
92.5°	6.1	6.5	6.8	7.2	7.4	7.4	7.5	7.6	7.7	7.8	7.7
95°	6.1	6.5	6.8	7.2	7.4	7.4	7.4	7.4	7.4	7.4	7.4
97.5°	6.6	6.7	6.9	7.0	7.1	7.1	7.2	7.3	7.3	7.4	7.3
100°	49.8	38.1	26.4	14.7	8.8	8.6	8.3	8.0	7.7	7.4	7.7
102.5°	82.9	83.1	83.2	83.4	83.5	80.2	73.6	66.9	60.3	53.7	60.3
105°	105.4	105.4	105.4	105.4	105.4	105.4	105.3	105.2	105.1	105.0	105.1
107.5°	128.8	128.9	129.0	129.1	129.1	128.9	128.6	128.3	128.0	127.7	128.0
110°	151.9	151.6	151.4	151.1	151.0	151.0	151.1	151.2	151.2	151.3	151.2

TEST NUMBER: P1027012

CATALOG NUMBER: S125DIP-B850D375UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	174.4	174.1	173.8	173.5	173.3	173.2	173.1	172.9	172.8	172.6	172.8
115°	197.0	196.7	196.4	196.1	195.9	195.7	195.2	194.7	194.3	193.8	194.3
117.5°	219.1	218.7	218.2	217.7	217.5	217.4	217.3	217.1	217.0	216.8	217.0
120°	239.9	239.8	239.6	239.5	239.4	239.2	238.8	238.4	238.0	237.6	238.0
122.5°	260.1	259.9	259.8	259.6	259.5	259.3	258.8	258.3	257.9	257.4	257.9
125°	279.8	279.4	279.1	278.8	278.6	278.5	278.3	278.0	277.8	277.6	277.8
127.5°	297.5	297.4	297.2	297.1	297.0	296.7	296.1	295.4	294.8	294.2	294.8
130°	315.2	315.0	314.7	314.5	314.4	314.2	313.8	313.4	313.0	312.6	313.0
132.5°	331.3	331.3	331.3	331.3	331.3	331.1	330.7	330.4	330.0	329.6	330.0
135°	347.4	347.3	347.1	347.0	346.9	346.7	346.2	345.7	345.3	344.8	345.3
137.5°	362.4	362.4	362.4	362.4	362.4	362.2	361.8	361.5	361.1	360.7	361.1
140°	376.1	376.2	376.4	376.5	376.6	376.4	375.9	375.4	375.0	374.5	375.0
142.5°	389.7	389.7	389.7	389.7	389.7	389.5	389.0	388.5	388.1	387.6	388.1
145°	402.2	402.2	402.3	402.4	402.4	402.2	401.7	401.2	400.8	400.3	400.8
147.5°	413.1	413.2	413.3	413.4	413.4	413.1	412.6	412.0	411.5	410.9	411.5
150°	423.5	423.6	423.8	423.9	424.0	423.7	423.0	422.4	421.7	421.1	421.7
152.5°	432.7	432.8	433.0	433.1	433.2	432.9	432.4	431.8	431.3	430.7	431.3
155°	440.8	441.1	441.3	441.6	441.7	441.4	440.7	440.1	439.4	438.8	439.4
157.5°	447.9	448.1	448.4	448.6	448.7	448.4	447.8	447.1	446.5	445.9	446.5
160°	454.3	454.6	454.9	455.2	455.4	455.1	454.5	453.8	453.2	452.6	453.2
162.5°	460.2	460.6	461.1	461.6	461.8	461.4	460.7	460.0	459.3	458.6	459.3
165°	465.1	465.6	466.1	466.6	466.8	466.5	465.8	465.2	464.5	463.9	464.5
167.5°	469.1	469.6	470.2	470.7	471.0	470.6	469.9	469.2	468.5	467.8	468.5
170°	472.0	472.6	473.3	473.9	474.2	473.8	473.1	472.4	471.7	471.0	471.7
172.5°	474.4	474.9	475.5	476.0	476.3	475.9	475.2	474.5	473.8	473.1	473.8
175°	475.8	476.5	477.1	477.8	478.1	477.7	477.0	476.3	475.6	474.9	475.6
177.5°	476.9	477.4	478.0	478.5	478.8	478.5	477.9	477.2	476.6	476.0	476.6
180°	477.0	477.0	477.0	477.0	477.0	477.0	477.0	477.0	477.0	477.0	477.0

TEST NUMBER: P1027012

CATALOG NUMBER: S125DIP-B850D375UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0
2.5°	1309.1	1301.9	1303.9	1301.9	1296.7	1293.5	1285.2	1274.9	1270.7	1265.5	1262.4
5°	1414.0	1408.8	1407.7	1399.4	1397.4	1384.9	1364.1	1353.8	1341.3	1328.8	1316.4
7.5°	1528.2	1521.9	1501.2	1498.1	1500.1	1484.6	1457.6	1436.8	1410.9	1393.2	1369.3
10°	1622.6	1610.2	1592.5	1593.6	1586.3	1565.5	1538.6	1516.8	1479.4	1456.5	1422.3
12.5°	1679.7	1669.4	1667.3	1656.9	1650.7	1623.7	1591.5	1563.5	1535.4	1504.3	1478.3
15°	1749.3	1735.8	1726.5	1711.9	1707.8	1679.7	1644.4	1612.3	1580.1	1551.0	1496.0
17.5°	1826.1	1811.6	1776.3	1773.2	1748.3	1721.3	1687.0	1639.3	1605.0	1563.5	1523.0
20°	1913.3	1892.6	1846.9	1835.5	1815.7	1771.1	1724.4	1671.4	1616.4	1573.9	1526.1
22.5°	2010.9	1974.6	1941.4	1905.0	1890.5	1835.5	1771.1	1706.7	1640.3	1582.2	1525.1
25°	2137.6	2089.8	2043.1	2006.8	1981.9	1910.2	1824.0	1738.9	1662.1	1586.3	1511.6
27.5°	2237.2	2195.7	2144.8	2097.1	2064.9	1979.8	1881.1	1771.1	1675.6	1583.2	1503.3
30°	2244.5	2232.0	2200.9	2174.9	2139.7	2048.3	1939.3	1814.7	1696.4	1584.2	1486.6
32.5°	2108.5	2133.4	2146.9	2151.1	2143.8	2090.9	1991.2	1854.2	1715.0	1574.9	1472.1
35°	1815.7	1882.2	1964.2	1995.3	2025.5	2053.5	2001.6	1882.2	1721.3	1572.8	1449.3
37.5°	1495.0	1555.2	1691.2	1753.5	1788.8	1899.8	1942.4	1878.0	1733.7	1574.9	1427.5
40°	1206.3	1301.9	1399.4	1483.5	1538.6	1663.1	1795.0	1809.5	1716.1	1555.2	1399.4
42.5°	1015.3	1071.4	1145.1	1223.0	1271.7	1419.2	1597.7	1702.6	1661.1	1523.0	1365.2
45°	864.8	906.3	975.9	1001.8	1064.1	1205.3	1394.3	1545.8	1566.6	1472.1	1325.7
47.5°	742.3	777.6	822.2	854.4	904.2	1010.1	1170.0	1337.2	1436.8	1402.6	1270.7
50°	654.0	683.1	720.5	739.2	771.4	866.9	987.3	1153.4	1287.3	1298.7	1199.1
52.5°	580.3	596.9	626.0	646.8	672.7	730.9	839.9	976.9	1127.4	1189.7	1110.8
55°	516.0	529.5	555.4	568.9	582.4	632.2	717.4	841.9	983.1	1065.2	1020.5
57.5°	457.8	469.2	491.1	503.5	510.8	558.5	623.9	721.5	848.2	947.8	922.9
60°	410.1	420.5	432.9	442.3	450.6	490.0	535.7	614.6	727.8	824.3	818.1
62.5°	359.2	368.5	382.0	391.4	398.7	423.6	462.0	522.2	618.7	708.0	725.7
65°	314.6	321.8	331.2	335.3	344.7	363.4	394.5	448.5	527.4	607.3	619.8
67.5°	274.1	276.2	282.4	291.7	293.8	310.4	338.4	378.9	440.2	505.6	525.3
70°	230.5	233.6	238.8	246.0	250.2	260.6	284.5	311.4	364.4	421.5	436.0
72.5°	192.1	196.2	198.3	202.4	204.5	221.1	231.5	258.5	294.8	342.6	358.2
75°	155.7	159.9	160.9	163.0	165.1	172.3	186.9	203.5	233.6	264.7	285.5
77.5°	123.5	122.5	124.6	127.7	126.7	132.9	142.2	156.8	176.5	202.4	215.9
80°	87.2	87.2	90.3	93.4	92.4	98.6	101.7	112.1	128.7	145.3	150.5
82.5°	58.1	58.1	61.3	61.3	63.3	64.4	68.5	73.7	87.2	95.5	98.6
85°	33.2	33.2	34.3	34.3	34.3	36.3	39.5	41.5	45.7	50.9	52.9
87.5°	13.5	14.5	14.5	14.5	14.5	16.6	16.6	18.7	19.7	21.8	21.8
90°	8.0	7.8	7.5	7.4	7.2	6.8	6.5	6.1	5.7	5.1	4.6
92.5°	7.6	7.5	7.4	7.4	7.2	6.8	6.5	6.1	5.7	5.2	4.7
95°	7.4	7.4	7.4	7.4	7.2	6.8	6.5	6.1	5.7	8.7	11.7
97.5°	7.3	7.2	7.1	7.1	7.0	6.9	6.7	6.6	6.4	13.9	21.3
100°	8.0	8.3	8.6	8.8	14.7	26.4	38.1	49.8	61.5	61.2	60.9
102.5°	66.9	73.6	80.2	83.5	83.4	83.2	83.1	82.9	82.7	82.5	82.4
105°	105.2	105.3	105.4	105.4	105.4	105.4	105.4	105.4	105.4	105.4	105.4
107.5°	128.3	128.6	128.9	129.1	129.1	129.0	128.9	128.8	128.7	128.5	128.4
110°	151.2	151.1	151.0	151.0	151.1	151.4	151.6	151.9	152.1	151.9	151.7

TEST NUMBER: P1027012

CATALOG NUMBER: S125DIP-B850D375UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	172.9	173.1	173.2	173.3	173.5	173.8	174.1	174.4	174.7	174.6	174.5
115°	194.7	195.2	195.7	195.9	196.1	196.4	196.7	197.0	197.3	197.2	197.2
117.5°	217.1	217.3	217.4	217.5	217.7	218.2	218.7	219.1	219.6	219.3	219.0
120°	238.4	238.8	239.2	239.4	239.5	239.6	239.8	239.9	240.1	239.9	239.6
122.5°	258.3	258.8	259.3	259.5	259.6	259.8	259.9	260.1	260.3	260.2	260.1
125°	278.0	278.3	278.5	278.6	278.8	279.1	279.4	279.8	280.1	280.1	280.1
127.5°	295.4	296.1	296.7	297.0	297.1	297.2	297.4	297.5	297.7	297.8	297.9
130°	313.4	313.8	314.2	314.4	314.5	314.7	315.0	315.2	315.4	315.3	315.3
132.5°	330.4	330.7	331.1	331.3	331.3	331.3	331.3	331.3	331.3	331.5	331.8
135°	345.7	346.2	346.7	346.9	347.0	347.1	347.3	347.4	347.6	347.8	347.9
137.5°	361.5	361.8	362.2	362.4	362.4	362.4	362.4	362.4	362.4	362.6	362.8
140°	375.4	375.9	376.4	376.6	376.5	376.4	376.2	376.1	375.9	376.0	376.0
142.5°	388.5	389.0	389.5	389.7	389.7	389.7	389.7	389.7	389.7	389.5	389.4
145°	401.2	401.7	402.2	402.4	402.4	402.3	402.2	402.2	402.1	402.1	402.1
147.5°	412.0	412.6	413.1	413.4	413.4	413.3	413.2	413.1	413.0	412.9	412.9
150°	422.4	423.0	423.7	424.0	423.9	423.8	423.6	423.5	423.3	423.1	423.0
152.5°	431.8	432.4	432.9	433.2	433.1	433.0	432.8	432.7	432.5	432.3	432.2
155°	440.1	440.7	441.4	441.7	441.6	441.3	441.1	440.8	440.6	440.4	440.3
157.5°	447.1	447.8	448.4	448.7	448.6	448.4	448.1	447.9	447.7	447.7	447.7
160°	453.8	454.5	455.1	455.4	455.2	454.9	454.6	454.3	454.0	453.9	453.9
162.5°	460.0	460.7	461.4	461.8	461.6	461.1	460.6	460.2	459.7	459.6	459.5
165°	465.2	465.8	466.5	466.8	466.6	466.1	465.6	465.1	464.6	464.5	464.5
167.5°	469.2	469.9	470.6	471.0	470.7	470.2	469.6	469.1	468.5	468.4	468.4
170°	472.4	473.1	473.8	474.2	473.9	473.3	472.6	472.0	471.4	471.3	471.2
172.5°	474.5	475.2	475.9	476.3	476.0	475.5	474.9	474.4	473.8	473.6	473.5
175°	476.3	477.0	477.7	478.1	477.8	477.1	476.5	475.8	475.2	475.1	475.1
177.5°	477.2	477.9	478.5	478.8	478.5	478.0	477.4	476.9	476.3	476.2	476.2
180°	477.0	477.0	477.0	477.0	477.0	477.0	477.0	477.0	477.0	477.0	477.0

TEST NUMBER: P1027012

CATALOG NUMBER: S125DIP-B850D375UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0
2.5°	1258.3	1253.1	1246.8	1246.8	1239.6	1236.5	1230.2	1228.1	1223.0	1214.6	1208.4
5°	1302.9	1289.4	1281.1	1273.8	1258.3	1246.8	1235.4	1223.0	1210.5	1196.0	1179.4
7.5°	1346.5	1321.6	1310.2	1297.7	1274.9	1251.0	1228.1	1211.5	1194.9	1172.1	1151.3
10°	1392.2	1361.0	1340.3	1323.7	1288.4	1258.3	1225.0	1201.2	1175.2	1146.1	1119.1
12.5°	1430.6	1390.1	1372.4	1341.3	1300.8	1264.5	1223.0	1186.6	1152.4	1118.1	1084.9
15°	1462.8	1424.4	1380.8	1368.3	1312.2	1260.3	1213.6	1166.9	1124.3	1090.1	1051.7
17.5°	1473.2	1424.4	1402.6	1372.4	1306.0	1252.0	1192.8	1142.0	1101.5	1050.6	1020.5
20°	1476.3	1429.5	1399.4	1371.4	1312.2	1240.6	1182.5	1120.2	1071.4	1020.5	972.8
22.5°	1468.0	1412.9	1383.9	1356.9	1290.4	1229.2	1161.7	1093.2	1036.1	989.4	941.6
25°	1452.4	1388.0	1360.0	1330.9	1267.6	1200.1	1126.4	1061.0	1008.1	952.0	905.3
27.5°	1431.6	1357.9	1325.7	1295.6	1233.3	1170.0	1100.5	1033.0	973.8	914.6	871.0
30°	1405.7	1320.5	1291.5	1252.0	1191.8	1131.6	1068.3	1000.8	934.3	878.3	830.5
32.5°	1372.4	1283.2	1244.8	1207.4	1142.0	1087.0	1026.7	963.4	899.0	844.0	794.2
35°	1342.3	1240.6	1198.0	1160.7	1088.0	1029.9	980.0	920.8	863.8	806.7	762.0
37.5°	1301.9	1198.0	1147.2	1108.8	1035.0	975.9	929.2	883.5	823.3	768.2	726.7
40°	1259.3	1145.1	1097.3	1058.9	982.1	917.7	873.1	832.6	783.8	732.9	689.3
42.5°	1220.9	1094.2	1043.4	996.6	918.8	861.7	816.0	784.9	740.2	694.5	655.1
45°	1172.1	1040.2	985.2	936.4	861.7	799.4	755.8	730.9	697.6	653.0	618.7
47.5°	1122.3	982.1	925.0	877.2	796.3	741.2	698.7	674.8	652.0	616.7	582.4
50°	1056.8	920.8	868.9	813.9	734.0	677.9	642.6	618.7	601.1	576.2	547.1
52.5°	985.2	857.5	801.5	753.7	674.8	623.9	583.4	570.0	552.3	533.6	508.7
55°	909.4	789.0	735.0	688.3	615.6	563.7	530.5	516.0	502.5	487.9	471.3
57.5°	833.6	717.4	666.5	625.0	557.5	507.7	480.7	460.9	451.6	443.3	429.8
60°	739.2	640.5	601.1	563.7	497.3	451.6	425.6	411.1	402.8	398.7	392.4
62.5°	656.1	575.1	531.5	495.2	442.3	401.8	376.9	365.4	358.2	356.1	348.8
65°	567.9	498.3	464.1	432.9	387.2	350.9	330.1	316.6	311.4	310.4	310.4
67.5°	484.8	428.8	394.5	372.7	333.2	301.1	281.3	276.2	273.0	268.9	267.8
70°	407.0	362.3	332.2	313.5	278.2	254.3	238.8	230.5	230.5	227.4	225.3
72.5°	338.4	293.8	274.1	258.5	229.4	208.7	197.3	195.2	187.9	186.9	186.9
75°	264.7	231.5	218.0	204.5	182.7	168.2	158.8	153.6	149.5	149.5	150.5
77.5°	199.3	176.5	164.0	153.6	138.1	128.7	121.5	119.4	115.2	115.2	115.2
80°	141.2	128.7	119.4	111.1	99.7	91.4	87.2	83.1	83.1	82.0	83.1
82.5°	91.4	81.0	75.8	74.7	64.4	61.3	56.1	57.1	54.0	52.9	55.0
85°	52.9	47.8	41.5	39.5	35.3	31.1	29.1	30.1	29.1	28.0	29.1
87.5°	20.8	17.6	16.6	16.6	13.5	12.5	11.4	12.5	10.4	10.4	11.4
90°	4.0	3.5	3.2	2.9	2.3	1.6	1.0	0.4	1.0	1.6	2.3
92.5°	4.2	3.7	3.5	3.9	4.6	5.3	6.0	6.7	6.0	5.3	4.6
95°	14.6	17.6	19.1	19.2	19.5	19.7	20.0	20.2	20.0	19.7	19.5
97.5°	28.8	36.3	40.0	39.8	39.3	38.8	38.3	37.8	38.3	38.8	39.3
100°	60.6	60.3	60.1	60.0	59.8	59.5	59.3	59.1	59.3	59.5	59.8
102.5°	82.2	82.1	82.0	81.8	81.5	81.2	80.9	80.6	80.9	81.2	81.5
105°	105.4	105.4	105.4	105.2	104.9	104.6	104.3	104.0	104.3	104.6	104.9
107.5°	128.2	128.1	128.0	128.0	128.0	128.0	128.0	128.0	128.0	128.0	128.0
110°	151.6	151.4	151.3	151.3	151.3	151.3	151.3	151.3	151.3	151.3	151.3

TEST NUMBER: P1027012

CATALOG NUMBER: S125DIP-B850D375UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	174.4	174.3	174.3	174.2	174.0	173.7	173.5	173.3	173.5	173.7	174.0
115°	197.1	197.0	197.0	196.8	196.4	196.0	195.6	195.2	195.6	196.0	196.4
117.5°	218.7	218.4	218.2	218.2	218.2	218.2	218.2	218.2	218.2	218.2	218.2
120°	239.4	239.1	239.0	239.0	239.1	239.2	239.3	239.4	239.3	239.2	239.1
122.5°	260.0	259.9	259.9	259.7	259.3	258.9	258.5	258.1	258.5	258.9	259.3
125°	280.1	280.1	280.1	279.8	279.3	278.7	278.2	277.6	278.2	278.7	279.3
127.5°	298.0	298.1	298.1	297.9	297.5	297.1	296.7	296.3	296.7	297.1	297.5
130°	315.2	315.1	315.1	314.9	314.5	314.1	313.7	313.3	313.7	314.1	314.5
132.5°	332.0	332.3	332.4	332.2	331.7	331.2	330.8	330.3	330.8	331.2	331.7
135°	348.1	348.2	348.3	348.1	347.6	347.1	346.7	346.2	346.7	347.1	347.6
137.5°	362.9	363.1	363.2	363.0	362.5	362.0	361.5	361.0	361.5	362.0	362.5
140°	376.1	376.2	376.2	376.1	376.0	375.8	375.7	375.5	375.7	375.8	376.0
142.5°	389.2	389.1	389.0	389.0	388.9	388.8	388.7	388.6	388.7	388.8	388.9
145°	402.1	402.1	402.1	402.0	401.8	401.7	401.5	401.3	401.5	401.7	401.8
147.5°	412.8	412.7	412.7	412.7	412.7	412.7	412.7	412.7	412.7	412.7	412.7
150°	422.8	422.7	422.6	422.7	422.8	423.0	423.1	423.3	423.1	423.0	422.8
152.5°	432.0	431.9	431.8	432.0	432.4	432.7	433.1	433.5	433.1	432.7	432.4
155°	440.1	440.0	439.9	440.1	440.6	441.1	441.5	442.0	441.5	441.1	440.6
157.5°	447.7	447.7	447.7	447.8	448.0	448.3	448.5	448.7	448.5	448.3	448.0
160°	453.8	453.7	453.7	453.9	454.4	454.9	455.3	455.8	455.3	454.9	454.4
162.5°	459.4	459.3	459.3	459.5	460.0	460.5	461.0	461.5	461.0	460.5	460.0
165°	464.4	464.3	464.3	464.5	465.0	465.5	465.9	466.4	465.9	465.5	465.0
167.5°	468.3	468.2	468.2	468.4	468.9	469.4	469.8	470.3	469.8	469.4	468.9
170°	471.1	471.0	471.0	471.3	471.8	472.4	472.9	473.5	472.9	472.4	471.8
172.5°	473.3	473.2	473.1	473.4	473.9	474.5	475.0	475.6	475.0	474.5	473.9
175°	475.0	474.9	474.9	475.1	475.6	476.1	476.5	477.0	476.5	476.1	475.6
177.5°	476.1	476.0	476.0	476.2	476.7	477.2	477.6	478.1	477.6	477.2	476.7
180°	477.0	477.0	477.0	477.0	477.0	477.0	477.0	477.0	477.0	477.0	477.0

TEST NUMBER: P1027012

CATALOG NUMBER: S125DIP-B850D375UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0
2.5°	1206.3	1204.3	1199.1	1196.0	1185.6	1173.1	1169.0	1158.6	1162.7	1155.5	1155.5
5°	1174.2	1164.8	1158.6	1149.2	1129.5	1116.0	1101.5	1094.2	1090.1	1084.9	1080.7
7.5°	1132.6	1125.4	1119.1	1101.5	1079.7	1061.0	1043.4	1036.1	1022.6	1013.2	1009.1
10°	1096.3	1085.9	1071.4	1050.6	1027.8	1003.9	988.3	972.8	962.4	957.2	945.8
12.5°	1058.9	1046.5	1030.9	1000.8	975.9	961.3	933.3	918.8	913.6	909.4	895.9
15°	1020.5	1007.0	988.3	960.3	938.5	904.2	887.6	876.2	863.8	862.7	852.3
17.5°	986.3	969.6	954.1	919.8	892.8	862.7	853.4	840.9	829.5	817.0	811.8
20°	942.7	927.1	915.7	878.3	848.2	829.5	813.9	803.5	796.3	783.8	781.7
22.5°	903.2	886.6	871.0	843.0	817.0	793.2	774.5	763.0	759.9	754.7	745.4
25°	864.8	848.2	829.5	803.5	776.5	759.9	743.3	736.1	729.8	721.5	714.3
27.5°	832.6	817.0	799.4	767.2	744.4	731.9	714.3	705.9	697.6	693.5	690.4
30°	794.2	776.5	763.0	738.1	713.2	696.6	684.1	676.9	669.6	665.5	663.4
32.5°	756.8	740.2	730.9	703.9	684.1	664.4	655.1	649.9	645.7	641.6	637.4
35°	726.7	710.1	695.6	670.7	650.9	637.4	630.2	621.9	618.7	614.6	614.6
37.5°	689.3	676.9	662.3	638.5	620.8	610.4	604.2	593.8	592.8	590.7	587.6
40°	657.2	644.7	631.2	610.4	594.9	582.4	574.1	568.9	565.8	563.7	561.6
42.5°	622.9	609.4	603.2	579.3	565.8	553.3	549.2	544.0	543.0	538.8	533.6
45°	589.7	578.3	565.8	548.1	536.7	526.3	520.1	516.0	510.8	509.7	506.6
47.5°	560.6	547.1	535.7	519.1	506.6	498.3	493.1	487.9	483.8	480.7	477.6
50°	523.2	512.9	503.5	485.9	475.5	467.2	459.9	455.8	451.6	451.6	451.6
52.5°	486.9	477.6	469.2	456.8	444.3	437.1	428.8	425.6	423.6	420.5	423.6
55°	451.6	442.3	434.0	424.6	410.1	403.8	395.5	392.4	393.5	393.5	396.6
57.5°	414.2	407.0	401.8	390.3	376.9	370.6	365.4	362.3	362.3	366.5	367.5
60°	377.9	370.6	361.3	350.9	342.6	335.3	332.2	333.2	333.2	335.3	340.5
62.5°	337.4	333.2	328.1	313.5	308.3	303.1	299.0	302.1	301.1	306.3	313.5
65°	300.0	295.9	288.6	281.3	275.1	269.9	268.9	269.9	272.0	277.2	285.5
67.5°	258.5	258.5	252.3	246.0	240.9	235.7	236.7	237.7	239.8	246.0	258.5
70°	224.2	220.1	213.9	209.7	205.6	203.5	201.4	205.6	211.8	215.9	225.3
72.5°	186.9	183.8	178.6	174.4	173.4	171.3	170.3	172.3	178.6	185.8	196.2
75°	147.4	148.5	145.3	142.2	142.2	139.1	141.2	141.2	147.4	154.7	163.0
77.5°	114.2	113.2	112.1	110.0	109.0	109.0	109.0	111.1	117.3	121.5	129.8
80°	81.0	82.0	78.9	79.9	78.9	79.9	79.9	84.1	87.2	92.4	98.6
82.5°	54.0	54.0	51.9	52.9	52.9	52.9	54.0	56.1	60.2	64.4	68.5
85°	30.1	31.1	29.1	31.1	31.1	31.1	32.2	33.2	36.3	37.4	41.5
87.5°	11.4	13.5	13.5	11.4	12.5	13.5	14.5	13.5	15.6	17.6	18.7
90°	2.9	3.2	3.5	4.0	4.6	5.1	5.7	6.1	6.5	6.8	7.2
92.5°	3.9	3.5	3.7	4.2	4.7	5.2	5.7	6.1	6.5	6.8	7.2
95°	19.2	19.1	17.6	14.6	11.7	8.7	5.7	6.1	6.5	6.8	7.2
97.5°	39.8	40.0	36.3	28.8	21.3	13.9	6.4	6.6	6.7	6.9	7.0
100°	60.0	60.1	60.3	60.6	60.9	61.2	61.5	49.8	38.1	26.4	14.7
102.5°	81.8	82.0	82.1	82.2	82.4	82.5	82.7	82.9	83.1	83.2	83.4
105°	105.2	105.4	105.4	105.4	105.4	105.4	105.4	105.4	105.4	105.4	105.4
107.5°	128.0	128.0	128.1	128.2	128.4	128.5	128.7	128.8	128.9	129.0	129.1
110°	151.3	151.3	151.4	151.6	151.7	151.9	152.1	151.9	151.6	151.4	151.1

TEST NUMBER: P1027012

CATALOG NUMBER: S125DIP-B850D375UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	174.2	174.3	174.3	174.4	174.5	174.6	174.7	174.4	174.1	173.8	173.5
115°	196.8	197.0	197.0	197.1	197.2	197.2	197.3	197.0	196.7	196.4	196.1
117.5°	218.2	218.2	218.4	218.7	219.0	219.3	219.6	219.1	218.7	218.2	217.7
120°	239.0	239.0	239.1	239.4	239.6	239.9	240.1	239.9	239.8	239.6	239.5
122.5°	259.7	259.9	259.9	260.0	260.1	260.2	260.3	260.1	259.9	259.8	259.6
125°	279.8	280.1	280.1	280.1	280.1	280.1	280.1	279.8	279.4	279.1	278.8
127.5°	297.9	298.1	298.1	298.0	297.9	297.8	297.7	297.5	297.4	297.2	297.1
130°	314.9	315.1	315.1	315.2	315.3	315.3	315.4	315.2	315.0	314.7	314.5
132.5°	332.2	332.4	332.3	332.0	331.8	331.5	331.3	331.3	331.3	331.3	331.3
135°	348.1	348.3	348.2	348.1	347.9	347.8	347.6	347.4	347.3	347.1	347.0
137.5°	363.0	363.2	363.1	362.9	362.8	362.6	362.4	362.4	362.4	362.4	362.4
140°	376.1	376.2	376.2	376.1	376.0	376.0	375.9	376.1	376.2	376.4	376.5
142.5°	389.0	389.0	389.1	389.2	389.4	389.5	389.7	389.7	389.7	389.7	389.7
145°	402.0	402.1	402.1	402.1	402.1	402.1	402.1	402.2	402.2	402.3	402.4
147.5°	412.7	412.7	412.7	412.8	412.9	412.9	413.0	413.1	413.2	413.3	413.4
150°	422.7	422.6	422.7	422.8	423.0	423.1	423.3	423.5	423.6	423.8	423.9
152.5°	432.0	431.8	431.9	432.0	432.2	432.3	432.5	432.7	432.8	433.0	433.1
155°	440.1	439.9	440.0	440.1	440.3	440.4	440.6	440.8	441.1	441.3	441.6
157.5°	447.8	447.7	447.7	447.7	447.7	447.7	447.7	447.9	448.1	448.4	448.6
160°	453.9	453.7	453.7	453.8	453.9	453.9	454.0	454.3	454.6	454.9	455.2
162.5°	459.5	459.3	459.3	459.4	459.5	459.6	459.7	460.2	460.6	461.1	461.6
165°	464.5	464.3	464.3	464.4	464.5	464.5	464.6	465.1	465.6	466.1	466.6
167.5°	468.4	468.2	468.2	468.3	468.4	468.4	468.5	469.1	469.6	470.2	470.7
170°	471.3	471.0	471.0	471.1	471.2	471.3	471.4	472.0	472.6	473.3	473.9
172.5°	473.4	473.1	473.2	473.3	473.5	473.6	473.8	474.4	474.9	475.5	476.0
175°	475.1	474.9	474.9	475.0	475.1	475.1	475.2	475.8	476.5	477.1	477.8
177.5°	476.2	476.0	476.0	476.1	476.2	476.2	476.3	476.9	477.4	478.0	478.5
180°	477.0	477.0	477.0	477.0	477.0	477.0	477.0	477.0	477.0	477.0	477.0

TEST NUMBER: P1027012

CATALOG NUMBER: S125DIP-B850D375UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0
2.5°	1159.6	1152.4	1151.3	1153.4	1149.2	1155.5	1153.4	1155.5	1150.3	1155.5	1152.4
5°	1079.7	1077.6	1073.5	1068.3	1069.3	1070.3	1075.5	1070.3	1074.5	1075.5	1080.7
7.5°	1004.9	1000.8	1003.9	1001.8	992.5	990.4	992.5	995.6	1001.8	1006.0	1009.1
10°	944.7	942.7	938.5	935.4	930.2	927.1	931.2	927.1	935.4	942.7	942.7
12.5°	899.0	890.7	885.6	884.5	873.1	875.2	879.3	882.4	891.8	895.9	895.9
15°	851.3	845.1	843.0	838.8	834.7	838.8	836.8	839.9	844.0	848.2	850.3
17.5°	809.8	808.7	809.8	799.4	802.5	797.3	798.3	803.5	800.4	803.5	809.8
20°	772.4	774.5	771.4	767.2	767.2	761.0	768.2	766.2	767.2	773.4	782.8
22.5°	744.4	743.3	740.2	737.1	732.9	734.0	735.0	732.9	741.2	746.4	747.5
25°	714.3	712.2	711.1	708.0	703.9	708.0	707.0	708.0	710.1	718.4	712.2
27.5°	686.2	682.1	684.1	681.0	680.0	681.0	681.0	682.1	684.1	685.2	686.2
30°	662.3	658.2	657.2	655.1	654.0	655.1	657.2	655.1	663.4	662.3	662.3
32.5°	636.4	633.3	631.2	631.2	630.2	629.1	630.2	631.2	637.4	633.3	637.4
35°	611.5	609.4	609.4	607.3	606.3	606.3	606.3	610.4	608.4	611.5	611.5
37.5°	587.6	587.6	586.6	584.5	583.4	584.5	583.4	585.5	584.5	585.5	586.6
40°	562.7	560.6	559.6	559.6	556.5	553.3	556.5	556.5	557.5	560.6	561.6
42.5°	532.6	533.6	533.6	529.5	529.5	529.5	530.5	531.5	531.5	533.6	533.6
45°	506.6	504.5	504.5	504.5	502.5	503.5	505.6	505.6	505.6	505.6	503.5
47.5°	477.6	477.6	478.6	478.6	481.7	480.7	480.7	479.6	477.6	477.6	478.6
50°	450.6	453.7	454.7	454.7	455.8	456.8	456.8	454.7	453.7	450.6	450.6
52.5°	424.6	426.7	428.8	431.9	434.0	432.9	432.9	430.8	426.7	425.6	424.6
55°	396.6	399.7	403.8	407.0	410.1	411.1	411.1	407.0	402.8	397.6	397.6
57.5°	370.6	373.7	381.0	384.1	388.3	388.3	386.2	383.1	376.9	372.7	369.6
60°	344.7	349.9	355.1	361.3	366.5	367.5	364.4	360.2	353.0	347.8	343.6
62.5°	316.6	321.8	332.2	338.4	342.6	342.6	342.6	337.4	328.1	320.8	314.6
65°	289.6	294.8	304.2	312.5	315.6	318.7	315.6	310.4	303.1	294.8	288.6
67.5°	261.6	267.8	277.2	283.4	287.6	290.7	288.6	284.5	275.1	263.7	259.5
70°	230.5	233.6	247.1	253.3	259.5	261.6	259.5	253.3	244.0	231.5	227.4
72.5°	201.4	204.5	217.0	222.2	227.4	229.4	226.3	222.2	213.9	202.4	197.3
75°	168.2	173.4	179.6	187.9	194.1	196.2	193.1	190.0	179.6	172.3	168.2
77.5°	132.9	138.1	146.4	153.6	159.9	158.8	154.7	155.7	144.3	136.0	132.9
80°	100.7	104.9	111.1	117.3	120.4	120.4	119.4	115.2	111.1	104.9	99.7
82.5°	69.6	74.7	79.9	84.1	84.1	85.1	83.1	82.0	77.9	72.7	71.6
85°	41.5	42.6	46.7	46.7	50.9	48.8	47.8	50.9	46.7	43.6	42.6
87.5°	18.7	17.6	18.7	18.7	17.6	19.7	19.7	18.7	19.7	18.7	18.7
90°	7.4	7.5	7.8	8.0	8.3	8.5	8.3	8.0	7.8	7.5	7.4
92.5°	7.4	7.4	7.5	7.6	7.7	7.8	7.7	7.6	7.5	7.4	7.4
95°	7.4	7.4	7.4	7.4	7.4	7.4	7.4	7.4	7.4	7.4	7.4
97.5°	7.1	7.1	7.2	7.3	7.3	7.4	7.3	7.3	7.2	7.1	7.1
100°	8.8	8.6	8.3	8.0	7.7	7.4	7.7	8.0	8.3	8.6	8.8
102.5°	83.5	80.2	73.6	66.9	60.3	53.7	60.3	66.9	73.6	80.2	83.5
105°	105.4	105.4	105.3	105.2	105.1	105.0	105.1	105.2	105.3	105.4	105.4
107.5°	129.1	128.9	128.6	128.3	128.0	127.7	128.0	128.3	128.6	128.9	129.1
110°	151.0	151.0	151.1	151.2	151.2	151.3	151.2	151.2	151.1	151.0	151.0

TEST NUMBER: P1027012

CATALOG NUMBER: S125DIP-B850D375UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	173.3	173.2	173.1	172.9	172.8	172.6	172.8	172.9	173.1	173.2	173.3
115°	195.9	195.7	195.2	194.7	194.3	193.8	194.3	194.7	195.2	195.7	195.9
117.5°	217.5	217.4	217.3	217.1	217.0	216.8	217.0	217.1	217.3	217.4	217.5
120°	239.4	239.2	238.8	238.4	238.0	237.6	238.0	238.4	238.8	239.2	239.4
122.5°	259.5	259.3	258.8	258.3	257.9	257.4	257.9	258.3	258.8	259.3	259.5
125°	278.6	278.5	278.3	278.0	277.8	277.6	277.8	278.0	278.3	278.5	278.6
127.5°	297.0	296.7	296.1	295.4	294.8	294.2	294.8	295.4	296.1	296.7	297.0
130°	314.4	314.2	313.8	313.4	313.0	312.6	313.0	313.4	313.8	314.2	314.4
132.5°	331.3	331.1	330.7	330.4	330.0	329.6	330.0	330.4	330.7	331.1	331.3
135°	346.9	346.7	346.2	345.7	345.3	344.8	345.3	345.7	346.2	346.7	346.9
137.5°	362.4	362.2	361.8	361.5	361.1	360.7	361.1	361.5	361.8	362.2	362.4
140°	376.6	376.4	375.9	375.4	375.0	374.5	375.0	375.4	375.9	376.4	376.6
142.5°	389.7	389.5	389.0	388.5	388.1	387.6	388.1	388.5	389.0	389.5	389.7
145°	402.4	402.2	401.7	401.2	400.8	400.3	400.8	401.2	401.7	402.2	402.4
147.5°	413.4	413.1	412.6	412.0	411.5	410.9	411.5	412.0	412.6	413.1	413.4
150°	424.0	423.7	423.0	422.4	421.7	421.1	421.7	422.4	423.0	423.7	424.0
152.5°	433.2	432.9	432.4	431.8	431.3	430.7	431.3	431.8	432.4	432.9	433.2
155°	441.7	441.4	440.7	440.1	439.4	438.8	439.4	440.1	440.7	441.4	441.7
157.5°	448.7	448.4	447.8	447.1	446.5	445.9	446.5	447.1	447.8	448.4	448.7
160°	455.4	455.1	454.5	453.8	453.2	452.6	453.2	453.8	454.5	455.1	455.4
162.5°	461.8	461.4	460.7	460.0	459.3	458.6	459.3	460.0	460.7	461.4	461.8
165°	466.8	466.5	465.8	465.2	464.5	463.9	464.5	465.2	465.8	466.5	466.8
167.5°	471.0	470.6	469.9	469.2	468.5	467.8	468.5	469.2	469.9	470.6	471.0
170°	474.2	473.8	473.1	472.4	471.7	471.0	471.7	472.4	473.1	473.8	474.2
172.5°	476.3	475.9	475.2	474.5	473.8	473.1	473.8	474.5	475.2	475.9	476.3
175°	478.1	477.7	477.0	476.3	475.6	474.9	475.6	476.3	477.0	477.7	478.1
177.5°	478.8	478.5	477.9	477.2	476.6	476.0	476.6	477.2	477.9	478.5	478.8
180°	477.0	477.0	477.0	477.0	477.0	477.0	477.0	477.0	477.0	477.0	477.0

TEST NUMBER: P1027012

CATALOG NUMBER: S125DIP-B850D375UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0
2.5°	1161.7	1155.5	1162.7	1153.4	1155.5	1166.9	1165.9	1176.2	1182.5	1181.4	1186.6
5°	1084.9	1084.9	1088.0	1087.0	1097.3	1106.7	1119.1	1129.5	1140.9	1147.2	1154.4
7.5°	1009.1	1019.5	1021.6	1026.7	1039.2	1054.8	1067.2	1082.8	1099.4	1110.8	1119.1
10°	946.8	955.1	963.4	967.6	981.1	1001.8	1019.5	1044.4	1065.2	1077.6	1089.0
12.5°	891.8	901.1	905.3	924.0	933.3	946.8	971.7	998.7	1021.6	1035.0	1044.4
15°	852.3	857.5	866.9	878.3	887.6	904.2	925.0	955.1	976.9	988.3	1020.5
17.5°	819.1	825.3	830.5	835.7	850.3	867.9	887.6	913.6	941.6	961.3	977.9
20°	784.9	788.0	794.2	802.5	812.9	829.5	847.1	874.1	899.0	914.6	936.4
22.5°	744.4	753.7	759.9	766.2	777.6	796.3	812.9	832.6	863.8	881.4	904.2
25°	720.5	724.6	728.8	736.1	744.4	761.0	779.7	800.4	825.3	844.0	863.8
27.5°	689.3	695.6	700.8	710.1	715.3	728.8	746.4	767.2	797.3	812.9	829.5
30°	663.4	669.6	673.8	677.9	685.2	699.7	716.3	732.9	761.0	780.7	797.3
32.5°	637.4	643.7	648.9	652.0	659.2	668.6	682.1	702.8	726.7	740.2	762.0
35°	614.6	614.6	620.8	625.0	631.2	639.5	652.0	667.5	692.5	710.1	729.8
37.5°	588.6	589.7	594.9	598.0	604.2	612.5	625.0	639.5	660.3	673.8	693.5
40°	561.6	564.8	566.8	572.0	579.3	582.4	594.9	611.5	632.2	644.7	661.3
42.5°	534.7	536.7	541.9	546.1	552.3	557.5	565.8	581.4	596.9	615.6	629.1
45°	504.5	509.7	512.9	520.1	523.2	528.4	536.7	549.2	567.9	579.3	594.9
47.5°	478.6	480.7	482.7	492.1	498.3	501.4	509.7	517.0	536.7	547.1	561.6
50°	450.6	450.6	453.7	457.8	465.1	471.3	478.6	486.9	502.5	512.9	527.4
52.5°	424.6	421.5	423.6	425.6	432.9	439.1	446.4	457.8	472.4	478.6	491.1
55°	396.6	391.4	394.5	397.6	399.7	408.0	416.3	423.6	435.0	444.3	455.8
57.5°	366.5	365.4	363.4	364.4	369.6	374.8	381.0	390.3	403.8	411.1	417.3
60°	339.5	333.2	331.2	333.2	336.4	339.5	347.8	356.1	367.5	374.8	382.0
62.5°	311.4	305.2	301.1	298.0	301.1	308.3	313.5	319.8	329.1	337.4	343.6
65°	284.5	275.1	271.0	268.9	267.8	273.0	277.2	285.5	293.8	296.9	304.2
67.5°	254.3	246.0	240.9	237.7	237.7	237.7	241.9	250.2	258.5	259.5	266.8
70°	224.2	214.9	209.7	205.6	203.5	205.6	210.7	211.8	219.1	221.1	225.3
72.5°	192.1	183.8	177.5	172.3	173.4	175.4	175.4	177.5	181.7	186.9	186.9
75°	162.0	150.5	147.4	143.3	141.2	141.2	141.2	145.3	148.5	152.6	151.6
77.5°	127.7	121.5	115.2	113.2	110.0	109.0	111.1	111.1	113.2	116.3	117.3
80°	98.6	91.4	87.2	85.1	81.0	79.9	81.0	81.0	84.1	83.1	84.1
82.5°	68.5	63.3	60.2	57.1	55.0	56.1	55.0	55.0	56.1	55.0	55.0
85°	39.5	38.4	36.3	35.3	34.3	32.2	34.3	33.2	32.2	31.1	33.2
87.5°	18.7	17.6	17.6	15.6	15.6	14.5	15.6	15.6	14.5	14.5	14.5
90°	7.2	6.8	6.5	6.1	5.7	5.1	4.6	4.0	3.5	3.2	2.9
92.5°	7.2	6.8	6.5	6.1	5.7	5.2	4.7	4.2	3.7	3.5	3.9
95°	7.2	6.8	6.5	6.1	5.7	8.7	11.7	14.6	17.6	19.1	19.2
97.5°	7.0	6.9	6.7	6.6	6.4	13.9	21.3	28.8	36.3	40.0	39.8
100°	14.7	26.4	38.1	49.8	61.5	61.2	60.9	60.6	60.3	60.1	60.0
102.5°	83.4	83.2	83.1	82.9	82.7	82.5	82.4	82.2	82.1	82.0	81.8
105°	105.4	105.4	105.4	105.4	105.4	105.4	105.4	105.4	105.4	105.4	105.2
107.5°	129.1	129.0	128.9	128.8	128.7	128.5	128.4	128.2	128.1	128.0	128.0
110°	151.1	151.4	151.6	151.9	152.1	151.9	151.7	151.6	151.4	151.3	151.3

TEST NUMBER: P1027012

CATALOG NUMBER: S125DIP-B850D375UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	173.5	173.8	174.1	174.4	174.7	174.6	174.5	174.4	174.3	174.3	174.2
115°	196.1	196.4	196.7	197.0	197.3	197.2	197.2	197.1	197.0	197.0	196.8
117.5°	217.7	218.2	218.7	219.1	219.6	219.3	219.0	218.7	218.4	218.2	218.2
120°	239.5	239.6	239.8	239.9	240.1	239.9	239.6	239.4	239.1	239.0	239.0
122.5°	259.6	259.8	259.9	260.1	260.3	260.2	260.1	260.0	259.9	259.9	259.7
125°	278.8	279.1	279.4	279.8	280.1	280.1	280.1	280.1	280.1	280.1	279.8
127.5°	297.1	297.2	297.4	297.5	297.7	297.8	297.9	298.0	298.1	298.1	297.9
130°	314.5	314.7	315.0	315.2	315.4	315.3	315.3	315.2	315.1	315.1	314.9
132.5°	331.3	331.3	331.3	331.3	331.3	331.5	331.8	332.0	332.3	332.4	332.2
135°	347.0	347.1	347.3	347.4	347.6	347.8	347.9	348.1	348.2	348.3	348.1
137.5°	362.4	362.4	362.4	362.4	362.4	362.6	362.8	362.9	363.1	363.2	363.0
140°	376.5	376.4	376.2	376.1	375.9	376.0	376.0	376.1	376.2	376.2	376.1
142.5°	389.7	389.7	389.7	389.7	389.7	389.5	389.4	389.2	389.1	389.0	389.0
145°	402.4	402.3	402.2	402.2	402.1	402.1	402.1	402.1	402.1	402.1	402.0
147.5°	413.4	413.3	413.2	413.1	413.0	412.9	412.9	412.8	412.7	412.7	412.7
150°	423.9	423.8	423.6	423.5	423.3	423.1	423.0	422.8	422.7	422.6	422.7
152.5°	433.1	433.0	432.8	432.7	432.5	432.3	432.2	432.0	431.9	431.8	432.0
155°	441.6	441.3	441.1	440.8	440.6	440.4	440.3	440.1	440.0	439.9	440.1
157.5°	448.6	448.4	448.1	447.9	447.7	447.7	447.7	447.7	447.7	447.7	447.8
160°	455.2	454.9	454.6	454.3	454.0	453.9	453.9	453.8	453.7	453.7	453.9
162.5°	461.6	461.1	460.6	460.2	459.7	459.6	459.5	459.4	459.3	459.3	459.5
165°	466.6	466.1	465.6	465.1	464.6	464.5	464.5	464.4	464.3	464.3	464.5
167.5°	470.7	470.2	469.6	469.1	468.5	468.4	468.4	468.3	468.2	468.2	468.4
170°	473.9	473.3	472.6	472.0	471.4	471.3	471.2	471.1	471.0	471.0	471.3
172.5°	476.0	475.5	474.9	474.4	473.8	473.6	473.5	473.3	473.2	473.1	473.4
175°	477.8	477.1	476.5	475.8	475.2	475.1	475.1	475.0	474.9	474.9	475.1
177.5°	478.5	478.0	477.4	476.9	476.3	476.2	476.2	476.1	476.0	476.0	476.2
180°	477.0	477.0	477.0	477.0	477.0	477.0	477.0	477.0	477.0	477.0	477.0

TEST NUMBER: P1027012

CATALOG NUMBER: S125DIP-B850D375UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1223.0	1223.0	1223.0	1223.0
2.5°	1193.9	1204.3	1211.5	1225.0
5°	1166.9	1185.6	1203.2	1221.9
7.5°	1139.9	1161.7	1189.7	1213.6
10°	1109.8	1137.8	1171.0	1203.2
12.5°	1079.7	1112.9	1149.2	1191.8
15°	1043.4	1085.9	1128.5	1174.2
17.5°	1011.2	1054.8	1100.5	1157.6
20°	974.8	1022.6	1072.4	1130.6
22.5°	942.7	995.6	1047.5	1108.8
25°	906.3	958.2	1015.3	1080.7
27.5°	876.2	924.0	980.0	1050.6
30°	839.9	891.8	947.8	1018.4
32.5°	805.6	855.4	914.6	984.2
35°	770.3	821.2	874.1	940.6
37.5°	737.1	780.7	833.6	897.0
40°	699.7	747.5	795.2	845.1
42.5°	665.5	709.1	753.7	793.2
45°	627.0	664.4	707.0	739.2
47.5°	591.8	625.0	658.2	683.1
50°	556.5	582.4	607.3	629.1
52.5°	514.9	544.0	557.5	571.0
55°	477.6	494.2	506.6	520.1
57.5°	441.2	448.5	454.7	467.2
60°	393.5	401.8	409.0	418.4
62.5°	351.9	356.1	358.2	367.5
65°	312.5	311.4	316.6	321.8
67.5°	269.9	268.9	274.1	276.2
70°	228.4	227.4	228.4	233.6
72.5°	188.9	188.9	190.0	192.1
75°	152.6	152.6	153.6	155.7
77.5°	115.2	117.3	116.3	120.4
80°	84.1	82.0	84.1	86.2
82.5°	55.0	57.1	57.1	55.0
85°	31.1	31.1	31.1	31.1
87.5°	13.5	13.5	14.5	15.6
90°	2.3	1.6	1.0	0.4
92.5°	4.6	5.3	6.0	6.7
95°	19.5	19.7	20.0	20.2
97.5°	39.3	38.8	38.3	37.8
100°	59.8	59.5	59.3	59.1
102.5°	81.5	81.2	80.9	80.6
105°	104.9	104.6	104.3	104.0
107.5°	128.0	128.0	128.0	128.0
110°	151.3	151.3	151.3	151.3

TEST NUMBER: P1027012

CATALOG NUMBER: S125DIP-B850D375UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	174.0	173.7	173.5	173.3
115°	196.4	196.0	195.6	195.2
117.5°	218.2	218.2	218.2	218.2
120°	239.1	239.2	239.3	239.4
122.5°	259.3	258.9	258.5	258.1
125°	279.3	278.7	278.2	277.6
127.5°	297.5	297.1	296.7	296.3
130°	314.5	314.1	313.7	313.3
132.5°	331.7	331.2	330.8	330.3
135°	347.6	347.1	346.7	346.2
137.5°	362.5	362.0	361.5	361.0
140°	376.0	375.8	375.7	375.5
142.5°	388.9	388.8	388.7	388.6
145°	401.8	401.7	401.5	401.3
147.5°	412.7	412.7	412.7	412.7
150°	422.8	423.0	423.1	423.3
152.5°	432.4	432.7	433.1	433.5
155°	440.6	441.1	441.5	442.0
157.5°	448.0	448.3	448.5	448.7
160°	454.4	454.9	455.3	455.8
162.5°	460.0	460.5	461.0	461.5
165°	465.0	465.5	465.9	466.4
167.5°	468.9	469.4	469.8	470.3
170°	471.8	472.4	472.9	473.5
172.5°	473.9	474.5	475.0	475.6
175°	475.6	476.1	476.5	477.0
177.5°	476.7	477.2	477.6	478.1
180°	477.0	477.0	477.0	477.0

(END OF REPORT)