

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026735

Luminaire Tested: S125DIP-B1090D610UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026735
REPORT IS A COMBINATION OF REPORTS P1001419 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B1090D610UB2750-4F0-XX-W2A-F_3000K
Description: Define 5 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6785.0 lumens
Efficiency: N/A
Efficacy: 109.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 62.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026735

CATALOG NUMBER: S125DIP-B1090D610UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1026735

CATALOG NUMBER: S125DIP-B1090D610UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	111	111	111	111	104	104	104	104	92	92	92	80	80	80	70	70	70	65		
1	101	97	93	89	95	91	87	84	80	78	75	71	69	67	62	60	59	55		
2	92	84	78	73	86	80	74	69	70	66	62	62	59	56	54	52	50	46		
3	84	74	67	61	79	70	63	58	62	57	52	55	51	47	48	45	42	39		
4	77	66	58	51	72	62	55	49	55	49	45	49	44	40	43	39	36	33		
5	71	59	50	44	66	55	48	42	49	43	39	44	39	35	39	35	32	29		
6	65	53	44	38	61	50	42	37	45	38	34	40	35	31	35	31	28	25		
7	60	48	39	34	57	45	38	32	41	34	30	36	31	27	32	28	25	22		
8	56	43	35	30	53	41	34	29	37	31	27	33	28	24	30	25	22	20		
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	27	23	20	18		
10	49	36	29	24	46	35	28	23	31	26	22	28	23	20	25	21	18	16		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10868	10868	10868
5°	10869	10616	10636
10°	10779	10372	10340
15°	10637	10081	9991
20°	10446	9744	9591
25°	10241	9376	9163
30°	9993	8992	8711
35°	9728	8590	8205
40°	9454	8165	7755
45°	9158	7751	7278
50°	8833	7281	6721
55°	8511	6763	6209
60°	8126	6217	5613
65°	7666	5584	4997
70°	7199	4858	4285
75°	6412	4000	3466
80°	5465	2988	2549
85°	4220	1768	1405

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9158 cd/sqm

TEST NUMBER: P1026735

CATALOG NUMBER: S125DIP-B1090D610UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	160.1	2.4
10°-20°	452.1	6.7
20°-30°	667.5	9.8
30°-40°	778.8	11.5
40°-50°	782.2	11.5
50°-60°	686.6	10.1
60°-70°	511.4	7.5
70°-80°	292.1	4.3
80°-90°	85.5	1.3
90°-100°	26.2	0.4
100°-110°	174.1	2.6
110°-120°	313.4	4.6
120°-130°	402.3	5.9
130°-140°	432.7	6.4
140°-150°	406.1	6.0
150°-160°	328.5	4.8
160°-170°	212.4	3.1
170°-180°	73.3	1.1
0°-30°	1279.7	18.9
0°-40°	2058.4	30.3
0°-60°	3527.2	52.0
0°-90°	4416.1	65.1
90°-120°	513.6	7.6
90°-150°	1754.7	25.9
90°-180°	2369.0	34.9
0°-180°	6785.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1696	1696	1696	1696	1696	
5°	1694	1691	1678	1690	1688	161
15°	1614	1610	1596	1602	1602	455
25°	1466	1459	1441	1444	1440	674
35°	1266	1260	1241	1235	1224	792
45°	1036	1031	1014	998	994	798
55°	789	785	766	754	745	704
65°	533	530	515	503	498	528
75°	283	280	274	270	264	301
85°	74	75	75	74	71	81
90°	1	5	9	12	14	7
95°	33	31	9	12	12	40
105°	168	170	170	170	170	178
115°	316	318	319	317	313	313
125°	449	453	453	450	449	401
135°	560	563	562	561	557	431
145°	649	650	650	650	647	406
155°	715	711	712	714	709	329
165°	754	751	751	755	750	213
175°	771	768	768	773	768	73
180°	771	771	771	771	771	

TEST NUMBER: P1026735

CATALOG NUMBER: S125DIP-B1090D610UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1696.3	1696.3	1696.3	1696.3	1696.3
2.5°	1701.6	1697.6	1684.2	1697.6	1696.3
5°	1693.6	1690.9	1677.5	1689.6	1688.2
7.5°	1681.5	1678.8	1664.1	1676.2	1674.8
10°	1664.1	1661.4	1646.6	1657.4	1656.0
12.5°	1642.6	1637.2	1623.8	1631.9	1631.9
15°	1614.4	1610.4	1595.6	1602.3	1602.3
17.5°	1584.9	1578.2	1563.4	1571.5	1564.8
20°	1546.0	1543.3	1525.8	1535.2	1528.5
22.5°	1507.1	1501.7	1485.6	1491.0	1486.9
25°	1465.5	1458.7	1441.3	1444.0	1440.0
27.5°	1417.1	1413.1	1395.7	1397.0	1393.0
30°	1370.2	1366.1	1346.0	1343.3	1339.3
32.5°	1319.2	1312.5	1295.0	1289.7	1281.6
35°	1265.5	1260.1	1241.3	1234.6	1223.9
37.5°	1210.5	1203.8	1186.3	1176.9	1170.2
40°	1154.1	1147.4	1128.6	1116.5	1112.5
42.5°	1093.7	1088.4	1069.6	1058.8	1052.1
45°	1036.0	1030.7	1014.5	998.4	994.4
47.5°	972.9	974.3	954.2	938.1	928.7
50°	912.6	908.5	892.4	875.0	865.6
52.5°	850.8	848.1	830.7	815.9	805.2
55°	789.1	785.1	766.3	754.2	744.8
57.5°	723.3	722.0	705.9	689.8	685.8
60°	661.6	656.2	641.5	628.1	618.7
62.5°	597.2	593.2	581.1	566.3	559.6
65°	532.8	530.1	515.3	503.2	497.9
67.5°	469.7	464.3	453.6	442.9	440.2
70°	410.7	403.9	391.9	383.8	378.4
72.5°	346.2	342.2	335.5	326.1	320.7
75°	283.2	280.5	273.8	269.7	264.4
77.5°	224.1	222.8	218.7	216.1	212.0
80°	169.1	169.1	166.4	165.1	162.4
82.5°	120.8	118.1	118.1	115.4	115.4
85°	73.8	75.2	75.2	73.8	71.1
87.5°	36.2	36.2	34.9	34.9	32.2
90°	0.6	5.1	9.1	12.0	13.7
92.5°	10.9	5.7	9.1	12.0	12.6
95°	32.6	30.9	9.1	12.0	12.0
97.5°	61.2	64.6	10.3	11.4	12.0
100°	95.5	97.2	99.5	14.3	12.0
102.5°	130.3	132.6	133.8	134.9	86.9
105°	168.1	170.4	170.4	170.4	169.8
107.5°	206.9	206.9	208.1	208.7	206.4
110°	244.7	244.7	245.8	244.1	244.7



TEST NUMBER: P1026735

CATALOG NUMBER: S125DIP-B1090D610UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	280.1	281.8	282.4	280.1	279.0
115°	315.6	318.4	319.0	316.7	313.3
117.5°	352.7	352.7	355.0	351.6	350.4
120°	387.0	386.4	388.2	387.0	384.2
122.5°	417.3	420.2	420.7	419.6	416.2
125°	448.8	452.8	452.8	450.5	448.8
127.5°	479.0	481.9	481.3	480.2	475.6
130°	506.5	509.3	509.9	508.2	505.3
132.5°	533.9	537.4	535.6	535.6	532.8
135°	559.7	563.1	561.9	560.8	557.4
137.5°	583.7	587.1	585.9	585.9	583.1
140°	607.1	608.2	607.7	608.8	605.4
142.5°	628.3	628.8	630.0	630.0	626.5
145°	648.8	650.0	650.0	650.5	647.1
147.5°	667.1	667.1	667.7	668.3	664.3
150°	684.3	683.1	684.3	685.4	680.8
152.5°	700.9	698.0	699.1	700.3	696.3
155°	714.6	711.1	712.3	714.0	709.4
157.5°	725.4	723.7	723.7	725.4	720.9
160°	736.9	733.4	734.0	736.3	731.7
162.5°	746.0	742.6	743.2	746.6	741.4
165°	754.0	750.6	751.2	754.6	750.0
167.5°	760.3	756.9	757.4	761.4	756.3
170°	765.4	761.4	762.0	766.6	761.4
172.5°	768.9	764.9	766.0	770.0	764.9
175°	771.2	767.7	768.3	772.9	767.7
177.5°	772.9	769.5	770.0	774.0	769.5
180°	771.2	771.2	771.2	771.2	771.2

(END OF REPORT)