

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026737

Luminaire Tested: S125DIP-B1090D610UB2750-4F0-XX-W2A-F_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026737
REPORT IS A COMBINATION OF REPORTS P1001421 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B1090D610UB2750-4F0-XX-W2A-F_4000K
Description: Define 5 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6747.0 lumens
Efficiency: N/A
Efficacy: 108.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 62.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026737

CATALOG NUMBER: S125DIP-B1090D610UB2750-4F0-XX-W2A-F_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1026737

CATALOG NUMBER: S125DIP-B1090D610UB2750-4F0-XX-W2A-F_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	111	111	111	111	104	104	104	104	92	92	92	80	80	80	70	70	70	65		
1	101	97	93	89	95	91	87	84	80	78	75	71	69	67	62	60	59	55		
2	92	84	78	73	86	80	74	69	70	66	62	62	59	56	54	52	50	46		
3	84	74	67	61	79	70	63	58	62	57	52	55	51	47	48	45	42	39		
4	77	66	58	51	72	62	55	49	55	49	45	49	44	40	43	39	36	33		
5	71	59	50	44	66	55	48	42	49	43	39	44	39	35	39	35	32	29		
6	65	53	44	38	61	50	42	37	45	38	34	40	35	31	35	31	28	25		
7	60	48	39	34	57	45	38	32	41	34	30	36	31	27	32	28	25	22		
8	56	43	35	30	53	41	34	29	37	31	27	33	28	24	30	25	22	20		
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	27	23	20	18		
10	49	36	29	24	46	35	28	23	31	26	22	28	23	20	25	21	18	16		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10807	10807	10807
5°	10807	10556	10576
10°	10717	10314	10281
15°	10577	10024	9935
20°	10387	9689	9537
25°	10183	9322	9111
30°	9936	8941	8662
35°	9673	8542	8159
40°	9401	8119	7711
45°	9107	7707	7237
50°	8783	7240	6683
55°	8462	6724	6174
60°	8081	6181	5582
65°	7623	5553	4969
70°	7157	4830	4262
75°	6376	3977	3446
80°	5432	2971	2535
85°	4197	1756	1397

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9107 cd/sqm

TEST NUMBER: P1026737

CATALOG NUMBER: S125DIP-B1090D610UB2750-4F0-XX-W2A-F_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	159.2	2.4
10°-20°	449.6	6.7
20°-30°	663.7	9.8
30°-40°	774.4	11.5
40°-50°	777.7	11.5
50°-60°	682.7	10.1
60°-70°	508.5	7.5
70°-80°	290.4	4.3
80°-90°	85.0	1.3
90°-100°	26.0	0.4
100°-110°	173.1	2.6
110°-120°	311.7	4.6
120°-130°	400.1	5.9
130°-140°	430.3	6.4
140°-150°	403.9	6.0
150°-160°	326.7	4.8
160°-170°	211.3	3.1
170°-180°	72.9	1.1
0°-30°	1272.4	18.9
0°-40°	2046.8	30.3
0°-60°	3507.2	52.0
0°-90°	4391.1	65.1
90°-120°	510.8	7.6
90°-150°	1745.0	25.9
90°-180°	2356.0	34.9
0°-180°	6747.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1687	1687	1687	1687	1687	
5°	1684	1681	1668	1680	1679	160
15°	1605	1601	1587	1593	1593	453
25°	1457	1450	1433	1436	1432	670
35°	1258	1253	1234	1228	1217	787
45°	1030	1025	1009	993	989	794
55°	785	781	762	750	741	700
65°	530	527	512	500	495	525
75°	282	279	272	268	263	300
85°	73	75	75	73	71	80
90°	1	5	9	12	14	7
95°	32	31	9	12	12	40
105°	167	169	169	169	169	177
115°	314	317	317	315	312	311
125°	446	450	450	448	446	399
135°	557	560	559	558	554	429
145°	645	646	646	647	644	404
155°	711	707	708	710	706	327
165°	750	746	747	750	746	212
175°	767	764	764	769	764	73
180°	767	767	767	767	767	



TEST NUMBER: P1026737

CATALOG NUMBER: S125DIP-B1090D610UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1686.7	1686.7	1686.7	1686.7	1686.7
2.5°	1692.0	1688.0	1674.7	1688.0	1686.7
5°	1684.0	1681.3	1668.0	1680.0	1678.7
7.5°	1672.0	1669.3	1654.6	1666.7	1665.3
10°	1654.6	1652.0	1637.3	1648.0	1646.6
12.5°	1633.3	1628.0	1614.6	1622.6	1622.6
15°	1605.3	1601.3	1586.6	1593.3	1593.3
17.5°	1575.9	1569.2	1554.6	1562.6	1555.9
20°	1537.2	1534.6	1517.2	1526.5	1519.9
22.5°	1498.5	1493.2	1477.2	1482.5	1478.5
25°	1457.2	1450.5	1433.1	1435.8	1431.8
27.5°	1409.1	1405.1	1387.8	1389.1	1385.1
30°	1362.4	1358.4	1338.4	1335.7	1331.7
32.5°	1311.7	1305.0	1287.7	1282.4	1274.3
35°	1258.3	1253.0	1234.3	1227.6	1217.0
37.5°	1203.6	1197.0	1179.6	1170.3	1163.6
40°	1147.6	1140.9	1122.2	1110.2	1106.2
42.5°	1087.5	1082.2	1063.5	1052.8	1046.2
45°	1030.2	1024.8	1008.8	992.8	988.8
47.5°	967.4	968.8	948.8	932.7	923.4
50°	907.4	903.4	887.4	870.0	860.7
52.5°	846.0	843.3	826.0	811.3	800.6
55°	784.6	780.6	761.9	749.9	740.6
57.5°	719.2	717.9	701.9	685.9	681.9
60°	657.9	652.5	637.8	624.5	615.2
62.5°	593.8	589.8	577.8	563.1	556.4
65°	529.8	527.1	512.4	500.4	495.1
67.5°	467.0	461.7	451.0	440.4	437.7
70°	408.3	401.7	389.6	381.6	376.3
72.5°	344.3	340.3	333.6	324.3	318.9
75°	281.6	278.9	272.2	268.2	262.9
77.5°	222.8	221.5	217.5	214.8	210.8
80°	168.1	168.1	165.5	164.1	161.5
82.5°	120.1	117.4	117.4	114.8	114.8
85°	73.4	74.7	74.7	73.4	70.7
87.5°	36.0	36.0	34.7	34.7	32.0
90°	0.6	5.1	9.1	11.9	13.6
92.5°	10.8	5.7	9.1	11.9	12.5
95°	32.4	30.7	9.1	11.9	11.9
97.5°	60.8	64.2	10.2	11.4	11.9
100°	94.9	96.6	98.9	14.2	11.9
102.5°	129.6	131.9	133.0	134.2	86.4
105°	167.1	169.4	169.4	169.4	168.9
107.5°	205.8	205.8	206.9	207.5	205.2
110°	243.3	243.3	244.5	242.8	243.3



TEST NUMBER: P1026737

CATALOG NUMBER: S125DIP-B1090D610UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	278.6	280.3	280.8	278.6	277.4
115°	313.8	316.7	317.2	315.0	311.5
117.5°	350.8	350.8	353.1	349.6	348.5
120°	384.9	384.3	386.0	384.9	382.0
122.5°	415.0	417.9	418.4	417.3	413.9
125°	446.3	450.3	450.3	448.0	446.3
127.5°	476.4	479.3	478.7	477.6	473.0
130°	503.7	506.6	507.1	505.4	502.6
132.5°	531.0	534.4	532.7	532.7	529.9
135°	556.6	560.0	558.9	557.7	554.3
137.5°	580.5	583.9	582.7	582.7	579.9
140°	603.8	604.9	604.3	605.5	602.1
142.5°	624.8	625.4	626.5	626.5	623.1
145°	645.3	646.4	646.4	647.0	643.6
147.5°	663.5	663.5	664.0	664.6	660.6
150°	680.5	679.4	680.5	681.7	677.1
152.5°	697.0	694.2	695.3	696.4	692.5
155°	710.7	707.2	708.4	710.1	705.5
157.5°	721.5	719.7	719.7	721.5	716.9
160°	732.8	729.4	730.0	732.3	727.7
162.5°	741.9	738.5	739.1	742.5	737.4
165°	749.9	746.5	747.0	750.4	745.9
167.5°	756.1	752.7	753.3	757.3	752.2
170°	761.2	757.3	757.8	762.4	757.3
172.5°	764.7	760.7	761.8	765.8	760.7
175°	766.9	763.5	764.1	768.6	763.5
177.5°	768.6	765.2	765.8	769.8	765.2
180°	766.9	766.9	766.9	766.9	766.9

(END OF REPORT)