

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027020

Luminaire Tested: S125DIP-B850D375UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027020
REPORT IS A COMBINATION OF REPORTS P1002559 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B850D375UB2750-4F0-XX-W2A-F_3000K
Description: Define 5 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4909.0 lumens
Efficiency: N/A
Efficacy: 108.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 45.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027020

CATALOG NUMBER: S125DIP-B850D375UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1027020

CATALOG NUMBER: S125DIP-B850D375UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	112	112	112	112	106	106	106	106	94	94	94	84	84	84	74	74	74
1	102	98	94	90	96	93	89	86	83	80	78	74	72	70	66	64	63
2	93	85	79	74	88	81	75	70	73	68	64	65	61	58	58	55	53
3	85	75	67	61	80	71	64	59	64	59	54	57	53	49	51	48	45
4	78	66	58	52	73	63	56	50	57	51	46	51	46	42	46	42	39
5	71	59	51	45	67	56	49	43	51	45	40	46	41	37	41	37	34
6	66	53	45	39	62	51	43	38	46	40	35	42	36	32	37	33	30
7	61	48	40	34	58	46	38	33	42	35	31	38	33	29	34	30	26
8	57	44	36	30	54	42	35	29	38	32	27	35	29	26	31	27	24
9	53	40	32	27	50	38	31	26	35	29	25	32	27	23	29	25	21
10	50	37	30	25	47	35	29	24	32	26	22	30	25	21	27	23	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8456	8456	8456
5°	8456	8259	8275
10°	8386	8070	8045
15°	8276	7843	7774
20°	8127	7581	7462
25°	7968	7295	7128
30°	7774	6996	6777
35°	7569	6683	6384
40°	7356	6353	6034
45°	7126	6030	5662
50°	6872	5665	5229
55°	6621	5262	4831
60°	6322	4837	4367
65°	5964	4345	3888
70°	5601	3780	3334
75°	4988	3112	2696
80°	4253	2325	1983
85°	3282	1376	1092

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7126 cd/sqm

TEST NUMBER: P1027020

CATALOG NUMBER: S125DIP-B850D375UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	124.5	2.5
10°-20°	351.8	7.2
20°-30°	519.3	10.6
30°-40°	605.9	12.3
40°-50°	608.5	12.4
50°-60°	534.2	10.9
60°-70°	397.9	8.1
70°-80°	227.2	4.6
80°-90°	66.3	1.4
90°-100°	16.3	0.3
100°-110°	108.2	2.2
110°-120°	194.9	4.0
120°-130°	250.2	5.1
130°-140°	269.1	5.5
140°-150°	252.6	5.1
150°-160°	204.3	4.2
160°-170°	132.1	2.7
170°-180°	45.6	0.9
0°-30°	995.6	20.3
0°-40°	1601.5	32.6
0°-60°	2744.3	55.9
0°-90°	3435.7	70.0
90°-120°	319.5	6.5
90°-150°	1091.3	22.2
90°-180°	1473.0	30.0
0°-180°	4909.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1320	1320	1320	1320	1320	
5°	1318	1316	1305	1314	1314	125
15°	1256	1253	1241	1247	1247	354
25°	1140	1135	1121	1124	1120	525
35°	985	980	966	961	952	616
45°	806	802	789	777	774	621
55°	614	611	596	587	580	548
65°	414	412	401	392	387	411
75°	220	218	213	210	206	235
85°	57	58	58	57	55	63
90°	0	3	6	8	8	5
95°	20	19	6	8	8	25
105°	104	106	106	106	106	111
115°	196	198	198	197	195	195
125°	279	282	282	280	279	249
135°	348	350	350	349	347	268
145°	404	404	404	405	402	252
155°	444	442	443	444	441	205
165°	469	467	467	469	466	132
175°	480	478	478	481	478	46
180°	480	480	480	480	480	

TEST NUMBER: P1027020

CATALOG NUMBER: S125DIP-B850D375UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1319.8	1319.8	1319.8	1319.8	1319.8
2.5°	1323.9	1320.8	1310.4	1320.8	1319.8
5°	1317.7	1315.6	1305.1	1314.5	1313.5
7.5°	1308.3	1306.2	1294.7	1304.1	1303.1
10°	1294.7	1292.6	1281.1	1289.5	1288.4
12.5°	1278.0	1273.8	1263.4	1269.6	1269.6
15°	1256.1	1252.9	1241.4	1246.7	1246.7
17.5°	1233.1	1227.9	1216.4	1222.7	1217.4
20°	1202.8	1200.7	1187.2	1194.5	1189.2
22.5°	1172.5	1168.4	1155.8	1160.0	1156.9
25°	1140.2	1134.9	1121.4	1123.5	1120.3
27.5°	1102.6	1099.4	1085.9	1086.9	1083.8
30°	1066.0	1062.9	1047.2	1045.2	1042.0
32.5°	1026.4	1021.1	1007.6	1003.4	997.1
35°	984.6	980.4	965.8	960.6	952.2
37.5°	941.8	936.6	923.0	915.7	910.5
40°	897.9	892.7	878.1	868.7	865.6
42.5°	851.0	846.8	832.2	823.8	818.6
45°	806.1	801.9	789.3	776.8	773.7
47.5°	757.0	758.0	742.4	729.8	722.5
50°	710.0	706.9	694.3	680.8	673.5
52.5°	662.0	659.9	646.3	634.8	626.5
55°	613.9	610.8	596.2	586.8	579.5
57.5°	562.8	561.7	549.2	536.7	533.5
60°	514.7	510.6	499.1	488.6	481.3
62.5°	464.6	461.5	452.1	440.6	435.4
65°	414.5	412.4	400.9	391.5	387.4
67.5°	365.4	361.3	352.9	344.6	342.5
70°	319.5	314.3	304.9	298.6	294.4
72.5°	269.4	266.2	261.0	253.7	249.5
75°	220.3	218.2	213.0	209.9	205.7
77.5°	174.4	173.3	170.2	168.1	165.0
80°	131.6	131.6	129.5	128.4	126.3
82.5°	94.0	91.9	91.9	89.8	89.8
85°	57.4	58.5	58.5	57.4	55.3
87.5°	28.2	28.2	27.1	27.1	25.1
90°	0.4	3.2	5.7	7.5	8.5
92.5°	6.8	3.6	5.7	7.5	7.8
95°	20.3	19.2	5.7	7.5	7.5
97.5°	38.0	40.2	6.4	7.1	7.5
100°	59.4	60.4	61.9	8.9	7.5
102.5°	81.1	82.5	83.2	83.9	54.0
105°	104.5	105.9	105.9	105.9	105.6
107.5°	128.7	128.7	129.4	129.8	128.3
110°	152.2	152.2	152.9	151.8	152.2

TEST NUMBER: P1027020

CATALOG NUMBER: S125DIP-B850D375UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	174.2	175.3	175.6	174.2	173.5
115°	196.3	198.0	198.4	197.0	194.8
117.5°	219.4	219.4	220.8	218.7	217.9
120°	240.7	240.3	241.4	240.7	238.9
122.5°	259.5	261.3	261.7	261.0	258.8
125°	279.1	281.6	281.6	280.2	279.1
127.5°	297.9	299.7	299.4	298.7	295.8
130°	315.0	316.8	317.1	316.1	314.3
132.5°	332.1	334.2	333.1	333.1	331.4
135°	348.1	350.2	349.5	348.8	346.6
137.5°	363.0	365.1	364.4	364.4	362.6
140°	377.6	378.3	377.9	378.6	376.5
142.5°	390.7	391.1	391.8	391.8	389.7
145°	403.5	404.2	404.2	404.6	402.5
147.5°	414.9	414.9	415.3	415.6	413.1
150°	425.6	424.9	425.6	426.3	423.4
152.5°	435.9	434.1	434.8	435.5	433.0
155°	444.4	442.3	443.0	444.1	441.2
157.5°	451.2	450.1	450.1	451.2	448.3
160°	458.3	456.2	456.5	457.9	455.1
162.5°	464.0	461.8	462.2	464.3	461.1
165°	469.0	466.8	467.2	469.3	466.5
167.5°	472.9	470.7	471.1	473.6	470.4
170°	476.1	473.6	473.9	476.8	473.6
172.5°	478.2	475.7	476.4	478.9	475.7
175°	479.6	477.5	477.8	480.7	477.5
177.5°	480.7	478.6	478.9	481.4	478.6
180°	479.6	479.6	479.6	479.6	479.6

(END OF REPORT)