

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026738

Luminaire Tested: S125DIP-B1090D610UB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026738
REPORT IS A COMBINATION OF REPORTS P1001422 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B1090D610UB2750-4F0-XX-W2A-F_5000K
Description: Define 5 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6524.0 lumens
Efficiency: N/A
Efficacy: 104.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 62.2
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026738

CATALOG NUMBER: S125DIP-B1090D610UB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1026738

CATALOG NUMBER: S125DIP-B1090D610UB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	104	104	104	104	92	92	92	80	80	80	70	70	70
1	101	97	93	89	95	91	87	84	80	78	75	71	69	67	62	60	59
2	92	84	78	73	86	80	74	69	70	66	62	62	59	56	54	52	50
3	84	74	67	61	79	70	63	58	62	57	52	55	51	47	48	45	42
4	77	66	58	51	72	62	55	49	55	49	45	49	44	40	43	39	36
5	71	59	50	44	66	55	48	42	49	43	39	44	39	35	39	35	32
6	65	53	44	38	61	50	42	37	45	38	34	40	35	31	35	31	28
7	60	48	39	34	57	45	38	32	41	34	30	36	31	27	32	28	25
8	56	43	35	30	53	41	34	29	37	31	27	33	28	24	30	25	22
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	27	23	20
10	49	36	29	24	46	35	28	23	31	26	22	28	23	20	25	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10450	10450	10450
5°	10450	10207	10227
10°	10364	9973	9942
15°	10228	9693	9606
20°	10043	9369	9222
25°	9846	9015	8810
30°	9608	8646	8375
35°	9354	8259	7889
40°	9091	7851	7457
45°	8806	7453	6997
50°	8493	7001	6462
55°	8183	6503	5969
60°	7813	5978	5396
65°	7372	5370	4804
70°	6920	4671	4121
75°	6166	3846	3332
80°	5254	2873	2451
85°	4059	1700	1351

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8806 cd/sqm

TEST NUMBER: P1026738

CATALOG NUMBER: S125DIP-B1090D610UB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	153.9	2.4
10°-20°	434.7	6.7
20°-30°	641.8	9.8
30°-40°	748.8	11.5
40°-50°	752.0	11.5
50°-60°	660.2	10.1
60°-70°	491.7	7.5
70°-80°	280.8	4.3
80°-90°	82.2	1.3
90°-100°	25.2	0.4
100°-110°	167.3	2.6
110°-120°	301.4	4.6
120°-130°	386.9	5.9
130°-140°	416.1	6.4
140°-150°	390.5	6.0
150°-160°	315.9	4.8
160°-170°	204.3	3.1
170°-180°	70.4	1.1
0°-30°	1230.4	18.9
0°-40°	1979.2	30.3
0°-60°	3391.4	52.0
0°-90°	4246.1	65.1
90°-120°	493.9	7.6
90°-150°	1687.3	25.9
90°-180°	2278.0	34.9
0°-180°	6524.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1631	1631	1631	1631	1631	
5°	1628	1626	1613	1624	1623	155
15°	1552	1548	1534	1541	1541	438
25°	1409	1403	1386	1388	1384	648
35°	1217	1212	1194	1187	1177	761
45°	996	991	976	960	956	767
55°	759	755	737	725	716	677
65°	512	510	496	484	479	508
75°	272	270	263	259	254	290
85°	71	72	72	71	68	78
90°	0	5	9	12	13	6
95°	31	30	9	12	12	38
105°	162	164	164	164	163	171
115°	303	306	307	304	301	301
125°	432	435	435	433	432	385
135°	538	542	540	539	536	415
145°	624	625	625	626	622	390
155°	687	684	685	687	682	317
165°	725	722	722	726	721	205
175°	742	738	739	743	738	71
180°	742	742	742	742	742	

TEST NUMBER: P1026738

CATALOG NUMBER: S125DIP-B1090D610UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1631.0	1631.0	1631.0	1631.0	1631.0
2.5°	1636.1	1632.3	1619.4	1632.3	1631.0
5°	1628.4	1625.8	1612.9	1624.5	1623.2
7.5°	1616.8	1614.2	1600.0	1611.6	1610.3
10°	1600.0	1597.4	1583.2	1593.5	1592.3
12.5°	1579.4	1574.2	1561.3	1569.0	1569.0
15°	1552.3	1548.4	1534.2	1540.6	1540.6
17.5°	1523.9	1517.4	1503.2	1511.0	1504.5
20°	1486.4	1483.9	1467.1	1476.1	1469.7
22.5°	1449.0	1443.9	1428.4	1433.5	1429.7
25°	1409.0	1402.6	1385.8	1388.4	1384.5
27.5°	1362.6	1358.7	1341.9	1343.2	1339.4
30°	1317.4	1313.5	1294.2	1291.6	1287.7
32.5°	1268.4	1261.9	1245.2	1240.0	1232.3
35°	1216.8	1211.6	1193.5	1187.1	1176.8
37.5°	1163.9	1157.4	1140.6	1131.6	1125.2
40°	1109.7	1103.2	1085.2	1073.5	1069.7
42.5°	1051.6	1046.4	1028.4	1018.1	1011.6
45°	996.1	991.0	975.5	960.0	956.1
47.5°	935.5	936.8	917.4	901.9	892.9
50°	877.4	873.5	858.1	841.3	832.3
52.5°	818.1	815.5	798.7	784.5	774.2
55°	758.7	754.8	736.8	725.2	716.1
57.5°	695.5	694.2	678.7	663.2	659.4
60°	636.1	631.0	616.8	603.9	594.8
62.5°	574.2	570.3	558.7	544.5	538.1
65°	512.3	509.7	495.5	483.9	478.7
67.5°	451.6	446.5	436.1	425.8	423.2
70°	394.8	388.4	376.8	369.0	363.9
72.5°	332.9	329.0	322.6	313.5	308.4
75°	272.3	269.7	263.2	259.4	254.2
77.5°	215.5	214.2	210.3	207.7	203.9
80°	162.6	162.6	160.0	158.7	156.1
82.5°	116.1	113.5	113.5	111.0	111.0
85°	71.0	72.3	72.3	71.0	68.4
87.5°	34.8	34.8	33.5	33.5	31.0
90°	0.5	4.9	8.8	11.5	13.2
92.5°	10.4	5.5	8.8	11.5	12.1
95°	31.3	29.7	8.8	11.5	11.5
97.5°	58.8	62.1	9.9	11.0	11.5
100°	91.8	93.5	95.6	13.7	11.5
102.5°	125.3	127.5	128.6	129.7	83.6
105°	161.6	163.8	163.8	163.8	163.3
107.5°	199.0	199.0	200.1	200.6	198.4
110°	235.3	235.3	236.4	234.7	235.3



TEST NUMBER: P1026738

CATALOG NUMBER: S125DIP-B1090D610UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	269.4	271.0	271.6	269.4	268.3
115°	303.4	306.2	306.7	304.5	301.2
117.5°	339.2	339.2	341.4	338.1	337.0
120°	372.2	371.6	373.3	372.2	369.4
122.5°	401.3	404.0	404.6	403.5	400.2
125°	431.5	435.4	435.4	433.2	431.5
127.5°	460.7	463.4	462.9	461.8	457.4
130°	487.0	489.8	490.3	488.7	485.9
132.5°	513.4	516.7	515.1	515.1	512.3
135°	538.2	541.5	540.4	539.3	536.0
137.5°	561.3	564.5	563.4	563.4	560.7
140°	583.8	584.9	584.3	585.4	582.1
142.5°	604.1	604.7	605.8	605.8	602.5
145°	623.9	625.0	625.0	625.6	622.3
147.5°	641.5	641.5	642.1	642.6	638.8
150°	658.0	656.9	658.0	659.1	654.7
152.5°	673.9	671.2	672.3	673.4	669.5
155°	687.1	683.8	684.9	686.6	682.2
157.5°	697.6	695.9	695.9	697.6	693.2
160°	708.6	705.3	705.8	708.0	703.6
162.5°	717.4	714.1	714.6	717.9	713.0
165°	725.1	721.8	722.3	725.6	721.2
167.5°	731.1	727.8	728.4	732.2	727.3
170°	736.1	732.2	732.8	737.2	732.2
172.5°	739.4	735.5	736.6	740.5	735.5
175°	741.6	738.3	738.8	743.2	738.3
177.5°	743.2	739.9	740.5	744.3	739.9
180°	741.6	741.6	741.6	741.6	741.6

(END OF REPORT)