

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026753

Luminaire Tested: S125DIP-B1090D850UB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026753
REPORT IS A COMBINATION OF REPORTS P1001482 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B1090D850UB2750-4F0-XX-W2A-F_5000K
Description: Define 5 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7290.0 lumens
Efficiency: N/A
Efficacy: 107.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 67.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026753

CATALOG NUMBER: S125DIP-B1090D850UB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1026753

CATALOG NUMBER: S125DIP-B1090D850UB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	64	64	64
1	100	95	91	88	93	89	85	82	77	74	72	66	64	63	56	55	54
2	91	83	77	72	84	78	72	67	67	63	60	58	55	52	49	47	45
3	83	73	66	60	77	68	62	56	60	54	50	51	47	44	44	41	38
4	76	65	57	50	70	61	53	48	53	47	43	46	41	38	39	36	33
5	69	58	49	43	65	54	47	41	47	41	37	41	36	33	35	32	29
6	64	52	43	38	59	49	41	36	43	37	32	37	32	29	32	28	25
7	59	47	39	33	55	44	37	31	39	33	28	34	29	25	29	25	23
8	55	42	35	29	51	40	33	28	35	29	25	31	26	23	27	23	20
9	51	39	31	26	48	37	30	25	32	27	23	29	24	20	25	21	18
10	48	36	28	23	45	34	27	22	30	24	20	26	22	19	23	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10450	10450	10450
5°	10450	10207	10227
10°	10364	9973	9942
15°	10228	9693	9606
20°	10043	9369	9222
25°	9846	9015	8810
30°	9608	8646	8375
35°	9354	8259	7889
40°	9091	7851	7457
45°	8806	7453	6997
50°	8493	7001	6462
55°	8183	6503	5969
60°	7813	5978	5396
65°	7372	5370	4804
70°	6920	4671	4121
75°	6166	3846	3332
80°	5254	2873	2451
85°	4059	1700	1351

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8806 cd/sqm

TEST NUMBER: P1026753

CATALOG NUMBER: S125DIP-B1090D850UB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	153.9	2.1
10°-20°	434.7	6.0
20°-30°	641.8	8.8
30°-40°	748.8	10.3
40°-50°	752.0	10.3
50°-60°	660.2	9.1
60°-70°	491.7	6.7
70°-80°	280.8	3.9
80°-90°	82.5	1.1
90°-100°	33.6	0.5
100°-110°	223.6	3.1
110°-120°	402.7	5.5
120°-130°	516.9	7.1
130°-140°	555.9	7.6
140°-150°	521.7	7.2
150°-160°	422.0	5.8
160°-170°	272.9	3.7
170°-180°	94.1	1.3
0°-30°	1230.4	16.9
0°-40°	1979.2	27.1
0°-60°	3391.4	46.5
0°-90°	4246.5	58.3
90°-120°	659.9	9.1
90°-150°	2254.4	30.9
90°-180°	3044.0	41.8
0°-180°	7290.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1631	1631	1631	1631	1631	
5°	1628	1626	1613	1624	1623	155
15°	1552	1548	1534	1541	1541	438
25°	1409	1403	1386	1388	1384	648
35°	1217	1212	1194	1187	1177	761
45°	996	991	976	960	956	767
55°	759	755	737	725	716	677
65°	512	510	496	484	479	508
75°	272	270	263	259	254	290
85°	71	72	72	71	68	78
90°	1	7	12	15	18	7
95°	42	40	12	15	15	51
105°	216	219	219	219	218	229
115°	405	409	410	407	402	402
125°	577	582	582	579	577	515
135°	719	724	722	720	716	554
145°	834	835	835	836	831	521
155°	918	914	915	917	912	423
165°	969	964	965	970	964	274
175°	991	986	987	993	986	94
180°	991	991	991	991	991	

TEST NUMBER: P1026753

CATALOG NUMBER: S125DIP-B1090D850UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1631.0	1631.0	1631.0	1631.0	1631.0
2.5°	1636.1	1632.3	1619.4	1632.3	1631.0
5°	1628.4	1625.8	1612.9	1624.5	1623.2
7.5°	1616.8	1614.2	1600.0	1611.6	1610.3
10°	1600.0	1597.4	1583.2	1593.5	1592.3
12.5°	1579.4	1574.2	1561.3	1569.0	1569.0
15°	1552.3	1548.4	1534.2	1540.6	1540.6
17.5°	1523.9	1517.4	1503.2	1511.0	1504.5
20°	1486.4	1483.9	1467.1	1476.1	1469.7
22.5°	1449.0	1443.9	1428.4	1433.5	1429.7
25°	1409.0	1402.6	1385.8	1388.4	1384.5
27.5°	1362.6	1358.7	1341.9	1343.2	1339.4
30°	1317.4	1313.5	1294.2	1291.6	1287.7
32.5°	1268.4	1261.9	1245.2	1240.0	1232.3
35°	1216.8	1211.6	1193.5	1187.1	1176.8
37.5°	1163.9	1157.4	1140.6	1131.6	1125.2
40°	1109.7	1103.2	1085.2	1073.5	1069.7
42.5°	1051.6	1046.4	1028.4	1018.1	1011.6
45°	996.1	991.0	975.5	960.0	956.1
47.5°	935.5	936.8	917.4	901.9	892.9
50°	877.4	873.5	858.1	841.3	832.3
52.5°	818.1	815.5	798.7	784.5	774.2
55°	758.7	754.8	736.8	725.2	716.1
57.5°	695.5	694.2	678.7	663.2	659.4
60°	636.1	631.0	616.8	603.9	594.8
62.5°	574.2	570.3	558.7	544.5	538.1
65°	512.3	509.7	495.5	483.9	478.7
67.5°	451.6	446.5	436.1	425.8	423.2
70°	394.8	388.4	376.8	369.0	363.9
72.5°	332.9	329.0	322.6	313.5	308.4
75°	272.3	269.7	263.2	259.4	254.2
77.5°	215.5	214.2	210.3	207.7	203.9
80°	162.6	162.6	160.0	158.7	156.1
82.5°	116.1	113.5	113.5	111.0	111.0
85°	71.0	72.3	72.3	71.0	68.4
87.5°	34.8	34.8	33.5	33.5	31.0
90°	0.7	6.6	11.8	15.4	17.6
92.5°	14.0	7.3	11.8	15.4	16.2
95°	41.9	39.7	11.8	15.4	15.4
97.5°	78.6	83.0	13.2	14.7	15.4
100°	122.7	124.9	127.8	18.4	15.4
102.5°	167.5	170.4	171.9	173.3	111.6
105°	215.9	218.9	218.9	218.9	218.1
107.5°	265.9	265.9	267.3	268.1	265.1
110°	314.4	314.4	315.8	313.6	314.4



TEST NUMBER: P1026753

CATALOG NUMBER: S125DIP-B1090D850UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	359.9	362.1	362.8	359.9	358.4
115°	405.4	409.1	409.8	406.9	402.5
117.5°	453.2	453.2	456.1	451.7	450.2
120°	497.2	496.5	498.7	497.2	493.6
122.5°	536.2	539.8	540.6	539.1	534.7
125°	576.6	581.7	581.7	578.8	576.6
127.5°	615.5	619.2	618.4	617.0	611.1
130°	650.7	654.4	655.1	652.9	649.3
132.5°	686.0	690.4	688.2	688.2	684.5
135°	719.0	723.5	722.0	720.5	716.1
137.5°	749.9	754.3	752.8	752.8	749.2
140°	780.0	781.5	780.7	782.2	777.8
142.5°	807.2	807.9	809.4	809.4	805.0
145°	833.6	835.1	835.1	835.8	831.4
147.5°	857.1	857.1	857.9	858.6	853.5
150°	879.2	877.7	879.2	880.6	874.8
152.5°	900.5	896.8	898.3	899.7	894.6
155°	918.1	913.7	915.2	917.4	911.5
157.5°	932.0	929.8	929.8	932.0	926.2
160°	946.7	942.3	943.1	946.0	940.1
162.5°	958.5	954.1	954.8	959.2	952.6
165°	968.8	964.4	965.1	969.5	963.6
167.5°	976.8	972.4	973.2	978.3	971.7
170°	983.5	978.3	979.0	984.9	978.3
172.5°	987.9	982.7	984.2	989.3	982.7
175°	990.8	986.4	987.1	993.0	986.4
177.5°	993.0	988.6	989.3	994.5	988.6
180°	990.8	990.8	990.8	990.8	990.8

(END OF REPORT)