

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027034

Luminaire Tested: S125DIP-B850D610UB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027034
REPORT IS A COMBINATION OF REPORTS P1002618 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B850D610UB2750-4F0-XX-W2A-F_2700K
Description: Define 5 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5755.0 lumens
Efficiency: N/A
Efficacy: 112.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 51.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027034

CATALOG NUMBER: S125DIP-B850D610UB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1027034

CATALOG NUMBER: S125DIP-B850D610UB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	65	65	65
1	100	95	91	88	93	89	86	83	78	75	73	67	65	63	57	56	54
2	91	83	77	72	84	78	72	68	68	64	60	59	56	53	50	48	46
3	83	73	66	60	77	69	62	57	60	55	50	52	48	45	44	41	39
4	76	65	57	51	70	61	54	48	53	48	43	46	42	38	40	36	34
5	70	58	49	43	65	54	47	41	48	42	37	41	37	33	36	32	29
6	64	52	44	38	60	49	41	36	43	37	32	38	33	29	32	29	26
7	59	47	39	33	55	44	37	32	39	33	29	34	29	26	30	26	23
8	55	43	35	29	51	40	33	28	36	30	25	31	26	23	27	23	21
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	21	19
10	48	36	28	24	45	34	27	23	30	25	21	27	22	19	23	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8382	8382	8382
5°	8383	8187	8203
10°	8313	7999	7975
15°	8204	7775	7706
20°	8056	7515	7397
25°	7898	7231	7066
30°	7707	6935	6718
35°	7503	6625	6328
40°	7292	6297	5981
45°	7063	5978	5613
50°	6812	5616	5184
55°	6564	5216	4788
60°	6268	4794	4329
65°	5912	4307	3854
70°	5551	3746	3306
75°	4945	3084	2673
80°	4214	2304	1965
85°	3253	1364	1084

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7063 cd/sqm

TEST NUMBER: P1027034

CATALOG NUMBER: S125DIP-B850D610UB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	123.4	2.1
10°-20°	348.7	6.1
20°-30°	514.8	8.9
30°-40°	600.6	10.4
40°-50°	603.2	10.5
50°-60°	529.5	9.2
60°-70°	394.4	6.9
70°-80°	225.2	3.9
80°-90°	66.2	1.1
90°-100°	26.0	0.5
100°-110°	172.6	3.0
110°-120°	310.8	5.4
120°-130°	398.9	6.9
130°-140°	429.0	7.5
140°-150°	402.7	7.0
150°-160°	325.7	5.7
160°-170°	210.6	3.7
170°-180°	72.6	1.3
0°-30°	986.9	17.1
0°-40°	1587.5	27.6
0°-60°	2720.3	47.3
0°-90°	3406.1	59.2
90°-120°	509.3	8.8
90°-150°	1739.8	30.2
90°-180°	2349.0	40.8
0°-180°	5755.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1308	1308	1308	1308	1308	
5°	1306	1304	1294	1303	1302	124
15°	1245	1242	1231	1236	1236	351
25°	1130	1125	1112	1114	1110	520
35°	976	972	957	952	944	611
45°	799	795	782	770	767	616
55°	609	606	591	582	574	543
65°	411	409	397	388	384	408
75°	218	216	211	208	204	232
85°	57	58	58	57	55	62
90°	1	5	9	12	14	5
95°	32	31	9	12	12	40
105°	167	169	169	169	168	177
115°	313	316	316	314	311	310
125°	445	449	449	447	445	397
135°	555	558	557	556	553	428
145°	643	644	644	645	642	402
155°	708	705	706	708	703	326
165°	748	744	745	748	744	211
175°	765	761	762	766	761	73
180°	765	765	765	765	765	

TEST NUMBER: P1027034

CATALOG NUMBER: S125DIP-B850D610UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1308.2	1308.2	1308.2	1308.2	1308.2
2.5°	1312.4	1309.3	1298.9	1309.3	1308.2
5°	1306.2	1304.1	1293.7	1303.1	1302.0
7.5°	1296.8	1294.8	1283.4	1292.7	1291.7
10°	1283.4	1281.3	1269.9	1278.2	1277.2
12.5°	1266.8	1262.7	1252.3	1258.6	1258.6
15°	1245.1	1242.0	1230.6	1235.8	1235.8
17.5°	1222.3	1217.2	1205.8	1212.0	1206.8
20°	1192.3	1190.2	1176.8	1184.0	1178.9
22.5°	1162.3	1158.2	1145.7	1149.9	1146.8
25°	1130.2	1125.0	1111.6	1113.7	1110.5
27.5°	1093.0	1089.8	1076.4	1077.4	1074.3
30°	1056.7	1053.6	1038.1	1036.0	1032.9
32.5°	1017.4	1012.2	998.8	994.6	988.4
35°	976.0	971.9	957.4	952.2	943.9
37.5°	933.6	928.4	914.9	907.7	902.5
40°	890.1	884.9	870.4	861.1	858.0
42.5°	843.5	839.4	824.9	816.6	811.4
45°	799.0	794.9	782.5	770.0	766.9
47.5°	750.4	751.4	735.9	723.5	716.2
50°	703.8	700.7	688.3	674.8	667.6
52.5°	656.2	654.1	640.7	629.3	621.0
55°	608.6	605.5	591.0	581.7	574.4
57.5°	557.9	556.8	544.4	532.0	528.9
60°	510.3	506.1	494.7	484.4	477.1
62.5°	460.6	457.5	448.2	436.8	431.6
65°	410.9	408.8	397.4	388.1	384.0
67.5°	362.2	358.1	349.8	341.5	339.5
70°	316.7	311.5	302.2	296.0	291.9
72.5°	267.0	263.9	258.7	251.5	247.4
75°	218.4	216.3	211.1	208.0	203.9
77.5°	172.8	171.8	168.7	166.6	163.5
80°	130.4	130.4	128.3	127.3	125.2
82.5°	93.1	91.1	91.1	89.0	89.0
85°	56.9	58.0	58.0	56.9	54.9
87.5°	27.9	27.9	26.9	26.9	24.8
90°	0.6	5.1	9.1	11.9	13.6
92.5°	10.8	5.7	9.1	11.9	12.5
95°	32.3	30.6	9.1	11.9	11.9
97.5°	60.7	64.1	10.2	11.3	11.9
100°	94.7	96.4	98.6	14.2	11.9
102.5°	129.2	131.5	132.6	133.8	86.2
105°	166.6	168.9	168.9	168.9	168.3
107.5°	205.2	205.2	206.3	206.9	204.6
110°	242.6	242.6	243.7	242.0	242.6

TEST NUMBER: P1027034

CATALOG NUMBER: S125DIP-B850D610UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	277.7	279.4	280.0	277.7	276.6
115°	312.9	315.7	316.3	314.0	310.6
117.5°	349.7	349.7	352.0	348.6	347.5
120°	383.7	383.2	384.9	383.7	380.9
122.5°	413.8	416.6	417.2	416.1	412.7
125°	445.0	448.9	448.9	446.7	445.0
127.5°	475.0	477.8	477.3	476.1	471.6
130°	502.2	505.0	505.6	503.9	501.1
132.5°	529.4	532.8	531.1	531.1	528.3
135°	554.9	558.3	557.2	556.1	552.7
137.5°	578.7	582.1	581.0	581.0	578.2
140°	602.0	603.1	602.5	603.7	600.3
142.5°	622.9	623.5	624.6	624.6	621.2
145°	643.4	644.5	644.5	645.1	641.7
147.5°	661.5	661.5	662.1	662.6	658.7
150°	678.5	677.4	678.5	679.6	675.1
152.5°	694.9	692.1	693.2	694.4	690.4
155°	708.5	705.1	706.3	708.0	703.4
157.5°	719.3	717.6	717.6	719.3	714.8
160°	730.6	727.2	727.8	730.1	725.5
162.5°	739.7	736.3	736.9	740.3	735.2
165°	747.7	744.3	744.8	748.2	743.7
167.5°	753.9	750.5	751.1	755.0	749.9
170°	759.0	755.0	755.6	760.1	755.0
172.5°	762.4	758.4	759.6	763.5	758.4
175°	764.7	761.3	761.8	766.4	761.3
177.5°	766.4	763.0	763.5	767.5	763.0
180°	764.7	764.7	764.7	764.7	764.7

(END OF REPORT)