

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026765

Luminaire Tested: S125DIP-B1270D1090UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026765
REPORT IS A COMBINATION OF REPORTS P1001539 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B1270D1090UB2750-4F0-XX-W2A-F_3000K
Description: Define 5 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9239.0 lumens
Efficiency: N/A
Efficacy: 102.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 89.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026765

CATALOG NUMBER: S125DIP-B1270D1090UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1026765

CATALOG NUMBER: S125DIP-B1270D1090UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61
1	99	95	91	87	92	88	85	82	76	73	71	64	63	61	54	53	52
2	90	83	76	71	83	77	71	67	66	62	59	57	54	51	48	45	43
3	82	73	65	59	76	68	61	56	59	53	49	50	46	43	42	39	37
4	75	64	56	50	70	60	53	47	52	46	42	45	40	37	38	34	32
5	69	57	49	43	64	54	46	41	47	41	36	40	35	32	34	30	28
6	64	51	43	37	59	48	41	35	42	36	32	36	32	28	31	27	24
7	59	46	38	33	55	44	36	31	38	32	28	33	28	25	28	24	22
8	55	42	34	29	51	40	33	28	35	29	25	30	26	22	26	22	19
9	51	39	31	26	47	36	29	25	32	26	22	28	23	20	24	20	18
10	48	35	28	23	44	33	27	22	29	24	20	26	21	18	22	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12655	12655	12655
5°	12656	12362	12385
10°	12551	12078	12040
15°	12387	11739	11634
20°	12164	11346	11168
25°	11924	10918	10669
30°	11636	10471	10143
35°	11328	10003	9554
40°	11009	9508	9031
45°	10665	9026	8474
50°	10285	8479	7826
55°	9911	7875	7230
60°	9462	7239	6536
65°	8927	6503	5819
70°	8382	5657	4991
75°	7465	4658	4035
80°	6363	3480	2969
85°	4911	2057	1636

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10665 cd/sqm

TEST NUMBER: P1026765

CATALOG NUMBER: S125DIP-B1270D1090UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	186.4	2.0
10°-20°	526.5	5.7
20°-30°	777.2	8.4
30°-40°	906.8	9.8
40°-50°	910.8	9.9
50°-60°	799.5	8.7
60°-70°	595.5	6.4
70°-80°	340.1	3.7
80°-90°	100.2	1.1
90°-100°	45.3	0.5
100°-110°	300.9	3.3
110°-120°	541.9	5.9
120°-130°	695.6	7.5
130°-140°	748.1	8.1
140°-150°	702.2	7.6
150°-160°	568.0	6.1
160°-170°	367.3	4.0
170°-180°	126.7	1.4
0°-30°	1490.1	16.1
0°-40°	2396.9	25.9
0°-60°	4107.2	44.5
0°-90°	5143.0	55.7
90°-120°	888.1	9.6
90°-150°	3034.1	32.8
90°-180°	4096.0	44.3
0°-180°	9239.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1975	1975	1975	1975	1975	
5°	1972	1969	1953	1967	1966	187
15°	1880	1875	1858	1866	1866	530
25°	1706	1699	1678	1681	1677	785
35°	1474	1467	1446	1438	1425	922
45°	1206	1200	1181	1163	1158	929
55°	919	914	892	878	867	820
65°	620	617	600	586	580	615
75°	330	327	319	314	308	351
85°	86	88	88	86	83	94
90°	1	9	16	21	24	9
95°	56	53	16	21	21	69
105°	291	295	295	295	294	308
115°	546	551	552	548	542	541
125°	776	783	783	779	776	693
135°	968	974	972	970	964	746
145°	1122	1124	1124	1125	1119	702
155°	1236	1230	1232	1235	1227	569
165°	1304	1298	1299	1305	1297	368
175°	1333	1328	1328	1336	1328	127
180°	1333	1333	1333	1333	1333	

TEST NUMBER: P1026765

CATALOG NUMBER: S125DIP-B1270D1090UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1975.2	1975.2	1975.2	1975.2	1975.2
2.5°	1981.5	1976.8	1961.2	1976.8	1975.2
5°	1972.1	1969.0	1953.3	1967.4	1965.8
7.5°	1958.0	1954.9	1937.7	1951.8	1950.2
10°	1937.7	1934.6	1917.4	1929.9	1928.3
12.5°	1912.7	1906.5	1890.8	1900.2	1900.2
15°	1879.9	1875.2	1858.0	1865.8	1865.8
17.5°	1845.5	1837.7	1820.5	1829.9	1822.1
20°	1800.2	1797.1	1776.8	1787.7	1779.9
22.5°	1754.9	1748.6	1729.9	1736.1	1731.4
25°	1706.4	1698.6	1678.3	1681.4	1676.7
27.5°	1650.2	1645.5	1625.2	1626.7	1622.1
30°	1595.5	1590.8	1567.4	1564.2	1559.5
32.5°	1536.1	1528.3	1508.0	1501.7	1492.4
35°	1473.6	1467.3	1445.5	1437.7	1425.2
37.5°	1409.5	1401.7	1381.4	1370.5	1362.6
40°	1343.9	1336.1	1314.2	1300.1	1295.5
42.5°	1273.6	1267.3	1245.4	1232.9	1225.1
45°	1206.4	1200.1	1181.4	1162.6	1157.9
47.5°	1132.9	1134.5	1111.1	1092.3	1081.4
50°	1062.6	1057.9	1039.2	1018.9	1007.9
52.5°	990.7	987.6	967.3	950.1	937.6
55°	918.9	914.2	892.3	878.2	867.3
57.5°	842.3	840.7	822.0	803.2	798.5
60°	770.4	764.1	747.0	731.3	720.4
62.5°	695.4	690.7	676.6	659.4	651.6
65°	620.4	617.3	600.1	586.0	579.8
67.5°	546.9	540.7	528.2	515.7	512.6
70°	478.2	470.4	456.3	446.9	440.7
72.5°	403.2	398.5	390.7	379.7	373.5
75°	329.7	326.6	318.8	314.1	307.8
77.5°	261.0	259.4	254.7	251.6	246.9
80°	196.9	196.9	193.8	192.2	189.1
82.5°	140.6	137.5	137.5	134.4	134.4
85°	85.9	87.5	87.5	85.9	82.8
87.5°	42.2	42.2	40.6	40.6	37.5
90°	1.0	8.9	15.8	20.8	23.7
92.5°	18.8	9.9	15.8	20.8	21.7
95°	56.3	53.4	15.8	20.8	20.8
97.5°	105.8	111.7	17.8	19.8	20.8
100°	165.1	168.0	172.0	24.7	20.8
102.5°	225.4	229.3	231.3	233.3	150.2
105°	290.6	294.6	294.6	294.6	293.6
107.5°	357.8	357.8	359.8	360.8	356.8
110°	423.1	423.1	425.0	422.1	423.1

TEST NUMBER: P1026765

CATALOG NUMBER: S125DIP-B1270D1090UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	484.3	487.3	488.3	484.3	482.4
115°	545.6	550.6	551.6	547.6	541.7
117.5°	609.9	609.9	613.8	607.9	605.9
120°	669.2	668.2	671.2	669.2	664.2
122.5°	721.6	726.5	727.5	725.5	719.6
125°	775.9	782.9	782.9	778.9	775.9
127.5°	828.3	833.3	832.3	830.3	822.4
130°	875.8	880.7	881.7	878.7	873.8
132.5°	923.2	929.2	926.2	926.2	921.2
135°	967.7	973.6	971.7	969.7	963.7
137.5°	1009.2	1015.1	1013.2	1013.2	1008.2
140°	1049.7	1051.7	1050.7	1052.7	1046.8
142.5°	1086.3	1087.3	1089.3	1089.3	1083.4
145°	1121.9	1123.9	1123.9	1124.9	1118.9
147.5°	1153.5	1153.5	1154.5	1155.5	1148.6
150°	1183.2	1181.2	1183.2	1185.2	1177.3
152.5°	1211.9	1206.9	1208.9	1210.9	1203.9
155°	1235.6	1229.6	1231.6	1234.6	1226.7
157.5°	1254.4	1251.4	1251.4	1254.4	1246.4
160°	1274.1	1268.2	1269.2	1273.1	1265.2
162.5°	1289.9	1284.0	1285.0	1290.9	1282.0
165°	1303.8	1297.8	1298.8	1304.8	1296.9
167.5°	1314.7	1308.7	1309.7	1316.6	1307.7
170°	1323.5	1316.6	1317.6	1325.5	1316.6
172.5°	1329.5	1322.6	1324.5	1331.5	1322.6
175°	1333.4	1327.5	1328.5	1336.4	1327.5
177.5°	1336.4	1330.5	1331.5	1338.4	1330.5
180°	1333.4	1333.4	1333.4	1333.4	1333.4

(END OF REPORT)