

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026767

Luminaire Tested: S125DIP-B1270D1090UB2750-4F0-XX-W2A-F_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026767
REPORT IS A COMBINATION OF REPORTS P1001541 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B1270D1090UB2750-4F0-XX-W2A-F_4000K
Description: Define 5 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9186.0 lumens
Efficiency: N/A
Efficacy: 102.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 89.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026767

CATALOG NUMBER: S125DIP-B1270D1090UB2750-4F0-XX-W2A-F_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1026767

CATALOG NUMBER: S125DIP-B1270D1090UB2750-4F0-XX-W2A-F_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	108	108	108	108		101	101	101	101		86	86	86		73	73	73		61	61	61
1	99	95	91	87		92	88	85	82		76	73	71		64	63	61		54	53	52
2	90	83	76	71		83	77	71	67		66	62	59		57	54	51		48	45	43
3	82	73	65	59		76	68	61	56		59	53	49		50	46	43		42	39	37
4	75	64	56	50		70	60	53	47		52	46	42		45	40	37		38	34	32
5	69	57	49	43		64	54	46	41		47	41	36		40	35	32		34	30	28
6	64	51	43	37		59	48	41	35		42	36	32		36	32	28		31	27	24
7	59	46	38	33		55	44	36	31		38	32	28		33	28	25		28	24	22
8	55	42	34	29		51	40	33	28		35	29	25		30	26	22		26	22	19
9	51	39	31	26		47	36	29	25		32	26	22		28	23	20		24	20	18
10	48	35	28	23		44	33	27	22		29	24	20		26	21	18		22	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12582	12582	12582
5°	12582	12289	12313
10°	12478	12008	11970
15°	12314	11671	11566
20°	12093	11280	11103
25°	11855	10854	10607
30°	11568	10410	10084
35°	11262	9944	9498
40°	10945	9452	8978
45°	10602	8973	8425
50°	10225	8429	7780
55°	9852	7829	7187
60°	9407	7197	6498
65°	8875	6465	5785
70°	8333	5623	4961
75°	7422	4630	4011
80°	6324	3458	2951
85°	4883	2046	1626

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10602 cd/sqm

TEST NUMBER: P1026767

CATALOG NUMBER: S125DIP-B1270D1090UB2750-4F0-XX-W2A-F_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	185.3	2.0
10°-20°	523.4	5.7
20°-30°	772.7	8.4
30°-40°	901.5	9.8
40°-50°	905.5	9.9
50°-60°	794.8	8.7
60°-70°	592.0	6.4
70°-80°	338.1	3.7
80°-90°	99.6	1.1
90°-100°	45.0	0.5
100°-110°	299.2	3.3
110°-120°	538.9	5.9
120°-130°	691.7	7.5
130°-140°	744.0	8.1
140°-150°	698.2	7.6
150°-160°	564.8	6.1
160°-170°	365.3	4.0
170°-180°	126.0	1.4
0°-30°	1481.4	16.1
0°-40°	2383.0	25.9
0°-60°	4083.2	44.5
0°-90°	5113.0	55.7
90°-120°	883.1	9.6
90°-150°	3017.0	32.8
90°-180°	4073.0	44.3
0°-180°	9186.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1964	1964	1964	1964	1964	
5°	1961	1958	1942	1956	1954	186
15°	1869	1864	1847	1855	1855	527
25°	1696	1689	1668	1672	1667	781
35°	1465	1459	1437	1429	1417	916
45°	1199	1193	1174	1156	1151	924
55°	914	909	887	873	862	815
65°	617	614	597	583	576	612
75°	328	325	317	312	306	349
85°	85	87	87	85	82	94
90°	1	9	16	21	24	9
95°	56	53	16	21	21	69
105°	289	293	293	293	292	306
115°	543	548	548	544	539	538
125°	772	778	778	774	772	689
135°	962	968	966	964	958	742
145°	1116	1118	1118	1119	1113	698
155°	1229	1223	1225	1228	1220	566
165°	1296	1291	1292	1297	1290	366
175°	1326	1320	1321	1329	1320	126
180°	1326	1326	1326	1326	1326	

TEST NUMBER: P1026767

CATALOG NUMBER: S125DIP-B1270D1090UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1963.7	1963.7	1963.7	1963.7	1963.7
2.5°	1969.9	1965.2	1949.7	1965.2	1963.7
5°	1960.6	1957.5	1941.9	1955.9	1954.4
7.5°	1946.6	1943.5	1926.4	1940.4	1938.8
10°	1926.4	1923.3	1906.2	1918.6	1917.1
12.5°	1901.5	1895.3	1879.8	1889.1	1889.1
15°	1868.9	1864.3	1847.2	1854.9	1854.9
17.5°	1834.7	1827.0	1809.9	1819.2	1811.4
20°	1789.7	1786.6	1766.4	1777.3	1769.5
22.5°	1744.6	1738.4	1719.8	1726.0	1721.3
25°	1696.5	1688.7	1668.5	1671.6	1667.0
27.5°	1640.6	1635.9	1615.7	1617.2	1612.6
30°	1586.2	1581.5	1558.2	1555.1	1550.4
32.5°	1527.1	1519.4	1499.2	1493.0	1483.6
35°	1465.0	1458.8	1437.0	1429.3	1416.8
37.5°	1401.3	1393.5	1373.3	1362.5	1354.7
40°	1336.1	1328.3	1306.5	1292.6	1287.9
42.5°	1266.1	1259.9	1238.2	1225.8	1218.0
45°	1199.3	1193.1	1174.5	1155.8	1151.2
47.5°	1126.3	1127.9	1104.6	1085.9	1075.1
50°	1056.4	1051.8	1033.1	1012.9	1002.0
52.5°	985.0	981.8	961.6	944.6	932.1
55°	913.5	908.8	887.1	873.1	862.2
57.5°	837.4	835.8	817.2	798.5	793.9
60°	765.9	759.7	742.6	727.1	716.2
62.5°	691.3	686.7	672.7	655.6	647.8
65°	616.8	613.7	596.6	582.6	576.4
67.5°	543.7	537.5	525.1	512.7	509.6
70°	475.4	467.6	453.6	444.3	438.1
72.5°	400.8	396.2	388.4	377.5	371.3
75°	327.8	324.7	316.9	312.3	306.0
77.5°	259.4	257.9	253.2	250.1	245.5
80°	195.7	195.7	192.6	191.1	188.0
82.5°	139.8	136.7	136.7	133.6	133.6
85°	85.4	87.0	87.0	85.4	82.3
87.5°	41.9	41.9	40.4	40.4	37.3
90°	1.0	8.8	15.7	20.6	23.6
92.5°	18.7	9.8	15.7	20.6	21.6
95°	56.0	53.1	15.7	20.6	20.6
97.5°	105.2	111.1	17.7	19.7	20.6
100°	164.1	167.1	171.0	24.6	20.6
102.5°	224.1	228.0	230.0	232.0	149.4
105°	289.0	292.9	292.9	292.9	291.9
107.5°	355.8	355.8	357.8	358.8	354.8
110°	420.7	420.7	422.7	419.7	420.7



TEST NUMBER: P1026767

CATALOG NUMBER: S125DIP-B1270D1090UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	481.6	484.6	485.6	481.6	479.7
115°	542.6	547.5	548.5	544.5	538.6
117.5°	606.5	606.5	610.4	604.5	602.5
120°	665.4	664.4	667.4	665.4	660.5
122.5°	717.5	722.4	723.4	721.5	715.6
125°	771.6	778.5	778.5	774.5	771.6
127.5°	823.7	828.6	827.6	825.6	817.8
130°	870.9	875.8	876.8	873.8	868.9
132.5°	918.0	923.9	921.0	921.0	916.1
135°	962.3	968.2	966.2	964.2	958.3
137.5°	1003.6	1009.5	1007.5	1007.5	1002.6
140°	1043.9	1045.8	1044.8	1046.8	1040.9
142.5°	1080.2	1081.2	1083.2	1083.2	1077.3
145°	1115.6	1117.6	1117.6	1118.6	1112.7
147.5°	1147.1	1147.1	1148.0	1149.0	1142.1
150°	1176.5	1174.6	1176.5	1178.5	1170.6
152.5°	1205.1	1200.1	1202.1	1204.1	1197.2
155°	1228.6	1222.7	1224.7	1227.7	1219.8
157.5°	1247.3	1244.4	1244.4	1247.3	1239.5
160°	1267.0	1261.1	1262.1	1266.0	1258.1
162.5°	1282.7	1276.8	1277.8	1283.7	1274.8
165°	1296.5	1290.6	1291.5	1297.4	1289.6
167.5°	1307.3	1301.4	1302.4	1309.2	1300.4
170°	1316.1	1309.2	1310.2	1318.1	1309.2
172.5°	1322.0	1315.1	1317.1	1324.0	1315.1
175°	1325.9	1320.1	1321.0	1328.9	1320.1
177.5°	1328.9	1323.0	1324.0	1330.9	1323.0
180°	1325.9	1325.9	1325.9	1325.9	1325.9

(END OF REPORT)