

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027038

Luminaire Tested: S125DIP-B850D610UB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027038
REPORT IS A COMBINATION OF REPORTS P1002622 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B850D610UB2750-4F0-XX-W2A-F_5000K
Description: Define 5 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5582.0 lumens
Efficiency: N/A
Efficacy: 108.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 51.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027038

CATALOG NUMBER: S125DIP-B850D610UB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1027038

CATALOG NUMBER: S125DIP-B850D610UB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	65	65	65
1	100	95	91	88	93	89	86	83	78	75	73	67	65	63	57	56	54
2	91	83	77	72	84	78	72	68	68	64	60	59	56	53	50	48	46
3	83	73	66	60	77	69	62	57	60	55	50	52	48	45	44	41	39
4	76	65	57	51	70	61	54	48	53	48	43	46	42	38	40	36	34
5	70	58	49	43	65	54	47	41	48	42	37	41	37	33	36	32	29
6	64	52	44	38	60	49	41	36	43	37	32	38	33	29	32	29	26
7	59	47	39	33	55	44	37	32	39	33	29	34	29	26	30	26	23
8	55	43	35	29	51	40	33	28	36	30	25	31	26	23	27	23	21
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	21	19
10	48	36	28	24	45	34	27	23	30	25	21	27	22	19	23	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8131	8131	8131
5°	8131	7942	7957
10°	8064	7760	7735
15°	7958	7542	7475
20°	7815	7289	7175
25°	7662	7014	6855
30°	7476	6727	6517
35°	7278	6427	6138
40°	7073	6109	5802
45°	6852	5799	5445
50°	6608	5448	5028
55°	6367	5060	4645
60°	6080	4651	4199
65°	5735	4178	3738
70°	5385	3635	3206
75°	4796	2992	2593
80°	4088	2235	1907
85°	3156	1321	1051

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 6852 cd/sqm

TEST NUMBER: P1027038

CATALOG NUMBER: S125DIP-B850D610UB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	119.7	2.1
10°-20°	338.2	6.1
20°-30°	499.4	8.9
30°-40°	582.6	10.4
40°-50°	585.2	10.5
50°-60°	513.6	9.2
60°-70°	382.6	6.9
70°-80°	218.5	3.9
80°-90°	64.2	1.1
90°-100°	25.2	0.5
100°-110°	167.3	3.0
110°-120°	301.4	5.4
120°-130°	386.9	6.9
130°-140°	416.1	7.5
140°-150°	390.5	7.0
150°-160°	315.9	5.7
160°-170°	204.3	3.7
170°-180°	70.4	1.3
0°-30°	957.4	17.2
0°-40°	1540.0	27.6
0°-60°	2638.8	47.3
0°-90°	3304.1	59.2
90°-120°	493.9	8.8
90°-150°	1687.3	30.2
90°-180°	2278.0	40.8
0°-180°	5582.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1269	1269	1269	1269	1269	
5°	1267	1265	1255	1264	1263	120
15°	1208	1205	1194	1199	1199	341
25°	1096	1091	1078	1080	1077	504
35°	947	943	929	924	916	592
45°	775	771	759	747	744	597
55°	590	587	573	564	557	527
65°	399	397	386	376	372	395
75°	212	210	205	202	198	226
85°	55	56	56	55	53	60
90°	0	5	9	12	13	5
95°	31	30	9	12	12	38
105°	162	164	164	164	163	171
115°	303	306	307	304	301	301
125°	432	435	435	433	432	385
135°	538	542	540	539	536	415
145°	624	625	625	626	622	390
155°	687	684	685	687	682	317
165°	725	722	722	726	721	205
175°	742	738	739	743	738	71
180°	742	742	742	742	742	

TEST NUMBER: P1027038

CATALOG NUMBER: S125DIP-B850D610UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1269.0	1269.0	1269.0	1269.0	1269.0
2.5°	1273.1	1270.0	1260.0	1270.0	1269.0
5°	1267.0	1265.0	1255.0	1264.0	1263.0
7.5°	1258.0	1256.0	1244.9	1254.0	1253.0
10°	1244.9	1242.9	1231.9	1239.9	1238.9
12.5°	1228.9	1224.9	1214.8	1220.8	1220.8
15°	1207.8	1204.8	1193.7	1198.8	1198.8
17.5°	1185.7	1180.7	1169.6	1175.7	1170.6
20°	1156.6	1154.6	1141.5	1148.6	1143.5
22.5°	1127.5	1123.5	1111.4	1115.4	1112.4
25°	1096.4	1091.3	1078.3	1080.3	1077.3
27.5°	1060.2	1057.2	1044.1	1045.2	1042.1
30°	1025.1	1022.1	1007.0	1005.0	1002.0
32.5°	986.9	981.9	968.8	964.8	958.8
35°	946.8	942.7	928.7	923.7	915.6
37.5°	905.6	900.6	887.5	880.5	875.5
40°	863.4	858.4	844.4	835.3	832.3
42.5°	818.2	814.2	800.2	792.1	787.1
45°	775.1	771.1	759.0	747.0	744.0
47.5°	727.9	728.9	713.8	701.8	694.8
50°	682.7	679.7	667.7	654.6	647.6
52.5°	636.5	634.5	621.5	610.4	602.4
55°	590.3	587.3	573.3	564.2	557.2
57.5°	541.1	540.1	528.1	516.0	513.0
60°	495.0	490.9	479.9	469.9	462.8
62.5°	446.8	443.8	434.7	423.7	418.7
65°	398.6	396.6	385.5	376.5	372.5
67.5°	351.4	347.4	339.3	331.3	329.3
70°	307.2	302.2	293.2	287.1	283.1
72.5°	259.0	256.0	251.0	244.0	240.0
75°	211.8	209.8	204.8	201.8	197.8
77.5°	167.7	166.7	163.6	161.6	158.6
80°	126.5	126.5	124.5	123.5	121.5
82.5°	90.4	88.4	88.4	86.3	86.3
85°	55.2	56.2	56.2	55.2	53.2
87.5°	27.1	27.1	26.1	26.1	24.1
90°	0.5	4.9	8.8	11.5	13.2
92.5°	10.4	5.5	8.8	11.5	12.1
95°	31.3	29.7	8.8	11.5	11.5
97.5°	58.8	62.1	9.9	11.0	11.5
100°	91.8	93.5	95.6	13.7	11.5
102.5°	125.3	127.5	128.6	129.7	83.6
105°	161.6	163.8	163.8	163.8	163.3
107.5°	199.0	199.0	200.1	200.6	198.4
110°	235.3	235.3	236.4	234.7	235.3

TEST NUMBER: P1027038

CATALOG NUMBER: S125DIP-B850D610UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	269.4	271.0	271.6	269.4	268.3
115°	303.4	306.2	306.7	304.5	301.2
117.5°	339.2	339.2	341.4	338.1	337.0
120°	372.2	371.6	373.3	372.2	369.4
122.5°	401.3	404.0	404.6	403.5	400.2
125°	431.5	435.4	435.4	433.2	431.5
127.5°	460.7	463.4	462.9	461.8	457.4
130°	487.0	489.8	490.3	488.7	485.9
132.5°	513.4	516.7	515.1	515.1	512.3
135°	538.2	541.5	540.4	539.3	536.0
137.5°	561.3	564.5	563.4	563.4	560.7
140°	583.8	584.9	584.3	585.4	582.1
142.5°	604.1	604.7	605.8	605.8	602.5
145°	623.9	625.0	625.0	625.6	622.3
147.5°	641.5	641.5	642.1	642.6	638.8
150°	658.0	656.9	658.0	659.1	654.7
152.5°	673.9	671.2	672.3	673.4	669.5
155°	687.1	683.8	684.9	686.6	682.2
157.5°	697.6	695.9	695.9	697.6	693.2
160°	708.6	705.3	705.8	708.0	703.6
162.5°	717.4	714.1	714.6	717.9	713.0
165°	725.1	721.8	722.3	725.6	721.2
167.5°	731.1	727.8	728.4	732.2	727.3
170°	736.1	732.2	732.8	737.2	732.2
172.5°	739.4	735.5	736.6	740.5	735.5
175°	741.6	738.3	738.8	743.2	738.3
177.5°	743.2	739.9	740.5	744.3	739.9
180°	741.6	741.6	741.6	741.6	741.6

(END OF REPORT)