

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026774

Luminaire Tested: S125DIP-B1270D1270UB2750-4F0-XX-W2A-D_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026774
REPORT IS A COMBINATION OF REPORTS P1001593 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B1270D1270UB2750-4F0-XX-W2A-D_2700K
Description: Define 5 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9669.0 lumens
Efficiency: N/A
Efficacy: 100.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.21 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 96.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026774

CATALOG NUMBER: S125DIP-B1270D1270UB2750-4F0-XX-W2A-D_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1026774

CATALOG NUMBER: S125DIP-B1270D1270UB2750-4F0-XX-W2A-D_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54
1	97	92	88	84	89	85	81	78	71	68	66	58	56	55	47	45	44
2	88	80	73	68	80	74	68	63	62	58	54	51	48	45	41	38	37
3	80	70	62	56	73	64	58	53	54	49	45	45	41	38	36	33	31
4	73	62	54	47	67	57	50	44	48	42	38	40	35	32	32	29	26
5	67	55	47	40	61	51	43	38	43	37	33	35	31	28	29	25	23
6	61	49	41	35	56	45	38	33	38	33	28	32	28	24	26	23	20
7	57	44	36	31	52	41	34	29	35	29	25	29	25	21	24	20	18
8	53	40	32	27	48	37	30	25	32	26	22	27	22	19	22	18	16
9	49	37	29	24	45	34	27	23	29	24	20	24	20	17	20	17	14
10	46	34	26	21	42	31	25	20	27	21	18	22	18	15	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10124	10124	10124
5°	10140	9912	9936
10°	10065	9710	9682
15°	9942	9475	9370
20°	9776	9191	9059
25°	9581	8889	8684
30°	9344	8559	8343
35°	9122	8255	8028
40°	8897	7935	7711
45°	8641	7657	7426
50°	8397	7356	7169
55°	8103	7068	6870
60°	7782	6741	6564
65°	7445	6396	6219
70°	7061	5934	5859
75°	6453	5478	5421
80°	5658	4923	4937
85°	4871	4479	4682

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8641 cd/sqm

TEST NUMBER: P1026774

CATALOG NUMBER: S125DIP-B1270D1270UB2750-4F0-XX-W2A-D_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	149.5	1.5
10°-20°	424.5	4.4
20°-30°	631.2	6.5
30°-40°	747.5	7.7
40°-50°	772.8	8.0
50°-60°	711.9	7.4
60°-70°	575.5	6.0
70°-80°	385.1	4.0
80°-90°	201.3	2.1
90°-100°	164.8	1.7
100°-110°	433.2	4.5
110°-120°	686.6	7.1
120°-130°	841.7	8.7
130°-140°	885.3	9.2
140°-150°	820.7	8.5
150°-160°	661.7	6.8
160°-170°	427.9	4.4
170°-180°	147.6	1.5
0°-30°	1205.2	12.5
0°-40°	1952.7	20.2
0°-60°	3437.5	35.6
0°-90°	4599.5	47.6
90°-120°	1284.7	13.3
90°-150°	3832.3	39.6
90°-180°	5070.0	52.4
0°-180°	9669.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1580	1580	1580	1580	1580	
5°	1580	1577	1566	1579	1577	150
15°	1509	1510	1500	1509	1503	425
25°	1371	1376	1366	1373	1365	631
35°	1187	1198	1193	1198	1198	743
45°	978	995	1002	1013	1015	754
55°	751	776	801	818	824	672
65°	517	553	590	614	620	513
75°	285	325	375	406	414	302
85°	85	136	190	225	237	89
90°	26	85	145	187	201	21
95°	86	123	132	171	182	96
105°	352	382	428	459	469	373
115°	645	662	703	726	729	639
125°	910	917	948	968	972	813
135°	1130	1136	1144	1162	1163	872
145°	1308	1309	1309	1318	1317	818
155°	1439	1432	1435	1438	1429	663
165°	1519	1512	1513	1520	1511	429
175°	1553	1546	1548	1557	1546	148
180°	1553	1553	1553	1553	1553	

TEST NUMBER: P1026774

CATALOG NUMBER: S125DIP-B1270D1270UB2750-4F0-XX-W2A-D_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1580.1	1580.1	1580.1	1580.1	1580.1
2.5°	1584.8	1581.7	1570.8	1581.7	1580.1
5°	1580.1	1577.0	1566.2	1578.6	1577.0
7.5°	1569.3	1567.7	1556.9	1567.7	1566.2
10°	1553.8	1553.8	1541.4	1552.3	1550.7
12.5°	1532.1	1533.7	1524.4	1532.1	1527.5
15°	1508.9	1510.4	1499.6	1508.9	1502.7
17.5°	1479.4	1482.5	1471.7	1479.4	1474.8
20°	1446.9	1450.0	1439.2	1443.8	1443.8
22.5°	1409.7	1415.9	1403.5	1409.7	1405.1
25°	1371.0	1375.7	1366.4	1372.6	1364.8
27.5°	1329.2	1335.4	1324.5	1329.2	1326.1
30°	1281.2	1290.4	1281.2	1284.3	1282.7
32.5°	1237.8	1245.5	1239.3	1242.4	1240.9
35°	1186.7	1197.5	1192.9	1197.5	1197.5
37.5°	1137.1	1146.4	1144.8	1151.0	1149.5
40°	1086.0	1098.4	1096.8	1103.0	1106.1
42.5°	1030.2	1047.2	1051.9	1059.6	1059.6
45°	977.5	994.6	1002.3	1013.1	1014.7
47.5°	923.3	938.8	951.2	966.7	969.8
50°	867.5	884.6	901.6	918.7	923.3
52.5°	808.7	830.3	852.0	870.6	873.7
55°	751.3	776.1	800.9	818.0	824.2
57.5°	692.5	721.9	749.8	768.4	773.0
60°	633.6	664.6	695.6	718.8	723.5
62.5°	576.3	607.3	641.4	667.7	673.9
65°	517.4	553.0	590.2	613.5	619.7
67.5°	463.2	497.3	534.5	562.3	570.1
70°	402.8	438.4	478.7	508.1	517.4
72.5°	343.9	381.1	426.0	458.6	464.7
75°	285.0	325.3	374.9	405.9	413.6
77.5°	227.7	274.2	320.7	354.8	361.0
80°	175.1	221.5	274.2	308.3	314.5
82.5°	127.0	176.6	230.8	263.4	275.8
85°	85.2	136.3	190.5	224.6	237.0
87.5°	54.2	103.8	156.5	192.1	202.9
90°	26.0	84.8	145.4	186.9	201.1
92.5°	43.6	78.1	139.2	179.1	191.1
95°	85.7	122.6	131.5	171.4	182.2
97.5°	141.8	185.9	127.6	162.4	174.5
100°	209.3	245.4	299.5	160.5	165.2
102.5°	278.0	312.1	362.4	395.7	308.2
105°	352.4	381.9	428.4	459.4	469.0
107.5°	429.2	450.9	498.2	530.3	535.0
110°	503.6	522.2	568.0	593.9	605.9

TEST NUMBER: P1026774

CATALOG NUMBER: S125DIP-B1270D1270UB2750-4F0-XX-W2A-D_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	575.0	592.5	635.4	658.7	667.2
115°	644.9	661.5	702.9	726.2	728.6
117.5°	718.2	726.0	769.3	788.8	797.3
120°	787.3	790.8	829.9	854.0	857.5
122.5°	846.8	854.1	889.3	911.8	914.2
125°	910.1	916.6	947.6	967.8	972.1
127.5°	969.6	973.8	999.0	1020.0	1020.1
130°	1024.8	1029.1	1052.0	1070.2	1072.1
132.5°	1078.6	1085.5	1097.6	1119.3	1119.7
135°	1130.4	1135.7	1144.3	1162.1	1163.0
137.5°	1178.8	1184.1	1188.0	1206.6	1207.0
140°	1224.4	1226.7	1227.2	1246.5	1245.8
142.5°	1267.0	1266.7	1269.0	1282.9	1282.2
145°	1308.5	1309.3	1309.3	1318.1	1317.4
147.5°	1343.8	1343.8	1345.0	1349.2	1344.3
150°	1378.4	1376.1	1378.4	1380.7	1373.0
152.5°	1411.8	1406.0	1408.3	1410.6	1402.5
155°	1439.4	1432.5	1434.8	1438.2	1429.0
157.5°	1461.3	1457.8	1457.8	1461.3	1452.1
160°	1484.3	1477.4	1478.5	1483.2	1473.9
162.5°	1502.7	1495.8	1497.0	1503.9	1493.5
165°	1518.8	1511.9	1513.1	1520.0	1510.8
167.5°	1531.5	1524.6	1525.8	1533.8	1523.5
170°	1541.9	1533.8	1535.0	1544.2	1533.8
172.5°	1548.8	1540.7	1543.0	1551.1	1540.7
175°	1553.4	1546.5	1547.6	1556.8	1546.5
177.5°	1556.8	1549.9	1551.1	1559.2	1549.9
180°	1553.4	1553.4	1553.4	1553.4	1553.4

(END OF REPORT)