

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027045

Luminaire Tested: S125DIP-B850D850UB2750-4F0-XX-W2A-D_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027045
REPORT IS A COMBINATION OF REPORTS P1002674 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B850D850UB2750-4F0-XX-W2A-D_3000K
Description: Define 5 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6466.0 lumens
Efficiency: N/A
Efficacy: 113.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.21 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 57
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027045

CATALOG NUMBER: S125DIP-B850D850UB2750-4F0-XX-W2A-D_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1027045

CATALOG NUMBER: S125DIP-B850D850UB2750-4F0-XX-W2A-D_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	54	54	54
1	97	92	88	84	89	85	81	78	71	68	66	58	57	55	47	46	44
2	88	80	74	68	80	74	68	63	62	58	54	51	48	45	41	39	37
3	80	70	62	56	73	65	58	53	54	49	45	45	41	38	36	33	31
4	73	62	54	47	67	57	50	44	48	43	38	40	36	32	32	29	27
5	67	55	47	41	61	51	43	38	43	37	33	36	31	28	29	26	23
6	61	49	41	35	56	46	38	33	39	33	29	32	28	24	26	23	20
7	57	44	36	31	52	41	34	29	35	29	25	29	25	21	24	20	18
8	53	40	32	27	48	37	30	25	32	26	22	27	22	19	22	18	16
9	49	37	29	24	45	34	27	23	29	24	20	24	20	17	20	17	14
10	46	34	26	21	42	31	25	20	27	21	18	23	18	15	19	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6823	6823	6823
5°	6834	6680	6697
10°	6783	6544	6525
15°	6700	6385	6315
20°	6589	6194	6106
25°	6457	5991	5853
30°	6297	5768	5623
35°	6147	5563	5411
40°	5996	5348	5197
45°	5824	5161	5005
50°	5659	4957	4832
55°	5462	4764	4630
60°	5245	4543	4424
65°	5017	4311	4191
70°	4759	3999	3949
75°	4350	3692	3654
80°	3813	3318	3327
85°	3282	3019	3155

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5824 cd/sqm

TEST NUMBER: P1027045

CATALOG NUMBER: S125DIP-B850D850UB2750-4F0-XX-W2A-D_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.8	1.6
10°-20°	286.1	4.4
20°-30°	425.4	6.6
30°-40°	503.8	7.8
40°-50°	520.9	8.1
50°-60°	479.8	7.4
60°-70°	387.9	6.0
70°-80°	259.5	4.0
80°-90°	135.7	2.1
90°-100°	110.5	1.7
100°-110°	288.3	4.5
110°-120°	456.1	7.1
120°-130°	558.7	8.6
130°-140°	587.4	9.1
140°-150°	544.5	8.4
150°-160°	438.9	6.8
160°-170°	283.9	4.4
170°-180°	97.9	1.5
0°-30°	812.3	12.6
0°-40°	1316.1	20.4
0°-60°	2316.7	35.8
0°-90°	3099.8	47.9
90°-120°	854.9	13.2
90°-150°	2545.5	39.4
90°-180°	3366.0	52.1
0°-180°	6466.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1065	1065	1065	1065	1065	
5°	1065	1063	1056	1064	1063	101
15°	1017	1018	1011	1017	1013	287
25°	924	927	921	925	920	425
35°	800	807	804	807	807	501
45°	659	670	676	683	684	508
55°	506	523	540	551	555	453
65°	349	373	398	413	418	346
75°	192	219	253	274	279	204
85°	57	92	128	151	160	60
90°	18	57	98	126	135	14
95°	57	82	88	115	122	64
105°	234	254	285	306	312	248
115°	428	439	467	483	484	424
125°	604	608	629	643	646	539
135°	750	753	759	771	772	578
145°	868	869	869	874	874	543
155°	955	950	952	954	948	440
165°	1008	1003	1004	1008	1002	285
175°	1030	1026	1027	1033	1026	98
180°	1030	1030	1030	1030	1030	

TEST NUMBER: P1027045

CATALOG NUMBER: S125DIP-B850D850UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1064.9	1064.9	1064.9	1064.9	1064.9
2.5°	1068.1	1066.0	1058.7	1066.0	1064.9
5°	1064.9	1062.9	1055.5	1063.9	1062.9
7.5°	1057.6	1056.6	1049.3	1056.6	1055.5
10°	1047.2	1047.2	1038.8	1046.1	1045.1
12.5°	1032.6	1033.6	1027.4	1032.6	1029.4
15°	1016.9	1018.0	1010.6	1016.9	1012.7
17.5°	997.1	999.2	991.9	997.1	993.9
20°	975.2	977.2	969.9	973.1	973.1
22.5°	950.1	954.3	945.9	950.1	947.0
25°	924.0	927.1	920.9	925.0	919.8
27.5°	895.8	900.0	892.7	895.8	893.7
30°	863.4	869.7	863.4	865.5	864.5
32.5°	834.2	839.4	835.2	837.3	836.3
35°	799.7	807.1	803.9	807.1	807.1
37.5°	766.3	772.6	771.6	775.7	774.7
40°	731.9	740.2	739.2	743.4	745.5
42.5°	694.3	705.8	708.9	714.1	714.1
45°	658.8	670.3	675.5	682.8	683.9
47.5°	622.3	632.7	641.1	651.5	653.6
50°	584.7	596.2	607.6	619.1	622.3
52.5°	545.0	559.6	574.2	586.8	588.8
55°	506.4	523.1	539.8	551.3	555.4
57.5°	466.7	486.5	505.3	517.9	521.0
60°	427.0	447.9	468.8	484.4	487.6
62.5°	388.4	409.3	432.2	450.0	454.2
65°	348.7	372.7	397.8	413.4	417.6
67.5°	312.2	335.1	360.2	379.0	384.2
70°	271.5	295.5	322.6	342.5	348.7
72.5°	231.8	256.8	287.1	309.0	313.2
75°	192.1	219.3	252.7	273.5	278.8
77.5°	153.5	184.8	216.1	239.1	243.3
80°	118.0	149.3	184.8	207.8	211.9
82.5°	85.6	119.0	155.6	177.5	185.8
85°	57.4	91.9	128.4	151.4	159.7
87.5°	36.5	70.0	105.5	129.5	136.8
90°	17.5	57.0	97.8	125.6	135.2
92.5°	29.1	52.5	93.6	120.4	128.5
95°	57.1	82.0	88.4	115.2	122.5
97.5°	94.2	123.9	85.8	109.3	117.3
100°	139.1	163.3	199.7	107.8	111.0
102.5°	184.6	207.5	241.4	263.8	205.9
105°	234.0	253.7	285.0	305.9	312.5
107.5°	284.9	299.5	331.3	352.9	356.2
110°	334.2	346.7	377.6	395.1	403.1



TEST NUMBER: P1027045

CATALOG NUMBER: S125DIP-B850D850UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	381.6	393.3	422.3	438.0	443.8
115°	428.0	439.1	467.0	482.7	484.4
117.5°	476.5	481.7	510.9	524.1	529.9
120°	522.4	524.8	551.1	567.3	569.7
122.5°	561.8	566.7	590.4	605.6	607.3
125°	603.9	608.1	629.0	642.7	645.6
127.5°	643.2	646.1	663.0	677.2	677.4
130°	679.9	682.7	698.1	710.4	711.8
132.5°	715.6	720.2	728.3	742.9	743.3
135°	750.0	753.4	759.3	771.3	771.9
137.5°	782.0	785.5	788.2	800.7	801.1
140°	812.3	813.8	814.1	827.2	826.7
142.5°	840.5	840.3	841.8	851.2	850.8
145°	868.0	868.6	868.6	874.5	874.1
147.5°	891.5	891.5	892.2	895.1	891.8
150°	914.4	912.9	914.4	915.9	910.8
152.5°	936.5	932.7	934.2	935.8	930.4
155°	954.9	950.3	951.8	954.1	948.0
157.5°	969.4	967.1	967.1	969.4	963.3
160°	984.7	980.1	980.8	983.9	977.8
162.5°	996.9	992.3	993.1	997.7	990.8
165°	1007.6	1003.0	1003.8	1008.3	1002.2
167.5°	1016.0	1011.4	1012.2	1017.5	1010.6
170°	1022.9	1017.5	1018.3	1024.4	1017.5
172.5°	1027.4	1022.1	1023.6	1029.0	1022.1
175°	1030.5	1025.9	1026.7	1032.8	1025.9
177.5°	1032.8	1028.2	1029.0	1034.3	1028.2
180°	1030.5	1030.5	1030.5	1030.5	1030.5

(END OF REPORT)