

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027050

Luminaire Tested: S125DIP-B850D850UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027050
REPORT IS A COMBINATION OF REPORTS P1002679 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B850D850UB2750-4F0-XX-W2A-F_3000K
Description: Define 5 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6602.0 lumens
Efficiency: N/A
Efficacy: 115.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 57
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027050

CATALOG NUMBER: S125DIP-B850D850UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1027050

CATALOG NUMBER: S125DIP-B850D850UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	108	108	108	108	100	100	100	100	84	84	84	71	71	71	58	58	58	58	58	58
1	98	94	90	86	91	87	84	80	74	72	69	62	60	59	51	50	49	49	49	44
2	89	82	76	70	82	76	71	66	65	61	57	55	52	49	45	43	41	41	41	37
3	82	72	65	59	75	67	60	55	57	52	48	48	45	41	40	37	35	35	35	31
4	75	64	56	50	69	59	52	47	51	45	41	43	39	35	36	33	30	30	30	27
5	68	57	49	43	63	53	46	40	45	40	35	39	34	31	32	29	26	26	26	23
6	63	51	43	37	58	47	40	35	41	35	31	35	30	27	29	26	23	23	23	20
7	58	46	38	32	54	43	36	31	37	31	27	32	27	24	27	23	21	21	21	18
8	54	42	34	29	50	39	32	27	34	28	24	29	25	21	24	21	18	18	18	16
9	50	38	31	25	47	36	29	24	31	25	22	27	22	19	23	19	17	17	17	14
10	47	35	28	23	44	33	26	22	29	23	19	25	20	17	21	18	15	15	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8456	8456	8456
5°	8456	8259	8275
10°	8386	8070	8045
15°	8276	7843	7774
20°	8127	7581	7462
25°	7968	7295	7128
30°	7774	6996	6777
35°	7569	6683	6384
40°	7356	6353	6034
45°	7126	6030	5662
50°	6872	5665	5229
55°	6621	5262	4831
60°	6322	4837	4367
65°	5964	4345	3888
70°	5601	3780	3334
75°	4988	3112	2696
80°	4253	2325	1983
85°	3282	1376	1092

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 7126 cd/sqm

TEST NUMBER: P1027050

CATALOG NUMBER: S125DIP-B850D850UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	124.5	1.9
10°-20°	351.8	5.3
20°-30°	519.3	7.9
30°-40°	605.9	9.2
40°-50°	608.5	9.2
50°-60°	534.2	8.1
60°-70°	397.9	6.0
70°-80°	227.2	3.4
80°-90°	67.1	1.0
90°-100°	35.0	0.5
100°-110°	232.6	3.5
110°-120°	418.8	6.3
120°-130°	537.6	8.1
130°-140°	578.2	8.8
140°-150°	542.6	8.2
150°-160°	438.9	6.6
160°-170°	283.9	4.3
170°-180°	97.9	1.5
0°-30°	995.6	15.1
0°-40°	1601.5	24.3
0°-60°	2744.3	41.6
0°-90°	3436.5	52.1
90°-120°	686.3	10.4
90°-150°	2344.8	35.5
90°-180°	3165.0	47.9
0°-180°	6602.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1320	1320	1320	1320	1320	
5°	1318	1316	1305	1314	1314	125
15°	1256	1253	1241	1247	1247	354
25°	1140	1135	1121	1124	1120	525
35°	985	980	966	961	952	616
45°	806	802	789	777	774	621
55°	614	611	596	587	580	548
65°	414	412	401	392	387	411
75°	220	218	213	210	206	235
85°	57	58	58	57	55	63
90°	1	7	12	16	18	6
95°	44	41	12	16	16	53
105°	225	228	228	228	227	238
115°	422	426	426	423	419	418
125°	600	605	605	602	600	536
135°	748	752	751	749	745	577
145°	867	869	869	869	865	542
155°	955	950	952	954	948	440
165°	1008	1003	1004	1008	1002	285
175°	1030	1026	1027	1033	1026	98
180°	1030	1030	1030	1030	1030	

TEST NUMBER: P1027050

CATALOG NUMBER: S125DIP-B850D850UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1319.8	1319.8	1319.8	1319.8	1319.8
2.5°	1323.9	1320.8	1310.4	1320.8	1319.8
5°	1317.7	1315.6	1305.1	1314.5	1313.5
7.5°	1308.3	1306.2	1294.7	1304.1	1303.1
10°	1294.7	1292.6	1281.1	1289.5	1288.4
12.5°	1278.0	1273.8	1263.4	1269.6	1269.6
15°	1256.1	1252.9	1241.4	1246.7	1246.7
17.5°	1233.1	1227.9	1216.4	1222.7	1217.4
20°	1202.8	1200.7	1187.2	1194.5	1189.2
22.5°	1172.5	1168.4	1155.8	1160.0	1156.9
25°	1140.2	1134.9	1121.4	1123.5	1120.3
27.5°	1102.6	1099.4	1085.9	1086.9	1083.8
30°	1066.0	1062.9	1047.2	1045.2	1042.0
32.5°	1026.4	1021.1	1007.6	1003.4	997.1
35°	984.6	980.4	965.8	960.6	952.2
37.5°	941.8	936.6	923.0	915.7	910.5
40°	897.9	892.7	878.1	868.7	865.6
42.5°	851.0	846.8	832.2	823.8	818.6
45°	806.1	801.9	789.3	776.8	773.7
47.5°	757.0	758.0	742.4	729.8	722.5
50°	710.0	706.9	694.3	680.8	673.5
52.5°	662.0	659.9	646.3	634.8	626.5
55°	613.9	610.8	596.2	586.8	579.5
57.5°	562.8	561.7	549.2	536.7	533.5
60°	514.7	510.6	499.1	488.6	481.3
62.5°	464.6	461.5	452.1	440.6	435.4
65°	414.5	412.4	400.9	391.5	387.4
67.5°	365.4	361.3	352.9	344.6	342.5
70°	319.5	314.3	304.9	298.6	294.4
72.5°	269.4	266.2	261.0	253.7	249.5
75°	220.3	218.2	213.0	209.9	205.7
77.5°	174.4	173.3	170.2	168.1	165.0
80°	131.6	131.6	129.5	128.4	126.3
82.5°	94.0	91.9	91.9	89.8	89.8
85°	57.4	58.5	58.5	57.4	55.3
87.5°	28.2	28.2	27.1	27.1	25.1
90°	0.8	6.9	12.2	16.0	18.3
92.5°	14.5	7.6	12.2	16.0	16.8
95°	43.5	41.3	12.2	16.0	16.0
97.5°	81.7	86.3	13.8	15.3	16.0
100°	127.6	129.9	132.9	19.1	16.0
102.5°	174.2	177.2	178.8	180.3	116.1
105°	224.6	227.6	227.6	227.6	226.9
107.5°	276.5	276.5	278.1	278.8	275.8
110°	326.9	326.9	328.5	326.2	326.9

TEST NUMBER: P1027050

CATALOG NUMBER: S125DIP-B850D850UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	374.3	376.6	377.4	374.3	372.8
115°	421.7	425.5	426.3	423.2	418.6
117.5°	471.3	471.3	474.4	469.8	468.3
120°	517.2	516.4	518.7	517.2	513.3
122.5°	557.6	561.5	562.2	560.7	556.1
125°	599.7	605.0	605.0	602.0	599.7
127.5°	640.1	644.0	643.2	641.7	635.6
130°	676.8	680.6	681.4	679.1	675.3
132.5°	713.5	718.1	715.8	715.8	712.0
135°	747.9	752.4	750.9	749.4	744.8
137.5°	779.9	784.5	783.0	783.0	779.2
140°	811.3	812.8	812.0	813.6	809.0
142.5°	839.5	840.3	841.8	841.8	837.2
145°	867.0	868.6	868.6	869.3	864.7
147.5°	891.5	891.5	892.2	893.0	887.6
150°	914.4	912.9	914.4	915.9	909.8
152.5°	936.5	932.7	934.2	935.8	930.4
155°	954.9	950.3	951.8	954.1	948.0
157.5°	969.4	967.1	967.1	969.4	963.3
160°	984.7	980.1	980.8	983.9	977.8
162.5°	996.9	992.3	993.1	997.7	990.8
165°	1007.6	1003.0	1003.8	1008.3	1002.2
167.5°	1016.0	1011.4	1012.2	1017.5	1010.6
170°	1022.9	1017.5	1018.3	1024.4	1017.5
172.5°	1027.4	1022.1	1023.6	1029.0	1022.1
175°	1030.5	1025.9	1026.7	1032.8	1025.9
177.5°	1032.8	1028.2	1029.0	1034.3	1028.2
180°	1030.5	1030.5	1030.5	1030.5	1030.5

(END OF REPORT)