

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026792

Luminaire Tested: S125DIP-B1270D375UB2750-4F0-XX-W2A-D_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026792
REPORT IS A COMBINATION OF REPORTS P1001656 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B1270D375UB2750-4F0-XX-W2A-D_4000K
Description: Define 5 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6375.1 lumens
Efficiency: N/A
Efficacy: 90.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.21 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 70.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026792

CATALOG NUMBER: S125DIP-B1270D375UB2750-4F0-XX-W2A-D_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1026792

CATALOG NUMBER: S125DIP-B1270D375UB2750-4F0-XX-W2A-D_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	112	112	112	112	107	107	107	107	96	96	96	86	86	86	77	77	77
1	102	97	92	88	96	92	88	84	83	79	77	74	72	69	66	64	63
2	92	84	77	71	87	80	74	68	72	67	63	64	61	57	58	55	52
3	84	74	65	59	79	70	63	57	63	57	52	57	52	48	51	47	44
4	77	65	56	50	72	62	54	48	56	49	44	50	45	41	45	41	37
5	70	58	49	43	66	55	47	41	50	43	38	45	40	35	41	36	32
6	65	52	43	37	61	50	42	36	45	38	33	41	35	31	37	32	29
7	60	47	38	33	57	45	37	31	41	34	29	37	31	27	34	29	25
8	56	43	34	29	53	41	33	28	37	31	26	34	28	24	31	26	23
9	52	39	31	26	49	37	30	25	34	28	23	31	26	22	28	24	20
10	49	36	28	23	46	34	27	23	32	25	21	29	24	20	26	22	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10153	10153	10153
5°	10170	9940	9965
10°	10093	9737	9710
15°	9970	9502	9397
20°	9805	9217	9085
25°	9608	8914	8709
30°	9370	8583	8367
35°	9148	8279	8051
40°	8922	7957	7733
45°	8666	7679	7447
50°	8421	7377	7189
55°	8127	7089	6890
60°	7804	6761	6582
65°	7466	6414	6236
70°	7080	5952	5876
75°	6473	5494	5437
80°	5675	4937	4951
85°	4883	4493	4696

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8666 cd/sqm

TEST NUMBER: P1026792

CATALOG NUMBER: S125DIP-B1270D375UB2750-4F0-XX-W2A-D_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	150.0	2.4
10°-20°	425.7	6.7
20°-30°	633.0	9.9
30°-40°	749.7	11.8
40°-50°	775.0	12.2
50°-60°	714.0	11.2
60°-70°	577.2	9.1
70°-80°	386.2	6.1
80°-90°	200.3	3.1
90°-100°	128.6	2.0
100°-110°	190.5	3.0
110°-120°	249.4	3.9
120°-130°	280.3	4.4
130°-140°	281.4	4.4
140°-150°	253.9	4.0
150°-160°	203.2	3.2
160°-170°	131.4	2.1
170°-180°	45.3	0.7
0°-30°	1208.7	19.0
0°-40°	1958.3	30.7
0°-60°	3447.3	54.1
0°-90°	4611.0	72.3
90°-120°	568.5	8.9
90°-150°	1384.1	21.7
90°-180°	1764.0	27.7
0°-180°	6375.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1585	1585	1585	1585	1585	
5°	1585	1582	1571	1583	1582	150
15°	1513	1515	1504	1513	1507	426
25°	1375	1380	1370	1376	1369	633
35°	1190	1201	1196	1201	1201	745
45°	980	997	1005	1016	1018	756
55°	754	778	803	820	826	673
65°	519	555	592	615	621	515
75°	286	326	376	407	415	303
85°	85	137	191	225	238	89
90°	25	78	133	170	182	18
95°	40	80	119	155	166	41
105°	118	144	191	222	232	125
115°	204	217	258	284	292	203
125°	284	285	316	339	346	253
135°	349	350	360	380	385	269
145°	403	402	402	410	414	252
155°	442	440	441	442	439	204
165°	466	464	465	467	464	132
175°	477	475	475	478	475	45
180°	477	477	477	477	477	

TEST NUMBER: P1026792

CATALOG NUMBER: S125DIP-B1270D375UB2750-4F0-XX-W2A-D_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1584.7	1584.7	1584.7	1584.7	1584.7
2.5°	1589.3	1586.2	1575.3	1586.2	1584.7
5°	1584.7	1581.6	1570.7	1583.1	1581.6
7.5°	1573.8	1572.2	1561.4	1572.2	1570.7
10°	1558.2	1558.2	1545.8	1556.7	1555.1
12.5°	1536.5	1538.1	1528.7	1536.5	1531.8
15°	1513.2	1514.7	1503.9	1513.2	1507.0
17.5°	1483.7	1486.8	1475.9	1483.7	1479.0
20°	1451.1	1454.2	1443.3	1447.9	1447.9
22.5°	1413.8	1420.0	1407.6	1413.8	1409.1
25°	1374.9	1379.6	1370.3	1376.5	1368.7
27.5°	1333.0	1339.2	1328.3	1333.0	1329.9
30°	1284.8	1294.1	1284.8	1287.9	1286.4
32.5°	1241.3	1249.1	1242.9	1246.0	1244.4
35°	1190.0	1200.9	1196.3	1200.9	1200.9
37.5°	1140.3	1149.7	1148.1	1154.3	1152.8
40°	1089.1	1101.5	1099.9	1106.2	1109.3
42.5°	1033.1	1050.2	1054.9	1062.7	1062.7
45°	980.3	997.4	1005.2	1016.0	1017.6
47.5°	925.9	941.5	953.9	969.4	972.5
50°	870.0	887.1	904.2	921.3	925.9
52.5°	811.0	832.7	854.5	873.1	876.2
55°	753.5	778.3	803.2	820.3	826.5
57.5°	694.5	724.0	751.9	770.6	775.2
60°	635.4	666.5	697.6	720.9	725.5
62.5°	577.9	609.0	643.2	669.6	675.8
65°	518.9	554.6	591.9	615.2	621.4
67.5°	464.5	498.7	536.0	564.0	571.7
70°	403.9	439.7	480.1	509.6	518.9
72.5°	344.9	382.2	427.2	459.9	466.1
75°	285.9	326.3	376.0	407.0	414.8
77.5°	228.4	275.0	321.6	355.8	362.0
80°	175.6	222.2	275.0	309.2	315.4
82.5°	127.4	177.1	231.5	264.1	276.5
85°	85.4	136.7	191.1	225.3	237.7
87.5°	54.4	104.1	156.9	192.6	203.5
90°	25.3	77.8	133.1	170.5	182.5
92.5°	28.5	70.3	126.9	162.8	174.0
95°	40.4	79.7	119.1	155.0	165.9
97.5°	56.4	95.9	113.6	146.9	158.1
100°	76.2	109.8	160.9	140.9	148.8
102.5°	96.1	127.1	175.9	207.8	187.3
105°	118.0	144.2	190.8	221.9	232.4
107.5°	140.4	162.2	207.9	239.4	247.3
110°	162.2	180.8	225.1	253.5	264.7



TEST NUMBER: P1026792

CATALOG NUMBER: S125DIP-B1270D375UB2750-4F0-XX-W2A-D_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	184.2	199.2	241.5	268.1	278.2
115°	204.5	217.2	257.9	284.5	291.7
117.5°	226.0	233.7	274.0	298.3	308.5
120°	247.2	251.4	288.3	314.0	321.5
122.5°	264.3	267.7	302.2	326.3	333.5
125°	283.8	284.8	315.8	339.2	346.0
127.5°	301.0	301.2	327.2	349.8	356.3
130°	318.0	318.2	340.3	361.0	367.0
132.5°	333.4	335.5	349.9	371.7	376.2
135°	349.3	349.9	360.0	379.5	385.2
137.5°	364.1	364.8	370.2	388.8	393.3
140°	377.1	377.8	379.0	396.8	400.9
142.5°	390.2	389.0	389.7	403.7	407.8
145°	402.9	402.1	402.1	410.2	414.3
147.5°	412.7	412.7	413.0	416.5	417.1
150°	423.3	422.6	423.3	424.0	422.7
152.5°	433.5	431.8	432.5	433.2	430.7
155°	442.0	439.9	440.6	441.7	438.8
157.5°	448.7	447.7	447.7	448.7	445.9
160°	455.8	453.7	454.0	455.4	452.6
162.5°	461.5	459.3	459.7	461.8	458.6
165°	466.4	464.3	464.6	466.8	463.9
167.5°	470.3	468.2	468.5	471.0	467.8
170°	473.5	471.0	471.4	474.2	471.0
172.5°	475.6	473.1	473.8	476.3	473.1
175°	477.0	474.9	475.2	478.1	474.9
177.5°	478.1	476.0	476.3	478.8	476.0
180°	477.0	477.0	477.0	477.0	477.0

(END OF REPORT)