

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026793

Luminaire Tested: S125DIP-B1270D375UB2750-4F0-XX-W2A-D_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026793
REPORT IS A COMBINATION OF REPORTS P1001657 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B1270D375UB2750-4F0-XX-W2A-D_5000K
Description: Define 5 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6165.0 lumens
Efficiency: N/A
Efficacy: 87.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.21 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 70.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026793

CATALOG NUMBER: S125DIP-B1270D375UB2750-4F0-XX-W2A-D_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1026793

CATALOG NUMBER: S125DIP-B1270D375UB2750-4F0-XX-W2A-D_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	112	112	112	112	107	107	107	107	96	96	96	86	86	86	77	77	77
1	102	97	92	88	96	92	88	84	83	79	77	74	72	69	66	64	63
2	92	84	77	71	87	80	74	68	72	67	63	64	61	57	58	55	52
3	84	74	65	59	79	70	63	57	63	57	52	57	52	48	51	47	44
4	77	65	56	50	72	62	54	48	56	49	44	50	45	41	45	41	37
5	70	58	49	43	66	55	47	41	50	43	38	45	40	35	41	36	32
6	65	52	43	37	61	50	42	36	45	38	33	41	35	31	37	32	29
7	60	47	38	33	57	45	37	31	41	34	29	37	31	27	34	29	25
8	56	43	34	29	53	41	33	28	37	31	26	34	28	24	31	26	23
9	52	39	31	26	49	37	30	25	34	28	23	31	26	22	28	24	20
10	49	36	28	23	46	34	27	23	32	25	21	29	24	20	26	22	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9818	9818	9818
5°	9834	9612	9636
10°	9760	9416	9389
15°	9642	9188	9086
20°	9481	8913	8786
25°	9291	8619	8421
30°	9061	8300	8091
35°	8846	8005	7785
40°	8627	7695	7478
45°	8380	7426	7201
50°	8143	7133	6952
55°	7858	6855	6662
60°	7546	6537	6365
65°	7220	6203	6031
70°	6847	5755	5683
75°	6258	5313	5258
80°	5487	4774	4788
85°	4723	4345	4541

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8380 cd/sqm

TEST NUMBER: P1026793

CATALOG NUMBER: S125DIP-B1270D375UB2750-4F0-XX-W2A-D_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	145.0	2.4
10°-20°	411.6	6.7
20°-30°	612.1	9.9
30°-40°	724.9	11.8
40°-50°	749.5	12.2
50°-60°	690.4	11.2
60°-70°	558.1	9.1
70°-80°	373.4	6.1
80°-90°	193.7	3.1
90°-100°	124.4	2.0
100°-110°	184.3	3.0
110°-120°	241.2	3.9
120°-130°	271.1	4.4
130°-140°	272.2	4.4
140°-150°	245.6	4.0
150°-160°	196.5	3.2
160°-170°	127.1	2.1
170°-180°	43.8	0.7
0°-30°	1168.8	19.0
0°-40°	1893.7	30.7
0°-60°	3333.6	54.1
0°-90°	4458.8	72.3
90°-120°	549.8	8.9
90°-150°	1338.7	21.7
90°-180°	1706.0	27.7
0°-180°	6165.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1532	1532	1532	1532	1532	
5°	1532	1529	1519	1531	1529	145
15°	1463	1465	1454	1463	1457	412
25°	1330	1334	1325	1331	1324	612
35°	1151	1161	1157	1161	1161	720
45°	948	964	972	982	984	731
55°	729	753	777	793	799	651
65°	502	536	572	595	601	498
75°	276	316	364	394	401	293
85°	83	132	185	218	230	86
90°	24	75	129	165	176	18
95°	39	77	115	150	160	39
105°	114	140	184	215	225	121
115°	198	210	250	275	282	196
125°	274	275	306	328	335	245
135°	338	338	348	367	373	260
145°	390	389	389	397	401	243
155°	428	426	426	427	424	197
165°	451	449	449	452	449	127
175°	461	459	460	462	459	44
180°	461	461	461	461	461	

TEST NUMBER: P1026793

CATALOG NUMBER: S125DIP-B1270D375UB2750-4F0-XX-W2A-D_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1532.4	1532.4	1532.4	1532.4	1532.4
2.5°	1536.9	1533.9	1523.4	1533.9	1532.4
5°	1532.4	1529.4	1518.8	1530.9	1529.4
7.5°	1521.8	1520.3	1509.8	1520.3	1518.8
10°	1506.8	1506.8	1494.8	1505.3	1503.8
12.5°	1485.8	1487.3	1478.3	1485.8	1481.3
15°	1463.3	1464.8	1454.2	1463.3	1457.2
17.5°	1434.7	1437.7	1427.2	1434.7	1430.2
20°	1403.2	1406.2	1395.7	1400.2	1400.2
22.5°	1367.1	1373.1	1361.1	1367.1	1362.6
25°	1329.6	1334.1	1325.0	1331.1	1323.5
27.5°	1289.0	1295.0	1284.5	1289.0	1286.0
30°	1242.4	1251.4	1242.4	1245.4	1243.9
32.5°	1200.4	1207.9	1201.9	1204.9	1203.4
35°	1150.8	1161.3	1156.8	1161.3	1161.3
37.5°	1102.7	1111.7	1110.2	1116.2	1114.7
40°	1053.1	1065.1	1063.6	1069.7	1072.7
42.5°	999.0	1015.6	1020.1	1027.6	1027.6
45°	948.0	964.5	972.0	982.5	984.0
47.5°	895.4	910.4	922.4	937.4	940.5
50°	841.3	857.8	874.3	890.9	895.4
52.5°	784.2	805.2	826.3	844.3	847.3
55°	728.6	752.7	776.7	793.2	799.2
57.5°	671.5	700.1	727.1	745.2	749.7
60°	614.4	644.5	674.5	697.1	701.6
62.5°	558.9	588.9	622.0	647.5	653.5
65°	501.8	536.3	572.4	594.9	600.9
67.5°	449.2	482.2	518.3	545.3	552.9
70°	390.6	425.2	464.2	492.8	501.8
72.5°	333.5	369.6	413.1	444.7	450.7
75°	276.4	315.5	363.6	393.6	401.1
77.5°	220.8	265.9	311.0	344.0	350.0
80°	169.8	214.8	265.9	299.0	305.0
82.5°	123.2	171.3	223.8	255.4	267.4
85°	82.6	132.2	184.8	217.8	229.9
87.5°	52.6	100.7	151.7	186.3	196.8
90°	24.3	75.2	128.7	164.9	176.5
92.5°	27.5	68.0	122.7	157.4	168.2
95°	39.0	77.1	115.2	149.9	160.4
97.5°	54.6	92.7	109.9	142.0	152.9
100°	73.6	106.2	155.6	136.3	143.9
102.5°	93.0	123.0	170.1	200.9	181.2
105°	114.1	139.5	184.5	214.6	224.8
107.5°	135.8	156.9	201.1	231.5	239.2
110°	156.9	174.9	217.7	245.2	256.1



TEST NUMBER: P1026793

CATALOG NUMBER: S125DIP-B1270D375UB2750-4F0-XX-W2A-D_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	178.1	192.6	233.6	259.2	269.1
115°	197.8	210.0	249.5	275.1	282.0
117.5°	218.5	226.0	265.0	288.4	298.3
120°	239.1	243.2	278.8	303.7	310.9
122.5°	255.7	258.9	292.3	315.6	322.6
125°	274.5	275.4	305.5	328.1	334.6
127.5°	291.1	291.3	316.5	338.4	344.7
130°	307.5	307.7	329.1	349.2	355.0
132.5°	322.5	324.5	338.5	359.6	363.9
135°	337.8	338.4	348.2	367.0	372.6
137.5°	352.2	352.8	358.1	376.1	380.4
140°	364.7	365.4	366.6	383.8	387.7
142.5°	377.4	376.2	376.9	390.4	394.4
145°	389.7	388.9	388.9	396.7	400.7
147.5°	399.1	399.1	399.5	402.8	403.4
150°	409.4	408.7	409.4	410.1	408.9
152.5°	419.3	417.6	418.3	419.0	416.6
155°	427.5	425.5	426.2	427.2	424.5
157.5°	434.0	433.0	433.0	434.0	431.3
160°	440.9	438.8	439.2	440.5	437.8
162.5°	446.3	444.3	444.6	446.7	443.6
165°	451.1	449.1	449.4	451.5	448.7
167.5°	454.9	452.8	453.2	455.6	452.5
170°	458.0	455.6	455.9	458.7	455.6
172.5°	460.0	457.6	458.3	460.7	457.6
175°	461.4	459.3	459.7	462.4	459.3
177.5°	462.4	460.4	460.7	463.1	460.4
180°	461.4	461.4	461.4	461.4	461.4

(END OF REPORT)