

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026804

Luminaire Tested: S125DIP-B1270D610UB2750-4F0-XX-W2A-D_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026804
REPORT IS A COMBINATION OF REPORTS P1001713 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B1270D610UB2750-4F0-XX-W2A-D_2700K
Description: Define 5 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7244.9 lumens
Efficiency: N/A
Efficacy: 94.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.21 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 76.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026804

CATALOG NUMBER: S125DIP-B1270D610UB2750-4F0-XX-W2A-D_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1026804

CATALOG NUMBER: S125DIP-B1270D610UB2750-4F0-XX-W2A-D_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	104	104	104	104	91	91	91	79	79	79	68	68	68
1	100	95	91	87	93	89	85	82	78	75	73	68	66	64	59	57	56
2	91	82	76	70	85	77	72	67	68	64	60	59	56	53	51	49	46
3	82	72	64	58	77	68	61	55	60	54	50	52	48	44	45	42	39
4	75	64	55	49	70	60	52	47	53	47	42	46	42	38	40	37	33
5	69	57	48	42	64	54	46	40	47	41	36	42	37	33	36	32	29
6	64	51	42	36	59	48	40	35	43	36	32	38	32	28	33	29	25
7	59	46	38	32	55	43	36	30	39	32	28	34	29	25	30	26	23
8	55	42	34	28	51	40	32	27	35	29	25	31	26	22	28	23	20
9	51	38	30	25	48	36	29	24	32	26	22	29	24	20	25	21	18
10	48	35	28	23	45	33	26	22	30	24	20	27	22	18	24	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10124	10124	10124
5°	10140	9912	9936
10°	10065	9710	9682
15°	9942	9475	9370
20°	9776	9191	9059
25°	9581	8889	8684
30°	9344	8559	8343
35°	9122	8255	8028
40°	8897	7935	7711
45°	8641	7657	7426
50°	8397	7356	7169
55°	8103	7068	6870
60°	7782	6741	6564
65°	7445	6396	6219
70°	7061	5934	5859
75°	6453	5478	5421
80°	5658	4923	4937
85°	4871	4479	4682

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8641 cd/sqm

TEST NUMBER: P1026804

CATALOG NUMBER: S125DIP-B1270D610UB2750-4F0-XX-W2A-D_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	149.5	2.1
10°-20°	424.5	5.9
20°-30°	631.2	8.7
30°-40°	747.5	10.3
40°-50°	772.8	10.7
50°-60°	711.9	9.8
60°-70°	575.5	7.9
70°-80°	385.1	5.3
80°-90°	200.2	2.8
90°-100°	138.1	1.9
100°-110°	255.2	3.5
110°-120°	366.1	5.1
120°-130°	430.2	5.9
130°-140°	442.7	6.1
140°-150°	405.4	5.6
150°-160°	325.7	4.5
160°-170°	210.6	2.9
170°-180°	72.6	1.0
0°-30°	1205.2	16.6
0°-40°	1952.7	27.0
0°-60°	3437.5	47.4
0°-90°	4598.3	63.5
90°-120°	759.4	10.5
90°-150°	2037.6	28.1
90°-180°	2647.0	36.5
0°-180°	7244.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1580	1580	1580	1580	1580	
5°	1580	1577	1566	1579	1577	150
15°	1509	1510	1500	1509	1503	425
25°	1371	1376	1366	1373	1365	631
35°	1187	1198	1193	1198	1198	743
45°	978	995	1002	1013	1015	754
55°	751	776	801	818	824	672
65°	517	553	590	614	620	513
75°	285	325	375	406	414	302
85°	85	136	190	225	237	89
90°	25	80	136	175	187	19
95°	52	91	122	159	170	55
105°	180	208	254	285	295	191
115°	322	336	377	402	408	319
125°	451	454	484	507	513	403
135°	558	560	570	589	593	430
145°	645	644	644	653	656	403
155°	708	705	706	708	703	326
165°	748	744	745	748	744	211
175°	765	761	762	766	761	73
180°	765	765	765	765	765	

TEST NUMBER: P1026804

CATALOG NUMBER: S125DIP-B1270D610UB2750-4F0-XX-W2A-D_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1580.1	1580.1	1580.1	1580.1	1580.1
2.5°	1584.8	1581.7	1570.8	1581.7	1580.1
5°	1580.1	1577.0	1566.2	1578.6	1577.0
7.5°	1569.3	1567.7	1556.9	1567.7	1566.2
10°	1553.8	1553.8	1541.4	1552.3	1550.7
12.5°	1532.1	1533.7	1524.4	1532.1	1527.5
15°	1508.9	1510.4	1499.6	1508.9	1502.7
17.5°	1479.4	1482.5	1471.7	1479.4	1474.8
20°	1446.9	1450.0	1439.2	1443.8	1443.8
22.5°	1409.7	1415.9	1403.5	1409.7	1405.1
25°	1371.0	1375.7	1366.4	1372.6	1364.8
27.5°	1329.2	1335.4	1324.5	1329.2	1326.1
30°	1281.2	1290.4	1281.2	1284.3	1282.7
32.5°	1237.8	1245.5	1239.3	1242.4	1240.9
35°	1186.7	1197.5	1192.9	1197.5	1197.5
37.5°	1137.1	1146.4	1144.8	1151.0	1149.5
40°	1086.0	1098.4	1096.8	1103.0	1106.1
42.5°	1030.2	1047.2	1051.9	1059.6	1059.6
45°	977.5	994.6	1002.3	1013.1	1014.7
47.5°	923.3	938.8	951.2	966.7	969.8
50°	867.5	884.6	901.6	918.7	923.3
52.5°	808.7	830.3	852.0	870.6	873.7
55°	751.3	776.1	800.9	818.0	824.2
57.5°	692.5	721.9	749.8	768.4	773.0
60°	633.6	664.6	695.6	718.8	723.5
62.5°	576.3	607.3	641.4	667.7	673.9
65°	517.4	553.0	590.2	613.5	619.7
67.5°	463.2	497.3	534.5	562.3	570.1
70°	402.8	438.4	478.7	508.1	517.4
72.5°	343.9	381.1	426.0	458.6	464.7
75°	285.0	325.3	374.9	405.9	413.6
77.5°	227.7	274.2	320.7	354.8	361.0
80°	175.1	221.5	274.2	308.3	314.5
82.5°	127.0	176.6	230.8	263.4	275.8
85°	85.2	136.3	190.5	224.6	237.0
87.5°	54.2	103.8	156.5	192.1	202.9
90°	25.4	79.5	136.1	174.6	187.1
92.5°	32.5	72.3	129.9	166.8	178.3
95°	52.4	91.0	122.2	159.1	169.9
97.5°	79.3	119.9	117.1	150.7	162.2
100°	111.7	146.0	197.7	145.9	152.9
102.5°	144.7	176.4	225.5	257.7	219.4
105°	180.5	207.6	254.1	285.1	295.3
107.5°	217.6	239.3	285.3	316.9	323.9
110°	253.4	272.0	316.5	344.2	355.7



TEST NUMBER: P1026804

CATALOG NUMBER: S125DIP-B1270D610UB2750-4F0-XX-W2A-D_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	288.5	304.2	346.6	372.2	381.9
115°	322.2	335.8	376.7	402.3	408.2
117.5°	357.4	365.2	406.2	429.2	438.9
120°	391.4	395.6	432.9	458.1	464.6
122.5°	420.0	424.3	459.0	482.7	488.6
125°	451.2	453.5	484.5	507.1	513.2
127.5°	479.6	480.9	506.7	528.8	533.6
130°	506.8	508.1	530.4	550.4	555.3
132.5°	532.5	535.9	549.7	571.4	574.8
135°	558.0	559.8	569.6	588.6	593.0
137.5°	581.8	583.6	588.7	607.3	610.7
140°	603.5	604.6	605.6	623.8	626.6
142.5°	624.4	623.5	624.6	638.5	641.3
145°	644.9	644.5	644.5	652.8	655.6
147.5°	661.5	661.5	662.1	665.7	664.9
150°	678.5	677.4	678.5	679.6	676.6
152.5°	694.9	692.1	693.2	694.4	690.4
155°	708.5	705.1	706.3	708.0	703.4
157.5°	719.3	717.6	717.6	719.3	714.8
160°	730.6	727.2	727.8	730.1	725.5
162.5°	739.7	736.3	736.9	740.3	735.2
165°	747.7	744.3	744.8	748.2	743.7
167.5°	753.9	750.5	751.1	755.0	749.9
170°	759.0	755.0	755.6	760.1	755.0
172.5°	762.4	758.4	759.6	763.5	758.4
175°	764.7	761.3	761.8	766.4	761.3
177.5°	766.4	763.0	763.5	767.5	763.0
180°	764.7	764.7	764.7	764.7	764.7

(END OF REPORT)