

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027057

Luminaire Tested: S125RDIP-B1090D1090UB2750-4F0-XX-W2A-A_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027057
REPORT IS A COMBINATION OF REPORTS P1004928 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIP-B1090D1090UB2750-4F0-XX-W2A-A_4000K
Description: Define 5 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8285.0 lumens
Efficiency: N/A
Efficacy: 110.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.4 / 1.47
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 75.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027057

CATALOG NUMBER: S125RDIP-B1090D1090UB2750-4F0-XX-W2A-A_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1027057

CATALOG NUMBER: S125RDIP-B1090D1090UB2750-4F0-XX-W2A-A_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	57	57	57
1	98	94	91	87	91	87	84	81	74	72	70	62	61	59	51	50	49	49	49	44
2	90	83	77	72	83	77	72	67	65	62	58	55	52	50	45	43	42	42	42	37
3	82	73	66	60	76	68	62	57	58	53	50	49	46	43	41	38	36	36	36	32
4	75	65	57	51	69	60	54	48	52	47	42	44	40	37	36	34	31	31	31	28
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	33	30	27	27	27	24
6	64	52	44	38	59	49	41	36	42	36	32	36	31	28	30	27	24	24	24	21
7	59	47	39	34	55	44	37	32	38	33	28	33	28	25	27	24	22	22	22	19
8	55	43	35	30	51	40	33	28	35	29	25	30	25	22	25	22	19	19	19	17
9	51	39	32	27	47	37	30	25	32	26	23	27	23	20	23	20	18	18	18	15
10	48	36	29	24	44	34	27	23	29	24	20	25	21	18	22	18	16	16	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10412	10412	10412	10412
5°	10403	11734	10403	9019
10°	10344	13186	10309	7797
15°	10232	13951	10162	6788
20°	10096	15060	10006	6136
25°	9919	17046	9808	5569
30°	9740	18119	9594	5163
35°	9507	14901	9374	4785
40°	9093	10119	9017	4445
45°	8551	7274	8539	4111
50°	7993	5594	8032	3801
55°	7367	4549	7352	3504
60°	6784	3728	6752	3111
65°	6105	3106	6143	2504
70°	5543	2493	5520	2085
75°	4682	1889	4682	1713
80°	3794	1152	3752	1152
85°	2670	606	2596	685

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 135°

Vertical Angle: 45°

Luminance: 14820 cd/sqm

TEST NUMBER: P1027057

CATALOG NUMBER: S125RDIP-B1090D1090UB2750-4F0-XX-W2A-A_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	155.8	1.9
10°-20°	456.8	5.5
20°-30°	724.4	8.7
30°-40°	875.3	10.6
40°-50°	779.3	9.4
50°-60°	597.6	7.2
60°-70°	388.1	4.7
70°-80°	188.4	2.3
80°-90°	46.3	0.6
90°-100°	45.0	0.5
100°-110°	299.3	3.6
110°-120°	538.9	6.5
120°-130°	691.7	8.3
130°-140°	744.0	9.0
140°-150°	698.2	8.4
150°-160°	564.8	6.8
160°-170°	365.3	4.4
170°-180°	126.0	1.5
0°-30°	1337.0	16.1
0°-40°	2212.3	26.7
0°-60°	3589.2	43.3
0°-90°	4212.0	50.8
90°-120°	883.1	10.7
90°-150°	3017.0	36.4
90°-180°	4073.0	49.2
0°-180°	8285.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1625	1625	1625	1625	1625	
5°	1621	1862	1621	1432	1621	154
15°	1553	2237	1542	1089	1553	438
25°	1420	2679	1404	875	1420	654
35°	1237	2223	1219	714	1237	770
45°	967	994	966	562	967	746
55°	683	546	682	420	683	612
65°	424	310	427	250	424	424
75°	207	144	207	131	207	222
85°	47	31	45	35	47	53
90°	1	24	1	24	1	6
95°	56	21	56	21	56	69
105°	289	292	289	292	289	306
115°	543	539	543	539	543	538
125°	772	772	772	772	772	689
135°	962	958	962	958	962	742
145°	1116	1113	1116	1113	1116	698
155°	1229	1220	1229	1220	1229	566
165°	1296	1290	1296	1290	1296	366
175°	1326	1320	1326	1320	1326	126
180°	1326	1326	1326	1326	1326	

TEST NUMBER: P1027057

CATALOG NUMBER: S125RDIP-B1090D1090UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0
2.5°	1626.3	1639.7	1643.7	1654.3	1666.3	1669.0	1675.7	1685.0	1690.4	1689.0	1689.0
5°	1621.0	1643.7	1659.7	1678.4	1701.0	1710.4	1718.4	1738.4	1754.4	1763.7	1779.7
7.5°	1611.6	1645.0	1671.7	1699.7	1734.4	1750.4	1767.7	1795.8	1825.1	1843.8	1861.1
10°	1597.0	1639.7	1677.0	1718.4	1765.1	1789.1	1810.4	1853.1	1889.1	1913.2	1953.2
12.5°	1575.6	1629.0	1681.0	1735.7	1794.4	1819.8	1849.1	1895.8	1946.5	1981.2	2014.6
15°	1552.9	1617.0	1673.0	1738.4	1809.1	1847.8	1885.1	1934.5	1979.9	2018.6	2057.2
17.5°	1526.3	1594.3	1663.7	1738.4	1818.4	1857.1	1889.1	1947.8	1995.9	2034.6	2069.3
20°	1494.2	1570.3	1649.0	1731.7	1813.1	1849.1	1879.8	1943.8	1986.5	2027.9	2077.3
22.5°	1459.6	1542.3	1626.3	1707.7	1787.7	1826.4	1862.5	1918.5	1965.2	2021.2	2085.3
25°	1419.5	1510.2	1595.6	1677.0	1753.1	1789.1	1821.1	1882.5	1947.8	2018.6	2090.6
27.5°	1379.5	1467.6	1550.3	1625.0	1707.7	1741.1	1773.1	1850.5	1927.8	2002.5	2101.3
30°	1335.5	1424.9	1496.9	1566.3	1646.3	1681.0	1721.0	1809.1	1897.1	1998.5	2118.6
32.5°	1286.1	1367.5	1434.2	1506.2	1578.3	1621.0	1671.7	1767.7	1869.1	1990.5	2144.0
35°	1236.7	1302.1	1363.5	1431.5	1518.3	1563.6	1613.0	1714.4	1841.1	1986.5	2165.3
37.5°	1174.0	1236.7	1284.8	1354.2	1443.5	1496.9	1546.3	1663.7	1807.8	1977.2	2164.0
40°	1110.0	1163.4	1208.7	1280.8	1378.2	1427.5	1480.9	1609.0	1773.1	1950.5	2132.0
42.5°	1040.6	1086.0	1135.4	1204.7	1299.5	1347.5	1408.9	1558.3	1725.0	1913.2	2049.2
45°	967.3	1011.3	1052.6	1124.7	1219.4	1271.4	1338.1	1491.6	1666.3	1834.4	1915.8
47.5°	895.2	933.9	977.9	1040.6	1136.7	1194.1	1262.1	1426.2	1587.6	1729.0	1735.7
50°	825.8	856.5	893.9	957.9	1058.0	1112.7	1183.4	1336.8	1494.2	1591.6	1526.3
52.5°	753.8	781.8	820.5	876.5	969.9	1034.0	1095.3	1248.8	1380.8	1446.2	1326.1
55°	683.1	707.1	747.1	809.8	891.2	940.6	1003.3	1146.0	1262.1	1263.4	1132.7
57.5°	613.7	635.1	668.4	724.4	800.5	857.9	915.2	1039.3	1118.0	1095.3	949.9
60°	552.3	565.7	596.4	651.1	721.8	763.1	824.5	928.6	980.6	939.2	783.1
62.5°	488.3	501.6	525.7	569.7	636.4	680.4	719.1	804.5	840.5	777.8	649.7
65°	424.3	440.3	457.6	492.3	555.0	584.4	619.0	681.7	716.4	643.1	532.3
67.5°	368.2	376.2	393.6	429.6	473.6	500.3	524.3	567.0	573.7	515.0	424.3
70°	316.2	318.9	334.9	356.2	389.6	405.6	425.6	450.9	450.9	402.9	330.9
72.5°	257.5	261.5	273.5	296.2	316.2	324.2	330.9	346.9	344.2	300.2	250.8
75°	206.8	209.5	218.8	229.5	237.5	252.2	257.5	254.8	253.5	216.1	188.1
77.5°	160.1	161.4	168.1	177.4	178.8	184.1	180.1	180.1	168.1	146.8	132.1
80°	117.4	118.7	121.4	124.1	124.1	124.1	124.1	117.4	109.4	96.1	92.1
82.5°	78.7	78.7	80.0	82.7	81.4	78.7	76.0	69.4	64.0	60.0	57.4
85°	46.7	46.7	48.0	46.7	41.4	40.0	37.4	36.0	34.7	33.4	33.4
87.5°	22.7	21.3	18.7	16.0	16.0	16.0	16.0	16.0	16.0	14.7	14.7
90°	1.0	2.7	4.5	6.2	7.9	8.8	9.6	11.1	12.6	14.2	15.7
92.5°	18.7	16.7	14.7	12.8	10.8	9.8	10.5	11.8	13.1	14.4	15.7
95°	56.0	55.4	54.7	54.1	53.4	53.1	48.9	40.6	32.3	24.0	15.7
97.5°	105.2	106.5	107.8	109.1	110.4	111.1	100.7	80.0	59.2	38.5	17.7
100°	164.1	164.8	165.4	166.1	166.8	167.1	167.5	168.4	169.3	170.1	171.0
102.5°	224.1	225.0	225.8	226.7	227.6	228.0	228.2	228.7	229.1	229.6	230.0
105°	289.0	289.9	290.7	291.6	292.5	292.9	292.9	292.9	292.9	292.9	292.9
107.5°	355.8	355.8	355.8	355.8	355.8	355.8	356.0	356.5	356.9	357.4	357.8
110°	420.7	420.7	420.7	420.7	420.7	420.7	420.9	421.4	421.8	422.3	422.7

TEST NUMBER: P1027057

CATALOG NUMBER: S125RDIP-B1090D1090UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	481.6	482.3	482.9	483.6	484.3	484.6	484.7	484.9	485.2	485.4	485.6
115°	542.6	543.7	544.8	545.9	547.0	547.5	547.6	547.8	548.1	548.3	548.5
117.5°	606.5	606.5	606.5	606.5	606.5	606.5	606.9	607.8	608.7	609.5	610.4
120°	665.4	665.2	665.0	664.7	664.5	664.4	664.7	665.4	666.1	666.7	667.4
122.5°	717.5	718.6	719.7	720.8	721.9	722.4	722.5	722.7	723.0	723.2	723.4
125°	771.6	773.1	774.7	776.2	777.7	778.5	778.5	778.5	778.5	778.5	778.5
127.5°	823.7	824.8	825.9	827.0	828.1	828.6	828.5	828.3	828.0	827.8	827.6
130°	870.9	872.0	873.1	874.2	875.3	875.8	875.9	876.1	876.4	876.6	876.8
132.5°	918.0	919.3	920.6	921.9	923.2	923.9	923.6	922.9	922.3	921.6	921.0
135°	962.3	963.6	964.9	966.2	967.5	968.2	968.0	967.5	967.1	966.6	966.2
137.5°	1003.6	1004.9	1006.2	1007.5	1008.8	1009.5	1009.3	1008.8	1008.4	1007.9	1007.5
140°	1043.9	1044.3	1044.7	1045.2	1045.6	1045.8	1045.7	1045.5	1045.2	1045.0	1044.8
142.5°	1080.2	1080.4	1080.6	1080.9	1081.1	1081.2	1081.4	1081.9	1082.3	1082.8	1083.2
145°	1115.6	1116.0	1116.5	1116.9	1117.4	1117.6	1117.6	1117.6	1117.6	1117.6	1117.6
147.5°	1147.1	1147.1	1147.1	1147.1	1147.1	1147.1	1147.2	1147.4	1147.6	1147.8	1148.0
150°	1176.5	1176.1	1175.7	1175.2	1174.8	1174.6	1174.8	1175.2	1175.7	1176.1	1176.5
152.5°	1205.1	1204.0	1202.9	1201.8	1200.7	1200.1	1200.3	1200.8	1201.2	1201.7	1202.1
155°	1228.6	1227.3	1226.0	1224.7	1223.4	1222.7	1222.9	1223.4	1223.8	1224.3	1224.7
157.5°	1247.3	1246.7	1246.0	1245.4	1244.7	1244.4	1244.4	1244.4	1244.4	1244.4	1244.4
160°	1267.0	1265.7	1264.4	1263.1	1261.8	1261.1	1261.2	1261.4	1261.7	1261.9	1262.1
162.5°	1282.7	1281.4	1280.1	1278.8	1277.5	1276.8	1276.9	1277.1	1277.4	1277.6	1277.8
165°	1296.5	1295.2	1293.9	1292.6	1291.3	1290.6	1290.7	1290.9	1291.1	1291.3	1291.5
167.5°	1307.3	1306.0	1304.7	1303.4	1302.1	1301.4	1301.5	1301.7	1302.0	1302.2	1302.4
170°	1316.1	1314.6	1313.0	1311.5	1310.0	1309.2	1309.3	1309.5	1309.8	1310.0	1310.2
172.5°	1322.0	1320.5	1318.9	1317.4	1315.9	1315.1	1315.3	1315.8	1316.2	1316.7	1317.1
175°	1325.9	1324.6	1323.3	1322.0	1320.7	1320.1	1320.2	1320.4	1320.6	1320.8	1321.0
177.5°	1328.9	1327.6	1326.3	1325.0	1323.7	1323.0	1323.1	1323.3	1323.6	1323.8	1324.0
180°	1325.9	1325.9	1325.9	1325.9	1325.9	1325.9	1325.9	1325.9	1325.9	1325.9	1325.9

TEST NUMBER: P1027057

CATALOG NUMBER: S125RDIP-B1090D1090UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0
2.5°	1695.7	1705.0	1713.0	1709.0	1725.0	1723.7	1726.4	1731.7	1733.0	1730.4	1725.0
5°	1787.7	1801.1	1823.8	1835.8	1833.1	1843.8	1849.1	1857.1	1865.1	1862.5	1862.5
7.5°	1890.5	1909.2	1931.8	1962.5	1966.5	1975.9	1991.9	1991.9	2001.2	1997.2	1995.9
10°	1979.9	2002.5	2038.6	2062.6	2073.3	2078.6	2094.6	2099.9	2110.6	2111.9	2111.9
12.5°	2053.2	2093.3	2117.3	2141.3	2146.6	2154.6	2166.6	2174.7	2178.7	2178.7	2174.7
15°	2091.9	2124.0	2152.0	2177.3	2192.0	2198.7	2210.7	2220.0	2225.3	2237.4	2240.0
17.5°	2107.9	2146.6	2192.0	2228.0	2253.4	2260.0	2284.1	2292.1	2302.7	2308.1	2314.7
20°	2130.6	2186.7	2241.4	2285.4	2309.4	2326.7	2352.1	2389.4	2400.1	2400.1	2396.1
22.5°	2150.6	2222.7	2297.4	2368.1	2388.1	2422.8	2469.5	2509.5	2525.5	2532.2	2526.9
25°	2174.7	2273.4	2370.8	2458.8	2513.5	2538.9	2601.6	2649.6	2668.3	2679.0	2681.6
27.5°	2216.0	2340.1	2464.2	2576.2	2632.3	2661.6	2727.0	2768.3	2791.0	2800.4	2793.7
30°	2262.7	2414.8	2558.9	2658.9	2696.3	2732.3	2775.0	2791.0	2785.7	2785.7	2805.7
32.5°	2310.7	2468.2	2596.2	2661.6	2675.0	2669.6	2652.3	2604.2	2576.2	2576.2	2593.6
35°	2337.4	2473.5	2538.9	2517.5	2465.5	2434.8	2340.1	2286.7	2226.7	2222.7	2242.7
37.5°	2322.7	2381.4	2354.8	2214.7	2144.0	2085.3	1937.2	1878.5	1834.4	1773.1	1867.8
40°	2220.0	2200.0	2061.2	1859.8	1781.1	1698.4	1581.0	1522.3	1460.9	1451.5	1474.2
42.5°	2046.6	1927.8	1725.0	1530.3	1450.2	1391.5	1302.1	1244.8	1206.1	1190.1	1216.7
45°	1830.4	1643.7	1440.9	1286.1	1198.1	1167.4	1086.0	1035.3	1005.9	993.9	1012.6
47.5°	1566.3	1378.2	1186.1	1055.3	1003.3	972.6	917.9	873.9	848.5	840.5	848.5
50°	1330.1	1136.7	975.3	891.2	844.5	819.2	773.8	745.8	725.8	720.4	733.8
52.5°	1126.0	949.9	827.2	752.5	721.8	700.4	668.4	644.4	632.4	627.0	636.4
55°	943.2	800.5	701.8	637.7	615.0	601.7	573.7	560.3	547.0	545.7	555.0
57.5°	781.8	683.1	592.4	547.0	540.3	520.3	496.3	484.3	477.6	476.3	480.3
60°	651.1	563.0	508.3	468.3	458.9	442.9	429.6	421.6	413.6	410.9	413.6
62.5°	541.7	472.3	428.3	401.6	388.2	384.2	369.6	360.2	358.9	358.9	361.6
65°	446.9	388.2	360.2	338.9	329.5	325.5	314.9	308.2	309.5	309.5	310.9
67.5°	364.2	321.5	296.2	285.5	277.5	276.2	265.5	262.8	260.2	260.2	262.8
70°	289.5	262.8	244.1	238.8	237.5	228.1	224.1	222.8	218.8	220.1	220.1
72.5°	226.8	209.5	198.8	190.8	192.1	186.8	181.4	181.4	178.8	182.8	182.8
75°	168.1	160.1	152.1	149.4	152.1	149.4	145.4	144.1	145.4	144.1	144.1
77.5°	124.1	120.1	117.4	116.1	116.1	110.7	108.1	110.7	105.4	108.1	108.1
80°	86.7	81.4	80.0	77.4	78.7	74.7	76.0	73.4	73.4	73.4	73.4
82.5°	54.7	53.4	53.4	53.4	52.0	52.0	52.0	52.0	52.0	52.0	50.7
85°	33.4	32.0	32.0	32.0	30.7	30.7	30.7	30.7	30.7	30.7	30.7
87.5°	13.3	14.7	14.7	16.0	14.7	13.3	13.3	13.3	14.7	14.7	13.3
90°	16.8	17.9	19.0	20.1	20.6	20.9	21.6	22.3	22.9	23.6	22.9
92.5°	16.8	17.9	19.0	20.1	20.6	20.7	20.9	21.2	21.4	21.6	21.4
95°	16.8	17.9	19.0	20.1	20.6	20.6	20.6	20.6	20.6	20.6	20.6
97.5°	18.1	18.6	19.0	19.5	19.7	19.8	20.0	20.2	20.4	20.6	20.4
100°	138.5	105.9	73.4	40.9	24.6	24.2	23.3	22.4	21.5	20.6	21.5
102.5°	230.4	230.9	231.3	231.8	232.0	222.8	204.5	186.1	167.8	149.4	167.8
105°	292.9	292.9	292.9	292.9	292.9	292.8	292.6	292.3	292.1	291.9	292.1
107.5°	358.0	358.2	358.5	358.7	358.8	358.4	357.5	356.6	355.7	354.8	355.7
110°	422.0	421.4	420.7	420.0	419.7	419.8	420.0	420.3	420.5	420.7	420.5

TEST NUMBER: P1027057

CATALOG NUMBER: S125RDIP-B1090D1090UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	484.7	483.8	482.9	482.0	481.6	481.4	481.0	480.5	480.1	479.7	480.1
115°	547.6	546.7	545.8	544.9	544.5	543.8	542.5	541.2	539.9	538.6	539.9
117.5°	609.1	607.8	606.5	605.2	604.5	604.3	603.8	603.4	602.9	602.5	602.9
120°	667.0	666.5	666.1	665.6	665.4	664.9	663.8	662.7	661.6	660.5	661.6
122.5°	723.0	722.6	722.1	721.7	721.5	720.8	719.5	718.2	716.9	715.6	716.9
125°	777.6	776.7	775.8	774.9	774.5	774.2	773.5	772.9	772.2	771.6	772.2
127.5°	827.2	826.7	826.3	825.8	825.6	824.7	823.0	821.3	819.5	817.8	819.5
130°	876.1	875.5	874.8	874.1	873.8	873.3	872.2	871.1	870.0	868.9	870.0
132.5°	921.0	921.0	921.0	921.0	921.0	920.5	919.4	918.3	917.2	916.1	917.2
135°	965.8	965.3	964.9	964.4	964.2	963.5	962.2	960.9	959.6	958.3	959.6
137.5°	1007.5	1007.5	1007.5	1007.5	1007.5	1007.0	1005.9	1004.8	1003.7	1002.6	1003.7
140°	1045.2	1045.7	1046.1	1046.6	1046.8	1046.1	1044.8	1043.5	1042.2	1040.9	1042.2
142.5°	1083.2	1083.2	1083.2	1083.2	1083.2	1082.5	1081.2	1079.9	1078.6	1077.3	1078.6
145°	1117.8	1118.0	1118.3	1118.5	1118.6	1117.9	1116.6	1115.3	1114.0	1112.7	1114.0
147.5°	1148.2	1148.4	1148.7	1148.9	1149.0	1148.2	1146.7	1145.2	1143.6	1142.1	1143.6
150°	1176.9	1177.4	1177.8	1178.3	1178.5	1177.6	1175.9	1174.1	1172.4	1170.6	1172.4
152.5°	1202.5	1203.0	1203.4	1203.9	1204.1	1203.3	1201.8	1200.3	1198.7	1197.2	1198.7
155°	1225.4	1226.0	1226.7	1227.4	1227.7	1226.8	1225.1	1223.3	1221.6	1219.8	1221.6
157.5°	1245.0	1245.7	1246.3	1247.0	1247.3	1246.4	1244.7	1243.0	1241.2	1239.5	1241.2
160°	1263.0	1263.8	1264.7	1265.6	1266.0	1265.1	1263.4	1261.6	1259.9	1258.1	1259.9
162.5°	1279.1	1280.4	1281.7	1283.0	1283.7	1282.7	1280.7	1278.8	1276.8	1274.8	1276.8
165°	1292.8	1294.1	1295.4	1296.7	1297.4	1296.5	1294.8	1293.1	1291.3	1289.6	1291.3
167.5°	1303.9	1305.4	1306.9	1308.4	1309.2	1308.2	1306.3	1304.3	1302.4	1300.4	1302.4
170°	1312.0	1313.7	1315.5	1317.2	1318.1	1317.1	1315.1	1313.2	1311.2	1309.2	1311.2
172.5°	1318.6	1320.2	1321.7	1323.2	1324.0	1323.0	1321.0	1319.1	1317.1	1315.1	1317.1
175°	1322.8	1324.5	1326.3	1328.0	1328.9	1327.9	1326.0	1324.0	1322.1	1320.1	1322.1
177.5°	1325.5	1327.1	1328.6	1330.1	1330.9	1330.0	1328.3	1326.5	1324.8	1323.0	1324.8
180°	1325.9	1325.9	1325.9	1325.9	1325.9	1325.9	1325.9	1325.9	1325.9	1325.9	1325.9

TEST NUMBER: P1027057

CATALOG NUMBER: S125RDIP-B1090D1090UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0
2.5°	1731.7	1722.4	1726.4	1722.4	1718.4	1714.4	1705.0	1691.7	1681.0	1673.0	1671.7
5°	1865.1	1853.1	1845.1	1841.1	1833.1	1822.4	1805.1	1785.1	1761.1	1751.7	1733.0
7.5°	1987.9	1983.9	1965.2	1962.5	1957.2	1937.2	1907.8	1881.1	1850.5	1825.1	1801.1
10°	2103.9	2094.6	2081.3	2062.6	2059.9	2034.6	2006.5	1969.2	1929.2	1905.2	1862.5
12.5°	2176.0	2165.3	2150.6	2138.6	2132.0	2115.9	2077.3	2039.9	2003.9	1959.9	1922.5
15°	2228.0	2214.7	2188.0	2178.7	2170.6	2149.3	2121.3	2082.6	2034.6	2003.9	1950.5
17.5°	2298.7	2282.7	2256.0	2238.7	2224.0	2190.7	2150.6	2098.6	2053.2	2018.6	1970.5
20°	2380.1	2356.1	2321.4	2298.7	2277.4	2238.7	2182.7	2121.3	2055.9	2013.2	1963.9
22.5°	2514.9	2469.5	2414.8	2382.8	2353.4	2286.7	2220.0	2144.0	2070.6	2006.5	1946.5
25°	2645.6	2600.2	2532.2	2488.2	2442.8	2365.4	2277.4	2172.0	2078.6	2003.9	1925.2
27.5°	2767.0	2720.3	2657.6	2604.2	2560.2	2444.1	2328.1	2209.3	2090.6	1987.9	1907.8
30°	2795.0	2775.0	2727.0	2680.3	2640.3	2533.5	2398.8	2248.0	2105.3	1973.2	1883.8
32.5°	2625.6	2675.0	2687.0	2680.3	2654.9	2578.9	2454.8	2296.1	2126.6	1966.5	1843.8
35°	2273.4	2362.8	2454.8	2504.2	2528.2	2538.9	2465.5	2320.1	2141.3	1955.9	1817.1
37.5°	1885.1	1971.9	2117.3	2190.7	2272.0	2378.8	2408.1	2314.7	2134.6	1947.8	1774.4
40°	1548.9	1659.7	1779.7	1846.5	1917.2	2109.3	2254.7	2244.0	2113.3	1918.5	1741.1
42.5°	1260.8	1330.1	1435.5	1508.9	1595.6	1810.4	2005.2	2101.3	2049.2	1882.5	1698.4
45°	1051.3	1104.7	1179.4	1254.1	1307.5	1502.2	1733.0	1890.5	1939.8	1818.4	1633.0
47.5°	885.9	925.9	991.3	1038.0	1095.3	1248.8	1448.9	1670.3	1774.4	1727.7	1563.6
50°	759.1	791.1	843.2	872.5	923.2	1055.3	1207.4	1439.5	1597.0	1602.3	1471.6
52.5°	648.4	680.4	724.4	749.8	780.5	869.9	1023.3	1219.4	1400.8	1467.6	1366.2
55°	564.3	583.0	619.0	639.1	667.1	753.8	851.2	1017.9	1207.4	1316.8	1252.8
57.5°	487.0	507.0	529.7	545.7	565.7	635.1	723.1	848.5	1036.6	1155.4	1134.0
60°	424.3	436.3	457.6	469.6	488.3	533.7	595.0	720.4	869.9	981.9	993.9
62.5°	365.6	376.2	390.9	401.6	413.6	449.6	495.0	584.4	715.1	836.5	852.5
65°	314.9	324.2	332.2	341.5	350.9	373.6	412.2	481.6	583.0	696.4	731.1
67.5°	269.5	272.2	284.2	285.5	290.8	308.2	336.2	392.2	465.6	556.3	601.7
70°	225.5	230.8	233.5	237.5	242.8	254.8	277.5	306.9	361.6	434.9	477.6
72.5°	182.8	184.1	188.1	190.8	196.1	205.5	216.1	238.8	273.5	326.9	365.6
75°	145.4	146.8	149.4	150.8	154.8	157.4	162.8	178.8	202.8	234.8	262.8
77.5°	109.4	112.1	114.7	114.7	116.1	118.7	121.4	126.7	138.8	160.1	184.1
80°	74.7	76.0	76.0	77.4	76.0	80.0	84.1	90.7	96.1	102.7	114.7
82.5°	52.0	52.0	52.0	53.4	53.4	54.7	54.7	56.0	57.4	61.4	66.7
85°	32.0	32.0	33.4	30.7	32.0	33.4	33.4	32.0	33.4	34.7	36.0
87.5°	13.3	13.3	14.7	14.7	14.7	14.7	13.3	14.7	13.3	14.7	14.7
90°	22.3	21.6	20.9	20.6	20.1	19.0	17.9	16.8	15.7	14.2	12.6
92.5°	21.2	20.9	20.7	20.6	20.1	19.0	17.9	16.8	15.7	14.4	13.1
95°	20.6	20.6	20.6	20.6	20.1	19.0	17.9	16.8	15.7	24.0	32.3
97.5°	20.2	20.0	19.8	19.7	19.5	19.0	18.6	18.1	17.7	38.5	59.2
100°	22.4	23.3	24.2	24.6	40.9	73.4	105.9	138.5	171.0	170.1	169.3
102.5°	186.1	204.5	222.8	232.0	231.8	231.3	230.9	230.4	230.0	229.6	229.1
105°	292.3	292.6	292.8	292.9	292.9	292.9	292.9	292.9	292.9	292.9	292.9
107.5°	356.6	357.5	358.4	358.8	358.7	358.5	358.2	358.0	357.8	357.4	356.9
110°	420.3	420.0	419.8	419.7	420.0	420.7	421.4	422.0	422.7	422.3	421.8

TEST NUMBER: P1027057

CATALOG NUMBER: S125RDIP-B1090D1090UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	480.5	481.0	481.4	481.6	482.0	482.9	483.8	484.7	485.6	485.4	485.2
115°	541.2	542.5	543.8	544.5	544.9	545.8	546.7	547.6	548.5	548.3	548.1
117.5°	603.4	603.8	604.3	604.5	605.2	606.5	607.8	609.1	610.4	609.5	608.7
120°	662.7	663.8	664.9	665.4	665.6	666.1	666.5	667.0	667.4	666.7	666.1
122.5°	718.2	719.5	720.8	721.5	721.7	722.1	722.6	723.0	723.4	723.2	723.0
125°	772.9	773.5	774.2	774.5	774.9	775.8	776.7	777.6	778.5	778.5	778.5
127.5°	821.3	823.0	824.7	825.6	825.8	826.3	826.7	827.2	827.6	827.8	828.0
130°	871.1	872.2	873.3	873.8	874.1	874.8	875.5	876.1	876.8	876.6	876.4
132.5°	918.3	919.4	920.5	921.0	921.0	921.0	921.0	921.0	921.0	921.6	922.3
135°	960.9	962.2	963.5	964.2	964.4	964.9	965.3	965.8	966.2	966.6	967.1
137.5°	1004.8	1005.9	1007.0	1007.5	1007.5	1007.5	1007.5	1007.5	1007.5	1007.9	1008.4
140°	1043.5	1044.8	1046.1	1046.8	1046.6	1046.1	1045.7	1045.2	1044.8	1045.0	1045.2
142.5°	1079.9	1081.2	1082.5	1083.2	1083.2	1083.2	1083.2	1083.2	1083.2	1082.8	1082.3
145°	1115.3	1116.6	1117.9	1118.6	1118.5	1118.3	1118.0	1117.8	1117.6	1117.6	1117.6
147.5°	1145.2	1146.7	1148.2	1149.0	1148.9	1148.7	1148.4	1148.2	1148.0	1147.8	1147.6
150°	1174.1	1175.9	1177.6	1178.5	1178.3	1177.8	1177.4	1176.9	1176.5	1176.1	1175.7
152.5°	1200.3	1201.8	1203.3	1204.1	1203.9	1203.4	1203.0	1202.5	1202.1	1201.7	1201.2
155°	1223.3	1225.1	1226.8	1227.7	1227.4	1226.7	1226.0	1225.4	1224.7	1224.3	1223.8
157.5°	1243.0	1244.7	1246.4	1247.3	1247.0	1246.3	1245.7	1245.0	1244.4	1244.4	1244.4
160°	1261.6	1263.4	1265.1	1266.0	1265.6	1264.7	1263.8	1263.0	1262.1	1261.9	1261.7
162.5°	1278.8	1280.7	1282.7	1283.7	1283.0	1281.7	1280.4	1279.1	1277.8	1277.6	1277.4
165°	1293.1	1294.8	1296.5	1297.4	1296.7	1295.4	1294.1	1292.8	1291.5	1291.3	1291.1
167.5°	1304.3	1306.3	1308.2	1309.2	1308.4	1306.9	1305.4	1303.9	1302.4	1302.2	1302.0
170°	1313.2	1315.1	1317.1	1318.1	1317.2	1315.5	1313.7	1312.0	1310.2	1310.0	1309.8
172.5°	1319.1	1321.0	1323.0	1324.0	1323.2	1321.7	1320.2	1318.6	1317.1	1316.7	1316.2
175°	1324.0	1326.0	1327.9	1328.9	1328.0	1326.3	1324.5	1322.8	1321.0	1320.8	1320.6
177.5°	1326.5	1328.3	1330.0	1330.9	1330.1	1328.6	1327.1	1325.5	1324.0	1323.8	1323.6
180°	1325.9	1325.9	1325.9	1325.9	1325.9	1325.9	1325.9	1325.9	1325.9	1325.9	1325.9

TEST NUMBER: P1027057

CATALOG NUMBER: S125RDIP-B1090D1090UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0
2.5°	1667.7	1659.7	1654.3	1653.0	1645.0	1638.3	1630.3	1629.0	1625.0	1614.3	1607.6
5°	1719.7	1701.0	1697.0	1685.0	1665.0	1650.3	1631.7	1621.0	1609.0	1589.0	1573.0
7.5°	1773.1	1747.7	1729.0	1711.7	1683.7	1657.0	1630.3	1609.0	1587.6	1558.3	1534.3
10°	1825.1	1786.4	1763.7	1738.4	1699.7	1659.7	1622.3	1591.6	1556.9	1522.3	1487.6
12.5°	1873.1	1823.8	1790.4	1754.4	1706.4	1657.0	1609.0	1566.3	1530.3	1483.6	1444.9
15°	1902.5	1847.8	1814.4	1779.7	1707.7	1653.0	1597.0	1542.3	1494.2	1444.9	1408.9
17.5°	1919.8	1858.5	1821.1	1789.1	1715.7	1641.0	1569.0	1510.2	1458.2	1399.5	1351.5
20°	1911.8	1851.8	1817.1	1786.4	1701.0	1626.3	1548.9	1480.9	1415.5	1355.5	1304.8
22.5°	1894.5	1831.8	1793.1	1765.1	1689.0	1601.0	1515.6	1442.2	1374.2	1314.1	1256.8
25°	1857.1	1795.8	1762.4	1727.7	1653.0	1569.0	1482.2	1403.5	1331.5	1267.4	1203.4
27.5°	1823.8	1749.1	1714.4	1683.7	1605.0	1530.3	1444.9	1358.2	1284.8	1218.1	1154.0
30°	1785.1	1701.0	1663.7	1622.3	1551.6	1480.9	1395.5	1315.5	1239.4	1168.7	1107.3
32.5°	1743.7	1646.3	1603.6	1556.9	1484.9	1418.2	1346.1	1267.4	1191.4	1122.0	1058.0
35°	1690.4	1586.3	1536.9	1492.9	1418.2	1351.5	1284.8	1219.4	1143.4	1070.0	1008.6
37.5°	1639.7	1524.9	1472.9	1422.2	1343.5	1279.4	1224.7	1163.4	1090.0	1019.3	960.6
40°	1582.3	1450.2	1396.8	1350.2	1268.8	1198.1	1148.7	1100.7	1036.6	968.6	904.5
42.5°	1530.3	1380.8	1324.8	1276.8	1191.4	1124.7	1078.0	1038.0	981.9	919.2	853.9
45°	1458.2	1306.1	1248.8	1198.1	1111.3	1048.6	1000.6	965.9	921.9	863.2	804.5
47.5°	1391.5	1234.1	1171.4	1110.0	1031.3	967.3	923.2	896.5	867.2	815.2	755.1
50°	1310.1	1151.4	1087.3	1036.6	947.2	892.5	848.5	829.8	803.2	753.8	705.8
52.5°	1222.1	1071.3	1011.3	949.9	867.2	813.8	775.1	753.8	732.4	696.4	651.1
55°	1119.3	981.9	925.9	871.2	788.5	739.1	704.4	681.7	669.7	636.4	603.0
57.5°	1020.6	891.2	839.2	788.5	716.4	660.4	637.7	617.7	600.4	576.3	548.3
60°	920.6	803.2	747.1	701.8	639.1	588.4	569.7	549.7	536.3	517.6	497.6
62.5°	805.8	705.8	663.1	620.4	567.0	527.0	505.6	489.6	472.3	460.3	442.9
65°	684.4	613.7	572.3	540.3	489.6	453.6	437.6	426.9	412.2	400.2	386.9
67.5°	571.0	515.0	497.6	462.9	424.3	392.2	380.2	366.9	354.9	348.2	336.2
70°	461.6	421.6	404.2	394.9	352.2	330.9	320.2	314.9	300.2	293.5	285.5
72.5°	357.5	342.9	330.9	318.9	290.8	277.5	265.5	260.2	249.5	244.1	241.5
75°	264.2	254.8	248.2	246.8	234.8	221.5	209.5	206.8	198.8	193.5	190.8
77.5°	185.4	182.8	181.4	182.8	174.8	166.8	164.1	161.4	152.1	150.8	150.8
80°	121.4	128.1	128.1	126.7	124.1	122.7	118.7	116.1	110.7	109.4	110.7
82.5°	74.7	78.7	80.0	82.7	81.4	80.0	77.4	76.0	77.4	74.7	76.0
85°	37.4	40.0	45.4	45.4	46.7	46.7	46.7	45.4	42.7	44.0	42.7
87.5°	14.7	16.0	16.0	16.0	14.7	18.7	20.0	20.0	20.0	17.3	17.3
90°	11.1	9.6	8.8	7.9	6.2	4.5	2.7	1.0	2.7	4.5	6.2
92.5°	11.8	10.5	9.8	10.8	12.8	14.7	16.7	18.7	16.7	14.7	12.8
95°	40.6	48.9	53.1	53.4	54.1	54.7	55.4	56.0	55.4	54.7	54.1
97.5°	80.0	100.7	111.1	110.4	109.1	107.8	106.5	105.2	106.5	107.8	109.1
100°	168.4	167.5	167.1	166.8	166.1	165.4	164.8	164.1	164.8	165.4	166.1
102.5°	228.7	228.2	228.0	227.6	226.7	225.8	225.0	224.1	225.0	225.8	226.7
105°	292.9	292.9	292.9	292.5	291.6	290.7	289.9	289.0	289.9	290.7	291.6
107.5°	356.5	356.0	355.8	355.8	355.8	355.8	355.8	355.8	355.8	355.8	355.8
110°	421.4	420.9	420.7	420.7	420.7	420.7	420.7	420.7	420.7	420.7	420.7

TEST NUMBER: P1027057

CATALOG NUMBER: S125RDIP-B1090D1090UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	484.9	484.7	484.6	484.3	483.6	482.9	482.3	481.6	482.3	482.9	483.6
115°	547.8	547.6	547.5	547.0	545.9	544.8	543.7	542.6	543.7	544.8	545.9
117.5°	607.8	606.9	606.5	606.5	606.5	606.5	606.5	606.5	606.5	606.5	606.5
120°	665.4	664.7	664.4	664.5	664.7	665.0	665.2	665.4	665.2	665.0	664.7
122.5°	722.7	722.5	722.4	721.9	720.8	719.7	718.6	717.5	718.6	719.7	720.8
125°	778.5	778.5	778.5	777.7	776.2	774.7	773.1	771.6	773.1	774.7	776.2
127.5°	828.3	828.5	828.6	828.1	827.0	825.9	824.8	823.7	824.8	825.9	827.0
130°	876.1	875.9	875.8	875.3	874.2	873.1	872.0	870.9	872.0	873.1	874.2
132.5°	922.9	923.6	923.9	923.2	921.9	920.6	919.3	918.0	919.3	920.6	921.9
135°	967.5	968.0	968.2	967.5	966.2	964.9	963.6	962.3	963.6	964.9	966.2
137.5°	1008.8	1009.3	1009.5	1008.8	1007.5	1006.2	1004.9	1003.6	1004.9	1006.2	1007.5
140°	1045.5	1045.7	1045.8	1045.6	1045.2	1044.7	1044.3	1043.9	1044.3	1044.7	1045.2
142.5°	1081.9	1081.4	1081.2	1081.1	1080.9	1080.6	1080.4	1080.2	1080.4	1080.6	1080.9
145°	1117.6	1117.6	1117.6	1117.4	1116.9	1116.5	1116.0	1115.6	1116.0	1116.5	1116.9
147.5°	1147.4	1147.2	1147.1	1147.1	1147.1	1147.1	1147.1	1147.1	1147.1	1147.1	1147.1
150°	1175.2	1174.8	1174.6	1174.8	1175.2	1175.7	1176.1	1176.5	1176.1	1175.7	1175.2
152.5°	1200.8	1200.3	1200.1	1200.7	1201.8	1202.9	1204.0	1205.1	1204.0	1202.9	1201.8
155°	1223.4	1222.9	1222.7	1223.4	1224.7	1226.0	1227.3	1228.6	1227.3	1226.0	1224.7
157.5°	1244.4	1244.4	1244.4	1244.7	1245.4	1246.0	1246.7	1247.3	1246.7	1246.0	1245.4
160°	1261.4	1261.2	1261.1	1261.8	1263.1	1264.4	1265.7	1267.0	1265.7	1264.4	1263.1
162.5°	1277.1	1276.9	1276.8	1277.5	1278.8	1280.1	1281.4	1282.7	1281.4	1280.1	1278.8
165°	1290.9	1290.7	1290.6	1291.3	1292.6	1293.9	1295.2	1296.5	1295.2	1293.9	1292.6
167.5°	1301.7	1301.5	1301.4	1302.1	1303.4	1304.7	1306.0	1307.3	1306.0	1304.7	1303.4
170°	1309.5	1309.3	1309.2	1310.0	1311.5	1313.0	1314.6	1316.1	1314.6	1313.0	1311.5
172.5°	1315.8	1315.3	1315.1	1315.9	1317.4	1318.9	1320.5	1322.0	1320.5	1318.9	1317.4
175°	1320.4	1320.2	1320.1	1320.7	1322.0	1323.3	1324.6	1325.9	1324.6	1323.3	1322.0
177.5°	1323.3	1323.1	1323.0	1323.7	1325.0	1326.3	1327.6	1328.9	1327.6	1326.3	1325.0
180°	1325.9	1325.9	1325.9	1325.9	1325.9	1325.9	1325.9	1325.9	1325.9	1325.9	1325.9

TEST NUMBER: P1027057

CATALOG NUMBER: S125RDIP-B1090D1090UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0
2.5°	1603.6	1598.3	1594.3	1590.3	1573.0	1554.3	1551.6	1547.6	1539.6	1548.9	1544.9
5°	1562.3	1550.3	1543.6	1526.3	1504.9	1488.9	1475.6	1459.6	1452.9	1447.5	1446.2
7.5°	1511.6	1500.9	1488.9	1471.6	1444.9	1418.2	1398.2	1382.2	1368.8	1362.2	1362.2
10°	1462.2	1448.9	1432.9	1403.5	1378.2	1344.8	1323.5	1307.5	1288.8	1278.1	1268.8
12.5°	1411.5	1396.8	1382.2	1344.8	1315.5	1280.8	1250.1	1230.1	1220.7	1208.7	1192.7
15°	1360.8	1338.1	1323.5	1286.1	1248.8	1214.1	1194.1	1172.7	1151.4	1139.4	1134.0
17.5°	1307.5	1291.4	1267.4	1227.4	1186.1	1155.4	1126.0	1106.0	1080.7	1068.6	1056.6
20°	1259.4	1235.4	1211.4	1171.4	1131.4	1090.0	1060.6	1036.6	1020.6	1011.3	1000.6
22.5°	1202.1	1179.4	1159.4	1116.7	1072.6	1034.0	1001.9	987.3	971.3	956.6	945.9
25°	1152.7	1130.0	1110.0	1063.3	1015.3	979.3	955.2	936.6	919.2	912.6	901.9
27.5°	1100.7	1079.3	1052.6	1005.9	963.3	932.6	907.2	889.9	876.5	863.2	855.2
30°	1051.3	1027.3	1003.3	952.6	917.9	887.2	863.2	841.8	831.2	824.5	811.2
32.5°	1003.3	972.6	952.6	905.9	872.5	843.2	823.2	804.5	791.1	779.1	768.5
35°	951.2	917.9	897.9	859.2	824.5	795.1	777.8	764.5	748.5	737.8	732.4
37.5°	901.9	873.9	853.9	813.8	779.1	755.1	736.4	719.1	712.4	697.8	695.1
40°	848.5	824.5	805.8	767.1	735.1	716.4	696.4	680.4	668.4	661.7	652.4
42.5°	800.5	780.5	760.5	724.4	693.8	671.1	656.4	641.7	631.0	620.4	613.7
45°	756.5	735.1	716.4	681.7	651.1	631.0	616.4	599.0	596.4	581.7	575.0
47.5°	709.8	691.1	675.1	639.1	611.0	591.0	573.7	561.7	549.7	544.3	535.0
50°	664.4	645.7	627.0	595.0	569.7	549.7	532.3	519.0	512.3	504.3	496.3
52.5°	615.0	600.4	585.7	552.3	527.0	509.6	495.0	477.6	471.0	464.3	458.9
55°	573.7	552.3	536.3	508.3	485.6	466.9	450.9	437.6	430.9	425.6	418.9
57.5°	517.6	504.3	491.0	465.6	444.3	425.6	409.6	398.9	390.9	386.9	388.2
60°	469.6	454.9	446.9	420.3	398.9	384.2	369.6	358.9	350.9	346.9	345.5
62.5°	418.9	408.2	393.6	374.9	353.5	340.2	329.5	321.5	308.2	306.9	302.9
65°	369.6	361.6	348.2	330.9	313.5	301.5	289.5	278.8	273.5	266.8	262.8
67.5°	321.5	313.5	301.5	286.8	274.8	262.8	252.2	241.5	232.1	226.8	224.1
70°	274.8	268.2	260.2	242.8	228.1	218.8	210.8	204.1	194.8	192.1	190.8
72.5°	229.5	222.8	218.8	204.1	190.8	182.8	174.8	168.1	164.1	162.8	158.8
75°	188.1	181.4	176.1	162.8	154.8	149.4	141.4	138.8	134.7	133.4	132.1
77.5°	146.8	140.1	138.8	129.4	120.1	117.4	114.7	109.4	109.4	109.4	106.7
80°	105.4	104.1	102.7	93.4	89.4	86.7	85.4	81.4	78.7	76.0	74.7
82.5°	70.7	69.4	68.0	64.0	60.0	58.7	57.4	54.7	54.7	56.0	53.4
85°	42.7	40.0	38.7	37.4	34.7	34.7	36.0	34.7	34.7	34.7	33.4
87.5°	16.0	16.0	16.0	16.0	17.3	14.7	16.0	16.0	14.7	14.7	13.3
90°	7.9	8.8	9.6	11.1	12.6	14.2	15.7	16.8	17.9	19.0	20.1
92.5°	10.8	9.8	10.5	11.8	13.1	14.4	15.7	16.8	17.9	19.0	20.1
95°	53.4	53.1	48.9	40.6	32.3	24.0	15.7	16.8	17.9	19.0	20.1
97.5°	110.4	111.1	100.7	80.0	59.2	38.5	17.7	18.1	18.6	19.0	19.5
100°	166.8	167.1	167.5	168.4	169.3	170.1	171.0	138.5	105.9	73.4	40.9
102.5°	227.6	228.0	228.2	228.7	229.1	229.6	230.0	230.4	230.9	231.3	231.8
105°	292.5	292.9	292.9	292.9	292.9	292.9	292.9	292.9	292.9	292.9	292.9
107.5°	355.8	355.8	356.0	356.5	356.9	357.4	357.8	358.0	358.2	358.5	358.7
110°	420.7	420.7	420.9	421.4	421.8	422.3	422.7	422.0	421.4	420.7	420.0

TEST NUMBER: P1027057

CATALOG NUMBER: S125RDIP-B1090D1090UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	484.3	484.6	484.7	484.9	485.2	485.4	485.6	484.7	483.8	482.9	482.0
115°	547.0	547.5	547.6	547.8	548.1	548.3	548.5	547.6	546.7	545.8	544.9
117.5°	606.5	606.5	606.9	607.8	608.7	609.5	610.4	609.1	607.8	606.5	605.2
120°	664.5	664.4	664.7	665.4	666.1	666.7	667.4	667.0	666.5	666.1	665.6
122.5°	721.9	722.4	722.5	722.7	723.0	723.2	723.4	723.0	722.6	722.1	721.7
125°	777.7	778.5	778.5	778.5	778.5	778.5	778.5	777.6	776.7	775.8	774.9
127.5°	828.1	828.6	828.5	828.3	828.0	827.8	827.6	827.2	826.7	826.3	825.8
130°	875.3	875.8	875.9	876.1	876.4	876.6	876.8	876.1	875.5	874.8	874.1
132.5°	923.2	923.9	923.6	922.9	922.3	921.6	921.0	921.0	921.0	921.0	921.0
135°	967.5	968.2	968.0	967.5	967.1	966.6	966.2	965.8	965.3	964.9	964.4
137.5°	1008.8	1009.5	1009.3	1008.8	1008.4	1007.9	1007.5	1007.5	1007.5	1007.5	1007.5
140°	1045.6	1045.8	1045.7	1045.5	1045.2	1045.0	1044.8	1045.2	1045.7	1046.1	1046.6
142.5°	1081.1	1081.2	1081.4	1081.9	1082.3	1082.8	1083.2	1083.2	1083.2	1083.2	1083.2
145°	1117.4	1117.6	1117.6	1117.6	1117.6	1117.6	1117.6	1117.8	1118.0	1118.3	1118.5
147.5°	1147.1	1147.1	1147.2	1147.4	1147.6	1147.8	1148.0	1148.2	1148.4	1148.7	1148.9
150°	1174.8	1174.6	1174.8	1175.2	1175.7	1176.1	1176.5	1176.9	1177.4	1177.8	1178.3
152.5°	1200.7	1200.1	1200.3	1200.8	1201.2	1201.7	1202.1	1202.5	1203.0	1203.4	1203.9
155°	1223.4	1222.7	1222.9	1223.4	1223.8	1224.3	1224.7	1225.4	1226.0	1226.7	1227.4
157.5°	1244.7	1244.4	1244.4	1244.4	1244.4	1244.4	1244.4	1245.0	1245.7	1246.3	1247.0
160°	1261.8	1261.1	1261.2	1261.4	1261.7	1261.9	1262.1	1263.0	1263.8	1264.7	1265.6
162.5°	1277.5	1276.8	1276.9	1277.1	1277.4	1277.6	1277.8	1279.1	1280.4	1281.7	1283.0
165°	1291.3	1290.6	1290.7	1290.9	1291.1	1291.3	1291.5	1292.8	1294.1	1295.4	1296.7
167.5°	1302.1	1301.4	1301.5	1301.7	1302.0	1302.2	1302.4	1303.9	1305.4	1306.9	1308.4
170°	1310.0	1309.2	1309.3	1309.5	1309.8	1310.0	1310.2	1312.0	1313.7	1315.5	1317.2
172.5°	1315.9	1315.1	1315.3	1315.8	1316.2	1316.7	1317.1	1318.6	1320.2	1321.7	1323.2
175°	1320.7	1320.1	1320.2	1320.4	1320.6	1320.8	1321.0	1322.8	1324.5	1326.3	1328.0
177.5°	1323.7	1323.0	1323.1	1323.3	1323.6	1323.8	1324.0	1325.5	1327.1	1328.6	1330.1
180°	1325.9	1325.9	1325.9	1325.9	1325.9	1325.9	1325.9	1325.9	1325.9	1325.9	1325.9

TEST NUMBER: P1027057

CATALOG NUMBER: S125RDIP-B1090D1090UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0
2.5°	1538.3	1540.9	1534.3	1531.6	1526.3	1532.9	1534.3	1532.9	1544.9	1539.6	1542.3
5°	1448.9	1443.5	1439.5	1430.2	1430.2	1431.5	1435.5	1428.9	1432.9	1442.2	1440.9
7.5°	1350.2	1347.5	1348.8	1338.1	1330.1	1332.8	1330.1	1342.1	1348.8	1346.1	1351.5
10°	1260.8	1266.1	1254.1	1248.8	1243.4	1248.8	1247.4	1250.1	1258.1	1263.4	1272.8
12.5°	1188.7	1187.4	1180.7	1175.4	1166.0	1168.7	1176.7	1174.0	1175.4	1187.4	1186.1
15°	1120.7	1112.7	1107.3	1095.3	1098.0	1088.7	1096.7	1106.0	1110.0	1120.7	1127.3
17.5°	1052.6	1051.3	1044.6	1043.3	1028.6	1024.6	1032.6	1035.3	1039.3	1044.6	1054.0
20°	995.3	993.9	984.6	981.9	969.9	977.9	975.3	980.6	983.3	993.9	997.9
22.5°	943.2	936.6	933.9	929.9	925.9	924.6	929.9	928.6	937.9	941.9	943.2
25°	895.2	889.9	888.5	881.9	879.2	875.2	879.2	883.2	893.9	897.9	903.2
27.5°	851.2	847.2	844.5	839.2	835.2	835.2	837.8	843.2	847.2	849.8	852.5
30°	811.2	808.5	800.5	797.8	793.8	793.8	793.8	796.5	803.2	811.2	815.2
32.5°	769.8	764.5	759.1	759.1	755.1	755.1	756.5	759.1	765.8	767.1	773.8
35°	729.8	724.4	720.4	717.8	719.1	713.8	716.4	720.4	728.4	731.1	735.1
37.5°	691.1	689.8	681.7	677.7	680.4	680.4	679.1	681.7	687.1	692.4	695.1
40°	648.4	645.7	645.7	641.7	643.1	637.7	641.7	644.4	647.1	652.4	656.4
42.5°	611.0	608.4	603.0	604.4	600.4	600.4	603.0	604.4	608.4	615.0	617.7
45°	571.0	571.0	568.3	564.3	565.7	561.7	564.3	565.7	571.0	577.7	575.0
47.5°	532.3	531.0	531.0	525.7	528.3	524.3	528.3	529.7	532.3	536.3	535.0
50°	495.0	491.0	492.3	491.0	489.6	489.6	492.3	492.3	495.0	495.0	499.0
52.5°	456.3	456.3	453.6	454.9	457.6	454.9	458.9	454.9	457.6	458.9	461.6
55°	421.6	418.9	420.3	418.9	424.3	420.3	424.3	421.6	424.3	422.9	425.6
57.5°	384.2	380.2	381.6	380.2	384.2	382.9	386.9	382.9	384.2	385.6	389.6
60°	341.5	341.5	341.5	338.9	342.9	342.9	341.5	341.5	346.9	349.5	348.2
62.5°	301.5	300.2	296.2	294.8	296.2	293.5	298.8	297.5	300.2	302.9	305.5
65°	257.5	254.8	253.5	250.8	250.8	249.5	250.8	256.2	257.5	258.8	265.5
67.5°	221.5	220.1	218.8	214.8	214.8	217.5	217.5	217.5	225.5	221.5	226.8
70°	189.4	186.8	184.1	182.8	182.8	184.1	185.4	186.8	185.4	190.8	192.1
72.5°	158.8	160.1	157.4	157.4	157.4	156.1	156.1	158.8	160.1	158.8	160.1
75°	132.1	132.1	130.7	132.1	132.1	130.7	130.7	133.4	133.4	132.1	136.1
77.5°	106.7	105.4	102.7	100.1	101.4	100.1	101.4	100.1	104.1	108.1	105.4
80°	74.7	73.4	73.4	73.4	74.7	73.4	76.0	73.4	74.7	74.7	76.0
82.5°	53.4	54.7	54.7	53.4	54.7	53.4	54.7	54.7	54.7	53.4	54.7
85°	34.7	34.7	34.7	34.7	33.4	34.7	34.7	34.7	36.0	34.7	36.0
87.5°	14.7	14.7	14.7	14.7	14.7	14.7	14.7	14.7	16.0	14.7	16.0
90°	20.6	20.9	21.6	22.3	22.9	23.6	22.9	22.3	21.6	20.9	20.6
92.5°	20.6	20.7	20.9	21.2	21.4	21.6	21.4	21.2	20.9	20.7	20.6
95°	20.6	20.6	20.6	20.6	20.6	20.6	20.6	20.6	20.6	20.6	20.6
97.5°	19.7	19.8	20.0	20.2	20.4	20.6	20.4	20.2	20.0	19.8	19.7
100°	24.6	24.2	23.3	22.4	21.5	20.6	21.5	22.4	23.3	24.2	24.6
102.5°	232.0	222.8	204.5	186.1	167.8	149.4	167.8	186.1	204.5	222.8	232.0
105°	292.9	292.8	292.6	292.3	292.1	291.9	292.1	292.3	292.6	292.8	292.9
107.5°	358.8	358.4	357.5	356.6	355.7	354.8	355.7	356.6	357.5	358.4	358.8
110°	419.7	419.8	420.0	420.3	420.5	420.7	420.5	420.3	420.0	419.8	419.7

TEST NUMBER: P1027057

CATALOG NUMBER: S125RDIP-B1090D1090UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	481.6	481.4	481.0	480.5	480.1	479.7	480.1	480.5	481.0	481.4	481.6
115°	544.5	543.8	542.5	541.2	539.9	538.6	539.9	541.2	542.5	543.8	544.5
117.5°	604.5	604.3	603.8	603.4	602.9	602.5	602.9	603.4	603.8	604.3	604.5
120°	665.4	664.9	663.8	662.7	661.6	660.5	661.6	662.7	663.8	664.9	665.4
122.5°	721.5	720.8	719.5	718.2	716.9	715.6	716.9	718.2	719.5	720.8	721.5
125°	774.5	774.2	773.5	772.9	772.2	771.6	772.2	772.9	773.5	774.2	774.5
127.5°	825.6	824.7	823.0	821.3	819.5	817.8	819.5	821.3	823.0	824.7	825.6
130°	873.8	873.3	872.2	871.1	870.0	868.9	870.0	871.1	872.2	873.3	873.8
132.5°	921.0	920.5	919.4	918.3	917.2	916.1	917.2	918.3	919.4	920.5	921.0
135°	964.2	963.5	962.2	960.9	959.6	958.3	959.6	960.9	962.2	963.5	964.2
137.5°	1007.5	1007.0	1005.9	1004.8	1003.7	1002.6	1003.7	1004.8	1005.9	1007.0	1007.5
140°	1046.8	1046.1	1044.8	1043.5	1042.2	1040.9	1042.2	1043.5	1044.8	1046.1	1046.8
142.5°	1083.2	1082.5	1081.2	1079.9	1078.6	1077.3	1078.6	1079.9	1081.2	1082.5	1083.2
145°	1118.6	1117.9	1116.6	1115.3	1114.0	1112.7	1114.0	1115.3	1116.6	1117.9	1118.6
147.5°	1149.0	1148.2	1146.7	1145.2	1143.6	1142.1	1143.6	1145.2	1146.7	1148.2	1149.0
150°	1178.5	1177.6	1175.9	1174.1	1172.4	1170.6	1172.4	1174.1	1175.9	1177.6	1178.5
152.5°	1204.1	1203.3	1201.8	1200.3	1198.7	1197.2	1198.7	1200.3	1201.8	1203.3	1204.1
155°	1227.7	1226.8	1225.1	1223.3	1221.6	1219.8	1221.6	1223.3	1225.1	1226.8	1227.7
157.5°	1247.3	1246.4	1244.7	1243.0	1241.2	1239.5	1241.2	1243.0	1244.7	1246.4	1247.3
160°	1266.0	1265.1	1263.4	1261.6	1259.9	1258.1	1259.9	1261.6	1263.4	1265.1	1266.0
162.5°	1283.7	1282.7	1280.7	1278.8	1276.8	1274.8	1276.8	1278.8	1280.7	1282.7	1283.7
165°	1297.4	1296.5	1294.8	1293.1	1291.3	1289.6	1291.3	1293.1	1294.8	1296.5	1297.4
167.5°	1309.2	1308.2	1306.3	1304.3	1302.4	1300.4	1302.4	1304.3	1306.3	1308.2	1309.2
170°	1318.1	1317.1	1315.1	1313.2	1311.2	1309.2	1311.2	1313.2	1315.1	1317.1	1318.1
172.5°	1324.0	1323.0	1321.0	1319.1	1317.1	1315.1	1317.1	1319.1	1321.0	1323.0	1324.0
175°	1328.9	1327.9	1326.0	1324.0	1322.1	1320.1	1322.1	1324.0	1326.0	1327.9	1328.9
177.5°	1330.9	1330.0	1328.3	1326.5	1324.8	1323.0	1324.8	1326.5	1328.3	1330.0	1330.9
180°	1325.9	1325.9	1325.9	1325.9	1325.9	1325.9	1325.9	1325.9	1325.9	1325.9	1325.9

TEST NUMBER: P1027057

CATALOG NUMBER: S125RDIP-B1090D1090UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0
2.5°	1536.9	1543.6	1538.3	1534.3	1544.9	1550.3	1550.3	1559.6	1569.0	1577.0	1578.3
5°	1442.2	1452.9	1455.5	1454.2	1470.2	1478.2	1495.6	1504.9	1518.3	1527.6	1538.3
7.5°	1355.5	1370.2	1371.5	1374.2	1398.2	1411.5	1426.2	1450.2	1468.9	1482.2	1494.2
10°	1268.8	1278.1	1287.4	1299.5	1323.5	1346.1	1367.5	1392.8	1416.9	1430.2	1447.5
12.5°	1203.4	1210.1	1220.7	1228.7	1254.1	1274.1	1302.1	1336.8	1371.5	1382.2	1403.5
15°	1135.4	1139.4	1160.7	1168.7	1190.1	1223.4	1240.8	1274.1	1311.5	1331.5	1355.5
17.5°	1056.6	1080.7	1094.0	1103.3	1130.0	1156.7	1184.7	1219.4	1267.4	1286.1	1303.5
20°	1000.6	1017.9	1032.6	1044.6	1068.6	1108.7	1134.0	1162.0	1207.4	1228.7	1254.1
22.5°	951.2	965.9	979.3	992.6	1008.6	1044.6	1074.0	1112.7	1158.0	1178.0	1207.4
25°	904.5	919.2	927.2	943.2	964.6	989.9	1024.6	1059.3	1104.7	1127.3	1155.4
27.5°	859.2	873.9	888.5	901.9	916.6	940.6	964.6	1008.6	1055.3	1082.0	1106.0
30°	820.5	827.2	840.5	855.2	869.9	892.5	920.6	951.2	1004.6	1028.6	1058.0
32.5°	777.8	789.8	799.2	809.8	828.5	847.2	872.5	911.2	953.9	976.6	1008.6
35°	737.8	748.5	755.1	773.8	785.8	805.8	831.2	865.9	901.9	927.2	955.2
37.5°	699.1	709.8	717.8	728.4	744.5	761.8	788.5	813.8	856.5	877.9	909.9
40°	659.1	668.4	677.7	689.8	704.4	725.8	741.8	773.8	808.5	832.5	856.5
42.5°	620.4	625.7	636.4	649.7	664.4	683.1	705.8	731.1	765.8	787.1	808.5
45°	579.0	588.4	600.4	609.7	623.0	641.7	661.7	684.4	719.1	740.4	763.1
47.5°	540.3	547.0	555.0	569.7	587.0	600.4	621.7	643.1	675.1	695.1	716.4
50°	500.3	507.0	519.0	528.3	541.7	559.0	579.0	601.7	632.4	645.7	667.1
52.5°	462.9	465.6	477.6	487.0	500.3	520.3	536.3	556.3	585.7	600.4	621.7
55°	425.6	428.3	434.9	444.3	458.9	475.0	492.3	515.0	540.3	553.7	573.7
57.5°	386.9	389.6	396.2	402.9	417.6	432.3	452.3	471.0	496.3	508.3	527.0
60°	348.2	348.2	354.9	364.2	374.9	388.2	405.6	428.3	446.9	461.6	475.0
62.5°	306.9	310.9	314.9	321.5	333.5	349.5	364.2	380.2	402.9	413.6	425.6
65°	265.5	269.5	277.5	284.2	293.5	304.2	322.9	336.2	353.5	365.6	376.2
67.5°	229.5	233.5	238.8	246.8	253.5	265.5	278.8	292.2	310.9	318.9	326.9
70°	192.1	196.1	200.1	210.8	217.5	226.8	236.1	249.5	265.5	270.8	277.5
72.5°	162.8	164.1	169.4	172.1	181.4	189.4	200.1	208.1	220.1	226.8	232.1
75°	137.4	137.4	138.8	141.4	146.8	152.1	160.1	168.1	178.8	182.8	189.4
77.5°	108.1	112.1	110.7	113.4	116.1	118.7	125.4	130.7	141.4	144.1	146.8
80°	77.4	78.7	82.7	86.7	86.7	90.7	94.7	96.1	102.7	106.7	106.7
82.5°	56.0	57.4	56.0	57.4	58.7	60.0	64.0	69.4	69.4	70.7	73.4
85°	34.7	34.7	36.0	37.4	37.4	36.0	38.7	37.4	38.7	41.4	41.4
87.5°	17.3	16.0	16.0	16.0	16.0	16.0	17.3	16.0	17.3	17.3	17.3
90°	20.1	19.0	17.9	16.8	15.7	14.2	12.6	11.1	9.6	8.8	7.9
92.5°	20.1	19.0	17.9	16.8	15.7	14.4	13.1	11.8	10.5	9.8	10.8
95°	20.1	19.0	17.9	16.8	15.7	24.0	32.3	40.6	48.9	53.1	53.4
97.5°	19.5	19.0	18.6	18.1	17.7	38.5	59.2	80.0	100.7	111.1	110.4
100°	40.9	73.4	105.9	138.5	171.0	170.1	169.3	168.4	167.5	167.1	166.8
102.5°	231.8	231.3	230.9	230.4	230.0	229.6	229.1	228.7	228.2	228.0	227.6
105°	292.9	292.9	292.9	292.9	292.9	292.9	292.9	292.9	292.9	292.9	292.5
107.5°	358.7	358.5	358.2	358.0	357.8	357.4	356.9	356.5	356.0	355.8	355.8
110°	420.0	420.7	421.4	422.0	422.7	422.3	421.8	421.4	420.9	420.7	420.7

TEST NUMBER: P1027057

CATALOG NUMBER: S125RDIP-B1090D1090UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	482.0	482.9	483.8	484.7	485.6	485.4	485.2	484.9	484.7	484.6	484.3
115°	544.9	545.8	546.7	547.6	548.5	548.3	548.1	547.8	547.6	547.5	547.0
117.5°	605.2	606.5	607.8	609.1	610.4	609.5	608.7	607.8	606.9	606.5	606.5
120°	665.6	666.1	666.5	667.0	667.4	666.7	666.1	665.4	664.7	664.4	664.5
122.5°	721.7	722.1	722.6	723.0	723.4	723.2	723.0	722.7	722.5	722.4	721.9
125°	774.9	775.8	776.7	777.6	778.5	778.5	778.5	778.5	778.5	778.5	777.7
127.5°	825.8	826.3	826.7	827.2	827.6	827.8	828.0	828.3	828.5	828.6	828.1
130°	874.1	874.8	875.5	876.1	876.8	876.6	876.4	876.1	875.9	875.8	875.3
132.5°	921.0	921.0	921.0	921.0	921.0	921.6	922.3	922.9	923.6	923.9	923.2
135°	964.4	964.9	965.3	965.8	966.2	966.6	967.1	967.5	968.0	968.2	967.5
137.5°	1007.5	1007.5	1007.5	1007.5	1007.5	1007.9	1008.4	1008.8	1009.3	1009.5	1008.8
140°	1046.6	1046.1	1045.7	1045.2	1044.8	1045.0	1045.2	1045.5	1045.7	1045.8	1045.6
142.5°	1083.2	1083.2	1083.2	1083.2	1083.2	1082.8	1082.3	1081.9	1081.4	1081.2	1081.1
145°	1118.5	1118.3	1118.0	1117.8	1117.6	1117.6	1117.6	1117.6	1117.6	1117.6	1117.4
147.5°	1148.9	1148.7	1148.4	1148.2	1148.0	1147.8	1147.6	1147.4	1147.2	1147.1	1147.1
150°	1178.3	1177.8	1177.4	1176.9	1176.5	1176.1	1175.7	1175.2	1174.8	1174.6	1174.8
152.5°	1203.9	1203.4	1203.0	1202.5	1202.1	1201.7	1201.2	1200.8	1200.3	1200.1	1200.7
155°	1227.4	1226.7	1226.0	1225.4	1224.7	1224.3	1223.8	1223.4	1222.9	1222.7	1223.4
157.5°	1247.0	1246.3	1245.7	1245.0	1244.4	1244.4	1244.4	1244.4	1244.4	1244.4	1244.7
160°	1265.6	1264.7	1263.8	1263.0	1262.1	1261.9	1261.7	1261.4	1261.2	1261.1	1261.8
162.5°	1283.0	1281.7	1280.4	1279.1	1277.8	1277.6	1277.4	1277.1	1276.9	1276.8	1277.5
165°	1296.7	1295.4	1294.1	1292.8	1291.5	1291.3	1291.1	1290.9	1290.7	1290.6	1291.3
167.5°	1308.4	1306.9	1305.4	1303.9	1302.4	1302.2	1302.0	1301.7	1301.5	1301.4	1302.1
170°	1317.2	1315.5	1313.7	1312.0	1310.2	1310.0	1309.8	1309.5	1309.3	1309.2	1310.0
172.5°	1323.2	1321.7	1320.2	1318.6	1317.1	1316.7	1316.2	1315.8	1315.3	1315.1	1315.9
175°	1328.0	1326.3	1324.5	1322.8	1321.0	1320.8	1320.6	1320.4	1320.2	1320.1	1320.7
177.5°	1330.1	1328.6	1327.1	1325.5	1324.0	1323.8	1323.6	1323.3	1323.1	1323.0	1323.7
180°	1325.9	1325.9	1325.9	1325.9	1325.9	1325.9	1325.9	1325.9	1325.9	1325.9	1325.9

TEST NUMBER: P1027057

CATALOG NUMBER: S125RDIP-B1090D1090UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1625.0	1625.0	1625.0	1625.0
2.5°	1587.6	1599.6	1611.6	1626.3
5°	1555.6	1577.0	1599.6	1621.0
7.5°	1520.9	1551.6	1581.0	1611.6
10°	1482.2	1520.9	1554.3	1597.0
12.5°	1439.5	1480.9	1527.6	1575.6
15°	1396.8	1448.9	1498.2	1552.9
17.5°	1356.8	1406.2	1460.9	1526.3
20°	1308.8	1363.5	1424.9	1494.2
22.5°	1258.1	1318.1	1384.8	1459.6
25°	1215.4	1276.8	1340.8	1419.5
27.5°	1168.7	1232.7	1295.5	1379.5
30°	1115.3	1184.7	1248.8	1335.5
32.5°	1064.6	1134.0	1204.7	1286.1
35°	1015.3	1083.3	1154.0	1236.7
37.5°	968.6	1030.0	1099.3	1174.0
40°	924.6	980.6	1042.0	1110.0
42.5°	868.5	933.9	991.3	1040.6
45°	820.5	873.9	927.2	967.3
47.5°	764.5	817.8	863.2	895.2
50°	717.8	760.5	797.8	825.8
52.5°	661.7	701.8	732.4	753.8
55°	607.0	641.7	668.4	683.1
57.5°	557.7	580.4	600.4	613.7
60°	503.0	520.3	537.7	552.3
62.5°	444.3	462.9	472.3	488.3
65°	392.2	404.2	418.9	424.3
67.5°	341.5	348.2	357.5	368.2
70°	288.2	292.2	301.5	316.2
72.5°	241.5	245.5	252.2	257.5
75°	192.1	196.1	201.5	206.8
77.5°	150.8	152.1	154.8	160.1
80°	109.4	113.4	116.1	117.4
82.5°	76.0	77.4	77.4	78.7
85°	48.0	45.4	45.4	46.7
87.5°	17.3	20.0	20.0	22.7
90°	6.2	4.5	2.7	1.0
92.5°	12.8	14.7	16.7	18.7
95°	54.1	54.7	55.4	56.0
97.5°	109.1	107.8	106.5	105.2
100°	166.1	165.4	164.8	164.1
102.5°	226.7	225.8	225.0	224.1
105°	291.6	290.7	289.9	289.0
107.5°	355.8	355.8	355.8	355.8
110°	420.7	420.7	420.7	420.7

TEST NUMBER: P1027057

CATALOG NUMBER: S125RDIP-B1090D1090UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	483.6	482.9	482.3	481.6
115°	545.9	544.8	543.7	542.6
117.5°	606.5	606.5	606.5	606.5
120°	664.7	665.0	665.2	665.4
122.5°	720.8	719.7	718.6	717.5
125°	776.2	774.7	773.1	771.6
127.5°	827.0	825.9	824.8	823.7
130°	874.2	873.1	872.0	870.9
132.5°	921.9	920.6	919.3	918.0
135°	966.2	964.9	963.6	962.3
137.5°	1007.5	1006.2	1004.9	1003.6
140°	1045.2	1044.7	1044.3	1043.9
142.5°	1080.9	1080.6	1080.4	1080.2
145°	1116.9	1116.5	1116.0	1115.6
147.5°	1147.1	1147.1	1147.1	1147.1
150°	1175.2	1175.7	1176.1	1176.5
152.5°	1201.8	1202.9	1204.0	1205.1
155°	1224.7	1226.0	1227.3	1228.6
157.5°	1245.4	1246.0	1246.7	1247.3
160°	1263.1	1264.4	1265.7	1267.0
162.5°	1278.8	1280.1	1281.4	1282.7
165°	1292.6	1293.9	1295.2	1296.5
167.5°	1303.4	1304.7	1306.0	1307.3
170°	1311.5	1313.0	1314.6	1316.1
172.5°	1317.4	1318.9	1320.5	1322.0
175°	1322.0	1323.3	1324.6	1325.9
177.5°	1325.0	1326.3	1327.6	1328.9
180°	1325.9	1325.9	1325.9	1325.9

(END OF REPORT)