

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027071

Luminaire Tested: S125RDIP-B1090D1270UB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027071
REPORT IS A COMBINATION OF REPORTS P1004972 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIP-B1090D1270UB2750-4F0-XX-W2A-F_3500K
Description: Define 5 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9052.0 lumens
Efficiency: N/A
Efficacy: 110.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 81.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027071

CATALOG NUMBER: S125RDIP-B1090D1270UB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1027071

CATALOG NUMBER: S125RDIP-B1090D1270UB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	106	106	106	106	98	98	98	98	81	81	81	67	67	67	53	53	53			47
1	97	93	89	86	89	86	82	79	72	69	67	59	57	56	47	46	45			40
2	89	81	75	70	81	75	70	65	63	59	56	52	49	47	42	40	38			34
3	81	72	65	59	74	66	60	55	56	51	47	46	43	40	37	35	33			29
4	74	64	56	50	68	59	52	47	50	44	40	41	37	34	33	31	28			25
5	68	57	49	43	62	52	45	40	44	39	35	37	33	30	30	27	25			22
6	63	51	43	37	58	47	40	35	40	35	31	34	29	26	27	24	22			19
7	58	46	38	33	53	43	36	31	36	31	27	31	26	23	25	22	20			17
8	54	42	34	29	49	39	32	27	33	28	24	28	24	21	23	20	18			15
9	50	38	31	26	46	35	29	24	30	25	21	26	22	19	21	18	16			14
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	14			13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11433	11433	11433
5°	11434	11148	11166
10°	11323	10867	10771
15°	11162	10474	10253
20°	10964	10001	9708
25°	10737	9539	9125
30°	10458	9031	8512
35°	10174	8515	7861
40°	9903	7985	7225
45°	9579	7414	6560
50°	9250	6807	5881
55°	8867	6209	5179
60°	8476	5525	4451
65°	8009	4762	3665
70°	7466	3876	2884
75°	6714	2915	2102
80°	5662	1887	1418
85°	4237	1013	798

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9579 cd/sqm

TEST NUMBER: P1027071

CATALOG NUMBER: S125RDIP-B1090D1270UB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	167.9	1.9
10°-20°	469.3	5.2
20°-30°	680.5	7.5
30°-40°	775.3	8.6
40°-50°	755.7	8.3
50°-60°	636.0	7.0
60°-70°	445.7	4.9
70°-80°	228.5	2.5
80°-90°	59.3	0.7
90°-100°	53.4	0.6
100°-110°	355.1	3.9
110°-120°	639.5	7.1
120°-130°	820.9	9.1
130°-140°	882.9	9.8
140°-150°	828.6	9.2
150°-160°	670.3	7.4
160°-170°	433.5	4.8
170°-180°	149.5	1.7
0°-30°	1317.8	14.6
0°-40°	2093.2	23.1
0°-60°	3484.9	38.5
0°-90°	4218.3	46.6
90°-120°	1048.1	11.6
90°-150°	3580.4	39.6
90°-180°	4834.0	53.4
0°-180°	9052.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1784	1784	1784	1784	1784	
5°	1782	1776	1762	1775	1772	169
15°	1694	1686	1658	1656	1644	478
25°	1536	1516	1466	1449	1434	707
35°	1324	1291	1230	1191	1173	829
45°	1084	1044	970	916	896	836
55°	822	779	704	643	621	735
65°	557	511	439	386	365	551
75°	296	256	200	170	160	313
85°	74	50	43	42	40	81
90°	1	10	19	24	28	8
95°	66	63	19	24	24	81
105°	343	348	348	348	346	363
115°	644	650	651	646	639	638
125°	916	924	924	919	916	818
135°	1142	1149	1147	1144	1137	880
145°	1324	1326	1326	1327	1320	828
155°	1458	1451	1453	1457	1448	672
165°	1539	1532	1533	1540	1530	435
175°	1574	1567	1568	1577	1567	150
180°	1574	1574	1574	1574	1574	

TEST NUMBER: P1027071

CATALOG NUMBER: S125RDIP-B1090D1270UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1784.4	1784.4	1784.4	1784.4	1784.4
2.5°	1788.5	1784.4	1771.0	1784.4	1783.1
5°	1781.7	1776.4	1761.5	1775.0	1772.3
7.5°	1768.3	1762.9	1745.4	1756.1	1753.4
10°	1748.1	1744.0	1725.1	1729.2	1725.1
12.5°	1725.1	1719.7	1692.8	1695.5	1688.8
15°	1694.1	1686.1	1657.8	1656.4	1644.3
17.5°	1661.8	1649.7	1616.0	1609.2	1599.8
20°	1622.7	1609.2	1566.1	1559.4	1547.2
22.5°	1579.6	1566.1	1520.3	1505.5	1496.0
25°	1536.5	1516.2	1466.4	1448.8	1434.0
27.5°	1487.9	1463.7	1411.1	1388.2	1373.4
30°	1434.0	1408.4	1351.8	1320.8	1308.7
32.5°	1381.5	1350.5	1292.5	1257.5	1241.3
35°	1323.5	1291.2	1230.5	1191.4	1172.6
37.5°	1268.2	1229.2	1167.2	1121.3	1102.5
40°	1208.9	1168.5	1103.8	1052.6	1036.4
42.5°	1146.9	1105.2	1037.8	989.3	963.7
45°	1083.6	1044.5	970.4	916.5	896.3
47.5°	1017.6	977.1	903.0	847.7	824.8
50°	955.6	911.1	834.3	777.7	757.4
52.5°	888.2	842.4	770.9	708.9	688.7
55°	822.1	779.0	703.5	642.9	621.3
57.5°	754.7	708.9	636.1	576.8	558.0
60°	690.1	642.9	570.1	510.8	490.6
62.5°	621.3	576.8	502.7	448.8	428.6
65°	556.6	510.8	439.4	385.5	365.2
67.5°	491.9	446.1	377.4	326.2	310.0
70°	425.9	380.1	312.7	270.9	254.7
72.5°	361.2	316.7	254.7	217.0	207.6
75°	296.5	256.1	199.5	169.8	160.4
77.5°	230.5	198.1	150.9	128.0	120.0
80°	175.2	142.9	105.1	93.0	90.3
82.5°	121.3	93.0	70.1	66.0	64.7
85°	74.1	49.9	43.1	41.8	40.4
87.5°	31.0	21.6	20.2	20.2	18.9
90°	1.2	10.5	18.7	24.5	28.0
92.5°	22.2	11.7	18.7	24.5	25.7
95°	66.5	63.0	18.7	24.5	24.5
97.5°	124.8	131.8	21.0	23.3	24.5
100°	194.8	198.3	203.0	29.2	24.5
102.5°	266.0	270.6	273.0	275.3	177.3
105°	342.9	347.6	347.6	347.6	346.4
107.5°	422.3	422.3	424.6	425.8	421.1
110°	499.2	499.2	501.6	498.1	499.2

TEST NUMBER: P1027071

CATALOG NUMBER: S125RDIP-B1090D1270UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	571.6	575.1	576.2	571.6	569.2
115°	643.9	649.7	650.9	646.2	639.2
117.5°	719.7	719.7	724.4	717.4	715.0
120°	789.7	788.5	792.0	789.7	783.9
122.5°	851.5	857.4	858.5	856.2	849.2
125°	915.7	923.8	923.8	919.2	915.7
127.5°	977.5	983.3	982.2	979.8	970.5
130°	1033.5	1039.3	1040.5	1037.0	1031.2
132.5°	1089.5	1096.5	1093.0	1093.0	1087.1
135°	1142.0	1149.0	1146.6	1144.3	1137.3
137.5°	1191.0	1198.0	1195.6	1195.6	1189.8
140°	1238.8	1241.1	1240.0	1242.3	1235.3
142.5°	1281.9	1283.1	1285.4	1285.4	1278.5
145°	1323.9	1326.3	1326.3	1327.4	1320.4
147.5°	1361.3	1361.3	1362.4	1363.6	1355.4
150°	1396.3	1393.9	1396.3	1398.6	1389.3
152.5°	1430.1	1424.3	1426.6	1428.9	1420.8
155°	1458.1	1451.1	1453.4	1456.9	1447.6
157.5°	1480.2	1476.8	1476.8	1480.2	1470.9
160°	1503.6	1496.6	1497.7	1502.4	1493.1
162.5°	1522.2	1515.2	1516.4	1523.4	1512.9
165°	1538.6	1531.6	1532.7	1539.7	1530.4
167.5°	1551.4	1544.4	1545.6	1553.7	1543.2
170°	1561.9	1553.7	1554.9	1564.2	1553.7
172.5°	1568.9	1560.7	1563.1	1571.2	1560.7
175°	1573.6	1566.6	1567.7	1577.1	1566.6
177.5°	1577.1	1570.1	1571.2	1579.4	1570.1
180°	1573.6	1573.6	1573.6	1573.6	1573.6

(END OF REPORT)