

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027103

Luminaire Tested: S125RDIP-B1090D850UB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027103
REPORT IS A COMBINATION OF REPORTS P1005094 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIP-B1090D850UB2750-4F0-XX-W2A-F_5000K
Description: Define 5 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7081.0 lumens
Efficiency: N/A
Efficacy: 104.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 67.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027103

CATALOG NUMBER: S125RDIP-B1090D850UB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1027103

CATALOG NUMBER: S125RDIP-B1090D850UB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	63	63	63
1	100	95	92	88	93	89	86	83	77	74	72	66	64	63	56	55	53
2	91	84	77	72	84	78	73	68	68	64	60	58	55	53	49	47	45
3	83	74	66	61	77	69	62	57	60	55	51	52	48	45	44	41	39
4	76	65	57	51	71	61	54	49	53	48	44	46	42	39	39	36	34
5	70	58	50	44	65	55	48	42	48	42	38	42	37	34	36	32	29
6	65	52	44	39	60	49	42	37	43	37	33	38	33	30	32	29	26
7	60	47	40	34	56	45	37	32	39	34	29	34	30	26	30	26	23
8	56	43	35	30	52	41	34	29	36	30	26	31	27	23	27	24	21
9	52	40	32	27	48	37	30	26	33	27	23	29	24	21	25	22	19
10	48	36	29	24	45	34	28	23	30	25	21	27	22	19	23	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10945	10945	10945
5°	10946	10672	10689
10°	10839	10403	10312
15°	10686	10027	9815
20°	10496	9574	9294
25°	10279	9132	8735
30°	10012	8646	8148
35°	9739	8152	7525
40°	9481	7645	6917
45°	9170	7097	6279
50°	8855	6516	5630
55°	8488	5944	4958
60°	8114	5290	4261
65°	7668	4558	3510
70°	7147	3710	2762
75°	6426	2791	2012
80°	5419	1806	1356
85°	4059	971	764

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9170 cd/sqm

TEST NUMBER: P1027103

CATALOG NUMBER: S125RDIP-B1090D850UB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	160.8	2.3
10°-20°	449.3	6.3
20°-30°	651.5	9.2
30°-40°	742.2	10.5
40°-50°	723.5	10.2
50°-60°	608.8	8.6
60°-70°	426.7	6.0
70°-80°	218.7	3.1
80°-90°	56.0	0.8
90°-100°	33.6	0.5
100°-110°	223.6	3.2
110°-120°	402.7	5.7
120°-130°	516.9	7.3
130°-140°	555.9	7.9
140°-150°	521.7	7.4
150°-160°	422.0	6.0
160°-170°	272.9	3.9
170°-180°	94.1	1.3
0°-30°	1261.6	17.8
0°-40°	2003.8	28.3
0°-60°	3336.1	47.1
0°-90°	4037.5	57.0
90°-120°	659.9	9.3
90°-150°	2254.4	31.8
90°-180°	3044.0	43.0
0°-180°	7081.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1708	1708	1708	1708	1708	
5°	1706	1700	1686	1699	1697	162
15°	1622	1614	1587	1586	1574	457
25°	1471	1452	1404	1387	1373	677
35°	1267	1236	1178	1141	1122	793
45°	1037	1000	929	877	858	800
55°	787	746	674	615	595	704
65°	533	489	421	369	350	528
75°	284	245	191	163	154	300
85°	71	48	41	40	39	78
90°	1	7	12	15	18	6
95°	42	40	12	15	15	51
105°	216	219	219	219	218	229
115°	405	409	410	407	402	402
125°	577	582	582	579	577	515
135°	719	724	722	720	716	554
145°	834	835	835	836	831	521
155°	918	914	915	917	912	423
165°	969	964	965	970	964	274
175°	991	986	987	993	986	94
180°	991	991	991	991	991	

TEST NUMBER: P1027103

CATALOG NUMBER: S125RDIP-B1090D850UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1708.3	1708.3	1708.3	1708.3	1708.3
2.5°	1712.1	1708.3	1695.4	1708.3	1707.0
5°	1705.7	1700.5	1686.3	1699.2	1696.6
7.5°	1692.8	1687.6	1670.8	1681.2	1678.6
10°	1673.4	1669.5	1651.5	1655.4	1651.5
12.5°	1651.5	1646.3	1620.5	1623.1	1616.6
15°	1621.8	1614.1	1587.0	1585.7	1574.1
17.5°	1590.8	1579.2	1547.0	1540.5	1531.5
20°	1553.4	1540.5	1499.2	1492.8	1481.2
22.5°	1512.1	1499.2	1455.4	1441.2	1432.1
25°	1470.9	1451.5	1403.8	1387.0	1372.8
27.5°	1424.4	1401.2	1350.9	1328.9	1314.7
30°	1372.8	1348.3	1294.1	1264.4	1252.8
32.5°	1322.5	1292.8	1237.3	1203.8	1188.3
35°	1267.0	1236.0	1178.0	1140.6	1122.5
37.5°	1214.1	1176.7	1117.3	1073.5	1055.4
40°	1157.3	1118.6	1056.7	1007.7	992.2
42.5°	1098.0	1058.0	993.5	947.0	922.5
45°	1037.3	999.9	929.0	877.4	858.0
47.5°	974.1	935.4	864.4	811.6	789.6
50°	914.8	872.2	798.6	744.5	725.1
52.5°	850.3	806.4	738.0	678.7	659.3
55°	787.0	745.7	673.5	615.4	594.8
57.5°	722.5	678.7	609.0	552.2	534.2
60°	660.6	615.4	545.8	489.0	469.6
62.5°	594.8	552.2	481.3	429.6	410.3
65°	532.9	489.0	420.6	369.0	349.7
67.5°	470.9	427.1	361.3	312.2	296.8
70°	407.7	363.8	299.3	259.3	243.9
72.5°	345.8	303.2	243.9	207.7	198.7
75°	283.8	245.1	191.0	162.6	153.5
77.5°	220.6	189.7	144.5	122.6	114.8
80°	167.7	136.8	100.6	89.0	86.4
82.5°	116.1	89.0	67.1	63.2	61.9
85°	71.0	47.7	41.3	40.0	38.7
87.5°	29.7	20.6	19.4	19.4	18.1
90°	0.7	6.6	11.8	15.4	17.6
92.5°	14.0	7.3	11.8	15.4	16.2
95°	41.9	39.7	11.8	15.4	15.4
97.5°	78.6	83.0	13.2	14.7	15.4
100°	122.7	124.9	127.8	18.4	15.4
102.5°	167.5	170.4	171.9	173.3	111.6
105°	215.9	218.9	218.9	218.9	218.1
107.5°	265.9	265.9	267.3	268.1	265.1
110°	314.4	314.4	315.8	313.6	314.4



TEST NUMBER: P1027103

CATALOG NUMBER: S125RDIP-B1090D850UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	359.9	362.1	362.8	359.9	358.4
115°	405.4	409.1	409.8	406.9	402.5
117.5°	453.2	453.2	456.1	451.7	450.2
120°	497.2	496.5	498.7	497.2	493.6
122.5°	536.2	539.8	540.6	539.1	534.7
125°	576.6	581.7	581.7	578.8	576.6
127.5°	615.5	619.2	618.4	617.0	611.1
130°	650.7	654.4	655.1	652.9	649.3
132.5°	686.0	690.4	688.2	688.2	684.5
135°	719.0	723.5	722.0	720.5	716.1
137.5°	749.9	754.3	752.8	752.8	749.2
140°	780.0	781.5	780.7	782.2	777.8
142.5°	807.2	807.9	809.4	809.4	805.0
145°	833.6	835.1	835.1	835.8	831.4
147.5°	857.1	857.1	857.9	858.6	853.5
150°	879.2	877.7	879.2	880.6	874.8
152.5°	900.5	896.8	898.3	899.7	894.6
155°	918.1	913.7	915.2	917.4	911.5
157.5°	932.0	929.8	929.8	932.0	926.2
160°	946.7	942.3	943.1	946.0	940.1
162.5°	958.5	954.1	954.8	959.2	952.6
165°	968.8	964.4	965.1	969.5	963.6
167.5°	976.8	972.4	973.2	978.3	971.7
170°	983.5	978.3	979.0	984.9	978.3
172.5°	987.9	982.7	984.2	989.3	982.7
175°	990.8	986.4	987.1	993.0	986.4
177.5°	993.0	988.6	989.3	994.5	988.6
180°	990.8	990.8	990.8	990.8	990.8

(END OF REPORT)