

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027111

Luminaire Tested: S125RDIP-B1270D1090UB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027111
REPORT IS A COMBINATION OF REPORTS P1005132 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIP-B1270D1090UB2750-4F0-XX-W2A-F_3500K
Description: Define 5 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9025.0 lumens
Efficiency: N/A
Efficacy: 100.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 89.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027111

CATALOG NUMBER: S125RDIP-B1270D1090UB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1027111

CATALOG NUMBER: S125RDIP-B1270D1090UB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60
1	99	95	91	88	92	88	85	82	76	73	71	64	62	61	54	52	51
2	90	83	77	72	84	77	72	68	67	63	59	57	54	51	47	45	44
3	83	73	66	60	76	68	62	57	59	54	50	50	47	44	42	40	37
4	76	65	57	51	70	61	54	48	52	47	43	45	41	37	38	35	32
5	70	58	50	44	64	54	47	42	47	41	37	40	36	33	34	31	28
6	64	52	44	38	59	49	42	36	42	37	32	37	32	29	31	28	25
7	59	47	39	34	55	44	37	32	39	33	29	33	29	25	28	25	22
8	55	43	35	30	51	40	33	28	35	30	26	31	26	23	26	23	20
9	51	39	32	27	48	37	30	25	32	27	23	28	24	21	24	21	18
10	48	36	29	24	45	34	27	23	30	24	21	26	22	19	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13313	13313	13313
5°	13314	12981	13001
10°	13184	12653	12542
15°	12997	12195	11938
20°	12766	11645	11304
25°	12501	11107	10624
30°	12177	10515	9911
35°	11847	9915	9153
40°	11532	9299	8413
45°	11153	8632	7638
50°	10769	7925	6848
55°	10325	7230	6030
60°	9869	6433	5182
65°	9326	5544	4268
70°	8693	4514	3359
75°	7816	3394	2447
80°	6592	2198	1650
85°	4934	1180	930

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11153 cd/sqm

TEST NUMBER: P1027111

CATALOG NUMBER: S125RDIP-B1270D1090UB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	195.6	2.2
10°-20°	546.5	6.1
20°-30°	792.4	8.8
30°-40°	902.8	10.0
40°-50°	879.9	9.7
50°-60°	740.5	8.2
60°-70°	518.9	5.7
70°-80°	266.0	2.9
80°-90°	68.3	0.8
90°-100°	45.4	0.5
100°-110°	302.3	3.3
110°-120°	544.3	6.0
120°-130°	698.7	7.7
130°-140°	751.4	8.3
140°-150°	705.3	7.8
150°-160°	570.5	6.3
160°-170°	368.9	4.1
170°-180°	127.2	1.4
0°-30°	1534.4	17.0
0°-40°	2437.2	27.0
0°-60°	4057.7	45.0
0°-90°	4911.0	54.4
90°-120°	892.0	9.9
90°-150°	3047.4	33.8
90°-180°	4114.0	45.6
0°-180°	9025.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2078	2078	2078	2078	2078	
5°	2075	2068	2051	2067	2064	197
15°	1973	1963	1930	1929	1914	556
25°	1789	1766	1707	1687	1670	823
35°	1541	1503	1433	1387	1365	965
45°	1262	1216	1130	1067	1044	973
55°	957	907	819	749	723	856
65°	648	595	512	449	425	642
75°	345	298	232	198	187	365
85°	86	58	50	49	47	95
90°	1	9	16	21	24	8
95°	57	54	16	21	21	69
105°	292	296	296	296	295	309
115°	548	553	554	550	544	543
125°	779	786	786	782	779	696
135°	972	978	976	974	968	749
145°	1127	1129	1129	1130	1124	705
155°	1241	1235	1237	1240	1232	572
165°	1310	1304	1304	1310	1303	370
175°	1339	1333	1334	1342	1333	128
180°	1339	1339	1339	1339	1339	

TEST NUMBER: P1027111

CATALOG NUMBER: S125RDIP-B1270D1090UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2077.8	2077.8	2077.8	2077.8	2077.8
2.5°	2082.5	2077.8	2062.1	2077.8	2076.2
5°	2074.6	2068.3	2051.1	2066.8	2063.6
7.5°	2058.9	2052.6	2032.2	2044.8	2041.7
10°	2035.4	2030.7	2008.7	2013.4	2008.7
12.5°	2008.7	2002.4	1971.0	1974.2	1966.3
15°	1972.6	1963.2	1930.2	1928.7	1914.5
17.5°	1935.0	1920.8	1881.6	1873.7	1862.8
20°	1889.4	1873.7	1823.5	1815.7	1801.6
22.5°	1839.2	1823.5	1770.2	1752.9	1741.9
25°	1789.0	1765.5	1707.4	1687.0	1669.7
27.5°	1732.5	1704.3	1643.1	1616.4	1599.1
30°	1669.7	1639.9	1574.0	1537.9	1523.8
32.5°	1608.5	1572.4	1505.0	1464.2	1445.3
35°	1541.1	1503.4	1432.8	1387.3	1365.3
37.5°	1476.7	1431.2	1359.0	1305.7	1283.7
40°	1407.7	1360.6	1285.3	1225.6	1206.8
42.5°	1335.5	1286.8	1208.4	1151.9	1122.1
45°	1261.7	1216.2	1129.9	1067.1	1043.6
47.5°	1184.8	1137.7	1051.4	987.1	960.4
50°	1112.6	1060.8	971.4	905.5	881.9
52.5°	1034.2	980.8	897.6	825.5	801.9
55°	957.3	907.1	819.2	748.6	723.4
57.5°	878.8	825.5	740.7	671.7	649.7
60°	803.5	748.6	663.8	594.8	571.2
62.5°	723.4	671.7	585.3	522.6	499.0
65°	648.1	594.8	511.6	448.8	425.3
67.5°	572.8	519.4	439.4	379.8	360.9
70°	495.9	442.5	364.1	315.4	296.6
72.5°	420.6	368.8	296.6	252.7	241.7
75°	345.2	298.2	232.3	197.7	186.7
77.5°	268.4	230.7	175.8	149.1	139.7
80°	204.0	166.3	122.4	108.3	105.1
82.5°	141.2	108.3	81.6	76.9	75.3
85°	86.3	58.1	50.2	48.6	47.1
87.5°	36.1	25.1	23.5	23.5	22.0
90°	1.0	8.9	15.9	20.8	23.8
92.5°	18.9	9.9	15.9	20.8	21.8
95°	56.6	53.6	15.9	20.8	20.8
97.5°	106.2	112.2	17.9	19.9	20.8
100°	165.8	168.8	172.7	24.8	20.8
102.5°	226.4	230.3	232.3	234.3	150.9
105°	291.9	295.9	295.9	295.9	294.9
107.5°	359.4	359.4	361.4	362.4	358.4
110°	424.9	424.9	426.9	423.9	424.9



TEST NUMBER: P1027111

CATALOG NUMBER: S125RDIP-B1270D1090UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	486.5	489.5	490.4	486.5	484.5
115°	548.0	553.0	554.0	550.0	544.1
117.5°	612.6	612.6	616.5	610.6	608.6
120°	672.1	671.1	674.1	672.1	667.2
122.5°	724.7	729.7	730.7	728.7	722.8
125°	779.3	786.3	786.3	782.3	779.3
127.5°	832.0	836.9	835.9	834.0	826.0
130°	879.6	884.6	885.6	882.6	877.6
132.5°	927.3	933.2	930.3	930.3	925.3
135°	972.0	977.9	975.9	973.9	968.0
137.5°	1013.7	1019.6	1017.6	1017.6	1012.7
140°	1054.4	1056.3	1055.3	1057.3	1051.4
142.5°	1091.1	1092.1	1094.1	1094.1	1088.1
145°	1126.8	1128.8	1128.8	1129.8	1123.9
147.5°	1158.6	1158.6	1159.6	1160.6	1153.6
150°	1188.4	1186.4	1188.4	1190.4	1182.4
152.5°	1217.2	1212.2	1214.2	1216.2	1209.2
155°	1241.0	1235.0	1237.0	1240.0	1232.1
157.5°	1259.9	1256.9	1256.9	1259.9	1251.9
160°	1279.7	1273.8	1274.8	1278.7	1270.8
162.5°	1295.6	1289.6	1290.6	1296.6	1287.7
165°	1309.5	1303.5	1304.5	1310.5	1302.6
167.5°	1320.4	1314.5	1315.5	1322.4	1313.5
170°	1329.4	1322.4	1323.4	1331.3	1322.4
172.5°	1335.3	1328.4	1330.4	1337.3	1328.4
175°	1339.3	1333.3	1334.3	1342.3	1333.3
177.5°	1342.3	1336.3	1337.3	1344.3	1336.3
180°	1339.3	1339.3	1339.3	1339.3	1339.3

(END OF REPORT)