

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026840

Luminaire Tested: S125DIP-B375D1090UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026840
REPORT IS A COMBINATION OF REPORTS P1001839 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B375D1090UB2750-4F0-XX-W2A-F_3000K
Description: Define 5 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5578.0 lumens
Efficiency: N/A
Efficacy: 134.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 41.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026840

CATALOG NUMBER: S125DIP-B375D1090UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1026840

CATALOG NUMBER: S125DIP-B375D1090UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	70	70	70	52	52	52	35	35	35
1	93	88	85	81	82	79	76	73	61	59	57	45	44	43	30	30	29
2	84	77	71	66	75	69	64	60	54	50	47	40	38	36	27	26	24
3	77	68	61	55	68	61	55	50	47	43	40	35	32	30	24	22	21
4	70	60	52	46	62	54	47	42	42	37	34	31	28	26	21	19	18
5	64	53	45	39	57	48	41	36	37	33	29	28	25	22	19	17	16
6	59	47	40	34	52	43	36	31	34	29	25	25	22	19	17	15	14
7	54	43	35	30	48	38	32	27	30	26	22	23	19	17	16	14	12
8	50	39	31	26	45	35	28	24	28	23	19	21	17	15	14	12	11
9	47	35	28	23	42	32	25	21	25	20	17	19	16	13	13	11	10
10	44	32	25	20	39	29	23	19	23	19	15	18	14	12	12	10	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3643	3643	3643
5°	3643	3559	3565
10°	3613	3477	3466
15°	3566	3380	3349
20°	3501	3266	3215
25°	3433	3143	3071
30°	3350	3014	2920
35°	3261	2879	2751
40°	3169	2737	2600
45°	3070	2598	2439
50°	2961	2441	2253
55°	2853	2267	2081
60°	2724	2084	1882
65°	2570	1872	1675
70°	2414	1629	1437
75°	2149	1341	1161
80°	1832	1002	854
85°	1412	593	470

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3070 cd/sqm

TEST NUMBER: P1026840

CATALOG NUMBER: S125DIP-B375D1090UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.7	1.0
10°-20°	151.6	2.7
20°-30°	223.8	4.0
30°-40°	261.1	4.7
40°-50°	262.2	4.7
50°-60°	230.2	4.1
60°-70°	171.4	3.1
70°-80°	97.9	1.8
80°-90°	30.2	0.5
90°-100°	45.3	0.8
100°-110°	300.9	5.4
110°-120°	541.9	9.7
120°-130°	695.6	12.5
130°-140°	748.1	13.4
140°-150°	702.2	12.6
150°-160°	568.0	10.2
160°-170°	367.3	6.6
170°-180°	126.7	2.3
0°-30°	429.0	7.7
0°-40°	690.0	12.4
0°-60°	1182.4	21.2
0°-90°	1482.0	26.6
90°-120°	888.1	15.9
90°-150°	3034.1	54.4
90°-180°	4096.0	73.4
0°-180°	5578.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	569	569	569	569	569	
5°	568	567	562	566	566	54
15°	541	540	535	537	537	153
25°	491	489	483	484	483	226
35°	424	422	416	414	410	265
45°	347	346	340	335	333	268
55°	264	263	257	253	250	236
65°	179	178	173	169	167	177
75°	95	94	92	90	89	101
85°	25	25	25	25	24	27
90°	1	9	16	21	24	5
95°	56	53	16	21	21	69
105°	291	295	295	295	294	308
115°	546	551	552	548	542	541
125°	776	783	783	779	776	693
135°	968	974	972	970	964	746
145°	1122	1124	1124	1125	1119	702
155°	1236	1230	1232	1235	1227	569
165°	1304	1298	1299	1305	1297	368
175°	1333	1328	1328	1336	1328	127
180°	1333	1333	1333	1333	1333	

TEST NUMBER: P1026840

CATALOG NUMBER: S125DIP-B375D1090UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	568.6	568.6	568.6	568.6	568.6
2.5°	570.4	569.1	564.6	569.1	568.6
5°	567.7	566.8	562.3	566.4	565.9
7.5°	563.7	562.8	557.8	561.9	561.4
10°	557.8	556.9	552.0	555.6	555.1
12.5°	550.6	548.8	544.3	547.0	547.0
15°	541.2	539.8	534.9	537.1	537.1
17.5°	531.3	529.0	524.1	526.8	524.5
20°	518.2	517.3	511.5	514.6	512.4
22.5°	505.2	503.4	498.0	499.8	498.4
25°	491.3	489.0	483.2	484.1	482.7
27.5°	475.1	473.7	467.9	468.3	467.0
30°	459.3	458.0	451.2	450.3	449.0
32.5°	442.2	440.0	434.1	432.3	429.6
35°	424.2	422.4	416.1	413.9	410.3
37.5°	405.8	403.5	397.7	394.5	392.3
40°	386.9	384.6	378.3	374.3	372.9
42.5°	366.6	364.8	358.5	354.9	352.7
45°	347.3	345.5	340.1	334.7	333.3
47.5°	326.2	326.6	319.9	314.5	311.3
50°	305.9	304.6	299.2	293.3	290.2
52.5°	285.2	284.3	278.5	273.5	269.9
55°	264.5	263.2	256.9	252.8	249.7
57.5°	242.5	242.0	236.6	231.2	229.9
60°	221.8	220.0	215.0	210.5	207.4
62.5°	200.2	198.8	194.8	189.8	187.6
65°	178.6	177.7	172.7	168.7	166.9
67.5°	157.5	155.7	152.1	148.5	147.6
70°	137.7	135.4	131.4	128.7	126.9
72.5°	116.1	114.7	112.5	109.3	107.5
75°	94.9	94.0	91.8	90.4	88.6
77.5°	75.1	74.7	73.3	72.4	71.1
80°	56.7	56.7	55.8	55.3	54.4
82.5°	40.5	39.6	39.6	38.7	38.7
85°	24.7	25.2	25.2	24.7	23.8
87.5°	12.1	12.1	11.7	11.7	10.8
90°	1.0	8.9	15.8	20.8	23.7
92.5°	18.8	9.9	15.8	20.8	21.7
95°	56.3	53.4	15.8	20.8	20.8
97.5°	105.8	111.7	17.8	19.8	20.8
100°	165.1	168.0	172.0	24.7	20.8
102.5°	225.4	229.3	231.3	233.3	150.2
105°	290.6	294.6	294.6	294.6	293.6
107.5°	357.8	357.8	359.8	360.8	356.8
110°	423.1	423.1	425.0	422.1	423.1

TEST NUMBER: P1026840

CATALOG NUMBER: S125DIP-B375D1090UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	484.3	487.3	488.3	484.3	482.4
115°	545.6	550.6	551.6	547.6	541.7
117.5°	609.9	609.9	613.8	607.9	605.9
120°	669.2	668.2	671.2	669.2	664.2
122.5°	721.6	726.5	727.5	725.5	719.6
125°	775.9	782.9	782.9	778.9	775.9
127.5°	828.3	833.3	832.3	830.3	822.4
130°	875.8	880.7	881.7	878.7	873.8
132.5°	923.2	929.2	926.2	926.2	921.2
135°	967.7	973.6	971.7	969.7	963.7
137.5°	1009.2	1015.1	1013.2	1013.2	1008.2
140°	1049.7	1051.7	1050.7	1052.7	1046.8
142.5°	1086.3	1087.3	1089.3	1089.3	1083.4
145°	1121.9	1123.9	1123.9	1124.9	1118.9
147.5°	1153.5	1153.5	1154.5	1155.5	1148.6
150°	1183.2	1181.2	1183.2	1185.2	1177.3
152.5°	1211.9	1206.9	1208.9	1210.9	1203.9
155°	1235.6	1229.6	1231.6	1234.6	1226.7
157.5°	1254.4	1251.4	1251.4	1254.4	1246.4
160°	1274.1	1268.2	1269.2	1273.1	1265.2
162.5°	1289.9	1284.0	1285.0	1290.9	1282.0
165°	1303.8	1297.8	1298.8	1304.8	1296.9
167.5°	1314.7	1308.7	1309.7	1316.6	1307.7
170°	1323.5	1316.6	1317.6	1325.5	1316.6
172.5°	1329.5	1322.6	1324.5	1331.5	1322.6
175°	1333.4	1327.5	1328.5	1336.4	1327.5
177.5°	1336.4	1330.5	1331.5	1338.4	1330.5
180°	1333.4	1333.4	1333.4	1333.4	1333.4

(END OF REPORT)