

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026843

Luminaire Tested: S125DIP-B375D1090UB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026843
REPORT IS A COMBINATION OF REPORTS P1001842 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B375D1090UB2750-4F0-XX-W2A-F_5000K
Description: Define 5 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5363.0 lumens
Efficiency: N/A
Efficacy: 129.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 41.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026843

CATALOG NUMBER: S125DIP-B375D1090UB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1026843

CATALOG NUMBER: S125DIP-B375D1090UB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	102	102	102	102	91	91	91	91	70	70	70	52	52	52	35	35	35			27
1	93	88	85	81	82	79	76	73	61	59	57	45	44	43	30	30	29			22
2	84	77	71	66	75	69	64	60	54	50	47	40	38	36	27	26	24			19
3	77	68	61	55	68	61	55	50	47	43	40	35	32	30	24	22	21			16
4	70	60	52	46	62	54	47	42	42	37	34	31	28	26	21	19	18			14
5	64	53	45	39	57	48	41	36	37	33	29	28	25	22	19	17	16			12
6	59	47	40	34	52	43	36	31	34	29	25	25	22	19	17	15	14			10
7	54	43	35	30	48	38	32	27	30	26	22	23	19	17	16	14	12			9
8	50	39	31	26	45	35	28	24	28	23	19	21	17	15	14	12	11			8
9	47	35	28	23	42	32	25	21	25	20	17	19	16	13	13	11	10			7
10	44	32	25	20	39	29	23	19	23	19	15	18	14	12	12	10	9			7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3503	3503	3503
5°	3503	3422	3428
10°	3474	3343	3333
15°	3428	3249	3221
20°	3367	3141	3091
25°	3300	3022	2953
30°	3221	2898	2808
35°	3136	2769	2645
40°	3047	2632	2500
45°	2952	2498	2346
50°	2847	2346	2166
55°	2743	2180	2001
60°	2619	2004	1809
65°	2471	1800	1611
70°	2321	1566	1382
75°	2067	1289	1117
80°	1761	962	821
85°	1361	569	452

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2952 cd/sqm

TEST NUMBER: P1026843

CATALOG NUMBER: S125DIP-B375D1090UB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.6	1.0
10°-20°	145.7	2.7
20°-30°	215.1	4.0
30°-40°	251.0	4.7
40°-50°	252.1	4.7
50°-60°	221.3	4.1
60°-70°	164.8	3.1
70°-80°	94.1	1.8
80°-90°	29.1	0.5
90°-100°	43.5	0.8
100°-110°	289.3	5.4
110°-120°	521.0	9.7
120°-130°	668.8	12.5
130°-140°	719.3	13.4
140°-150°	675.1	12.6
150°-160°	546.1	10.2
160°-170°	353.2	6.6
170°-180°	121.8	2.3
0°-30°	412.5	7.7
0°-40°	663.5	12.4
0°-60°	1136.8	21.2
0°-90°	1424.9	26.6
90°-120°	853.9	15.9
90°-150°	2917.1	54.4
90°-180°	3938.0	73.4
0°-180°	5363.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	547	547	547	547	547	
5°	546	545	541	545	544	52
15°	520	519	514	516	516	147
25°	472	470	464	465	464	217
35°	408	406	400	398	394	255
45°	334	332	327	322	320	257
55°	254	253	247	243	240	227
65°	172	171	166	162	160	170
75°	91	90	88	87	85	97
85°	24	24	24	24	23	26
90°	1	9	15	20	23	4
95°	54	51	15	20	20	66
105°	279	283	283	283	282	296
115°	525	529	530	526	521	520
125°	746	753	753	749	746	666
135°	930	936	934	932	927	717
145°	1079	1080	1080	1082	1076	675
155°	1188	1182	1184	1187	1179	547
165°	1254	1248	1249	1254	1247	354
175°	1282	1276	1277	1285	1276	122
180°	1282	1282	1282	1282	1282	

TEST NUMBER: P1026843

CATALOG NUMBER: S125DIP-B375D1090UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	546.7	546.7	546.7	546.7	546.7
2.5°	548.5	547.2	542.8	547.2	546.7
5°	545.9	545.0	540.7	544.6	544.1
7.5°	542.0	541.1	536.3	540.2	539.8
10°	536.3	535.5	530.7	534.2	533.8
12.5°	529.4	527.7	523.4	526.0	526.0
15°	520.3	519.0	514.3	516.5	516.5
17.5°	510.8	508.7	503.9	506.5	504.3
20°	498.3	497.4	491.8	494.8	492.7
22.5°	485.7	484.0	478.8	480.6	479.3
25°	472.3	470.2	464.5	465.4	464.1
27.5°	456.8	455.5	449.8	450.3	449.0
30°	441.6	440.3	433.8	433.0	431.7
32.5°	425.2	423.0	417.4	415.7	413.1
35°	407.9	406.2	400.1	397.9	394.5
37.5°	390.1	388.0	382.4	379.3	377.2
40°	372.0	369.8	363.8	359.9	358.6
42.5°	352.5	350.8	344.7	341.3	339.1
45°	333.9	332.2	327.0	321.8	320.5
47.5°	313.6	314.0	307.5	302.3	299.3
50°	294.1	292.8	287.6	282.0	279.0
52.5°	274.2	273.4	267.7	263.0	259.5
55°	254.3	253.0	247.0	243.1	240.1
57.5°	233.1	232.7	227.5	222.3	221.0
60°	213.2	211.5	206.8	202.4	199.4
62.5°	192.5	191.2	187.3	182.5	180.4
65°	171.7	170.9	166.1	162.2	160.5
67.5°	151.4	149.7	146.2	142.7	141.9
70°	132.4	130.2	126.3	123.7	122.0
72.5°	111.6	110.3	108.1	105.1	103.4
75°	91.3	90.4	88.2	86.9	85.2
77.5°	72.2	71.8	70.5	69.6	68.3
80°	54.5	54.5	53.6	53.2	52.3
82.5°	38.9	38.1	38.1	37.2	37.2
85°	23.8	24.2	24.2	23.8	22.9
87.5°	11.7	11.7	11.2	11.2	10.4
90°	1.0	8.6	15.2	20.0	22.8
92.5°	18.1	9.5	15.2	20.0	20.9
95°	54.2	51.3	15.2	20.0	20.0
97.5°	101.7	107.4	17.1	19.0	20.0
100°	158.7	161.6	165.4	23.8	20.0
102.5°	216.7	220.5	222.4	224.3	144.5
105°	279.4	283.2	283.2	283.2	282.3
107.5°	344.0	344.0	345.9	346.9	343.1
110°	406.7	406.7	408.7	405.8	406.7

TEST NUMBER: P1026843

CATALOG NUMBER: S125DIP-B375D1090UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	465.7	468.5	469.5	465.7	463.8
115°	524.6	529.3	530.3	526.5	520.8
117.5°	586.4	586.4	590.2	584.5	582.6
120°	643.4	642.4	645.3	643.4	638.6
122.5°	693.8	698.5	699.5	697.6	691.9
125°	746.0	752.7	752.7	748.9	746.0
127.5°	796.4	801.1	800.2	798.3	790.7
130°	842.0	846.8	847.7	844.9	840.1
132.5°	887.6	893.3	890.5	890.5	885.7
135°	930.4	936.1	934.2	932.3	926.6
137.5°	970.3	976.0	974.1	974.1	969.4
140°	1009.3	1011.2	1010.2	1012.1	1006.4
142.5°	1044.4	1045.4	1047.3	1047.3	1041.6
145°	1078.6	1080.5	1080.5	1081.5	1075.8
147.5°	1109.1	1109.1	1110.0	1111.0	1104.3
150°	1137.6	1135.7	1137.6	1139.5	1131.9
152.5°	1165.1	1160.4	1162.3	1164.2	1157.5
155°	1187.9	1182.2	1184.1	1187.0	1179.4
157.5°	1206.0	1203.1	1203.1	1206.0	1198.4
160°	1225.0	1219.3	1220.2	1224.1	1216.4
162.5°	1240.2	1234.5	1235.5	1241.2	1232.6
165°	1253.5	1247.8	1248.8	1254.5	1246.9
167.5°	1264.0	1258.3	1259.2	1265.9	1257.3
170°	1272.5	1265.9	1266.8	1274.4	1265.9
172.5°	1278.2	1271.6	1273.5	1280.1	1271.6
175°	1282.0	1276.3	1277.3	1284.9	1276.3
177.5°	1284.9	1279.2	1280.1	1286.8	1279.2
180°	1282.0	1282.0	1282.0	1282.0	1282.0

(END OF REPORT)