

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027120

Luminaire Tested: S125RDIP-B1270D1270UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027120
REPORT IS A COMBINATION OF REPORTS P1005171 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIP-B1270D1270UB2750-4F0-XX-W2A-F_3000K
Description: Define 5 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9703.0 lumens
Efficiency: N/A
Efficacy: 100.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 96.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027120

CATALOG NUMBER: S125RDIP-B1270D1270UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1027120

CATALOG NUMBER: S125RDIP-B1270D1270UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	99	99	99	99	84	84	84	69	69	69	56	56	56	56	56	56
1	98	94	90	87	90	87	84	81	74	71	69	61	60	58	50	49	48	48	48	43
2	90	82	76	71	82	76	71	66	65	61	58	54	51	49	45	43	41	41	41	36
3	82	72	65	59	75	67	61	56	57	53	49	48	45	42	40	37	35	35	35	31
4	75	64	56	50	69	60	53	47	51	46	42	43	39	36	36	33	30	30	30	27
5	69	57	49	43	63	53	46	41	46	40	36	39	34	31	32	29	27	27	27	23
6	63	51	43	38	58	48	41	36	41	36	31	35	31	27	29	26	23	23	23	21
7	59	47	39	33	54	43	36	31	37	32	28	32	28	24	27	23	21	21	21	18
8	54	42	35	29	50	39	33	28	34	29	25	29	25	22	25	21	19	19	19	16
9	51	39	31	26	47	36	29	25	31	26	22	27	23	20	23	19	17	17	17	15
10	47	35	28	24	44	33	27	22	29	24	20	25	21	18	21	18	15	15	15	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13256	13256	13256
5°	13257	12925	12946
10°	13128	12599	12488
15°	12942	12144	11887
20°	12712	11595	11256
25°	12448	11059	10579
30°	12125	10471	9869
35°	11796	9872	9114
40°	11482	9259	8377
45°	11106	8595	7605
50°	10724	7891	6819
55°	10281	7199	6005
60°	9826	6406	5161
65°	9285	5520	4250
70°	8656	4494	3344
75°	7785	3379	2437
80°	6563	2189	1644
85°	4911	1176	926

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11106 cd/sqm

TEST NUMBER: P1027120

CATALOG NUMBER: S125RDIP-B1270D1270UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	194.7	2.0
10°-20°	544.2	5.6
20°-30°	789.0	8.1
30°-40°	898.9	9.3
40°-50°	876.2	9.0
50°-60°	737.4	7.6
60°-70°	516.7	5.3
70°-80°	264.9	2.7
80°-90°	68.4	0.7
90°-100°	53.2	0.5
100°-110°	353.6	3.6
110°-120°	636.8	6.6
120°-130°	817.3	8.4
130°-140°	879.0	9.1
140°-150°	825.0	8.5
150°-160°	667.3	6.9
160°-170°	431.6	4.4
170°-180°	148.8	1.5
0°-30°	1527.9	15.7
0°-40°	2426.8	25.0
0°-60°	4040.3	41.6
0°-90°	4890.3	50.4
90°-120°	1043.5	10.8
90°-150°	3564.9	36.7
90°-180°	4813.0	49.6
0°-180°	9703.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2069	2069	2069	2069	2069	
5°	2066	2060	2042	2058	2055	196
15°	1964	1955	1922	1920	1906	554
25°	1781	1758	1700	1680	1663	820
35°	1534	1497	1427	1381	1360	961
45°	1256	1211	1125	1063	1039	969
55°	953	903	816	745	720	852
65°	645	592	509	447	424	639
75°	344	297	231	197	186	363
85°	86	58	50	48	47	94
90°	1	10	19	24	28	8
95°	66	63	19	24	24	81
105°	342	346	346	346	345	362
115°	641	647	648	643	636	636
125°	912	920	920	915	912	814
135°	1137	1144	1142	1139	1132	877
145°	1318	1320	1320	1322	1315	824
155°	1452	1445	1447	1451	1441	669
165°	1532	1525	1526	1533	1524	433
175°	1567	1560	1561	1570	1560	149
180°	1567	1567	1567	1567	1567	

TEST NUMBER: P1027120

CATALOG NUMBER: S125RDIP-B1270D1270UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2068.9	2068.9	2068.9	2068.9	2068.9
2.5°	2073.6	2068.9	2053.2	2068.9	2067.3
5°	2065.7	2059.5	2042.3	2057.9	2054.8
7.5°	2050.1	2043.9	2023.6	2036.1	2032.9
10°	2026.7	2022.0	2000.1	2004.8	2000.1
12.5°	2000.1	1993.9	1962.6	1965.7	1957.9
15°	1964.2	1954.8	1922.0	1920.4	1906.4
17.5°	1926.7	1912.6	1873.5	1865.7	1854.8
20°	1881.4	1865.7	1815.7	1807.9	1793.9
22.5°	1831.4	1815.7	1762.6	1745.4	1734.5
25°	1781.4	1757.9	1700.1	1679.8	1662.6
27.5°	1725.1	1697.0	1636.0	1609.5	1592.3
30°	1662.6	1632.9	1567.3	1531.3	1517.3
32.5°	1601.7	1565.7	1498.5	1457.9	1439.1
35°	1534.5	1497.0	1426.6	1381.3	1359.5
37.5°	1470.4	1425.1	1353.2	1300.1	1278.2
40°	1401.6	1354.8	1279.8	1220.4	1201.6
42.5°	1329.8	1281.3	1203.2	1146.9	1117.3
45°	1256.3	1211.0	1125.1	1062.6	1039.1
47.5°	1179.8	1132.9	1046.9	982.9	956.3
50°	1107.9	1056.3	967.2	901.6	878.2
52.5°	1029.7	976.6	893.8	821.9	798.5
55°	953.2	903.2	815.7	745.4	720.4
57.5°	875.1	821.9	737.5	668.8	646.9
60°	800.0	745.4	661.0	592.2	568.8
62.5°	720.4	668.8	582.8	520.3	496.9
65°	645.3	592.2	509.4	446.9	423.5
67.5°	570.3	517.2	437.5	378.1	359.4
70°	493.8	440.7	362.5	314.1	295.3
72.5°	418.8	367.2	295.3	251.6	240.6
75°	343.8	296.9	231.3	196.9	185.9
77.5°	267.2	229.7	175.0	148.4	139.1
80°	203.1	165.6	121.9	107.8	104.7
82.5°	140.6	107.8	81.3	76.6	75.0
85°	85.9	57.8	50.0	48.4	46.9
87.5°	35.9	25.0	23.4	23.4	21.9
90°	1.2	10.5	18.6	24.4	27.9
92.5°	22.1	11.6	18.6	24.4	25.6
95°	66.2	62.7	18.6	24.4	24.4
97.5°	124.3	131.2	20.9	23.2	24.4
100°	194.0	197.4	202.1	29.0	24.4
102.5°	264.8	269.4	271.8	274.1	176.5
105°	341.5	346.1	346.1	346.1	344.9
107.5°	420.4	420.4	422.8	423.9	419.3
110°	497.1	497.1	499.4	495.9	497.1

TEST NUMBER: P1027120

CATALOG NUMBER: S125RDIP-B1270D1270UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	569.1	572.6	573.7	569.1	566.8
115°	641.1	646.9	648.1	643.4	636.4
117.5°	716.6	716.6	721.2	714.3	711.9
120°	786.3	785.1	788.6	786.3	780.5
122.5°	847.8	853.6	854.8	852.5	845.5
125°	911.7	919.8	919.8	915.2	911.7
127.5°	973.3	979.1	977.9	975.6	966.3
130°	1029.0	1034.8	1036.0	1032.5	1026.7
132.5°	1084.8	1091.7	1088.2	1088.2	1082.4
135°	1137.0	1144.0	1141.7	1139.3	1132.4
137.5°	1185.8	1192.8	1190.4	1190.4	1184.6
140°	1233.4	1235.7	1234.6	1236.9	1229.9
142.5°	1276.4	1277.5	1279.9	1279.9	1272.9
145°	1318.2	1320.5	1320.5	1321.7	1314.7
147.5°	1355.4	1355.4	1356.5	1357.7	1349.6
150°	1390.2	1387.9	1390.2	1392.5	1383.2
152.5°	1423.9	1418.1	1420.4	1422.7	1414.6
155°	1451.8	1444.8	1447.1	1450.6	1441.3
157.5°	1473.8	1470.3	1470.3	1473.8	1464.5
160°	1497.0	1490.1	1491.2	1495.9	1486.6
162.5°	1515.6	1508.7	1509.8	1516.8	1506.3
165°	1531.9	1524.9	1526.1	1533.1	1523.8
167.5°	1544.7	1537.7	1538.9	1547.0	1536.5
170°	1555.1	1547.0	1548.2	1557.4	1547.0
172.5°	1562.1	1554.0	1556.3	1564.4	1554.0
175°	1566.7	1559.8	1560.9	1570.2	1559.8
177.5°	1570.2	1563.2	1564.4	1572.5	1563.2
180°	1566.7	1566.7	1566.7	1566.7	1566.7

(END OF REPORT)