

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026854

Luminaire Tested: S125DIP-B375D1270UB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026854
REPORT IS A COMBINATION OF REPORTS P1001898 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B375D1270UB2750-4F0-XX-W2A-F_2700K
Description: Define 5 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6241.0 lumens
Efficiency: N/A
Efficacy: 130.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 48
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026854

CATALOG NUMBER: S125DIP-B375D1270UB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1026854

CATALOG NUMBER: S125DIP-B375D1270UB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	69	69	69	49	49	49	32	32	32
1	92	88	84	81	81	78	75	72	60	58	56	43	42	41	28	27	27
2	84	76	71	66	74	68	63	59	52	49	46	38	36	34	25	23	22
3	76	67	60	55	67	60	54	49	46	42	39	34	31	29	22	20	19
4	70	59	52	46	62	53	47	42	41	36	33	30	27	25	19	18	16
5	64	53	45	39	56	47	40	35	36	32	28	27	24	21	17	16	14
6	59	47	39	34	52	42	35	31	33	28	24	24	21	18	16	14	12
7	54	42	35	29	48	38	31	27	30	25	21	22	19	16	14	13	11
8	50	38	31	26	44	34	28	23	27	22	19	20	17	14	13	11	10
9	46	35	28	23	41	31	25	21	24	20	17	18	15	13	12	10	9
10	43	32	25	20	38	28	22	18	22	18	15	17	14	11	11	9	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3611	3611	3611
5°	3611	3528	3534
10°	3581	3446	3436
15°	3534	3350	3320
20°	3471	3238	3187
25°	3402	3115	3045
30°	3321	2988	2894
35°	3232	2855	2726
40°	3142	2713	2577
45°	3043	2575	2418
50°	2935	2419	2233
55°	2828	2247	2063
60°	2700	2065	1865
65°	2547	1855	1660
70°	2391	1614	1424
75°	2131	1330	1151
80°	1816	993	848
85°	1401	588	466

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3043 cd/sqm

TEST NUMBER: P1026854

CATALOG NUMBER: S125DIP-B375D1270UB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.2	0.9
10°-20°	150.2	2.4
20°-30°	221.8	3.6
30°-40°	258.8	4.1
40°-50°	259.9	4.2
50°-60°	228.1	3.7
60°-70°	169.9	2.7
70°-80°	97.1	1.6
80°-90°	30.3	0.5
90°-100°	52.7	0.8
100°-110°	350.6	5.6
110°-120°	631.3	10.1
120°-130°	810.4	13.0
130°-140°	871.6	14.0
140°-150°	818.0	13.1
150°-160°	661.7	10.6
160°-170°	427.9	6.9
170°-180°	147.6	2.4
0°-30°	425.2	6.8
0°-40°	684.0	11.0
0°-60°	1172.0	18.8
0°-90°	1469.3	23.5
90°-120°	1034.6	16.6
90°-150°	3534.5	56.6
90°-180°	4772.0	76.5
0°-180°	6241.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	564	564	564	564	564	
5°	563	562	557	561	561	53
15°	536	535	530	532	532	151
25°	487	485	479	480	478	224
35°	420	419	412	410	407	263
45°	344	342	337	332	330	265
55°	262	261	255	251	248	234
65°	177	176	171	167	165	176
75°	94	93	91	90	88	100
85°	24	25	25	24	24	27
90°	1	10	18	24	28	5
95°	66	62	18	24	24	80
105°	338	343	343	343	342	359
115°	636	641	642	638	631	630
125°	904	912	912	907	904	807
135°	1127	1134	1132	1130	1123	869
145°	1307	1309	1309	1310	1304	817
155°	1439	1432	1435	1438	1429	663
165°	1519	1512	1513	1520	1511	429
175°	1553	1546	1548	1557	1546	148
180°	1553	1553	1553	1553	1553	

TEST NUMBER: P1026854

CATALOG NUMBER: S125DIP-B375D1270UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	563.6	563.6	563.6	563.6	563.6
2.5°	565.4	564.1	559.6	564.1	563.6
5°	562.7	561.9	557.4	561.4	561.0
7.5°	558.7	557.8	552.9	556.9	556.5
10°	552.9	552.0	547.1	550.7	550.3
12.5°	545.8	544.0	539.6	542.2	542.2
15°	536.4	535.1	530.2	532.4	532.4
17.5°	526.6	524.4	519.5	522.2	519.9
20°	513.7	512.8	507.0	510.1	507.9
22.5°	500.8	499.0	493.6	495.4	494.1
25°	486.9	484.7	478.9	479.8	478.5
27.5°	470.9	469.5	463.7	464.2	462.9
30°	455.3	453.9	447.3	446.4	445.0
32.5°	438.3	436.1	430.3	428.5	425.8
35°	420.5	418.7	412.5	410.2	406.7
37.5°	402.2	400.0	394.2	391.1	388.8
40°	383.5	381.3	375.0	371.0	369.7
42.5°	363.4	361.6	355.4	351.8	349.6
45°	344.2	342.5	337.1	331.8	330.4
47.5°	323.3	323.7	317.0	311.7	308.6
50°	303.2	301.9	296.5	290.7	287.6
52.5°	282.7	281.8	276.0	271.1	267.5
55°	262.2	260.9	254.6	250.6	247.5
57.5°	240.3	239.9	234.6	229.2	227.9
60°	219.8	218.1	213.1	208.7	205.6
62.5°	198.4	197.1	193.1	188.2	185.9
65°	177.0	176.1	171.2	167.2	165.4
67.5°	156.1	154.3	150.7	147.2	146.3
70°	136.4	134.2	130.2	127.5	125.7
72.5°	115.0	113.7	111.5	108.4	106.6
75°	94.1	93.2	91.0	89.6	87.8
77.5°	74.5	74.0	72.7	71.8	70.5
80°	56.2	56.2	55.3	54.8	54.0
82.5°	40.1	39.2	39.2	38.3	38.3
85°	24.5	25.0	25.0	24.5	23.6
87.5°	12.0	12.0	11.6	11.6	10.7
90°	1.2	10.4	18.4	24.2	27.6
92.5°	21.9	11.5	18.4	24.2	25.3
95°	65.6	62.2	18.4	24.2	24.2
97.5°	123.2	130.1	20.7	23.0	24.2
100°	192.3	195.8	200.4	28.8	24.2
102.5°	262.5	267.2	269.5	271.8	175.0
105°	338.5	343.2	343.2	343.2	342.0
107.5°	416.8	416.8	419.2	420.3	415.7
110°	492.8	492.8	495.2	491.7	492.8

TEST NUMBER: P1026854

CATALOG NUMBER: S125DIP-B375D1270UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	564.2	567.7	568.8	564.2	561.9
115°	635.6	641.4	642.5	637.9	631.0
117.5°	710.5	710.5	715.1	708.2	705.9
120°	779.6	778.4	781.9	779.6	773.8
122.5°	840.6	846.4	847.5	845.2	838.3
125°	903.9	912.0	912.0	907.4	903.9
127.5°	965.0	970.7	969.6	967.3	958.1
130°	1020.2	1026.0	1027.2	1023.7	1017.9
132.5°	1075.5	1082.4	1079.0	1079.0	1073.2
135°	1127.3	1134.2	1131.9	1129.6	1122.7
137.5°	1175.7	1182.6	1180.3	1180.3	1174.5
140°	1222.9	1225.2	1224.1	1226.4	1219.5
142.5°	1265.5	1266.7	1269.0	1269.0	1262.1
145°	1307.0	1309.3	1309.3	1310.4	1303.5
147.5°	1343.8	1343.8	1345.0	1346.1	1338.1
150°	1378.4	1376.1	1378.4	1380.7	1371.5
152.5°	1411.8	1406.0	1408.3	1410.6	1402.5
155°	1439.4	1432.5	1434.8	1438.2	1429.0
157.5°	1461.3	1457.8	1457.8	1461.3	1452.1
160°	1484.3	1477.4	1478.5	1483.2	1473.9
162.5°	1502.7	1495.8	1497.0	1503.9	1493.5
165°	1518.8	1511.9	1513.1	1520.0	1510.8
167.5°	1531.5	1524.6	1525.8	1533.8	1523.5
170°	1541.9	1533.8	1535.0	1544.2	1533.8
172.5°	1548.8	1540.7	1543.0	1551.1	1540.7
175°	1553.4	1546.5	1547.6	1556.8	1546.5
177.5°	1556.8	1549.9	1551.1	1559.2	1549.9
180°	1553.4	1553.4	1553.4	1553.4	1553.4

(END OF REPORT)