

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026869

Luminaire Tested: S125DIP-B375D375UB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026869
REPORT IS A COMBINATION OF REPORTS P1001958 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B375D375UB2750-4F0-XX-W2A-F_2700K
Description: Define 5 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2929.0 lumens
Efficiency: N/A
Efficacy: 131.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 22.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026869

CATALOG NUMBER: S125DIP-B375D375UB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1026869

CATALOG NUMBER: S125DIP-B375D375UB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56
1	98	93	89	86	90	86	83	80	73	71	68	61	59	58	50	48	47
2	89	82	75	70	82	75	70	66	64	60	57	53	51	48	44	42	40
3	81	72	64	58	75	66	60	55	56	52	48	47	44	41	39	36	34
4	74	63	55	49	68	59	52	46	50	45	40	42	38	35	35	32	29
5	68	56	48	42	63	52	45	40	45	39	35	38	33	30	31	28	25
6	63	51	42	37	58	47	40	35	40	35	30	34	30	26	28	25	22
7	58	46	38	32	53	43	35	30	37	31	27	31	27	23	26	22	20
8	54	41	34	28	50	39	32	27	33	28	24	28	24	21	24	20	18
9	50	38	30	25	46	35	29	24	31	25	21	26	22	19	22	19	16
10	47	35	27	23	43	32	26	22	28	23	19	24	20	17	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3611	3611	3611
5°	3611	3528	3534
10°	3581	3446	3436
15°	3534	3350	3320
20°	3471	3238	3187
25°	3402	3115	3045
30°	3321	2988	2894
35°	3232	2855	2726
40°	3142	2713	2577
45°	3043	2575	2418
50°	2935	2419	2233
55°	2828	2247	2063
60°	2700	2065	1865
65°	2547	1855	1660
70°	2391	1614	1424
75°	2131	1330	1151
80°	1816	993	848
85°	1401	588	466

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3043 cd/sqm

TEST NUMBER: P1026869

CATALOG NUMBER: S125DIP-B375D375UB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.2	1.8
10°-20°	150.2	5.1
20°-30°	221.8	7.6
30°-40°	258.8	8.8
40°-50°	259.9	8.9
50°-60°	228.1	7.8
60°-70°	169.9	5.8
70°-80°	97.1	3.3
80°-90°	28.7	1.0
90°-100°	16.1	0.6
100°-110°	107.4	3.7
110°-120°	193.3	6.6
120°-130°	248.2	8.5
130°-140°	266.9	9.1
140°-150°	250.5	8.6
150°-160°	202.6	6.9
160°-170°	131.0	4.5
170°-180°	45.2	1.5
0°-30°	425.2	14.5
0°-40°	684.0	23.4
0°-60°	1172.0	40.0
0°-90°	1467.7	50.1
90°-120°	316.8	10.8
90°-150°	1082.4	37.0
90°-180°	1461.0	49.9
0°-180°	2929.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	564	564	564	564	564	
5°	563	562	557	561	561	53
15°	536	535	530	532	532	151
25°	487	485	479	480	478	224
35°	420	419	412	410	407	263
45°	344	342	337	332	330	265
55°	262	261	255	251	248	234
65°	177	176	171	167	165	176
75°	94	93	91	90	88	100
85°	24	25	25	24	24	27
90°	0	3	6	7	8	3
95°	20	19	6	7	7	25
105°	104	105	105	105	105	110
115°	195	196	197	195	193	193
125°	277	279	279	278	277	247
135°	345	347	347	346	344	266
145°	400	401	401	401	399	250
155°	441	439	439	440	438	203
165°	465	463	463	466	463	131
175°	476	474	474	477	474	45
180°	476	476	476	476	476	

TEST NUMBER: P1026869

CATALOG NUMBER: S125DIP-B375D375UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	563.6	563.6	563.6	563.6	563.6
2.5°	565.4	564.1	559.6	564.1	563.6
5°	562.7	561.9	557.4	561.4	561.0
7.5°	558.7	557.8	552.9	556.9	556.5
10°	552.9	552.0	547.1	550.7	550.3
12.5°	545.8	544.0	539.6	542.2	542.2
15°	536.4	535.1	530.2	532.4	532.4
17.5°	526.6	524.4	519.5	522.2	519.9
20°	513.7	512.8	507.0	510.1	507.9
22.5°	500.8	499.0	493.6	495.4	494.1
25°	486.9	484.7	478.9	479.8	478.5
27.5°	470.9	469.5	463.7	464.2	462.9
30°	455.3	453.9	447.3	446.4	445.0
32.5°	438.3	436.1	430.3	428.5	425.8
35°	420.5	418.7	412.5	410.2	406.7
37.5°	402.2	400.0	394.2	391.1	388.8
40°	383.5	381.3	375.0	371.0	369.7
42.5°	363.4	361.6	355.4	351.8	349.6
45°	344.2	342.5	337.1	331.8	330.4
47.5°	323.3	323.7	317.0	311.7	308.6
50°	303.2	301.9	296.5	290.7	287.6
52.5°	282.7	281.8	276.0	271.1	267.5
55°	262.2	260.9	254.6	250.6	247.5
57.5°	240.3	239.9	234.6	229.2	227.9
60°	219.8	218.1	213.1	208.7	205.6
62.5°	198.4	197.1	193.1	188.2	185.9
65°	177.0	176.1	171.2	167.2	165.4
67.5°	156.1	154.3	150.7	147.2	146.3
70°	136.4	134.2	130.2	127.5	125.7
72.5°	115.0	113.7	111.5	108.4	106.6
75°	94.1	93.2	91.0	89.6	87.8
77.5°	74.5	74.0	72.7	71.8	70.5
80°	56.2	56.2	55.3	54.8	54.0
82.5°	40.1	39.2	39.2	38.3	38.3
85°	24.5	25.0	25.0	24.5	23.6
87.5°	12.0	12.0	11.6	11.6	10.7
90°	0.4	3.2	5.6	7.4	8.5
92.5°	6.7	3.5	5.6	7.4	7.8
95°	20.1	19.0	5.6	7.4	7.4
97.5°	37.7	39.8	6.3	7.1	7.4
100°	58.9	59.9	61.4	8.8	7.4
102.5°	80.4	81.8	82.5	83.2	53.6
105°	103.7	105.1	105.1	105.1	104.7
107.5°	127.7	127.7	128.4	128.7	127.3
110°	150.9	150.9	151.6	150.6	150.9



TEST NUMBER: P1026869

CATALOG NUMBER: S125DIP-B375D375UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	172.8	173.9	174.2	172.8	172.1
115°	194.7	196.4	196.8	195.4	193.2
117.5°	217.6	217.6	219.0	216.9	216.2
120°	238.7	238.4	239.4	238.7	237.0
122.5°	257.4	259.2	259.5	258.8	256.7
125°	276.8	279.3	279.3	277.9	276.8
127.5°	295.5	297.3	296.9	296.2	293.4
130°	312.4	314.2	314.6	313.5	311.7
132.5°	329.4	331.5	330.4	330.4	328.7
135°	345.2	347.4	346.6	345.9	343.8
137.5°	360.0	362.2	361.5	361.5	359.7
140°	374.5	375.2	374.9	375.6	373.4
142.5°	387.6	387.9	388.6	388.6	386.5
145°	400.2	401.0	401.0	401.3	399.2
147.5°	411.5	411.5	411.9	412.2	409.8
150°	422.1	421.4	422.1	422.8	420.0
152.5°	432.3	430.6	431.3	432.0	429.5
155°	440.8	438.7	439.4	440.5	437.6
157.5°	447.5	446.4	446.4	447.5	444.7
160°	454.6	452.4	452.8	454.2	451.4
162.5°	460.2	458.1	458.4	460.6	457.4
165°	465.1	463.0	463.4	465.5	462.7
167.5°	469.0	466.9	467.3	469.7	466.5
170°	472.2	469.7	470.1	472.9	469.7
172.5°	474.3	471.8	472.5	475.0	471.8
175°	475.7	473.6	474.0	476.8	473.6
177.5°	476.8	474.7	475.0	477.5	474.7
180°	475.7	475.7	475.7	475.7	475.7

(END OF REPORT)