

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026871

Luminaire Tested: S125DIP-B375D375UB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026871
REPORT IS A COMBINATION OF REPORTS P1001960 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B375D375UB2750-4F0-XX-W2A-F_3500K
Description: Define 5 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2967.0 lumens
Efficiency: N/A
Efficacy: 133.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 22.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026871

CATALOG NUMBER: S125DIP-B375D375UB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1026871

CATALOG NUMBER: S125DIP-B375D375UB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	107	107	107	107	99	99	99	99		83	83	83		69	69	69		56	56	56
1	98	93	89	86	90	86	83	80		73	71	68		61	59	58		50	48	47
2	89	82	75	70	82	75	70	66		64	60	57		53	51	48		44	42	40
3	81	72	64	58	75	66	60	55		56	52	48		47	44	41		39	36	34
4	74	63	55	49	68	59	52	46		50	45	40		42	38	35		35	32	29
5	68	56	48	42	63	52	45	40		45	39	35		38	33	30		31	28	25
6	63	51	42	37	58	47	40	35		40	35	30		34	30	26		28	25	22
7	58	46	38	32	53	43	35	30		37	31	27		31	27	23		26	22	20
8	54	41	34	28	50	39	32	27		33	28	24		28	24	21		24	20	18
9	50	38	30	25	46	35	29	24		31	25	21		26	22	19		22	19	16
10	47	35	27	23	43	32	26	22		28	23	19		24	20	17		20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3658	3658	3658
5°	3658	3573	3580
10°	3628	3491	3480
15°	3580	3393	3363
20°	3516	3280	3228
25°	3446	3156	3084
30°	3364	3026	2932
35°	3274	2891	2761
40°	3183	2748	2610
45°	3083	2609	2450
50°	2973	2451	2262
55°	2865	2276	2090
60°	2735	2092	1889
65°	2580	1879	1682
70°	2423	1635	1443
75°	2158	1346	1167
80°	1839	1005	859
85°	1418	595	472

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3083 cd/sqm

TEST NUMBER: P1026871

CATALOG NUMBER: S125DIP-B375D375UB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.9	1.8
10°-20°	152.2	5.1
20°-30°	224.7	7.6
30°-40°	262.1	8.8
40°-50°	263.3	8.9
50°-60°	231.1	7.8
60°-70°	172.1	5.8
70°-80°	98.3	3.3
80°-90°	29.1	1.0
90°-100°	16.4	0.6
100°-110°	108.8	3.7
110°-120°	195.8	6.6
120°-130°	251.4	8.5
130°-140°	270.4	9.1
140°-150°	253.8	8.6
150°-160°	205.3	6.9
160°-170°	132.7	4.5
170°-180°	45.8	1.5
0°-30°	430.7	14.5
0°-40°	692.8	23.4
0°-60°	1187.2	40.0
0°-90°	1486.7	50.1
90°-120°	321.0	10.8
90°-150°	1096.5	37.0
90°-180°	1480.0	49.9
0°-180°	2967.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	571	571	571	571	571	
5°	570	569	565	569	568	54
15°	543	542	537	539	539	153
25°	493	491	485	486	485	227
35°	426	424	418	416	412	266
45°	349	347	342	336	335	269
55°	266	264	258	254	251	237
65°	179	178	173	169	168	178
75°	95	94	92	91	89	101
85°	25	25	25	25	24	27
90°	0	3	6	8	9	3
95°	20	19	6	8	8	25
105°	105	106	106	106	106	111
115°	197	199	199	198	196	195
125°	280	283	283	282	280	251
135°	350	352	351	350	348	270
145°	406	406	406	406	404	254
155°	446	444	445	446	443	206
165°	471	469	469	472	469	133
175°	482	480	480	483	480	46
180°	482	482	482	482	482	

TEST NUMBER: P1026871

CATALOG NUMBER: S125DIP-B375D375UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	570.9	570.9	570.9	570.9	570.9
2.5°	572.7	571.4	566.9	571.4	570.9
5°	570.0	569.1	564.6	568.7	568.2
7.5°	566.0	565.1	560.1	564.2	563.7
10°	560.1	559.2	554.2	557.8	557.4
12.5°	552.9	551.1	546.5	549.3	549.3
15°	543.4	542.0	537.1	539.3	539.3
17.5°	533.4	531.2	526.2	528.9	526.7
20°	520.3	519.4	513.6	516.7	514.5
22.5°	507.2	505.4	500.0	501.8	500.5
25°	493.2	491.0	485.1	486.0	484.7
27.5°	477.0	475.6	469.8	470.2	468.9
30°	461.2	459.8	453.0	452.1	450.8
32.5°	444.0	441.8	435.9	434.1	431.4
35°	425.9	424.1	417.8	415.6	411.9
37.5°	407.4	405.2	399.3	396.1	393.9
40°	388.5	386.2	379.9	375.8	374.4
42.5°	368.1	366.3	360.0	356.4	354.1
45°	348.7	346.9	341.5	336.1	334.7
47.5°	327.5	327.9	321.2	315.7	312.6
50°	307.1	305.8	300.4	294.5	291.3
52.5°	286.4	285.5	279.6	274.6	271.0
55°	265.6	264.2	257.9	253.8	250.7
57.5°	243.5	243.0	237.6	232.2	230.8
60°	222.7	220.9	215.9	211.4	208.2
62.5°	201.0	199.6	195.6	190.6	188.4
65°	179.3	178.4	173.4	169.4	167.6
67.5°	158.1	156.3	152.7	149.1	148.2
70°	138.2	136.0	131.9	129.2	127.4
72.5°	116.5	115.2	112.9	109.8	108.0
75°	95.3	94.4	92.1	90.8	89.0
77.5°	75.4	75.0	73.6	72.7	71.4
80°	56.9	56.9	56.0	55.6	54.7
82.5°	40.7	39.7	39.7	38.8	38.8
85°	24.8	25.3	25.3	24.8	23.9
87.5°	12.2	12.2	11.7	11.7	10.8
90°	0.4	3.2	5.7	7.5	8.6
92.5°	6.8	3.6	5.7	7.5	7.9
95°	20.4	19.3	5.7	7.5	7.5
97.5°	38.2	40.4	6.4	7.1	7.5
100°	59.7	60.7	62.2	8.9	7.5
102.5°	81.4	82.9	83.6	84.3	54.3
105°	105.0	106.5	106.5	106.5	106.1
107.5°	129.3	129.3	130.0	130.4	129.0
110°	152.9	152.9	153.6	152.5	152.9



TEST NUMBER: P1026871

CATALOG NUMBER: S125DIP-B375D375UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	175.0	176.1	176.5	175.0	174.3
115°	197.2	199.0	199.3	197.9	195.8
117.5°	220.4	220.4	221.8	219.7	219.0
120°	241.8	241.5	242.6	241.8	240.1
122.5°	260.8	262.6	262.9	262.2	260.1
125°	280.4	282.9	282.9	281.5	280.4
127.5°	299.4	301.1	300.8	300.1	297.2
130°	316.5	318.3	318.6	317.6	315.8
132.5°	333.6	335.8	334.7	334.7	332.9
135°	349.7	351.9	351.2	350.4	348.3
137.5°	364.7	366.9	366.2	366.2	364.4
140°	379.4	380.1	379.7	380.4	378.3
142.5°	392.6	392.9	393.7	393.7	391.5
145°	405.5	406.2	406.2	406.5	404.4
147.5°	416.9	416.9	417.2	417.6	415.1
150°	427.6	426.9	427.6	428.3	425.5
152.5°	438.0	436.2	436.9	437.6	435.1
155°	446.5	444.4	445.1	446.2	443.3
157.5°	453.3	452.2	452.2	453.3	450.5
160°	460.5	458.3	458.7	460.1	457.2
162.5°	466.2	464.0	464.4	466.5	463.3
165°	471.2	469.0	469.4	471.5	468.7
167.5°	475.1	473.0	473.3	475.8	472.6
170°	478.3	475.8	476.2	479.0	475.8
172.5°	480.5	478.0	478.7	481.2	478.0
175°	481.9	479.8	480.1	483.0	479.8
177.5°	483.0	480.8	481.2	483.7	480.8
180°	481.9	481.9	481.9	481.9	481.9

(END OF REPORT)