

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026872

Luminaire Tested: S125DIP-B375D375UB2750-4F0-XX-W2A-F_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026872
REPORT IS A COMBINATION OF REPORTS P1001961 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B375D375UB2750-4F0-XX-W2A-F_4000K
Description: Define 5 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2938.0 lumens
Efficiency: N/A
Efficacy: 131.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 22.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026872

CATALOG NUMBER: S125DIP-B375D375UB2750-4F0-XX-W2A-F_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1026872

CATALOG NUMBER: S125DIP-B375D375UB2750-4F0-XX-W2A-F_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	56	56	56
1	98	93	89	86	90	86	83	80	73	71	68	61	59	58	50	48	47	47	47	42
2	89	82	75	70	82	75	70	66	64	60	57	53	51	48	44	42	40	40	40	35
3	81	72	64	58	75	66	60	55	56	52	48	47	44	41	39	36	34	34	34	30
4	74	63	55	49	68	59	52	46	50	45	40	42	38	35	35	32	29	29	29	26
5	68	56	48	42	63	52	45	40	45	39	35	38	33	30	31	28	25	25	25	22
6	63	51	42	37	58	47	40	35	40	35	30	34	30	26	28	25	22	22	22	19
7	58	46	38	32	53	43	35	30	37	31	27	31	27	23	26	22	20	20	20	17
8	54	41	34	28	50	39	32	27	33	28	24	28	24	21	24	20	18	18	18	15
9	50	38	30	25	46	35	29	24	31	25	21	26	22	19	22	19	16	16	16	14
10	47	35	27	23	43	32	26	22	28	23	19	24	20	17	20	17	15	15	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3624	3624	3624
5°	3624	3540	3546
10°	3594	3458	3447
15°	3547	3361	3331
20°	3482	3249	3198
25°	3414	3126	3055
30°	3331	2998	2904
35°	3243	2864	2736
40°	3152	2722	2586
45°	3053	2585	2426
50°	2945	2427	2241
55°	2838	2255	2070
60°	2709	2073	1872
65°	2555	1862	1666
70°	2400	1620	1429
75°	2137	1334	1155
80°	1823	996	849
85°	1407	590	468

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3053 cd/sqm

TEST NUMBER: P1026872

CATALOG NUMBER: S125DIP-B375D375UB2750-4F0-XX-W2A-F_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.4	1.8
10°-20°	150.7	5.1
20°-30°	222.5	7.6
30°-40°	259.6	8.8
40°-50°	260.8	8.9
50°-60°	228.9	7.8
60°-70°	170.5	5.8
70°-80°	97.4	3.3
80°-90°	28.8	1.0
90°-100°	16.2	0.6
100°-110°	107.7	3.7
110°-120°	193.9	6.6
120°-130°	248.8	8.5
130°-140°	267.6	9.1
140°-150°	251.2	8.5
150°-160°	203.2	6.9
160°-170°	131.4	4.5
170°-180°	45.3	1.5
0°-30°	426.7	14.5
0°-40°	686.3	23.4
0°-60°	1176.0	40.0
0°-90°	1472.7	50.1
90°-120°	317.7	10.8
90°-150°	1085.4	36.9
90°-180°	1465.0	49.9
0°-180°	2938.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	566	566	566	566	566	
5°	565	564	559	563	563	54
15°	538	537	532	534	534	152
25°	489	486	480	481	480	225
35°	422	420	414	412	408	264
45°	345	344	338	333	332	266
55°	263	262	256	252	248	235
65°	178	177	172	168	166	176
75°	94	94	91	90	88	100
85°	25	25	25	25	24	27
90°	0	3	6	7	8	3
95°	20	19	6	7	7	25
105°	104	105	105	105	105	110
115°	195	197	197	196	194	194
125°	278	280	280	279	278	248
135°	346	348	348	347	345	267
145°	401	402	402	402	400	251
155°	442	440	441	442	439	204
165°	466	464	465	467	464	132
175°	477	475	475	478	475	45
180°	477	477	477	477	477	

TEST NUMBER: P1026872

CATALOG NUMBER: S125DIP-B375D375UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	565.6	565.6	565.6	565.6	565.6
2.5°	567.3	566.0	561.5	566.0	565.6
5°	564.7	563.8	559.3	563.3	562.9
7.5°	560.6	559.7	554.8	558.8	558.4
10°	554.8	553.9	549.0	552.6	552.1
12.5°	547.7	545.9	541.4	544.1	544.1
15°	538.3	536.9	532.0	534.2	534.2
17.5°	528.4	526.2	521.3	523.9	521.7
20°	515.4	514.5	508.7	511.9	509.6
22.5°	502.5	500.7	495.3	497.1	495.8
25°	488.6	486.4	480.5	481.4	480.1
27.5°	472.5	471.1	465.3	465.8	464.4
30°	456.8	455.5	448.8	447.9	446.5
32.5°	439.8	437.6	431.8	430.0	427.3
35°	421.9	420.1	413.9	411.6	408.1
37.5°	403.6	401.3	395.5	392.4	390.2
40°	384.8	382.6	376.3	372.3	370.9
42.5°	364.7	362.9	356.6	353.0	350.8
45°	345.4	343.6	338.3	332.9	331.5
47.5°	324.4	324.8	318.1	312.8	309.6
50°	304.3	302.9	297.5	291.7	288.6
52.5°	283.7	282.8	277.0	272.0	268.5
55°	263.1	261.7	255.5	251.5	248.3
57.5°	241.2	240.7	235.3	230.0	228.6
60°	220.6	218.8	213.9	209.4	206.3
62.5°	199.1	197.8	193.7	188.8	186.6
65°	177.6	176.7	171.8	167.8	166.0
67.5°	156.6	154.8	151.2	147.7	146.8
70°	136.9	134.7	130.7	128.0	126.2
72.5°	115.4	114.1	111.9	108.7	106.9
75°	94.4	93.5	91.3	89.9	88.1
77.5°	74.7	74.3	72.9	72.0	70.7
80°	56.4	56.4	55.5	55.0	54.1
82.5°	40.3	39.4	39.4	38.5	38.5
85°	24.6	25.1	25.1	24.6	23.7
87.5°	12.1	12.1	11.6	11.6	10.7
90°	0.4	3.2	5.7	7.4	8.5
92.5°	6.7	3.5	5.7	7.4	7.8
95°	20.2	19.1	5.7	7.4	7.4
97.5°	37.8	40.0	6.4	7.1	7.4
100°	59.1	60.1	61.5	8.8	7.4
102.5°	80.6	82.0	82.7	83.5	53.7
105°	104.0	105.4	105.4	105.4	105.0
107.5°	128.0	128.0	128.7	129.1	127.7
110°	151.3	151.3	152.1	151.0	151.3



TEST NUMBER: P1026872

CATALOG NUMBER: S125DIP-B375D375UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	173.3	174.3	174.7	173.3	172.6
115°	195.2	197.0	197.3	195.9	193.8
117.5°	218.2	218.2	219.6	217.5	216.8
120°	239.4	239.0	240.1	239.4	237.6
122.5°	258.1	259.9	260.3	259.5	257.4
125°	277.6	280.1	280.1	278.6	277.6
127.5°	296.3	298.1	297.7	297.0	294.2
130°	313.3	315.1	315.4	314.4	312.6
132.5°	330.3	332.4	331.3	331.3	329.6
135°	346.2	348.3	347.6	346.9	344.8
137.5°	361.0	363.2	362.4	362.4	360.7
140°	375.5	376.2	375.9	376.6	374.5
142.5°	388.6	389.0	389.7	389.7	387.6
145°	401.3	402.1	402.1	402.4	400.3
147.5°	412.7	412.7	413.0	413.4	410.9
150°	423.3	422.6	423.3	424.0	421.1
152.5°	433.5	431.8	432.5	433.2	430.7
155°	442.0	439.9	440.6	441.7	438.8
157.5°	448.7	447.7	447.7	448.7	445.9
160°	455.8	453.7	454.0	455.4	452.6
162.5°	461.5	459.3	459.7	461.8	458.6
165°	466.4	464.3	464.6	466.8	463.9
167.5°	470.3	468.2	468.5	471.0	467.8
170°	473.5	471.0	471.4	474.2	471.0
172.5°	475.6	473.1	473.8	476.3	473.1
175°	477.0	474.9	475.2	478.1	474.9
177.5°	478.1	476.0	476.3	478.8	476.0
180°	477.0	477.0	477.0	477.0	477.0

(END OF REPORT)