

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027152

Luminaire Tested: S125RDIP-B1270D850UB2750-4F0-XX-W2A-F_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027152
REPORT IS A COMBINATION OF REPORTS P1005293 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIP-B1270D850UB2750-4F0-XX-W2A-F_4000K
Description: Define 5 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8009.0 lumens
Efficiency: N/A
Efficacy: 97.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 82.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027152

CATALOG NUMBER: S125RDIP-B1270D850UB2750-4F0-XX-W2A-F_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1027152

CATALOG NUMBER: S125RDIP-B1270D850UB2750-4F0-XX-W2A-F_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66
1	100	96	92	89	94	90	87	84	79	76	74	68	67	65	59	57	56
2	92	84	78	73	86	79	74	69	69	65	62	60	57	55	52	50	48
3	84	74	67	61	78	70	63	58	61	56	52	54	50	46	46	43	41
4	77	66	58	52	72	62	55	50	55	49	45	48	44	40	42	38	35
5	71	59	51	45	66	56	48	43	49	43	39	43	39	35	38	34	31
6	65	53	45	39	61	50	43	37	44	38	34	39	34	31	34	30	27
7	60	48	40	34	56	45	38	33	40	34	30	36	31	27	31	27	25
8	56	44	36	31	52	41	34	29	37	31	27	33	28	24	29	25	22
9	52	40	32	27	49	38	31	26	34	28	24	30	25	22	27	23	20
10	49	37	30	25	46	35	28	24	31	26	22	28	23	20	25	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13179	13179	13179
5°	13181	12851	12872
10°	13053	12527	12417
15°	12868	12074	11818
20°	12639	11528	11191
25°	12376	10996	10519
30°	12056	10411	9812
35°	11728	9816	9062
40°	11416	9205	8328
45°	11042	8546	7561
50°	10662	7846	6779
55°	10221	7158	5970
60°	9771	6369	5131
65°	9233	5489	4225
70°	8605	4468	3325
75°	7739	3359	2424
80°	6528	2176	1634
85°	4888	1169	921

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11042 cd/sqm

TEST NUMBER: P1027152

CATALOG NUMBER: S125RDIP-B1270D850UB2750-4F0-XX-W2A-F_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	193.6	2.4
10°-20°	541.0	6.8
20°-30°	784.5	9.8
30°-40°	893.8	11.2
40°-50°	871.1	10.9
50°-60°	733.1	9.2
60°-70°	513.8	6.4
70°-80°	263.4	3.3
80°-90°	67.2	0.8
90°-100°	34.8	0.4
100°-110°	231.2	2.9
110°-120°	416.4	5.2
120°-130°	534.5	6.7
130°-140°	574.9	7.2
140°-150°	539.6	6.7
150°-160°	436.4	5.4
160°-170°	282.3	3.5
170°-180°	97.3	1.2
0°-30°	1519.1	19.0
0°-40°	2412.9	30.1
0°-60°	4017.2	50.2
0°-90°	4861.5	60.7
90°-120°	682.5	8.5
90°-150°	2331.4	29.1
90°-180°	3147.0	39.3
0°-180°	8009.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2057	2057	2057	2057	2057	
5°	2054	2048	2031	2046	2043	195
15°	1953	1944	1911	1909	1895	551
25°	1771	1748	1690	1670	1653	815
35°	1526	1488	1418	1373	1352	955
45°	1249	1204	1119	1056	1033	963
55°	948	898	811	741	716	847
65°	642	589	506	444	421	635
75°	342	295	230	196	185	361
85°	86	58	50	48	47	94
90°	1	7	12	16	18	7
95°	43	41	12	16	16	53
105°	223	226	226	226	226	237
115°	419	423	424	421	416	416
125°	596	602	602	598	596	533
135°	744	748	747	745	741	573
145°	862	864	864	864	860	539
155°	949	945	946	949	943	437
165°	1002	997	998	1003	996	283
175°	1025	1020	1021	1027	1020	98
180°	1025	1025	1025	1025	1025	

TEST NUMBER: P1027152

CATALOG NUMBER: S125RDIP-B1270D850UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2057.0	2057.0	2057.0	2057.0	2057.0
2.5°	2061.7	2057.0	2041.5	2057.0	2055.5
5°	2053.9	2047.7	2030.6	2046.1	2043.0
7.5°	2038.4	2032.2	2012.0	2024.4	2021.3
10°	2015.1	2010.4	1988.7	1993.3	1988.7
12.5°	1988.7	1982.4	1951.4	1954.5	1946.7
15°	1952.9	1943.6	1911.0	1909.4	1895.4
17.5°	1915.6	1901.7	1862.8	1855.0	1844.2
20°	1870.6	1855.0	1805.3	1797.6	1783.6
22.5°	1820.9	1805.3	1752.5	1735.4	1724.5
25°	1771.1	1747.8	1690.4	1670.2	1653.1
27.5°	1715.2	1687.3	1626.7	1600.2	1583.2
30°	1653.1	1623.6	1558.3	1522.6	1508.6
32.5°	1592.5	1556.7	1489.9	1449.5	1430.9
35°	1525.7	1488.4	1418.5	1373.4	1351.7
37.5°	1462.0	1416.9	1345.5	1292.6	1270.9
40°	1393.6	1347.0	1272.4	1213.4	1194.7
42.5°	1322.1	1274.0	1196.3	1140.4	1110.9
45°	1249.1	1204.1	1118.6	1056.5	1033.2
47.5°	1173.0	1126.4	1040.9	977.2	950.8
50°	1101.5	1050.3	961.7	896.4	873.1
52.5°	1023.8	971.0	888.7	817.2	793.9
55°	947.7	898.0	811.0	741.1	716.2
57.5°	870.0	817.2	733.3	665.0	643.2
60°	795.5	741.1	657.2	588.8	565.5
62.5°	716.2	665.0	579.5	517.4	494.1
65°	641.7	588.8	506.5	444.3	421.0
67.5°	567.1	514.3	435.0	376.0	357.3
70°	490.9	438.1	360.4	312.3	293.6
72.5°	416.4	365.1	293.6	250.1	239.3
75°	341.8	295.2	229.9	195.8	184.9
77.5°	265.7	228.4	174.0	147.6	138.3
80°	202.0	164.7	121.2	107.2	104.1
82.5°	139.8	107.2	80.8	76.1	74.6
85°	85.5	57.5	49.7	48.2	46.6
87.5°	35.7	24.9	23.3	23.3	21.8
90°	0.8	6.8	12.2	16.0	18.2
92.5°	14.4	7.6	12.2	16.0	16.7
95°	43.3	41.0	12.2	16.0	16.0
97.5°	81.3	85.8	13.7	15.2	16.0
100°	126.8	129.1	132.2	19.0	16.0
102.5°	173.2	176.2	177.7	179.3	115.5
105°	223.3	226.3	226.3	226.3	225.6
107.5°	275.0	275.0	276.5	277.2	274.2
110°	325.1	325.1	326.6	324.3	325.1



TEST NUMBER: P1027152

CATALOG NUMBER: S125RDIP-B1270D850UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	372.2	374.5	375.2	372.2	370.7
115°	419.3	423.1	423.8	420.8	416.2
117.5°	468.6	468.6	471.7	467.1	465.6
120°	514.2	513.5	515.7	514.2	510.4
122.5°	554.5	558.3	559.0	557.5	553.0
125°	596.3	601.6	601.6	598.5	596.3
127.5°	636.5	640.3	639.5	638.0	632.0
130°	673.0	676.8	677.5	675.2	671.4
132.5°	709.4	714.0	711.7	711.7	707.9
135°	743.6	748.2	746.6	745.1	740.6
137.5°	775.5	780.1	778.5	778.5	774.7
140°	806.6	808.2	807.4	808.9	804.4
142.5°	834.8	835.5	837.0	837.0	832.5
145°	862.1	863.6	863.6	864.4	859.8
147.5°	886.4	886.4	887.2	887.9	882.6
150°	909.2	907.7	909.2	910.7	904.6
152.5°	931.2	927.4	928.9	930.5	925.1
155°	949.4	944.9	946.4	948.7	942.6
157.5°	963.9	961.6	961.6	963.9	957.8
160°	979.1	974.5	975.3	978.3	972.2
162.5°	991.2	986.7	987.4	992.0	985.1
165°	1001.9	997.3	998.1	1002.6	996.5
167.5°	1010.2	1005.7	1006.4	1011.7	1004.9
170°	1017.0	1011.7	1012.5	1018.6	1011.7
172.5°	1021.6	1016.3	1017.8	1023.1	1016.3
175°	1024.6	1020.1	1020.8	1026.9	1020.1
177.5°	1026.9	1022.4	1023.1	1028.4	1022.4
180°	1024.6	1024.6	1024.6	1024.6	1024.6

(END OF REPORT)