

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026881

Luminaire Tested: S125DIP-B375D610UB2750-4F0-XX-W2A-D_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026881
REPORT IS A COMBINATION OF REPORTS P1002015 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B375D610UB2750-4F0-XX-W2A-D_3500K
Description: Define 5 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3808.1 lumens
Efficiency: N/A
Efficacy: 134.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.21 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 28.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026881

CATALOG NUMBER: S125DIP-B375D610UB2750-4F0-XX-W2A-D_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1026881

CATALOG NUMBER: S125DIP-B375D610UB2750-4F0-XX-W2A-D_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	43	43	43	35		
1	94	89	85	82	85	81	78	75	65	63	60	50	49	47	37	36	35	29		
2	85	78	72	66	77	70	65	61	57	53	50	44	41	39	32	30	29	24		
3	78	68	61	55	70	62	55	50	50	45	41	39	35	33	28	26	24	20		
4	71	60	52	46	64	55	48	42	44	39	35	34	31	28	25	23	21	17		
5	65	53	45	39	58	49	41	36	39	34	30	31	27	24	23	20	18	14		
6	60	48	40	34	54	43	36	31	35	30	26	28	24	21	20	18	16	13		
7	55	43	35	30	50	39	32	27	32	27	23	25	21	18	19	16	14	11		
8	51	39	31	26	46	35	29	24	29	24	20	23	19	16	17	14	12	10		
9	47	35	28	23	43	32	26	21	26	21	18	21	17	15	16	13	11	9		
10	44	32	25	21	40	30	23	19	24	19	16	19	16	13	15	12	10	8		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2954	2954	2954
5°	2958	2892	2899
10°	2936	2833	2825
15°	2900	2764	2734
20°	2852	2681	2643
25°	2795	2593	2534
30°	2725	2497	2434
35°	2661	2408	2342
40°	2595	2315	2250
45°	2521	2234	2166
50°	2450	2146	2092
55°	2364	2062	2004
60°	2270	1966	1915
65°	2171	1866	1815
70°	2060	1731	1709
75°	1884	1598	1582
80°	1651	1436	1440
85°	1424	1307	1365

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2521 cd/sqm

TEST NUMBER: P1026881

CATALOG NUMBER: S125DIP-B375D610UB2750-4F0-XX-W2A-D_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	43.6	1.1
10°-20°	123.8	3.3
20°-30°	184.1	4.8
30°-40°	218.1	5.7
40°-50°	225.5	5.9
50°-60°	207.7	5.5
60°-70°	167.9	4.4
70°-80°	112.3	3.0
80°-90°	59.2	1.6
90°-100°	59.0	1.5
100°-110°	198.9	5.2
110°-120°	330.9	8.7
120°-130°	413.1	10.8
130°-140°	438.5	11.5
140°-150°	408.6	10.7
150°-160°	329.9	8.7
160°-170°	213.3	5.6
170°-180°	73.6	1.9
0°-30°	351.6	9.2
0°-40°	569.7	15.0
0°-60°	1002.8	26.3
0°-90°	1342.3	35.2
90°-120°	588.8	15.5
90°-150°	1849.0	48.6
90°-180°	2466.0	64.8
0°-180°	3808.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	461	461	461	461	461	
5°	461	460	457	460	460	44
15°	440	441	438	440	438	124
25°	400	401	399	400	398	184
35°	346	349	348	349	349	217
45°	285	290	292	296	296	220
55°	219	226	234	239	240	196
65°	151	161	172	179	181	150
75°	83	95	109	118	121	88
85°	25	40	56	66	69	26
90°	8	27	46	60	64	7
95°	39	49	42	55	58	45
105°	173	182	196	205	208	183
115°	320	326	338	344	343	317
125°	452	456	465	470	470	404
135°	563	566	568	573	572	434
145°	652	653	653	656	654	408
155°	718	714	715	717	712	331
165°	757	754	754	758	753	214
175°	774	771	772	776	771	74
180°	774	774	774	774	774	

TEST NUMBER: P1026881

CATALOG NUMBER: S125DIP-B375D610UB2750-4F0-XX-W2A-D_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	461.0	461.0	461.0	461.0	461.0
2.5°	462.3	461.4	458.3	461.4	461.0
5°	461.0	460.1	456.9	460.5	460.1
7.5°	457.8	457.4	454.2	457.4	456.9
10°	453.3	453.3	449.7	452.8	452.4
12.5°	447.0	447.4	444.7	447.0	445.6
15°	440.2	440.6	437.5	440.2	438.4
17.5°	431.6	432.5	429.3	431.6	430.2
20°	422.1	423.0	419.8	421.2	421.2
22.5°	411.3	413.1	409.4	411.3	409.9
25°	400.0	401.3	398.6	400.4	398.2
27.5°	387.8	389.6	386.4	387.8	386.9
30°	373.7	376.5	373.7	374.6	374.2
32.5°	361.1	363.4	361.5	362.4	362.0
35°	346.2	349.3	348.0	349.3	349.3
37.5°	331.7	334.4	334.0	335.8	335.3
40°	316.8	320.4	320.0	321.8	322.7
42.5°	300.5	305.5	306.9	309.1	309.1
45°	285.2	290.1	292.4	295.6	296.0
47.5°	269.4	273.9	277.5	282.0	282.9
50°	253.1	258.1	263.0	268.0	269.4
52.5°	235.9	242.2	248.6	254.0	254.9
55°	219.2	226.4	233.6	238.6	240.4
57.5°	202.0	210.6	218.7	224.2	225.5
60°	184.8	193.9	202.9	209.7	211.1
62.5°	168.1	177.2	187.1	194.8	196.6
65°	150.9	161.3	172.2	179.0	180.8
67.5°	135.1	145.1	155.9	164.1	166.3
70°	117.5	127.9	139.6	148.2	150.9
72.5°	100.3	111.2	124.3	133.8	135.6
75°	83.2	94.9	109.4	118.4	120.7
77.5°	66.4	80.0	93.5	103.5	105.3
80°	51.1	64.6	80.0	89.9	91.7
82.5°	37.1	51.5	67.3	76.8	80.4
85°	24.9	39.8	55.6	65.5	69.1
87.5°	15.8	30.3	45.6	56.0	59.2
90°	7.8	26.9	46.3	59.6	64.4
92.5°	17.2	25.1	44.5	57.3	61.0
95°	38.6	48.6	42.2	55.0	58.2
97.5°	66.8	81.2	41.5	52.2	55.9
100°	100.9	112.1	128.8	52.8	53.2
102.5°	135.4	146.3	161.4	171.7	126.2
105°	172.9	182.4	196.0	205.0	207.6
107.5°	211.4	217.7	232.0	241.6	242.0
110°	248.9	254.3	268.0	274.9	278.7

TEST NUMBER: P1026881

CATALOG NUMBER: S125DIP-B375D610UB2750-4F0-XX-W2A-D_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	284.5	290.2	303.0	308.9	310.8
115°	319.6	325.7	337.9	343.8	343.1
117.5°	356.5	358.7	372.3	376.6	378.6
120°	390.9	391.7	403.8	410.3	410.2
122.5°	420.9	424.2	434.7	440.8	440.0
125°	452.4	456.1	465.1	470.0	470.5
127.5°	482.5	484.8	492.0	497.6	495.7
130°	510.0	512.4	519.3	523.9	523.3
132.5°	537.1	540.5	543.3	549.7	548.6
135°	562.9	566.0	567.9	572.7	571.5
137.5°	587.0	590.1	590.7	596.1	595.1
140°	610.2	611.3	611.1	617.3	615.6
142.5°	631.4	631.5	632.6	636.7	635.1
145°	652.1	652.7	652.7	655.6	653.9
147.5°	669.9	669.9	670.5	672.0	668.9
150°	687.2	686.0	687.2	688.3	684.2
152.5°	703.8	700.9	702.1	703.2	699.2
155°	717.6	714.1	715.3	717.0	712.4
157.5°	728.5	726.8	726.8	728.5	723.9
160°	740.0	736.5	737.1	739.4	734.8
162.5°	749.2	745.7	746.3	749.7	744.6
165°	757.2	753.8	754.3	757.8	753.2
167.5°	763.5	760.1	760.6	764.7	759.5
170°	768.7	764.7	765.2	769.8	764.7
172.5°	772.1	768.1	769.3	773.3	768.1
175°	774.4	771.0	771.5	776.1	771.0
177.5°	776.1	772.7	773.3	777.3	772.7
180°	774.4	774.4	774.4	774.4	774.4

(END OF REPORT)