

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027159

Luminaire Tested: S125RDIP-B375D1090UB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027159
REPORT IS A COMBINATION OF REPORTS P1005330 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIP-B375D1090UB2750-4F0-XX-W2A-F_2700K
Description: Define 5 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5458.0 lumens
Efficiency: N/A
Efficacy: 131.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 41.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027159

CATALOG NUMBER: S125RDIP-B375D1090UB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1027159

CATALOG NUMBER: S125RDIP-B375D1090UB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	34	34	34
1	92	88	85	81	82	79	76	73	61	59	57	45	44	43	30	29	29
2	84	77	71	66	75	69	64	60	54	50	48	40	37	36	26	25	24
3	77	68	61	55	68	61	55	50	47	43	40	35	32	30	24	22	21
4	70	60	52	47	62	54	47	42	42	38	34	31	28	26	21	19	18
5	64	53	46	40	57	48	41	36	38	33	29	28	25	22	19	17	16
6	59	48	40	34	53	43	36	31	34	29	25	25	22	20	17	15	14
7	55	43	35	30	49	39	32	27	30	26	22	23	20	17	16	14	12
8	51	39	31	26	45	35	29	24	28	23	20	21	18	15	14	12	11
9	47	35	28	23	42	32	26	21	25	21	17	19	16	14	13	11	10
10	44	32	25	21	39	29	23	19	23	19	16	18	14	12	12	10	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3783	3783	3783
5°	3783	3689	3695
10°	3747	3596	3564
15°	3694	3466	3393
20°	3628	3309	3213
25°	3553	3156	3019
30°	3461	2988	2816
35°	3366	2818	2601
40°	3277	2642	2390
45°	3169	2453	2171
50°	3061	2252	1946
55°	2934	2055	1714
60°	2804	1828	1472
65°	2650	1576	1213
70°	2470	1283	955
75°	2221	964	696
80°	1874	625	469
85°	1401	336	265

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3169 cd/sqm

TEST NUMBER: P1027159

CATALOG NUMBER: S125RDIP-B375D1090UB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	55.6	1.0
10°-20°	155.3	2.8
20°-30°	225.2	4.1
30°-40°	256.5	4.7
40°-50°	250.0	4.6
50°-60°	210.4	3.9
60°-70°	147.5	2.7
70°-80°	75.6	1.4
80°-90°	20.8	0.4
90°-100°	44.9	0.8
100°-110°	298.4	5.5
110°-120°	537.3	9.8
120°-130°	689.7	12.6
130°-140°	741.8	13.6
140°-150°	696.2	12.8
150°-160°	563.1	10.3
160°-170°	364.2	6.7
170°-180°	125.6	2.3
0°-30°	436.0	8.0
0°-40°	692.6	12.7
0°-60°	1153.1	21.1
0°-90°	1397.0	25.6
90°-120°	880.5	16.1
90°-150°	3008.1	55.1
90°-180°	4061.0	74.4
0°-180°	5458.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	590	590	590	590	590	
5°	590	588	583	587	586	56
15°	561	558	548	548	544	158
25°	508	502	485	479	474	234
35°	438	427	407	394	388	274
45°	358	346	321	303	297	277
55°	272	258	233	213	206	243
65°	184	169	145	128	121	182
75°	98	85	66	56	53	104
85°	24	16	14	14	13	27
90°	1	9	16	21	24	4
95°	56	53	16	21	21	68
105°	288	292	292	292	291	305
115°	541	546	547	543	537	536
125°	769	776	776	772	769	687
135°	959	965	963	961	956	740
145°	1112	1114	1114	1115	1109	696
155°	1225	1219	1221	1224	1216	564
165°	1293	1287	1288	1294	1286	365
175°	1322	1316	1317	1325	1316	126
180°	1322	1322	1322	1322	1322	

TEST NUMBER: P1027159

CATALOG NUMBER: S125RDIP-B375D1090UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	590.4	590.4	590.4	590.4	590.4
2.5°	591.8	590.4	586.0	590.4	590.0
5°	589.5	587.8	582.9	587.3	586.4
7.5°	585.1	583.3	577.5	581.1	580.2
10°	578.4	577.1	570.8	572.2	570.8
12.5°	570.8	569.0	560.1	561.0	558.8
15°	560.6	557.9	548.5	548.1	544.1
17.5°	549.9	545.8	534.7	532.5	529.3
20°	536.9	532.5	518.2	516.0	512.0
22.5°	522.7	518.2	503.0	498.1	495.0
25°	508.4	501.7	485.2	479.4	474.5
27.5°	492.3	484.3	466.9	459.3	454.4
30°	474.5	466.0	447.3	437.0	433.0
32.5°	457.1	446.8	427.7	416.1	410.7
35°	437.9	427.2	407.2	394.2	388.0
37.5°	419.6	406.7	386.2	371.0	364.8
40°	400.0	386.6	365.2	348.3	342.9
42.5°	379.5	365.7	343.4	327.3	318.9
45°	358.5	345.6	321.1	303.2	296.6
47.5°	336.7	323.3	298.8	280.5	272.9
50°	316.2	301.5	276.0	257.3	250.6
52.5°	293.9	278.7	255.1	234.6	227.9
55°	272.0	257.8	232.8	212.7	205.6
57.5°	249.7	234.6	210.5	190.9	184.6
60°	228.3	212.7	188.6	169.0	162.3
62.5°	205.6	190.9	166.3	148.5	141.8
65°	184.2	169.0	145.4	127.5	120.9
67.5°	162.8	147.6	124.9	107.9	102.6
70°	140.9	125.8	103.5	89.6	84.3
72.5°	119.5	104.8	84.3	71.8	68.7
75°	98.1	84.7	66.0	56.2	53.1
77.5°	76.3	65.6	49.9	42.4	39.7
80°	58.0	47.3	34.8	30.8	29.9
82.5°	40.1	30.8	23.2	21.9	21.4
85°	24.5	16.5	14.3	13.8	13.4
87.5°	10.3	7.1	6.7	6.7	6.2
90°	1.0	8.8	15.7	20.6	23.5
92.5°	18.6	9.8	15.7	20.6	21.6
95°	55.9	52.9	15.7	20.6	20.6
97.5°	104.9	110.7	17.6	19.6	20.6
100°	163.7	166.6	170.5	24.5	20.6
102.5°	223.4	227.4	229.3	231.3	149.0
105°	288.1	292.0	292.0	292.0	291.1
107.5°	354.8	354.8	356.7	357.7	353.8
110°	419.4	419.4	421.4	418.5	419.4

TEST NUMBER: P1027159

CATALOG NUMBER: S125RDIP-B375D1090UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	480.2	483.1	484.1	480.2	478.2
115°	541.0	545.9	546.8	542.9	537.0
117.5°	604.7	604.7	608.6	602.7	600.8
120°	663.5	662.5	665.4	663.5	658.6
122.5°	715.4	720.3	721.3	719.3	713.5
125°	769.3	776.2	776.2	772.3	769.3
127.5°	821.3	826.2	825.2	823.2	815.4
130°	868.3	873.2	874.2	871.2	866.3
132.5°	915.3	921.2	918.3	918.3	913.4
135°	959.4	965.3	963.4	961.4	955.5
137.5°	1000.6	1006.5	1004.5	1004.5	999.6
140°	1040.8	1042.7	1041.8	1043.7	1037.8
142.5°	1077.0	1078.0	1080.0	1080.0	1074.1
145°	1112.3	1114.3	1114.3	1115.3	1109.4
147.5°	1143.7	1143.7	1144.7	1145.6	1138.8
150°	1173.1	1171.1	1173.1	1175.0	1167.2
152.5°	1201.5	1196.6	1198.6	1200.5	1193.7
155°	1225.0	1219.1	1221.1	1224.0	1216.2
157.5°	1243.6	1240.7	1240.7	1243.6	1235.8
160°	1263.2	1257.4	1258.3	1262.3	1254.4
162.5°	1278.9	1273.0	1274.0	1279.9	1271.1
165°	1292.6	1286.8	1287.7	1293.6	1285.8
167.5°	1303.4	1297.5	1298.5	1305.4	1296.6
170°	1312.2	1305.4	1306.4	1314.2	1305.4
172.5°	1318.1	1311.3	1313.2	1320.1	1311.3
175°	1322.0	1316.2	1317.1	1325.0	1316.2
177.5°	1325.0	1319.1	1320.1	1326.9	1319.1
180°	1322.0	1322.0	1322.0	1322.0	1322.0

(END OF REPORT)