

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027172

Luminaire Tested: S125RDIP-B375D1270UB2750-4F0-XX-W2A-F_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027172
REPORT IS A COMBINATION OF REPORTS P1005373 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIP-B375D1270UB2750-4F0-XX-W2A-F_4000K
Description: Define 5 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6187.1 lumens
Efficiency: N/A
Efficacy: 128.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 48
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027172

CATALOG NUMBER: S125RDIP-B375D1270UB2750-4F0-XX-W2A-F_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1027172

CATALOG NUMBER: S125RDIP-B375D1270UB2750-4F0-XX-W2A-F_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	101	101	101	101	89	89	89	89	68	68	68	49	49	49	31	31	31			23
1	92	88	84	81	81	78	75	72	60	58	56	43	42	41	27	27	26			19
2	84	77	71	66	74	68	63	59	52	49	46	38	36	34	24	23	22			16
3	76	67	60	55	67	60	54	49	46	42	39	33	31	29	22	20	19			14
4	70	59	52	46	62	53	47	42	41	37	33	30	27	25	19	18	16			12
5	64	53	45	39	56	47	41	36	37	32	28	27	24	21	17	16	14			10
6	59	47	40	34	52	42	36	31	33	28	25	24	21	19	16	14	13			9
7	54	42	35	30	48	38	32	27	30	25	22	22	19	16	14	13	11			8
8	50	38	31	26	44	34	28	24	27	22	19	20	17	14	13	11	10			7
9	47	35	28	23	41	31	25	21	25	20	17	18	15	13	12	10	9			7
10	43	32	25	20	38	29	23	19	23	18	15	17	14	12	11	9	8			6

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3794	3794	3794
5°	3794	3699	3705
10°	3758	3606	3575
15°	3704	3476	3402
20°	3639	3319	3221
25°	3562	3165	3028
30°	3471	2997	2825
35°	3376	2826	2609
40°	3287	2650	2397
45°	3179	2460	2177
50°	3069	2258	1951
55°	2942	2061	1719
60°	2813	1834	1477
65°	2658	1580	1216
70°	2477	1287	957
75°	2228	967	697
80°	1878	627	471
85°	1407	336	265

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3179 cd/sqm

TEST NUMBER: P1027172

CATALOG NUMBER: S125RDIP-B375D1270UB2750-4F0-XX-W2A-F_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	55.7	0.9
10°-20°	155.7	2.5
20°-30°	225.8	3.6
30°-40°	257.3	4.2
40°-50°	250.8	4.1
50°-60°	211.0	3.4
60°-70°	147.9	2.4
70°-80°	75.8	1.2
80°-90°	21.2	0.3
90°-100°	52.9	0.9
100°-110°	351.6	5.7
110°-120°	633.2	10.2
120°-130°	812.7	13.1
130°-140°	874.1	14.1
140°-150°	820.4	13.3
150°-160°	663.6	10.7
160°-170°	429.2	6.9
170°-180°	148.0	2.4
0°-30°	437.3	7.1
0°-40°	694.6	11.2
0°-60°	1156.4	18.7
0°-90°	1401.3	22.6
90°-120°	1037.7	16.8
90°-150°	3544.9	57.3
90°-180°	4786.0	77.4
0°-180°	6187.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	592	592	592	592	592	
5°	591	589	584	589	588	56
15°	562	560	550	550	546	159
25°	510	503	487	481	476	235
35°	439	428	408	395	389	275
45°	360	347	322	304	297	277
55°	273	258	234	213	206	244
65°	185	170	146	128	121	183
75°	98	85	66	56	53	104
85°	25	16	14	14	13	27
90°	1	10	18	24	28	5
95°	66	62	18	24	24	81
105°	340	344	344	344	343	360
115°	638	643	644	640	633	632
125°	907	915	915	910	907	810
135°	1131	1138	1135	1133	1126	872
145°	1311	1313	1313	1314	1307	820
155°	1444	1437	1439	1442	1433	665
165°	1523	1516	1518	1524	1515	430
175°	1558	1551	1552	1561	1551	148
180°	1558	1558	1558	1558	1558	

TEST NUMBER: P1027172

CATALOG NUMBER: S125RDIP-B375D1270UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	592.1	592.1	592.1	592.1	592.1
2.5°	593.5	592.1	587.7	592.1	591.7
5°	591.2	589.4	584.5	589.0	588.1
7.5°	586.8	585.0	579.2	582.7	581.8
10°	580.1	578.7	572.5	573.8	572.5
12.5°	572.5	570.7	561.7	562.6	560.4
15°	562.2	559.5	550.1	549.6	545.6
17.5°	551.4	547.4	536.2	534.0	530.9
20°	538.5	534.0	519.7	517.4	513.4
22.5°	524.2	519.7	504.5	499.6	496.4
25°	509.8	503.1	486.6	480.8	475.9
27.5°	493.7	485.7	468.3	460.6	455.7
30°	475.9	467.4	448.6	438.3	434.3
32.5°	458.4	448.1	428.9	417.3	411.9
35°	439.2	428.4	408.3	395.4	389.1
37.5°	420.8	407.9	387.3	372.1	365.8
40°	401.2	387.7	366.3	349.3	343.9
42.5°	380.6	366.7	344.4	328.3	319.8
45°	359.6	346.6	322.0	304.1	297.4
47.5°	337.7	324.2	299.6	281.3	273.7
50°	317.1	302.3	276.8	258.1	251.3
52.5°	294.7	279.5	255.8	235.2	228.5
55°	272.8	258.5	233.5	213.3	206.2
57.5°	250.4	235.2	211.1	191.4	185.2
60°	229.0	213.3	189.2	169.5	162.8
62.5°	206.2	191.4	166.8	148.9	142.2
65°	184.7	169.5	145.8	127.9	121.2
67.5°	163.2	148.0	125.2	108.2	102.9
70°	141.3	126.1	103.8	89.9	84.5
72.5°	119.9	105.1	84.5	72.0	68.9
75°	98.4	85.0	66.2	56.4	53.2
77.5°	76.5	65.7	50.1	42.5	39.8
80°	58.1	47.4	34.9	30.9	30.0
82.5°	40.3	30.9	23.3	21.9	21.5
85°	24.6	16.5	14.3	13.9	13.4
87.5°	10.3	7.2	6.7	6.7	6.3
90°	1.2	10.4	18.5	24.3	27.7
92.5°	21.9	11.5	18.5	24.3	25.4
95°	65.8	62.4	18.5	24.3	24.3
97.5°	123.6	130.5	20.8	23.1	24.3
100°	192.9	196.3	201.0	28.9	24.3
102.5°	263.3	267.9	270.2	272.6	175.5
105°	339.5	344.2	344.2	344.2	343.0
107.5°	418.1	418.1	420.4	421.5	416.9
110°	494.3	494.3	496.6	493.1	494.3

TEST NUMBER: P1027172

CATALOG NUMBER: S125RDIP-B375D1270UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	565.9	569.4	570.5	565.9	563.6
115°	637.5	643.3	644.4	639.8	632.9
117.5°	712.6	712.6	717.2	710.3	707.9
120°	781.9	780.7	784.2	781.9	776.1
122.5°	843.1	848.8	850.0	847.7	840.8
125°	906.6	914.7	914.7	910.1	906.6
127.5°	967.8	973.6	972.4	970.1	960.9
130°	1023.2	1029.0	1030.2	1026.7	1020.9
132.5°	1078.7	1085.6	1082.1	1082.1	1076.4
135°	1130.6	1137.6	1135.3	1132.9	1126.0
137.5°	1179.1	1186.1	1183.8	1183.8	1178.0
140°	1226.5	1228.8	1227.6	1230.0	1223.0
142.5°	1269.2	1270.4	1272.7	1272.7	1265.8
145°	1310.8	1313.1	1313.1	1314.3	1307.3
147.5°	1347.8	1347.8	1348.9	1350.1	1342.0
150°	1382.4	1380.1	1382.4	1384.7	1375.5
152.5°	1415.9	1410.1	1412.4	1414.7	1406.7
155°	1443.6	1436.7	1439.0	1442.5	1433.2
157.5°	1465.6	1462.1	1462.1	1465.6	1456.3
160°	1488.7	1481.7	1482.9	1487.5	1478.3
162.5°	1507.1	1500.2	1501.4	1508.3	1497.9
165°	1523.3	1516.4	1517.5	1524.5	1515.2
167.5°	1536.0	1529.1	1530.2	1538.3	1527.9
170°	1546.4	1538.3	1539.5	1548.7	1538.3
172.5°	1553.3	1545.2	1547.6	1555.6	1545.2
175°	1557.9	1551.0	1552.2	1561.4	1551.0
177.5°	1561.4	1554.5	1555.6	1563.7	1554.5
180°	1557.9	1557.9	1557.9	1557.9	1557.9

(END OF REPORT)