

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026903

Luminaire Tested: S125DIP-B375D850UB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026903
REPORT IS A COMBINATION OF REPORTS P1002082 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B375D850UB2750-4F0-XX-W2A-F_5000K
Description: Define 5 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4468.0 lumens
Efficiency: N/A
Efficacy: 131.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 34.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026903

CATALOG NUMBER: S125DIP-B375D850UB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1026903

CATALOG NUMBER: S125DIP-B375D850UB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	73	73	73	56	56	56	39	39	39
1	94	89	86	82	84	81	77	75	64	62	60	49	47	46	35	34	33
2	85	78	72	67	76	70	65	61	56	53	50	43	41	38	31	29	28
3	78	69	61	56	70	62	56	51	49	45	42	38	35	32	27	25	24
4	71	61	53	47	64	55	48	43	44	39	35	34	30	28	24	22	20
5	65	54	46	40	58	49	42	37	39	34	30	30	27	24	22	20	18
6	60	48	40	35	54	44	37	32	35	30	26	27	24	21	20	17	16
7	55	43	36	30	50	39	33	28	32	27	23	25	21	18	18	16	14
8	51	39	32	27	46	36	29	24	29	24	20	22	19	16	16	14	12
9	48	36	28	24	43	32	26	22	26	22	18	21	17	15	15	13	11
10	44	33	26	21	40	30	24	19	24	19	16	19	16	13	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3503	3503	3503
5°	3503	3422	3428
10°	3474	3343	3333
15°	3428	3249	3221
20°	3367	3141	3091
25°	3300	3022	2953
30°	3221	2898	2808
35°	3136	2769	2645
40°	3047	2632	2500
45°	2952	2498	2346
50°	2847	2346	2166
55°	2743	2180	2001
60°	2619	2004	1809
65°	2471	1800	1611
70°	2321	1566	1382
75°	2067	1289	1117
80°	1761	962	821
85°	1361	569	452

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2952 cd/sqm

TEST NUMBER: P1026903

CATALOG NUMBER: S125DIP-B375D850UB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.6	1.2
10°-20°	145.7	3.3
20°-30°	215.1	4.8
30°-40°	251.0	5.6
40°-50°	252.1	5.6
50°-60°	221.3	5.0
60°-70°	164.8	3.7
70°-80°	94.1	2.1
80°-90°	28.6	0.6
90°-100°	33.6	0.8
100°-110°	223.6	5.0
110°-120°	402.7	9.0
120°-130°	516.9	11.6
130°-140°	555.9	12.4
140°-150°	521.7	11.7
150°-160°	422.0	9.4
160°-170°	272.9	6.1
170°-180°	94.1	2.1
0°-30°	412.5	9.2
0°-40°	663.5	14.8
0°-60°	1136.8	25.4
0°-90°	1424.5	31.9
90°-120°	659.9	14.8
90°-150°	2254.4	50.5
90°-180°	3044.0	68.1
0°-180°	4468.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	547	547	547	547	547	
5°	546	545	541	545	544	52
15°	520	519	514	516	516	147
25°	472	470	464	465	464	217
35°	408	406	400	398	394	255
45°	334	332	327	322	320	257
55°	254	253	247	243	240	227
65°	172	171	166	162	160	170
75°	91	90	88	87	85	97
85°	24	24	24	24	23	26
90°	1	7	12	15	18	4
95°	42	40	12	15	15	51
105°	216	219	219	219	218	229
115°	405	409	410	407	402	402
125°	577	582	582	579	577	515
135°	719	724	722	720	716	554
145°	834	835	835	836	831	521
155°	918	914	915	917	912	423
165°	969	964	965	970	964	274
175°	991	986	987	993	986	94
180°	991	991	991	991	991	

TEST NUMBER: P1026903

CATALOG NUMBER: S125DIP-B375D850UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	546.7	546.7	546.7	546.7	546.7
2.5°	548.5	547.2	542.8	547.2	546.7
5°	545.9	545.0	540.7	544.6	544.1
7.5°	542.0	541.1	536.3	540.2	539.8
10°	536.3	535.5	530.7	534.2	533.8
12.5°	529.4	527.7	523.4	526.0	526.0
15°	520.3	519.0	514.3	516.5	516.5
17.5°	510.8	508.7	503.9	506.5	504.3
20°	498.3	497.4	491.8	494.8	492.7
22.5°	485.7	484.0	478.8	480.6	479.3
25°	472.3	470.2	464.5	465.4	464.1
27.5°	456.8	455.5	449.8	450.3	449.0
30°	441.6	440.3	433.8	433.0	431.7
32.5°	425.2	423.0	417.4	415.7	413.1
35°	407.9	406.2	400.1	397.9	394.5
37.5°	390.1	388.0	382.4	379.3	377.2
40°	372.0	369.8	363.8	359.9	358.6
42.5°	352.5	350.8	344.7	341.3	339.1
45°	333.9	332.2	327.0	321.8	320.5
47.5°	313.6	314.0	307.5	302.3	299.3
50°	294.1	292.8	287.6	282.0	279.0
52.5°	274.2	273.4	267.7	263.0	259.5
55°	254.3	253.0	247.0	243.1	240.1
57.5°	233.1	232.7	227.5	222.3	221.0
60°	213.2	211.5	206.8	202.4	199.4
62.5°	192.5	191.2	187.3	182.5	180.4
65°	171.7	170.9	166.1	162.2	160.5
67.5°	151.4	149.7	146.2	142.7	141.9
70°	132.4	130.2	126.3	123.7	122.0
72.5°	111.6	110.3	108.1	105.1	103.4
75°	91.3	90.4	88.2	86.9	85.2
77.5°	72.2	71.8	70.5	69.6	68.3
80°	54.5	54.5	53.6	53.2	52.3
82.5°	38.9	38.1	38.1	37.2	37.2
85°	23.8	24.2	24.2	23.8	22.9
87.5°	11.7	11.7	11.2	11.2	10.4
90°	0.7	6.6	11.8	15.4	17.6
92.5°	14.0	7.3	11.8	15.4	16.2
95°	41.9	39.7	11.8	15.4	15.4
97.5°	78.6	83.0	13.2	14.7	15.4
100°	122.7	124.9	127.8	18.4	15.4
102.5°	167.5	170.4	171.9	173.3	111.6
105°	215.9	218.9	218.9	218.9	218.1
107.5°	265.9	265.9	267.3	268.1	265.1
110°	314.4	314.4	315.8	313.6	314.4

TEST NUMBER: P1026903

CATALOG NUMBER: S125DIP-B375D850UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	359.9	362.1	362.8	359.9	358.4
115°	405.4	409.1	409.8	406.9	402.5
117.5°	453.2	453.2	456.1	451.7	450.2
120°	497.2	496.5	498.7	497.2	493.6
122.5°	536.2	539.8	540.6	539.1	534.7
125°	576.6	581.7	581.7	578.8	576.6
127.5°	615.5	619.2	618.4	617.0	611.1
130°	650.7	654.4	655.1	652.9	649.3
132.5°	686.0	690.4	688.2	688.2	684.5
135°	719.0	723.5	722.0	720.5	716.1
137.5°	749.9	754.3	752.8	752.8	749.2
140°	780.0	781.5	780.7	782.2	777.8
142.5°	807.2	807.9	809.4	809.4	805.0
145°	833.6	835.1	835.1	835.8	831.4
147.5°	857.1	857.1	857.9	858.6	853.5
150°	879.2	877.7	879.2	880.6	874.8
152.5°	900.5	896.8	898.3	899.7	894.6
155°	918.1	913.7	915.2	917.4	911.5
157.5°	932.0	929.8	929.8	932.0	926.2
160°	946.7	942.3	943.1	946.0	940.1
162.5°	958.5	954.1	954.8	959.2	952.6
165°	968.8	964.4	965.1	969.5	963.6
167.5°	976.8	972.4	973.2	978.3	971.7
170°	983.5	978.3	979.0	984.9	978.3
172.5°	987.9	982.7	984.2	989.3	982.7
175°	990.8	986.4	987.1	993.0	986.4
177.5°	993.0	988.6	989.3	994.5	988.6
180°	990.8	990.8	990.8	990.8	990.8

(END OF REPORT)