

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027181

Luminaire Tested: S125RDIP-B375D375UB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027181
REPORT IS A COMBINATION OF REPORTS P1005412 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIP-B375D375UB2750-4F0-XX-W2A-F_3500K
Description: Define 5 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2894.0 lumens
Efficiency: N/A
Efficacy: 129.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 22.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027181

CATALOG NUMBER: S125RDIP-B375D375UB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1027181

CATALOG NUMBER: S125RDIP-B375D375UB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55
1	98	94	90	86	90	86	83	80	73	71	68	60	59	57	49	48	47
2	89	82	76	71	82	76	70	66	64	60	57	53	51	48	43	42	40
3	81	72	65	59	75	67	60	55	57	52	48	47	44	41	39	36	34
4	75	64	56	50	68	59	52	47	50	45	41	42	38	35	35	32	30
5	69	57	49	43	63	53	46	41	45	40	36	38	34	31	31	28	26
6	63	51	43	37	58	48	41	35	41	35	31	34	30	27	28	25	23
7	58	46	38	33	54	43	36	31	37	31	27	31	27	24	26	23	20
8	54	42	34	29	50	39	32	28	34	28	24	29	24	21	24	21	18
9	51	38	31	26	47	36	29	25	31	26	22	26	22	19	22	19	17
10	47	35	28	23	44	33	27	22	29	23	20	24	20	17	21	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3832	3832	3832
5°	3833	3736	3742
10°	3795	3642	3610
15°	3741	3510	3436
20°	3675	3352	3254
25°	3598	3197	3058
30°	3505	3027	2853
35°	3410	2854	2635
40°	3319	2676	2422
45°	3211	2484	2198
50°	3100	2281	1971
55°	2971	2081	1736
60°	2841	1852	1492
65°	2685	1596	1228
70°	2501	1299	967
75°	2251	977	705
80°	1897	632	476
85°	1418	341	269

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3211 cd/sqm

TEST NUMBER: P1027181

CATALOG NUMBER: S125RDIP-B375D375UB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.3	1.9
10°-20°	157.3	5.4
20°-30°	228.1	7.9
30°-40°	259.9	9.0
40°-50°	253.3	8.8
50°-60°	213.2	7.4
60°-70°	149.4	5.2
70°-80°	76.6	2.6
80°-90°	19.8	0.7
90°-100°	16.4	0.6
100°-110°	108.8	3.8
110°-120°	195.8	6.8
120°-130°	251.4	8.7
130°-140°	270.4	9.3
140°-150°	253.8	8.8
150°-160°	205.3	7.1
160°-170°	132.7	4.6
170°-180°	45.8	1.6
0°-30°	441.7	15.3
0°-40°	701.5	24.2
0°-60°	1168.0	40.4
0°-90°	1413.7	48.9
90°-120°	321.0	11.1
90°-150°	1096.5	37.9
90°-180°	1480.0	51.1
0°-180°	2894.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	598	598	598	598	598	
5°	597	595	590	595	594	57
15°	568	565	556	555	551	160
25°	515	508	492	486	481	237
35°	444	433	412	399	393	278
45°	363	350	325	307	300	280
55°	276	261	236	216	208	246
65°	187	171	147	129	122	185
75°	99	86	67	57	54	105
85°	25	17	14	14	14	27
90°	0	3	6	8	9	2
95°	20	19	6	8	8	25
105°	105	106	106	106	106	111
115°	197	199	199	198	196	195
125°	280	283	283	282	280	251
135°	350	352	351	350	348	270
145°	406	406	406	406	404	254
155°	446	444	445	446	443	206
165°	471	469	469	472	469	133
175°	482	480	480	483	480	46
180°	482	482	482	482	482	

TEST NUMBER: P1027181

CATALOG NUMBER: S125RDIP-B375D375UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	598.1	598.1	598.1	598.1	598.1
2.5°	599.4	598.1	593.5	598.1	597.6
5°	597.2	595.3	590.4	594.9	594.0
7.5°	592.6	590.8	585.0	588.6	587.7
10°	585.9	584.5	578.2	579.5	578.2
12.5°	578.2	576.4	567.3	568.2	566.0
15°	567.8	565.1	555.6	555.1	551.1
17.5°	557.0	552.9	541.6	539.3	536.2
20°	543.9	539.3	524.9	522.6	518.6
22.5°	529.4	524.9	509.5	504.6	501.4
25°	514.9	508.2	491.5	485.6	480.6
27.5°	498.7	490.6	472.9	465.3	460.3
30°	480.6	472.0	453.1	442.7	438.6
32.5°	463.0	452.6	433.2	421.4	416.0
35°	443.6	432.7	412.4	399.3	393.0
37.5°	425.1	412.0	391.2	375.8	369.5
40°	405.2	391.6	369.9	352.8	347.4
42.5°	384.4	370.4	347.8	331.6	323.0
45°	363.2	350.1	325.2	307.2	300.4
47.5°	341.0	327.5	302.6	284.1	276.4
50°	320.3	305.4	279.6	260.6	253.9
52.5°	297.7	282.3	258.4	237.6	230.8
55°	275.5	261.1	235.8	215.5	208.2
57.5°	253.0	237.6	213.2	193.3	187.0
60°	231.3	215.5	191.1	171.2	164.4
62.5°	208.2	193.3	168.5	150.4	143.6
65°	186.6	171.2	147.3	129.2	122.4
67.5°	164.9	149.5	126.5	109.3	103.9
70°	142.7	127.4	104.8	90.8	85.4
72.5°	121.1	106.2	85.4	72.7	69.6
75°	99.4	85.8	66.9	56.9	53.8
77.5°	77.2	66.4	50.6	42.9	40.2
80°	58.7	47.9	35.2	31.2	30.3
82.5°	40.7	31.2	23.5	22.1	21.7
85°	24.8	16.7	14.5	14.0	13.6
87.5°	10.4	7.2	6.8	6.8	6.3
90°	0.4	3.2	5.7	7.5	8.6
92.5°	6.8	3.6	5.7	7.5	7.9
95°	20.4	19.3	5.7	7.5	7.5
97.5°	38.2	40.4	6.4	7.1	7.5
100°	59.7	60.7	62.2	8.9	7.5
102.5°	81.4	82.9	83.6	84.3	54.3
105°	105.0	106.5	106.5	106.5	106.1
107.5°	129.3	129.3	130.0	130.4	129.0
110°	152.9	152.9	153.6	152.5	152.9



TEST NUMBER: P1027181

CATALOG NUMBER: S125RDIP-B375D375UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	175.0	176.1	176.5	175.0	174.3
115°	197.2	199.0	199.3	197.9	195.8
117.5°	220.4	220.4	221.8	219.7	219.0
120°	241.8	241.5	242.6	241.8	240.1
122.5°	260.8	262.6	262.9	262.2	260.1
125°	280.4	282.9	282.9	281.5	280.4
127.5°	299.4	301.1	300.8	300.1	297.2
130°	316.5	318.3	318.6	317.6	315.8
132.5°	333.6	335.8	334.7	334.7	332.9
135°	349.7	351.9	351.2	350.4	348.3
137.5°	364.7	366.9	366.2	366.2	364.4
140°	379.4	380.1	379.7	380.4	378.3
142.5°	392.6	392.9	393.7	393.7	391.5
145°	405.5	406.2	406.2	406.5	404.4
147.5°	416.9	416.9	417.2	417.6	415.1
150°	427.6	426.9	427.6	428.3	425.5
152.5°	438.0	436.2	436.9	437.6	435.1
155°	446.5	444.4	445.1	446.2	443.3
157.5°	453.3	452.2	452.2	453.3	450.5
160°	460.5	458.3	458.7	460.1	457.2
162.5°	466.2	464.0	464.4	466.5	463.3
165°	471.2	469.0	469.4	471.5	468.7
167.5°	475.1	473.0	473.3	475.8	472.6
170°	478.3	475.8	476.2	479.0	475.8
172.5°	480.5	478.0	478.7	481.2	478.0
175°	481.9	479.8	480.1	483.0	479.8
177.5°	483.0	480.8	481.2	483.7	480.8
180°	481.9	481.9	481.9	481.9	481.9

(END OF REPORT)