

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026912

Luminaire Tested: S125DIP-B610D1090UB2750-4F0-XX-W2A-D_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026912
REPORT IS A COMBINATION OF REPORTS P1002136 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B610D1090UB2750-4F0-XX-W2A-D_4000K
Description: Define 5 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6452.0 lumens
Efficiency: N/A
Efficacy: 122.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.21 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 52.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026912

CATALOG NUMBER: S125DIP-B610D1090UB2750-4F0-XX-W2A-D_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1026912

CATALOG NUMBER: S125DIP-B610D1090UB2750-4F0-XX-W2A-D_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	75	75	75	58	58	58	42	42	42
1	94	89	85	82	85	81	77	74	65	62	60	50	48	47	36	35	34
2	85	78	72	66	77	70	65	61	56	53	49	44	41	39	32	30	29
3	78	68	61	55	70	62	55	50	50	45	41	38	35	33	28	26	24
4	71	60	52	46	64	54	48	42	44	39	35	34	30	28	25	22	21
5	65	53	45	39	58	48	41	36	39	34	30	30	27	24	22	20	18
6	60	48	40	34	54	43	36	31	35	30	26	27	24	21	20	18	16
7	55	43	35	30	49	39	32	27	32	26	23	25	21	18	18	16	14
8	51	39	31	26	46	35	29	24	29	24	20	23	19	16	17	14	12
9	47	35	28	23	43	32	26	21	26	21	18	21	17	14	15	13	11
10	44	32	25	20	40	30	23	19	24	19	16	19	16	13	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4916	4916	4916
5°	4924	4813	4825
10°	4887	4715	4702
15°	4828	4601	4550
20°	4747	4463	4399
25°	4653	4316	4217
30°	4537	4156	4051
35°	4429	4008	3898
40°	4320	3853	3744
45°	4196	3718	3606
50°	4078	3572	3482
55°	3934	3432	3336
60°	3779	3274	3187
65°	3616	3106	3020
70°	3429	2882	2846
75°	3134	2659	2633
80°	2747	2391	2397
85°	2367	2175	2274

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 4196 cd/sqm

TEST NUMBER: P1026912

CATALOG NUMBER: S125DIP-B610D1090UB2750-4F0-XX-W2A-D_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.6	1.1
10°-20°	206.1	3.2
20°-30°	306.5	4.8
30°-40°	363.0	5.6
40°-50°	375.3	5.8
50°-60°	345.7	5.4
60°-70°	279.5	4.3
70°-80°	187.0	2.9
80°-90°	98.6	1.5
90°-100°	99.4	1.5
100°-110°	339.4	5.3
110°-120°	565.8	8.8
120°-130°	706.9	11.0
130°-140°	750.6	11.6
140°-150°	699.6	10.8
150°-160°	564.8	8.8
160°-170°	365.3	5.7
170°-180°	126.0	2.0
0°-30°	585.2	9.1
0°-40°	948.2	14.7
0°-60°	1669.2	25.9
0°-90°	2234.4	34.6
90°-120°	1004.6	15.6
90°-150°	3161.7	49.0
90°-180°	4218.0	65.4
0°-180°	6452.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	767	767	767	767	767	
5°	767	766	760	767	766	73
15°	733	734	728	733	730	206
25°	666	668	664	666	663	307
35°	576	582	579	582	582	361
45°	475	483	487	492	493	366
55°	365	377	389	397	400	326
65°	251	269	287	298	301	249
75°	138	158	182	197	201	147
85°	41	66	92	109	115	43
90°	13	45	77	100	108	11
95°	66	82	71	92	97	76
105°	296	312	334	349	354	313
115°	547	557	578	587	586	542
125°	775	781	796	804	805	692
135°	964	969	972	980	978	743
145°	1116	1118	1118	1122	1120	698
155°	1229	1223	1225	1228	1220	566
165°	1296	1291	1292	1297	1290	366
175°	1326	1320	1321	1329	1320	126
180°	1326	1326	1326	1326	1326	

TEST NUMBER: P1026912

CATALOG NUMBER: S125DIP-B610D1090UB2750-4F0-XX-W2A-D_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	767.3	767.3	767.3	767.3	767.3
2.5°	769.6	768.1	762.8	768.1	767.3
5°	767.3	765.8	760.5	766.6	765.8
7.5°	762.0	761.3	756.0	761.3	760.5
10°	754.5	754.5	748.5	753.8	753.0
12.5°	744.0	744.7	740.2	744.0	741.7
15°	732.7	733.5	728.2	732.7	729.7
17.5°	718.4	719.9	714.7	718.4	716.2
20°	702.6	704.1	698.9	701.1	701.1
22.5°	684.6	687.6	681.6	684.6	682.3
25°	665.8	668.0	663.5	666.5	662.7
27.5°	645.4	648.5	643.2	645.4	643.9
30°	622.1	626.6	622.1	623.6	622.9
32.5°	601.1	604.8	601.8	603.3	602.6
35°	576.2	581.5	579.2	581.5	581.5
37.5°	552.2	556.7	555.9	558.9	558.2
40°	527.3	533.4	532.6	535.6	537.1
42.5°	500.3	508.5	510.8	514.6	514.6
45°	474.7	483.0	486.7	492.0	492.7
47.5°	448.4	455.9	461.9	469.4	470.9
50°	421.3	429.5	437.8	446.1	448.4
52.5°	392.7	403.2	413.7	422.8	424.3
55°	364.8	376.9	388.9	397.2	400.2
57.5°	336.3	350.6	364.1	373.1	375.4
60°	307.7	322.7	337.8	349.1	351.3
62.5°	279.8	294.9	311.4	324.2	327.2
65°	251.3	268.6	286.6	297.9	300.9
67.5°	224.9	241.5	259.5	273.1	276.8
70°	195.6	212.9	232.5	246.7	251.3
72.5°	167.0	185.1	206.9	222.7	225.7
75°	138.4	158.0	182.0	197.1	200.9
77.5°	110.6	133.2	155.7	172.3	175.3
80°	85.0	107.6	133.2	149.7	152.7
82.5°	61.7	85.8	112.1	127.9	133.9
85°	41.4	66.2	92.5	109.1	115.1
87.5°	26.3	50.4	76.0	93.3	98.5
90°	13.0	44.9	77.4	99.6	107.9
92.5°	29.2	42.1	74.4	95.8	102.1
95°	65.8	82.4	70.6	92.1	97.3
97.5°	114.2	138.2	69.6	87.4	93.6
100°	172.4	191.2	219.1	88.5	89.1
102.5°	231.6	249.8	275.1	292.2	214.1
105°	295.8	311.7	334.3	349.3	353.6
107.5°	361.8	372.3	396.2	412.2	412.7
110°	426.0	435.0	458.1	469.3	475.6

TEST NUMBER: P1026912

CATALOG NUMBER: S125DIP-B610D1090UB2750-4F0-XX-W2A-D_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	486.9	496.6	517.9	527.5	530.9
115°	547.1	557.3	577.8	587.4	586.0
117.5°	610.3	614.0	636.7	643.6	646.9
120°	669.2	670.4	690.7	701.5	701.1
122.5°	720.5	726.2	743.7	753.8	752.5
125°	774.6	780.8	795.8	803.8	804.7
127.5°	826.0	830.1	841.9	851.2	847.9
130°	873.2	877.3	888.8	896.4	895.2
132.5°	919.5	925.4	930.0	940.6	938.7
135°	963.8	969.0	972.2	980.0	977.9
137.5°	1005.1	1010.3	1011.3	1020.3	1018.4
140°	1044.7	1046.6	1046.3	1056.6	1053.7
142.5°	1081.0	1081.2	1083.2	1090.0	1087.1
145°	1116.4	1117.6	1117.6	1122.4	1119.5
147.5°	1147.1	1147.1	1148.0	1150.5	1145.1
150°	1176.5	1174.6	1176.5	1178.5	1171.4
152.5°	1205.1	1200.1	1202.1	1204.1	1197.2
155°	1228.6	1222.7	1224.7	1227.7	1219.8
157.5°	1247.3	1244.4	1244.4	1247.3	1239.5
160°	1267.0	1261.1	1262.1	1266.0	1258.1
162.5°	1282.7	1276.8	1277.8	1283.7	1274.8
165°	1296.5	1290.6	1291.5	1297.4	1289.6
167.5°	1307.3	1301.4	1302.4	1309.2	1300.4
170°	1316.1	1309.2	1310.2	1318.1	1309.2
172.5°	1322.0	1315.1	1317.1	1324.0	1315.1
175°	1325.9	1320.1	1321.0	1328.9	1320.1
177.5°	1328.9	1323.0	1324.0	1330.9	1323.0
180°	1325.9	1325.9	1325.9	1325.9	1325.9

(END OF REPORT)