

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026917

Luminaire Tested: S125DIP-B610D1090UB2750-4F0-XX-W2A-F_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026917
REPORT IS A COMBINATION OF REPORTS P1002141 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B610D1090UB2750-4F0-XX-W2A-F_4000K
Description: Define 5 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6550.0 lumens
Efficiency: N/A
Efficacy: 124.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 52.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026917

CATALOG NUMBER: S125DIP-B610D1090UB2750-4F0-XX-W2A-F_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1026917

CATALOG NUMBER: S125DIP-B610D1090UB2750-4F0-XX-W2A-F_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45
1	95	91	87	83	86	82	79	76	67	65	63	53	51	50	40	39	38
2	86	79	73	68	78	72	67	63	59	55	52	46	44	42	35	33	32
3	79	70	62	57	71	63	57	52	52	47	43	41	38	35	31	29	27
4	72	61	54	48	65	56	49	44	46	41	37	36	33	30	28	25	23
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	22	20
6	61	49	41	35	55	45	38	33	37	32	28	29	26	23	22	20	18
7	56	44	36	31	51	40	34	29	33	28	24	27	23	20	20	18	16
8	52	40	32	27	47	37	30	25	30	25	21	24	21	18	19	16	14
9	48	36	29	24	44	33	27	22	28	23	19	22	19	16	17	15	13
10	45	33	26	22	41	31	24	20	25	21	17	21	17	14	16	13	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6093	6093	6093
5°	6093	5951	5963
10°	6043	5815	5796
15°	5963	5652	5601
20°	5856	5462	5377
25°	5741	5256	5136
30°	5602	5041	4883
35°	5453	4816	4600
40°	5300	4577	4348
45°	5134	4345	4080
50°	4952	4082	3767
55°	4771	3791	3480
60°	4556	3485	3146
65°	4298	3131	2801
70°	4035	2724	2403
75°	3593	2243	1943
80°	3063	1675	1429
85°	2367	990	788

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5134 cd/sqm

TEST NUMBER: P1026917

CATALOG NUMBER: S125DIP-B610D1090UB2750-4F0-XX-W2A-F_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	89.7	1.4
10°-20°	253.5	3.9
20°-30°	374.2	5.7
30°-40°	436.6	6.7
40°-50°	438.5	6.7
50°-60°	384.9	5.9
60°-70°	286.7	4.4
70°-80°	163.7	2.5
80°-90°	49.2	0.8
90°-100°	45.0	0.7
100°-110°	299.2	4.6
110°-120°	538.9	8.2
120°-130°	691.7	10.6
130°-140°	744.0	11.4
140°-150°	698.2	10.7
150°-160°	564.8	8.6
160°-170°	365.3	5.6
170°-180°	126.0	1.9
0°-30°	717.4	11.0
0°-40°	1154.0	17.6
0°-60°	1977.3	30.2
0°-90°	2477.0	37.8
90°-120°	883.1	13.5
90°-150°	3017.0	46.1
90°-180°	4073.0	62.2
0°-180°	6550.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	951	951	951	951	951	
5°	949	948	940	947	946	90
15°	905	903	894	898	898	255
25°	822	818	808	810	807	378
35°	709	706	696	692	686	444
45°	581	578	569	560	558	447
55°	442	440	430	423	418	395
65°	299	297	289	282	279	296
75°	159	157	154	151	148	169
85°	41	42	42	41	40	45
90°	1	9	16	21	24	6
95°	56	53	16	21	21	69
105°	289	293	293	293	292	306
115°	543	548	548	544	539	538
125°	772	778	778	774	772	689
135°	962	968	966	964	958	742
145°	1116	1118	1118	1119	1113	698
155°	1229	1223	1225	1228	1220	566
165°	1296	1291	1292	1297	1290	366
175°	1326	1320	1321	1329	1320	126
180°	1326	1326	1326	1326	1326	

TEST NUMBER: P1026917

CATALOG NUMBER: S125DIP-B610D1090UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	950.9	950.9	950.9	950.9	950.9
2.5°	953.9	951.7	944.1	951.7	950.9
5°	949.4	947.9	940.4	947.2	946.4
7.5°	942.6	941.1	932.9	939.6	938.9
10°	932.9	931.4	923.1	929.1	928.3
12.5°	920.8	917.8	910.3	914.8	914.8
15°	905.0	902.8	894.5	898.3	898.3
17.5°	888.5	884.7	876.4	881.0	877.2
20°	866.7	865.2	855.4	860.6	856.9
22.5°	844.8	841.8	832.8	835.8	833.6
25°	821.5	817.8	808.0	809.5	807.2
27.5°	794.4	792.2	782.4	783.2	780.9
30°	768.1	765.8	754.6	753.1	750.8
32.5°	739.5	735.8	726.0	723.0	718.5
35°	709.4	706.4	695.9	692.1	686.1
37.5°	678.6	674.8	665.0	659.8	656.0
40°	647.0	643.2	632.7	625.9	623.7
42.5°	613.1	610.1	599.6	593.6	589.8
45°	580.8	577.8	568.7	559.7	557.5
47.5°	545.4	546.2	534.9	525.9	520.6
50°	511.6	509.3	500.3	490.5	485.2
52.5°	477.0	475.5	465.7	457.4	451.4
55°	442.4	440.1	429.6	422.8	417.5
57.5°	405.5	404.7	395.7	386.7	384.4
60°	370.9	367.9	359.6	352.1	346.8
62.5°	334.8	332.5	325.7	317.5	313.7
65°	298.7	297.2	288.9	282.1	279.1
67.5°	263.3	260.3	254.3	248.3	246.8
70°	230.2	226.4	219.7	215.2	212.2
72.5°	194.1	191.8	188.1	182.8	179.8
75°	158.7	157.2	153.5	151.2	148.2
77.5°	125.6	124.9	122.6	121.1	118.9
80°	94.8	94.8	93.3	92.5	91.0
82.5°	67.7	66.2	66.2	64.7	64.7
85°	41.4	42.1	42.1	41.4	39.9
87.5°	20.3	20.3	19.6	19.6	18.1
90°	1.0	8.8	15.7	20.6	23.6
92.5°	18.7	9.8	15.7	20.6	21.6
95°	56.0	53.1	15.7	20.6	20.6
97.5°	105.2	111.1	17.7	19.7	20.6
100°	164.1	167.1	171.0	24.6	20.6
102.5°	224.1	228.0	230.0	232.0	149.4
105°	289.0	292.9	292.9	292.9	291.9
107.5°	355.8	355.8	357.8	358.8	354.8
110°	420.7	420.7	422.7	419.7	420.7

TEST NUMBER: P1026917

CATALOG NUMBER: S125DIP-B610D1090UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	481.6	484.6	485.6	481.6	479.7
115°	542.6	547.5	548.5	544.5	538.6
117.5°	606.5	606.5	610.4	604.5	602.5
120°	665.4	664.4	667.4	665.4	660.5
122.5°	717.5	722.4	723.4	721.5	715.6
125°	771.6	778.5	778.5	774.5	771.6
127.5°	823.7	828.6	827.6	825.6	817.8
130°	870.9	875.8	876.8	873.8	868.9
132.5°	918.0	923.9	921.0	921.0	916.1
135°	962.3	968.2	966.2	964.2	958.3
137.5°	1003.6	1009.5	1007.5	1007.5	1002.6
140°	1043.9	1045.8	1044.8	1046.8	1040.9
142.5°	1080.2	1081.2	1083.2	1083.2	1077.3
145°	1115.6	1117.6	1117.6	1118.6	1112.7
147.5°	1147.1	1147.1	1148.0	1149.0	1142.1
150°	1176.5	1174.6	1176.5	1178.5	1170.6
152.5°	1205.1	1200.1	1202.1	1204.1	1197.2
155°	1228.6	1222.7	1224.7	1227.7	1219.8
157.5°	1247.3	1244.4	1244.4	1247.3	1239.5
160°	1267.0	1261.1	1262.1	1266.0	1258.1
162.5°	1282.7	1276.8	1277.8	1283.7	1274.8
165°	1296.5	1290.6	1291.5	1297.4	1289.6
167.5°	1307.3	1301.4	1302.4	1309.2	1300.4
170°	1316.1	1309.2	1310.2	1318.1	1309.2
172.5°	1322.0	1315.1	1317.1	1324.0	1315.1
175°	1325.9	1320.1	1321.0	1328.9	1320.1
177.5°	1328.9	1323.0	1324.0	1330.9	1323.0
180°	1325.9	1325.9	1325.9	1325.9	1325.9

(END OF REPORT)