

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027203

Luminaire Tested: S125RDIP-B375D850UB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027203
REPORT IS A COMBINATION OF REPORTS P1005494 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIP-B375D850UB2750-4F0-XX-W2A-F_5000K
Description: Define 5 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4398.0 lumens
Efficiency: N/A
Efficacy: 129.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 34.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027203

CATALOG NUMBER: S125RDIP-B375D850UB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1027203

CATALOG NUMBER: S125RDIP-B375D850UB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	38	38	38
1	94	89	86	82	84	81	77	75	64	62	60	48	47	46	34	33	33
2	85	78	72	67	76	71	66	61	56	53	50	43	40	38	30	29	28
3	78	69	62	56	70	62	56	51	49	45	42	38	35	33	27	25	24
4	71	61	53	48	64	55	49	44	44	39	36	34	31	28	24	22	21
5	65	54	46	41	58	49	42	37	39	34	31	30	27	24	22	20	18
6	60	48	41	35	54	44	37	32	35	30	27	27	24	21	20	18	16
7	55	44	36	31	50	40	33	28	32	27	23	25	21	19	18	16	14
8	51	40	32	27	46	36	29	25	29	24	21	23	19	17	17	14	13
9	48	36	29	24	43	33	26	22	27	22	18	21	17	15	15	13	11
10	45	33	26	21	40	30	24	20	24	20	17	19	16	13	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3669	3669	3669
5°	3670	3578	3584
10°	3634	3487	3457
15°	3582	3361	3290
20°	3519	3210	3115
25°	3446	3061	2928
30°	3356	2898	2732
35°	3265	2733	2523
40°	3179	2562	2319
45°	3075	2379	2105
50°	2969	2184	1888
55°	2845	1993	1662
60°	2721	1774	1428
65°	2570	1528	1176
70°	2396	1243	925
75°	2156	935	675
80°	1816	605	455
85°	1361	324	257

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3075 cd/sqm

TEST NUMBER: P1027203

CATALOG NUMBER: S125RDIP-B375D850UB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.9	1.2
10°-20°	150.6	3.4
20°-30°	218.4	5.0
30°-40°	248.8	5.7
40°-50°	242.5	5.5
50°-60°	204.1	4.6
60°-70°	143.0	3.3
70°-80°	73.3	1.7
80°-90°	19.8	0.4
90°-100°	33.6	0.8
100°-110°	223.6	5.1
110°-120°	402.7	9.2
120°-130°	516.9	11.8
130°-140°	555.9	12.6
140°-150°	521.7	11.9
150°-160°	422.0	9.6
160°-170°	272.9	6.2
170°-180°	94.1	2.1
0°-30°	422.9	9.6
0°-40°	671.7	15.3
0°-60°	1118.4	25.4
0°-90°	1354.5	30.8
90°-120°	659.9	15.0
90°-150°	2254.4	51.3
90°-180°	3044.0	69.2
0°-180°	4398.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	573	573	573	573	573	
5°	572	570	565	570	569	54
15°	544	541	532	532	528	153
25°	493	487	471	465	460	227
35°	425	414	395	382	376	266
45°	348	335	311	294	288	268
55°	264	250	226	206	199	236
65°	179	164	141	124	117	177
75°	95	82	64	54	52	101
85°	24	16	14	13	13	26
90°	1	7	12	15	18	3
95°	42	40	12	15	15	51
105°	216	219	219	219	218	229
115°	405	409	410	407	402	402
125°	577	582	582	579	577	515
135°	719	724	722	720	716	554
145°	834	835	835	836	831	521
155°	918	914	915	917	912	423
165°	969	964	965	970	964	274
175°	991	986	987	993	986	94
180°	991	991	991	991	991	

TEST NUMBER: P1027203

CATALOG NUMBER: S125RDIP-B375D850UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	572.7	572.7	572.7	572.7	572.7
2.5°	574.0	572.7	568.3	572.7	572.2
5°	571.8	570.1	565.3	569.6	568.8
7.5°	567.5	565.7	560.1	563.6	562.7
10°	561.0	559.7	553.6	554.9	553.6
12.5°	553.6	551.9	543.3	544.1	542.0
15°	543.7	541.1	532.0	531.6	527.7
17.5°	533.3	529.4	518.6	516.4	513.4
20°	520.8	516.4	502.6	500.4	496.5
22.5°	506.9	502.6	487.9	483.1	480.1
25°	493.1	486.6	470.6	465.0	460.2
27.5°	477.5	469.7	452.9	445.5	440.7
30°	460.2	452.0	433.8	423.9	420.0
32.5°	443.3	433.4	414.8	403.5	398.4
35°	424.7	414.4	394.9	382.4	376.3
37.5°	407.0	394.5	374.6	359.9	353.8
40°	388.0	375.0	354.2	337.8	332.6
42.5°	368.1	354.7	333.0	317.5	309.3
45°	347.8	335.2	311.4	294.1	287.6
47.5°	326.6	313.6	289.8	272.1	264.7
50°	306.7	292.4	267.7	249.6	243.1
52.5°	285.0	270.3	247.4	227.5	221.0
55°	263.8	250.0	225.8	206.3	199.4
57.5°	242.2	227.5	204.2	185.1	179.1
60°	221.5	206.3	183.0	163.9	157.4
62.5°	199.4	185.1	161.3	144.0	137.5
65°	178.6	163.9	141.0	123.7	117.2
67.5°	157.9	143.2	121.1	104.7	99.5
70°	136.7	122.0	100.3	86.9	81.7
72.5°	115.9	101.6	81.7	69.6	66.6
75°	95.2	82.2	64.0	54.5	51.5
77.5°	74.0	63.6	48.4	41.1	38.5
80°	56.2	45.8	33.7	29.8	29.0
82.5°	38.9	29.8	22.5	21.2	20.8
85°	23.8	16.0	13.8	13.4	13.0
87.5°	9.9	6.9	6.5	6.5	6.1
90°	0.7	6.6	11.8	15.4	17.6
92.5°	14.0	7.3	11.8	15.4	16.2
95°	41.9	39.7	11.8	15.4	15.4
97.5°	78.6	83.0	13.2	14.7	15.4
100°	122.7	124.9	127.8	18.4	15.4
102.5°	167.5	170.4	171.9	173.3	111.6
105°	215.9	218.9	218.9	218.9	218.1
107.5°	265.9	265.9	267.3	268.1	265.1
110°	314.4	314.4	315.8	313.6	314.4

TEST NUMBER: P1027203

CATALOG NUMBER: S125RDIP-B375D850UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	359.9	362.1	362.8	359.9	358.4
115°	405.4	409.1	409.8	406.9	402.5
117.5°	453.2	453.2	456.1	451.7	450.2
120°	497.2	496.5	498.7	497.2	493.6
122.5°	536.2	539.8	540.6	539.1	534.7
125°	576.6	581.7	581.7	578.8	576.6
127.5°	615.5	619.2	618.4	617.0	611.1
130°	650.7	654.4	655.1	652.9	649.3
132.5°	686.0	690.4	688.2	688.2	684.5
135°	719.0	723.5	722.0	720.5	716.1
137.5°	749.9	754.3	752.8	752.8	749.2
140°	780.0	781.5	780.7	782.2	777.8
142.5°	807.2	807.9	809.4	809.4	805.0
145°	833.6	835.1	835.1	835.8	831.4
147.5°	857.1	857.1	857.9	858.6	853.5
150°	879.2	877.7	879.2	880.6	874.8
152.5°	900.5	896.8	898.3	899.7	894.6
155°	918.1	913.7	915.2	917.4	911.5
157.5°	932.0	929.8	929.8	932.0	926.2
160°	946.7	942.3	943.1	946.0	940.1
162.5°	958.5	954.1	954.8	959.2	952.6
165°	968.8	964.4	965.1	969.5	963.6
167.5°	976.8	972.4	973.2	978.3	971.7
170°	983.5	978.3	979.0	984.9	978.3
172.5°	987.9	982.7	984.2	989.3	982.7
175°	990.8	986.4	987.1	993.0	986.4
177.5°	993.0	988.6	989.3	994.5	988.6
180°	990.8	990.8	990.8	990.8	990.8

(END OF REPORT)