

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027211

Luminaire Tested: S125RDIP-B610D1090UB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027211
REPORT IS A COMBINATION OF REPORTS P1005532 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIP-B610D1090UB2750-4F0-XX-W2A-F_3500K
Description: Define 5 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6493.0 lumens
Efficiency: N/A
Efficacy: 123.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 52.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027211

CATALOG NUMBER: S125RDIP-B610D1090UB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1027211

CATALOG NUMBER: S125RDIP-B610D1090UB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44
1	95	91	87	84	86	82	79	76	67	65	63	52	51	50	39	38	37
2	87	79	74	69	78	72	67	63	59	55	52	46	44	42	34	33	32
3	79	70	63	57	71	64	58	53	52	47	44	41	38	35	31	29	27
4	72	62	54	48	65	56	50	45	46	41	37	36	33	30	27	25	23
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	22	20
6	61	49	42	36	55	45	38	33	37	32	28	30	26	23	23	20	18
7	56	45	37	31	51	41	34	29	34	28	25	27	23	20	21	18	16
8	52	40	33	28	47	37	30	26	31	26	22	25	21	18	19	16	14
9	49	37	30	25	44	34	27	23	28	23	20	23	19	16	17	15	13
10	45	34	27	22	41	31	25	21	26	21	18	21	17	15	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6446	6446	6446
5°	6447	6286	6295
10°	6384	6127	6073
15°	6294	5905	5780
20°	6182	5639	5473
25°	6054	5378	5144
30°	5896	5092	4799
35°	5736	4801	4432
40°	5584	4502	4073
45°	5400	4180	3698
50°	5215	3838	3316
55°	4999	3501	2920
60°	4779	3115	2510
65°	4515	2684	2066
70°	4209	2186	1626
75°	3786	1644	1185
80°	3193	1065	799
85°	2390	571	450

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5400 cd/sqm

TEST NUMBER: P1027211

CATALOG NUMBER: S125RDIP-B610D1090UB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.7	1.5
10°-20°	264.6	4.1
20°-30°	383.7	5.9
30°-40°	437.1	6.7
40°-50°	426.1	6.6
50°-60°	358.6	5.5
60°-70°	251.3	3.9
70°-80°	128.8	2.0
80°-90°	34.1	0.5
90°-100°	45.4	0.7
100°-110°	302.3	4.7
110°-120°	544.3	8.4
120°-130°	698.7	10.8
130°-140°	751.4	11.6
140°-150°	705.3	10.9
150°-160°	570.5	8.8
160°-170°	368.9	5.7
170°-180°	127.2	2.0
0°-30°	743.0	11.4
0°-40°	1180.1	18.2
0°-60°	1964.8	30.3
0°-90°	2379.0	36.6
90°-120°	892.0	13.7
90°-150°	3047.4	46.9
90°-180°	4114.0	63.4
0°-180°	6493.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1006	1006	1006	1006	1006	
5°	1005	1002	993	1001	999	95
15°	955	951	935	934	927	269
25°	866	855	827	817	808	399
35°	746	728	694	672	661	467
45°	611	589	547	517	505	471
55°	464	439	397	362	350	414
65°	314	288	248	217	206	311
75°	167	144	112	96	90	177
85°	42	28	24	24	23	46
90°	1	9	16	21	24	5
95°	57	54	16	21	21	69
105°	292	296	296	296	295	309
115°	548	553	554	550	544	543
125°	779	786	786	782	779	696
135°	972	978	976	974	968	749
145°	1127	1129	1129	1130	1124	705
155°	1241	1235	1237	1240	1232	572
165°	1310	1304	1304	1310	1303	370
175°	1339	1333	1334	1342	1333	128
180°	1339	1339	1339	1339	1339	

TEST NUMBER: P1027211

CATALOG NUMBER: S125RDIP-B610D1090UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1006.1	1006.1	1006.1	1006.1	1006.1
2.5°	1008.4	1006.1	998.5	1006.1	1005.3
5°	1004.6	1001.5	993.2	1000.8	999.2
7.5°	997.0	993.9	984.0	990.1	988.6
10°	985.6	983.3	972.6	974.9	972.6
12.5°	972.6	969.6	954.4	955.9	952.1
15°	955.2	950.6	934.6	933.9	927.0
17.5°	936.9	930.1	911.1	907.3	902.0
20°	914.9	907.3	883.0	879.2	872.3
22.5°	890.6	883.0	857.1	848.8	843.5
25°	866.3	854.9	826.7	816.9	808.5
27.5°	838.9	825.2	795.6	782.7	774.3
30°	808.5	794.1	762.2	744.7	737.8
32.5°	778.9	761.4	728.7	709.0	699.8
35°	746.2	728.0	693.8	671.7	661.1
37.5°	715.0	693.0	658.1	632.2	621.6
40°	681.6	658.8	622.3	593.5	584.3
42.5°	646.7	623.1	585.1	557.7	543.3
45°	610.9	588.9	547.1	516.7	505.3
47.5°	573.7	550.9	509.1	478.0	465.0
50°	538.8	513.7	470.4	438.4	427.1
52.5°	500.8	474.9	434.6	399.7	388.3
55°	463.5	439.2	396.7	362.5	350.3
57.5°	425.5	399.7	358.7	325.2	314.6
60°	389.1	362.5	321.4	288.0	276.6
62.5°	350.3	325.2	283.4	253.0	241.6
65°	313.8	288.0	247.7	217.3	205.9
67.5°	277.4	251.5	212.8	183.9	174.8
70°	240.1	214.3	176.3	152.7	143.6
72.5°	203.6	178.6	143.6	122.3	117.0
75°	167.2	144.4	112.5	95.7	90.4
77.5°	129.9	111.7	85.1	72.2	67.6
80°	98.8	80.5	59.3	52.4	50.9
82.5°	68.4	52.4	39.5	37.2	36.5
85°	41.8	28.1	24.3	23.6	22.8
87.5°	17.5	12.2	11.4	11.4	10.6
90°	1.0	8.9	15.9	20.8	23.8
92.5°	18.9	9.9	15.9	20.8	21.8
95°	56.6	53.6	15.9	20.8	20.8
97.5°	106.2	112.2	17.9	19.9	20.8
100°	165.8	168.8	172.7	24.8	20.8
102.5°	226.4	230.3	232.3	234.3	150.9
105°	291.9	295.9	295.9	295.9	294.9
107.5°	359.4	359.4	361.4	362.4	358.4
110°	424.9	424.9	426.9	423.9	424.9

TEST NUMBER: P1027211

CATALOG NUMBER: S125RDIP-B610D1090UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	486.5	489.5	490.4	486.5	484.5
115°	548.0	553.0	554.0	550.0	544.1
117.5°	612.6	612.6	616.5	610.6	608.6
120°	672.1	671.1	674.1	672.1	667.2
122.5°	724.7	729.7	730.7	728.7	722.8
125°	779.3	786.3	786.3	782.3	779.3
127.5°	832.0	836.9	835.9	834.0	826.0
130°	879.6	884.6	885.6	882.6	877.6
132.5°	927.3	933.2	930.3	930.3	925.3
135°	972.0	977.9	975.9	973.9	968.0
137.5°	1013.7	1019.6	1017.6	1017.6	1012.7
140°	1054.4	1056.3	1055.3	1057.3	1051.4
142.5°	1091.1	1092.1	1094.1	1094.1	1088.1
145°	1126.8	1128.8	1128.8	1129.8	1123.9
147.5°	1158.6	1158.6	1159.6	1160.6	1153.6
150°	1188.4	1186.4	1188.4	1190.4	1182.4
152.5°	1217.2	1212.2	1214.2	1216.2	1209.2
155°	1241.0	1235.0	1237.0	1240.0	1232.1
157.5°	1259.9	1256.9	1256.9	1259.9	1251.9
160°	1279.7	1273.8	1274.8	1278.7	1270.8
162.5°	1295.6	1289.6	1290.6	1296.6	1287.7
165°	1309.5	1303.5	1304.5	1310.5	1302.6
167.5°	1320.4	1314.5	1315.5	1322.4	1313.5
170°	1329.4	1322.4	1323.4	1331.3	1322.4
172.5°	1335.3	1328.4	1330.4	1337.3	1328.4
175°	1339.3	1333.3	1334.3	1342.3	1333.3
177.5°	1342.3	1336.3	1337.3	1344.3	1336.3
180°	1339.3	1339.3	1339.3	1339.3	1339.3

(END OF REPORT)