

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026932

Luminaire Tested: S125DIP-B610D1270UB2750-4F0-XX-W2A-F_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026932
REPORT IS A COMBINATION OF REPORTS P1002201 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B610D1270UB2750-4F0-XX-W2A-F_4000K
Description: Define 5 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7263.1 lumens
Efficiency: N/A
Efficacy: 123.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 59
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026932

CATALOG NUMBER: S125DIP-B610D1270UB2750-4F0-XX-W2A-F_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1026932

CATALOG NUMBER: S125DIP-B610D1270UB2750-4F0-XX-W2A-F_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	75	75	75	57	57	57	42	42	42
1	94	90	86	83	85	81	78	75	65	63	61	50	49	48	37	36	35
2	86	78	72	67	77	71	66	62	57	53	50	44	42	40	32	31	29
3	78	69	62	56	70	62	56	51	50	46	42	39	36	33	28	27	25
4	71	61	53	47	64	55	49	43	45	40	36	35	31	29	25	23	21
5	65	54	46	40	59	49	42	37	40	35	31	31	27	25	23	21	19
6	60	48	41	35	54	44	37	32	36	31	27	28	24	22	21	18	16
7	56	44	36	30	50	40	33	28	32	27	24	25	22	19	19	16	15
8	51	39	32	27	46	36	29	25	29	24	21	23	20	17	17	15	13
9	48	36	29	24	43	33	26	22	27	22	19	21	18	15	16	14	12
10	45	33	26	21	40	30	24	20	25	20	17	20	16	14	15	12	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6093	6093	6093
5°	6093	5951	5963
10°	6043	5815	5796
15°	5963	5652	5601
20°	5856	5462	5377
25°	5741	5256	5136
30°	5602	5041	4883
35°	5453	4816	4600
40°	5300	4577	4348
45°	5134	4345	4080
50°	4952	4082	3767
55°	4771	3791	3480
60°	4556	3485	3146
65°	4298	3131	2801
70°	4035	2724	2403
75°	3593	2243	1943
80°	3063	1675	1429
85°	2367	990	788

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5134 cd/sqm

TEST NUMBER: P1026932

CATALOG NUMBER: S125DIP-B610D1270UB2750-4F0-XX-W2A-F_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	89.7	1.2
10°-20°	253.5	3.5
20°-30°	374.2	5.2
30°-40°	436.6	6.0
40°-50°	438.5	6.0
50°-60°	384.9	5.3
60°-70°	286.7	3.9
70°-80°	163.7	2.3
80°-90°	49.6	0.7
90°-100°	52.9	0.7
100°-110°	351.6	4.8
110°-120°	633.2	8.7
120°-130°	812.7	11.2
130°-140°	874.1	12.0
140°-150°	820.4	11.3
150°-160°	663.6	9.1
160°-170°	429.2	5.9
170°-180°	148.0	2.0
0°-30°	717.4	9.9
0°-40°	1154.0	15.9
0°-60°	1977.3	27.2
0°-90°	2477.3	34.1
90°-120°	1037.7	14.3
90°-150°	3544.9	48.8
90°-180°	4786.0	65.9
0°-180°	7263.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	951	951	951	951	951	
5°	949	948	940	947	946	90
15°	905	903	894	898	898	255
25°	822	818	808	810	807	378
35°	709	706	696	692	686	444
45°	581	578	569	560	558	447
55°	442	440	430	423	418	395
65°	299	297	289	282	279	296
75°	159	157	154	151	148	169
85°	41	42	42	41	40	45
90°	1	10	18	24	28	6
95°	66	62	18	24	24	81
105°	340	344	344	344	343	360
115°	638	643	644	640	633	632
125°	907	915	915	910	907	810
135°	1131	1138	1135	1133	1126	872
145°	1311	1313	1313	1314	1307	820
155°	1444	1437	1439	1442	1433	665
165°	1523	1516	1518	1524	1515	430
175°	1558	1551	1552	1561	1551	148
180°	1558	1558	1558	1558	1558	

TEST NUMBER: P1026932

CATALOG NUMBER: S125DIP-B610D1270UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	950.9	950.9	950.9	950.9	950.9
2.5°	953.9	951.7	944.1	951.7	950.9
5°	949.4	947.9	940.4	947.2	946.4
7.5°	942.6	941.1	932.9	939.6	938.9
10°	932.9	931.4	923.1	929.1	928.3
12.5°	920.8	917.8	910.3	914.8	914.8
15°	905.0	902.8	894.5	898.3	898.3
17.5°	888.5	884.7	876.4	881.0	877.2
20°	866.7	865.2	855.4	860.6	856.9
22.5°	844.8	841.8	832.8	835.8	833.6
25°	821.5	817.8	808.0	809.5	807.2
27.5°	794.4	792.2	782.4	783.2	780.9
30°	768.1	765.8	754.6	753.1	750.8
32.5°	739.5	735.8	726.0	723.0	718.5
35°	709.4	706.4	695.9	692.1	686.1
37.5°	678.6	674.8	665.0	659.8	656.0
40°	647.0	643.2	632.7	625.9	623.7
42.5°	613.1	610.1	599.6	593.6	589.8
45°	580.8	577.8	568.7	559.7	557.5
47.5°	545.4	546.2	534.9	525.9	520.6
50°	511.6	509.3	500.3	490.5	485.2
52.5°	477.0	475.5	465.7	457.4	451.4
55°	442.4	440.1	429.6	422.8	417.5
57.5°	405.5	404.7	395.7	386.7	384.4
60°	370.9	367.9	359.6	352.1	346.8
62.5°	334.8	332.5	325.7	317.5	313.7
65°	298.7	297.2	288.9	282.1	279.1
67.5°	263.3	260.3	254.3	248.3	246.8
70°	230.2	226.4	219.7	215.2	212.2
72.5°	194.1	191.8	188.1	182.8	179.8
75°	158.7	157.2	153.5	151.2	148.2
77.5°	125.6	124.9	122.6	121.1	118.9
80°	94.8	94.8	93.3	92.5	91.0
82.5°	67.7	66.2	66.2	64.7	64.7
85°	41.4	42.1	42.1	41.4	39.9
87.5°	20.3	20.3	19.6	19.6	18.1
90°	1.2	10.4	18.5	24.3	27.7
92.5°	21.9	11.5	18.5	24.3	25.4
95°	65.8	62.4	18.5	24.3	24.3
97.5°	123.6	130.5	20.8	23.1	24.3
100°	192.9	196.3	201.0	28.9	24.3
102.5°	263.3	267.9	270.2	272.6	175.5
105°	339.5	344.2	344.2	344.2	343.0
107.5°	418.1	418.1	420.4	421.5	416.9
110°	494.3	494.3	496.6	493.1	494.3

TEST NUMBER: P1026932

CATALOG NUMBER: S125DIP-B610D1270UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	565.9	569.4	570.5	565.9	563.6
115°	637.5	643.3	644.4	639.8	632.9
117.5°	712.6	712.6	717.2	710.3	707.9
120°	781.9	780.7	784.2	781.9	776.1
122.5°	843.1	848.8	850.0	847.7	840.8
125°	906.6	914.7	914.7	910.1	906.6
127.5°	967.8	973.6	972.4	970.1	960.9
130°	1023.2	1029.0	1030.2	1026.7	1020.9
132.5°	1078.7	1085.6	1082.1	1082.1	1076.4
135°	1130.6	1137.6	1135.3	1132.9	1126.0
137.5°	1179.1	1186.1	1183.8	1183.8	1178.0
140°	1226.5	1228.8	1227.6	1230.0	1223.0
142.5°	1269.2	1270.4	1272.7	1272.7	1265.8
145°	1310.8	1313.1	1313.1	1314.3	1307.3
147.5°	1347.8	1347.8	1348.9	1350.1	1342.0
150°	1382.4	1380.1	1382.4	1384.7	1375.5
152.5°	1415.9	1410.1	1412.4	1414.7	1406.7
155°	1443.6	1436.7	1439.0	1442.5	1433.2
157.5°	1465.6	1462.1	1462.1	1465.6	1456.3
160°	1488.7	1481.7	1482.9	1487.5	1478.3
162.5°	1507.1	1500.2	1501.4	1508.3	1497.9
165°	1523.3	1516.4	1517.5	1524.5	1515.2
167.5°	1536.0	1529.1	1530.2	1538.3	1527.9
170°	1546.4	1538.3	1539.5	1548.7	1538.3
172.5°	1553.3	1545.2	1547.6	1555.6	1545.2
175°	1557.9	1551.0	1552.2	1561.4	1551.0
177.5°	1561.4	1554.5	1555.6	1563.7	1554.5
180°	1557.9	1557.9	1557.9	1557.9	1557.9

(END OF REPORT)