

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027229

Luminaire Tested: S125RDIP-B610D375UB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027229
REPORT IS A COMBINATION OF REPORTS P1005610 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIP-B610D375UB2750-4F0-XX-W2A-F_2700K
Description: Define 5 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3809.0 lumens
Efficiency: N/A
Efficacy: 114.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 33.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027229

CATALOG NUMBER: S125RDIP-B610D375UB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1027229

CATALOG NUMBER: S125RDIP-B610D375UB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67
1	101	96	93	89	94	90	87	84	79	77	74	69	67	65	60	58	57
2	92	84	78	73	86	79	74	69	70	66	62	61	58	55	53	50	48
3	84	75	67	61	78	70	64	58	62	57	53	54	50	47	47	44	41
4	77	66	58	52	72	62	55	50	55	49	45	48	44	40	42	39	36
5	71	59	51	45	66	56	48	43	49	44	39	44	39	35	38	34	31
6	65	53	45	39	61	50	43	37	45	39	34	39	35	31	35	31	28
7	61	48	40	34	57	46	38	33	41	35	30	36	31	28	32	28	25
8	56	44	36	31	53	42	34	29	37	31	27	33	28	25	29	25	22
9	52	40	33	27	49	38	31	26	34	28	24	30	26	22	27	23	20
10	49	37	30	25	46	35	28	24	32	26	22	28	24	20	25	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6365	6365	6365
5°	6366	6206	6216
10°	6303	6050	5997
15°	6214	5831	5707
20°	6103	5567	5404
25°	5977	5310	5080
30°	5822	5027	4738
35°	5664	4740	4376
40°	5513	4446	4022
45°	5332	4127	3651
50°	5149	3789	3274
55°	4936	3456	2883
60°	4718	3076	2478
65°	4459	2651	2040
70°	4156	2158	1606
75°	3738	1622	1171
80°	3151	1050	790
85°	2361	564	444

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5332 cd/sqm

TEST NUMBER: P1027229

CATALOG NUMBER: S125RDIP-B610D375UB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	93.5	2.5
10°-20°	261.3	6.9
20°-30°	378.8	9.9
30°-40°	431.6	11.3
40°-50°	420.7	11.0
50°-60°	354.1	9.3
60°-70°	248.1	6.5
70°-80°	127.2	3.3
80°-90°	32.4	0.9
90°-100°	16.1	0.4
100°-110°	107.4	2.8
110°-120°	193.3	5.1
120°-130°	248.2	6.5
130°-140°	266.9	7.0
140°-150°	250.5	6.6
150°-160°	202.6	5.3
160°-170°	131.0	3.4
170°-180°	45.2	1.2
0°-30°	733.6	19.3
0°-40°	1165.2	30.6
0°-60°	1940.0	50.9
0°-90°	2347.7	61.6
90°-120°	316.8	8.3
90°-150°	1082.4	28.4
90°-180°	1461.0	38.4
0°-180°	3809.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	993	993	993	993	993	
5°	992	989	981	988	987	94
15°	943	939	923	922	915	266
25°	855	844	816	807	798	394
35°	737	719	685	663	653	461
45°	603	582	540	510	499	465
55°	458	434	392	358	346	409
65°	310	284	245	215	203	307
75°	165	143	111	94	89	174
85°	41	28	24	23	22	45
90°	0	3	6	7	8	3
95°	20	19	6	7	7	25
105°	104	105	105	105	105	110
115°	195	196	197	195	193	193
125°	277	279	279	278	277	247
135°	345	347	347	346	344	266
145°	400	401	401	401	399	250
155°	441	439	439	440	438	203
165°	465	463	463	466	463	131
175°	476	474	474	477	474	45
180°	476	476	476	476	476	

TEST NUMBER: P1027229

CATALOG NUMBER: S125RDIP-B610D375UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	993.4	993.4	993.4	993.4	993.4
2.5°	995.6	993.4	985.9	993.4	992.6
5°	991.9	988.9	980.6	988.1	986.6
7.5°	984.4	981.4	971.6	977.6	976.1
10°	973.1	970.9	960.4	962.6	960.4
12.5°	960.4	957.4	942.4	943.9	940.1
15°	943.1	938.6	922.9	922.1	915.3
17.5°	925.1	918.3	899.6	895.8	890.6
20°	903.3	895.8	871.8	868.1	861.3
22.5°	879.3	871.8	846.3	838.1	832.8
25°	855.3	844.1	816.3	806.6	798.3
27.5°	828.3	814.8	785.5	772.8	764.5
30°	798.3	784.0	752.5	735.3	728.5
32.5°	769.0	751.8	719.5	700.0	691.0
35°	736.8	718.8	685.0	663.3	652.7
37.5°	706.0	684.3	649.7	624.2	613.7
40°	673.0	650.5	614.5	586.0	577.0
42.5°	638.5	615.2	577.7	550.7	536.5
45°	603.2	581.5	540.2	510.2	498.9
47.5°	566.5	544.0	502.7	471.9	459.2
50°	532.0	507.2	464.4	432.9	421.7
52.5°	494.4	468.9	429.2	394.7	383.4
55°	457.7	433.7	391.6	357.9	345.9
57.5°	420.2	394.7	354.1	321.1	310.6
60°	384.1	357.9	317.4	284.4	273.1
62.5°	345.9	321.1	279.9	249.8	238.6
65°	309.9	284.4	244.6	214.6	203.3
67.5°	273.9	248.3	210.1	181.6	172.6
70°	237.1	211.6	174.1	150.8	141.8
72.5°	201.1	176.3	141.8	120.8	115.5
75°	165.1	142.6	111.0	94.5	89.3
77.5°	128.3	110.3	84.0	71.3	66.8
80°	97.5	79.5	58.5	51.8	50.3
82.5°	67.5	51.8	39.0	36.8	36.0
85°	41.3	27.8	24.0	23.3	22.5
87.5°	17.3	12.0	11.3	11.3	10.5
90°	0.4	3.2	5.6	7.4	8.5
92.5°	6.7	3.5	5.6	7.4	7.8
95°	20.1	19.0	5.6	7.4	7.4
97.5°	37.7	39.8	6.3	7.1	7.4
100°	58.9	59.9	61.4	8.8	7.4
102.5°	80.4	81.8	82.5	83.2	53.6
105°	103.7	105.1	105.1	105.1	104.7
107.5°	127.7	127.7	128.4	128.7	127.3
110°	150.9	150.9	151.6	150.6	150.9



TEST NUMBER: P1027229

CATALOG NUMBER: S125RDIP-B610D375UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	172.8	173.9	174.2	172.8	172.1
115°	194.7	196.4	196.8	195.4	193.2
117.5°	217.6	217.6	219.0	216.9	216.2
120°	238.7	238.4	239.4	238.7	237.0
122.5°	257.4	259.2	259.5	258.8	256.7
125°	276.8	279.3	279.3	277.9	276.8
127.5°	295.5	297.3	296.9	296.2	293.4
130°	312.4	314.2	314.6	313.5	311.7
132.5°	329.4	331.5	330.4	330.4	328.7
135°	345.2	347.4	346.6	345.9	343.8
137.5°	360.0	362.2	361.5	361.5	359.7
140°	374.5	375.2	374.9	375.6	373.4
142.5°	387.6	387.9	388.6	388.6	386.5
145°	400.2	401.0	401.0	401.3	399.2
147.5°	411.5	411.5	411.9	412.2	409.8
150°	422.1	421.4	422.1	422.8	420.0
152.5°	432.3	430.6	431.3	432.0	429.5
155°	440.8	438.7	439.4	440.5	437.6
157.5°	447.5	446.4	446.4	447.5	444.7
160°	454.6	452.4	452.8	454.2	451.4
162.5°	460.2	458.1	458.4	460.6	457.4
165°	465.1	463.0	463.4	465.5	462.7
167.5°	469.0	466.9	467.3	469.7	466.5
170°	472.2	469.7	470.1	472.9	469.7
172.5°	474.3	471.8	472.5	475.0	471.8
175°	475.7	473.6	474.0	476.8	473.6
177.5°	476.8	474.7	475.0	477.5	474.7
180°	475.7	475.7	475.7	475.7	475.7

(END OF REPORT)