

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026944

Luminaire Tested: S125DIP-B610D375UB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026944
REPORT IS A COMBINATION OF REPORTS P1002258 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B610D375UB2750-4F0-XX-W2A-F_2700K
Description: Define 5 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3930.0 lumens
Efficiency: N/A
Efficacy: 118.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 33.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026944

CATALOG NUMBER: S125DIP-B610D375UB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1026944

CATALOG NUMBER: S125DIP-B610D375UB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	90	90	90	79	79	79	68	68	68
1	101	96	92	89	94	90	87	84	79	77	74	69	67	65	60	59	57
2	92	84	78	72	86	79	73	69	69	65	61	61	57	55	53	50	48
3	84	74	66	60	78	69	63	57	61	56	52	54	50	46	47	44	41
4	76	65	57	51	71	62	54	49	54	49	44	48	43	40	42	38	35
5	70	58	50	44	66	55	47	42	49	43	38	43	38	34	38	34	31
6	65	52	44	38	61	49	42	36	44	38	33	39	34	30	34	30	27
7	60	47	39	33	56	45	37	32	40	34	29	35	30	27	31	27	24
8	56	43	35	30	52	41	34	28	36	30	26	32	27	24	29	25	22
9	52	39	32	27	49	37	30	26	34	28	23	30	25	21	26	22	20
10	49	36	29	24	46	34	28	23	31	25	21	28	23	19	25	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6075	6075	6075
5°	6075	5934	5946
10°	6025	5799	5780
15°	5947	5636	5585
20°	5839	5447	5362
25°	5725	5241	5122
30°	5586	5027	4870
35°	5438	4802	4587
40°	5285	4564	4335
45°	5119	4332	4068
50°	4937	4070	3757
55°	4757	3781	3470
60°	4542	3475	3137
65°	4285	3122	2793
70°	4025	2716	2396
75°	3584	2235	1937
80°	3054	1670	1425
85°	2361	988	786

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5119 cd/sqm

TEST NUMBER: P1026944

CATALOG NUMBER: S125DIP-B610D375UB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	89.5	2.3
10°-20°	252.7	6.4
20°-30°	373.1	9.5
30°-40°	435.3	11.1
40°-50°	437.2	11.1
50°-60°	383.8	9.8
60°-70°	285.9	7.3
70°-80°	163.3	4.2
80°-90°	47.8	1.2
90°-100°	16.1	0.4
100°-110°	107.4	2.7
110°-120°	193.3	4.9
120°-130°	248.2	6.3
130°-140°	266.9	6.8
140°-150°	250.5	6.4
150°-160°	202.6	5.2
160°-170°	131.0	3.3
170°-180°	45.2	1.1
0°-30°	715.3	18.2
0°-40°	1150.7	29.3
0°-60°	1971.7	50.2
0°-90°	2468.7	62.8
90°-120°	316.8	8.1
90°-150°	1082.4	27.5
90°-180°	1461.0	37.2
0°-180°	3930.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	948	948	948	948	948	
5°	947	945	938	944	944	90
15°	902	900	892	896	896	254
25°	819	815	806	807	805	377
35°	707	704	694	690	684	443
45°	579	576	567	558	556	446
55°	441	439	428	422	416	394
65°	298	296	288	281	278	295
75°	158	157	153	151	148	169
85°	41	42	42	41	40	45
90°	0	3	6	7	8	4
95°	20	19	6	7	7	25
105°	104	105	105	105	105	110
115°	195	196	197	195	193	193
125°	277	279	279	278	277	247
135°	345	347	347	346	344	266
145°	400	401	401	401	399	250
155°	441	439	439	440	438	203
165°	465	463	463	466	463	131
175°	476	474	474	477	474	45
180°	476	476	476	476	476	

TEST NUMBER: P1026944

CATALOG NUMBER: S125DIP-B610D375UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	948.2	948.2	948.2	948.2	948.2
2.5°	951.2	949.0	941.5	949.0	948.2
5°	946.7	945.2	937.7	944.5	943.7
7.5°	940.0	938.5	930.2	937.0	936.2
10°	930.2	928.7	920.5	926.5	925.7
12.5°	918.2	915.2	907.7	912.2	912.2
15°	902.5	900.2	892.0	895.7	895.7
17.5°	886.0	882.2	874.0	878.5	874.7
20°	864.2	862.7	853.0	858.2	854.5
22.5°	842.5	839.5	830.4	833.4	831.2
25°	819.2	815.4	805.7	807.2	804.9
27.5°	792.2	789.9	780.2	780.9	778.7
30°	765.9	763.7	752.4	750.9	748.7
32.5°	737.4	733.7	723.9	720.9	716.4
35°	707.4	704.4	693.9	690.2	684.2
37.5°	676.7	672.9	663.2	657.9	654.2
40°	645.2	641.4	630.9	624.1	621.9
42.5°	611.4	608.4	597.9	591.9	588.1
45°	579.1	576.1	567.1	558.1	555.9
47.5°	543.9	544.6	533.4	524.4	519.1
50°	510.1	507.9	498.9	489.1	483.9
52.5°	475.6	474.1	464.4	456.1	450.1
55°	441.1	438.9	428.4	421.6	416.3
57.5°	404.3	403.6	394.6	385.6	383.3
60°	369.8	366.8	358.6	351.1	345.8
62.5°	333.8	331.6	324.8	316.6	312.8
65°	297.8	296.3	288.1	281.3	278.3
67.5°	262.6	259.6	253.6	247.6	246.1
70°	229.6	225.8	219.1	214.6	211.6
72.5°	193.5	191.3	187.5	182.3	179.3
75°	158.3	156.8	153.0	150.8	147.8
77.5°	125.3	124.5	122.3	120.8	118.5
80°	94.5	94.5	93.0	92.3	90.8
82.5°	67.5	66.0	66.0	64.5	64.5
85°	41.3	42.0	42.0	41.3	39.8
87.5°	20.3	20.3	19.5	19.5	18.0
90°	0.4	3.2	5.6	7.4	8.5
92.5°	6.7	3.5	5.6	7.4	7.8
95°	20.1	19.0	5.6	7.4	7.4
97.5°	37.7	39.8	6.3	7.1	7.4
100°	58.9	59.9	61.4	8.8	7.4
102.5°	80.4	81.8	82.5	83.2	53.6
105°	103.7	105.1	105.1	105.1	104.7
107.5°	127.7	127.7	128.4	128.7	127.3
110°	150.9	150.9	151.6	150.6	150.9



TEST NUMBER: P1026944

CATALOG NUMBER: S125DIP-B610D375UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	172.8	173.9	174.2	172.8	172.1
115°	194.7	196.4	196.8	195.4	193.2
117.5°	217.6	217.6	219.0	216.9	216.2
120°	238.7	238.4	239.4	238.7	237.0
122.5°	257.4	259.2	259.5	258.8	256.7
125°	276.8	279.3	279.3	277.9	276.8
127.5°	295.5	297.3	296.9	296.2	293.4
130°	312.4	314.2	314.6	313.5	311.7
132.5°	329.4	331.5	330.4	330.4	328.7
135°	345.2	347.4	346.6	345.9	343.8
137.5°	360.0	362.2	361.5	361.5	359.7
140°	374.5	375.2	374.9	375.6	373.4
142.5°	387.6	387.9	388.6	388.6	386.5
145°	400.2	401.0	401.0	401.3	399.2
147.5°	411.5	411.5	411.9	412.2	409.8
150°	422.1	421.4	422.1	422.8	420.0
152.5°	432.3	430.6	431.3	432.0	429.5
155°	440.8	438.7	439.4	440.5	437.6
157.5°	447.5	446.4	446.4	447.5	444.7
160°	454.6	452.4	452.8	454.2	451.4
162.5°	460.2	458.1	458.4	460.6	457.4
165°	465.1	463.0	463.4	465.5	462.7
167.5°	469.0	466.9	467.3	469.7	466.5
170°	472.2	469.7	470.1	472.9	469.7
172.5°	474.3	471.8	472.5	475.0	471.8
175°	475.7	473.6	474.0	476.8	473.6
177.5°	476.8	474.7	475.0	477.5	474.7
180°	475.7	475.7	475.7	475.7	475.7

(END OF REPORT)