

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026955

Luminaire Tested: S125DIP-B610D610UB2750-4F0-XX-W2A-D_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026955
REPORT IS A COMBINATION OF REPORTS P1002314 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B610D610UB2750-4F0-XX-W2A-D_3000K
Description: Define 5 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4761.0 lumens
Efficiency: N/A
Efficacy: 120.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.21 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 39.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026955

CATALOG NUMBER: S125DIP-B610D610UB2750-4F0-XX-W2A-D_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1026955

CATALOG NUMBER: S125DIP-B610D610UB2750-4F0-XX-W2A-D_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	54	54	54
1	96	92	88	84	88	84	81	78	71	68	66	58	56	54	46	45	44
2	88	80	73	68	80	73	68	63	61	57	54	50	47	45	40	38	36
3	80	70	62	56	73	64	58	52	54	49	45	44	41	38	35	33	31
4	73	62	54	47	66	57	50	44	48	42	38	39	35	32	32	29	26
5	67	55	47	40	61	51	43	38	43	37	33	35	31	28	28	25	23
6	61	49	41	35	56	45	38	33	38	33	28	32	27	24	26	22	20
7	57	44	36	31	52	41	34	29	35	29	25	29	25	21	23	20	18
8	53	40	32	27	48	37	30	25	32	26	22	26	22	19	21	18	16
9	49	37	29	24	45	34	27	22	29	24	20	24	20	17	20	17	14
10	46	34	26	21	42	31	25	20	27	21	18	22	18	15	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4945	4945	4945
5°	4953	4841	4853
10°	4916	4743	4730
15°	4856	4628	4577
20°	4776	4489	4425
25°	4680	4342	4242
30°	4564	4181	4075
35°	4455	4032	3921
40°	4345	3876	3767
45°	4221	3740	3627
50°	4102	3593	3502
55°	3958	3453	3356
60°	3801	3293	3206
65°	3636	3124	3038
70°	3448	2898	2862
75°	3152	2675	2648
80°	2763	2404	2411
85°	2378	2189	2288

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4221 cd/sqm

TEST NUMBER: P1026955

CATALOG NUMBER: S125DIP-B610D610UB2750-4F0-XX-W2A-D_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.0	1.5
10°-20°	207.3	4.4
20°-30°	308.3	6.5
30°-40°	365.1	7.7
40°-50°	377.5	7.9
50°-60°	347.7	7.3
60°-70°	281.1	5.9
70°-80°	188.1	4.0
80°-90°	98.4	2.1
90°-100°	80.9	1.7
100°-110°	214.4	4.5
110°-120°	340.4	7.2
120°-130°	417.6	8.8
130°-140°	439.4	9.2
140°-150°	407.4	8.6
150°-160°	328.5	6.9
160°-170°	212.4	4.5
170°-180°	73.3	1.5
0°-30°	588.7	12.4
0°-40°	953.8	20.0
0°-60°	1679.1	35.3
0°-90°	2246.6	47.2
90°-120°	635.8	13.4
90°-150°	1900.2	39.9
90°-180°	2514.0	52.8
0°-180°	4761.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	772	772	772	772	772	
5°	772	770	765	771	770	73
15°	737	738	732	737	734	208
25°	670	672	667	670	667	308
35°	580	585	583	585	585	363
45°	478	486	490	495	496	368
55°	367	379	391	400	403	328
65°	253	270	288	300	303	251
75°	139	159	183	198	202	148
85°	42	67	93	110	116	43
90°	13	41	71	92	98	10
95°	42	60	64	84	89	48
105°	175	189	212	227	232	185
115°	320	328	348	360	361	317
125°	452	455	470	480	482	403
135°	561	564	568	577	577	433
145°	650	650	650	654	654	406
155°	715	711	712	714	709	329
165°	754	751	751	755	750	213
175°	771	768	768	773	768	73
180°	771	771	771	771	771	

TEST NUMBER: P1026955

CATALOG NUMBER: S125DIP-B610D610UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	771.8	771.8	771.8	771.8	771.8
2.5°	774.1	772.6	767.3	772.6	771.8
5°	771.8	770.3	765.0	771.1	770.3
7.5°	766.5	765.8	760.5	765.8	765.0
10°	759.0	759.0	752.9	758.2	757.5
12.5°	748.4	749.1	744.6	748.4	746.1
15°	737.0	737.8	732.5	737.0	734.0
17.5°	722.6	724.2	718.9	722.6	720.4
20°	706.8	708.3	703.0	705.2	705.2
22.5°	688.6	691.6	685.6	688.6	686.3
25°	669.7	671.9	667.4	670.4	666.7
27.5°	649.2	652.3	647.0	649.2	647.7
30°	625.8	630.3	625.8	627.3	626.5
32.5°	604.6	608.4	605.4	606.9	606.1
35°	579.6	584.9	582.7	584.9	584.9
37.5°	555.4	560.0	559.2	562.2	561.5
40°	530.4	536.5	535.7	538.8	540.3
42.5°	503.2	511.5	513.8	517.6	517.6
45°	477.5	485.8	489.6	494.9	495.6
47.5°	451.0	458.6	464.6	472.2	473.7
50°	423.8	432.1	440.4	448.7	451.0
52.5°	395.0	405.6	416.2	425.3	426.8
55°	367.0	379.1	391.2	399.5	402.6
57.5°	338.2	352.6	366.2	375.3	377.6
60°	309.5	324.6	339.8	351.1	353.4
62.5°	281.5	296.6	313.3	326.1	329.2
65°	252.7	270.1	288.3	299.7	302.7
67.5°	226.3	242.9	261.1	274.7	278.5
70°	196.7	214.1	233.8	248.2	252.7
72.5°	168.0	186.1	208.1	224.0	227.0
75°	139.2	158.9	183.1	198.3	202.0
77.5°	111.2	133.9	156.6	173.3	176.3
80°	85.5	108.2	133.9	150.6	153.6
82.5°	62.0	86.3	112.7	128.6	134.7
85°	41.6	66.6	93.1	109.7	115.8
87.5°	26.5	50.7	76.4	93.8	99.1
90°	12.7	41.4	71.1	91.5	98.5
92.5°	21.5	38.2	68.1	87.7	93.6
95°	42.4	60.4	64.3	83.9	89.2
97.5°	70.3	91.8	62.5	79.5	85.4
100°	103.8	121.4	147.9	78.6	80.9
102.5°	137.9	154.5	179.2	195.4	152.0
105°	174.9	189.3	212.0	227.2	231.8
107.5°	213.0	223.5	246.7	262.4	264.7
110°	250.0	259.1	281.4	294.0	299.9



TEST NUMBER: P1026955

CATALOG NUMBER: S125DIP-B610D610UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	285.4	293.9	314.9	326.3	330.5
115°	320.1	328.2	348.5	359.8	361.0
117.5°	356.5	360.3	381.5	390.9	395.0
120°	390.8	392.5	411.7	423.3	425.1
122.5°	420.3	424.0	441.1	452.1	453.3
125°	451.8	455.1	470.2	480.0	482.1
127.5°	481.3	483.4	495.7	505.9	505.9
130°	508.8	510.8	522.0	530.9	531.8
132.5°	535.4	538.9	544.7	555.3	555.5
135°	561.2	563.9	568.0	576.7	577.1
137.5°	585.2	587.9	589.7	598.8	599.0
140°	607.9	609.0	609.2	618.6	618.3
142.5°	629.1	628.8	630.0	636.8	636.3
145°	649.6	650.0	650.0	654.3	653.9
147.5°	667.1	667.1	667.7	669.8	667.3
150°	684.3	683.1	684.3	685.4	681.6
152.5°	700.9	698.0	699.1	700.3	696.3
155°	714.6	711.1	712.3	714.0	709.4
157.5°	725.4	723.7	723.7	725.4	720.9
160°	736.9	733.4	734.0	736.3	731.7
162.5°	746.0	742.6	743.2	746.6	741.4
165°	754.0	750.6	751.2	754.6	750.0
167.5°	760.3	756.9	757.4	761.4	756.3
170°	765.4	761.4	762.0	766.6	761.4
172.5°	768.9	764.9	766.0	770.0	764.9
175°	771.2	767.7	768.3	772.9	767.7
177.5°	772.9	769.5	770.0	774.0	769.5
180°	771.2	771.2	771.2	771.2	771.2

(END OF REPORT)