

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027242

Luminaire Tested: S125RDIP-B610D610UB2750-4F0-XX-W2A-F_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027242
REPORT IS A COMBINATION OF REPORTS P1005653 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIP-B610D610UB2750-4F0-XX-W2A-F_4000K
Description: Define 5 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4710.0 lumens
Efficiency: N/A
Efficacy: 119.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 39.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027242

CATALOG NUMBER: S125RDIP-B610D610UB2750-4F0-XX-W2A-F_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1027242

CATALOG NUMBER: S125RDIP-B610D610UB2750-4F0-XX-W2A-F_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50		
1	98	94	90	87	90	87	83	80	73	71	69	61	60	58	50	49	48	43		
2	89	82	76	71	82	76	71	66	65	61	57	54	51	49	44	42	41	36		
3	82	72	65	59	75	67	61	56	57	52	48	48	44	42	39	37	35	31		
4	75	64	56	50	69	60	53	47	51	46	41	43	39	36	35	32	30	27		
5	69	57	49	43	63	53	46	41	46	40	36	38	34	31	32	29	26	23		
6	63	51	43	38	58	48	41	36	41	36	31	35	31	27	29	26	23	20		
7	59	46	39	33	54	43	36	31	37	32	28	32	27	24	26	23	21	18		
8	54	42	35	29	50	39	33	28	34	29	25	29	25	22	24	21	19	16		
9	51	39	31	26	47	36	29	25	31	26	22	27	23	19	23	19	17	15		
10	47	35	28	23	44	33	27	22	29	24	20	25	21	18	21	18	15	13		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6381	6381	6381
5°	6382	6222	6232
10°	6319	6065	6012
15°	6230	5846	5722
20°	6120	5582	5418
25°	5992	5324	5092
30°	5837	5041	4751
35°	5678	4753	4387
40°	5527	4457	4032
45°	5346	4138	3661
50°	5162	3799	3282
55°	4948	3466	2891
60°	4730	3084	2484
65°	4471	2657	2045
70°	4167	2163	1610
75°	3747	1626	1173
80°	3160	1054	791
85°	2367	567	446

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5346 cd/sqm

TEST NUMBER: P1027242

CATALOG NUMBER: S125RDIP-B610D610UB2750-4F0-XX-W2A-F_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	93.7	2.0
10°-20°	261.9	5.6
20°-30°	379.8	8.1
30°-40°	432.7	9.2
40°-50°	421.8	9.0
50°-60°	355.0	7.5
60°-70°	248.7	5.3
70°-80°	127.5	2.7
80°-90°	32.9	0.7
90°-100°	26.0	0.6
100°-110°	173.1	3.7
110°-120°	311.7	6.6
120°-130°	400.1	8.5
130°-140°	430.3	9.1
140°-150°	403.9	8.6
150°-160°	326.7	6.9
160°-170°	211.3	4.5
170°-180°	72.9	1.5
0°-30°	735.5	15.6
0°-40°	1168.2	24.8
0°-60°	1944.9	41.3
0°-90°	2354.1	50.0
90°-120°	510.8	10.8
90°-150°	1745.0	37.0
90°-180°	2356.0	50.0
0°-180°	4710.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	996	996	996	996	996	
5°	994	991	983	991	989	94
15°	946	941	925	924	918	267
25°	858	846	818	809	800	395
35°	739	721	687	665	654	463
45°	605	583	542	512	500	466
55°	459	435	393	359	347	410
65°	311	285	245	215	204	308
75°	166	143	111	95	90	175
85°	41	28	24	23	23	45
90°	1	5	9	12	14	4
95°	32	31	9	12	12	40
105°	167	169	169	169	169	177
115°	314	317	317	315	312	311
125°	446	450	450	448	446	399
135°	557	560	559	558	554	429
145°	645	646	646	647	644	404
155°	711	707	708	710	706	327
165°	750	746	747	750	746	212
175°	767	764	764	769	764	73
180°	767	767	767	767	767	

TEST NUMBER: P1027242

CATALOG NUMBER: S125RDIP-B610D610UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	995.9	995.9	995.9	995.9	995.9
2.5°	998.2	995.9	988.4	995.9	995.2
5°	994.4	991.4	983.1	990.7	989.1
7.5°	986.9	983.9	974.1	980.1	978.6
10°	975.6	973.4	962.8	965.1	962.8
12.5°	962.8	959.8	944.8	946.3	942.5
15°	945.5	941.0	925.2	924.5	917.7
17.5°	927.5	920.7	901.9	898.1	892.9
20°	905.7	898.1	874.1	870.3	863.5
22.5°	881.6	874.1	848.5	840.2	834.9
25°	857.5	846.2	818.4	808.6	800.3
27.5°	830.4	816.9	787.6	774.8	766.5
30°	800.3	786.1	754.5	737.2	730.4
32.5°	771.0	753.7	721.4	701.8	692.8
35°	738.7	720.6	686.8	664.9	654.4
37.5°	707.8	686.0	651.4	625.8	615.3
40°	674.7	652.2	616.1	587.5	578.4
42.5°	640.1	616.8	579.2	552.1	537.8
45°	604.8	583.0	541.6	511.5	500.2
47.5°	567.9	545.3	504.0	473.1	460.3
50°	533.3	508.5	465.6	434.0	422.7
52.5°	495.7	470.1	430.3	395.7	384.4
55°	458.8	434.8	392.7	358.8	346.8
57.5°	421.2	395.7	355.0	321.9	311.4
60°	385.1	358.8	318.2	285.1	273.8
62.5°	346.8	321.9	280.6	250.5	239.2
65°	310.7	285.1	245.2	215.1	203.8
67.5°	274.6	249.0	210.6	182.0	173.0
70°	237.7	212.1	174.5	151.2	142.2
72.5°	201.6	176.8	142.2	121.1	115.8
75°	165.5	142.9	111.3	94.8	89.5
77.5°	128.6	110.6	84.2	71.5	66.9
80°	97.8	79.7	58.7	51.9	50.4
82.5°	67.7	51.9	39.1	36.9	36.1
85°	41.4	27.8	24.1	23.3	22.6
87.5°	17.3	12.0	11.3	11.3	10.5
90°	0.6	5.1	9.1	11.9	13.6
92.5°	10.8	5.7	9.1	11.9	12.5
95°	32.4	30.7	9.1	11.9	11.9
97.5°	60.8	64.2	10.2	11.4	11.9
100°	94.9	96.6	98.9	14.2	11.9
102.5°	129.6	131.9	133.0	134.2	86.4
105°	167.1	169.4	169.4	169.4	168.9
107.5°	205.8	205.8	206.9	207.5	205.2
110°	243.3	243.3	244.5	242.8	243.3



TEST NUMBER: P1027242

CATALOG NUMBER: S125RDIP-B610D610UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	278.6	280.3	280.8	278.6	277.4
115°	313.8	316.7	317.2	315.0	311.5
117.5°	350.8	350.8	353.1	349.6	348.5
120°	384.9	384.3	386.0	384.9	382.0
122.5°	415.0	417.9	418.4	417.3	413.9
125°	446.3	450.3	450.3	448.0	446.3
127.5°	476.4	479.3	478.7	477.6	473.0
130°	503.7	506.6	507.1	505.4	502.6
132.5°	531.0	534.4	532.7	532.7	529.9
135°	556.6	560.0	558.9	557.7	554.3
137.5°	580.5	583.9	582.7	582.7	579.9
140°	603.8	604.9	604.3	605.5	602.1
142.5°	624.8	625.4	626.5	626.5	623.1
145°	645.3	646.4	646.4	647.0	643.6
147.5°	663.5	663.5	664.0	664.6	660.6
150°	680.5	679.4	680.5	681.7	677.1
152.5°	697.0	694.2	695.3	696.4	692.5
155°	710.7	707.2	708.4	710.1	705.5
157.5°	721.5	719.7	719.7	721.5	716.9
160°	732.8	729.4	730.0	732.3	727.7
162.5°	741.9	738.5	739.1	742.5	737.4
165°	749.9	746.5	747.0	750.4	745.9
167.5°	756.1	752.7	753.3	757.3	752.2
170°	761.2	757.3	757.8	762.4	757.3
172.5°	764.7	760.7	761.8	765.8	760.7
175°	766.9	763.5	764.1	768.6	763.5
177.5°	768.6	765.2	765.8	769.8	765.2
180°	766.9	766.9	766.9	766.9	766.9

(END OF REPORT)