

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027243

Luminaire Tested: S125RDIP-B610D610UB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027243
REPORT IS A COMBINATION OF REPORTS P1005654 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIP-B610D610UB2750-4F0-XX-W2A-F_5000K
Description: Define 5 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4555.0 lumens
Efficiency: N/A
Efficacy: 115.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 39.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027243

CATALOG NUMBER: S125RDIP-B610D610UB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1027243

CATALOG NUMBER: S125RDIP-B610D610UB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56
1	98	94	90	87	90	87	83	80	73	71	69	61	60	58	50	49	48
2	89	82	76	71	82	76	71	66	65	61	57	54	51	49	44	42	41
3	82	72	65	59	75	67	61	56	57	52	48	48	44	42	39	37	35
4	75	64	56	50	69	60	53	47	51	46	41	43	39	36	35	32	30
5	69	57	49	43	63	53	46	41	46	40	36	38	34	31	32	29	26
6	63	51	43	38	58	48	41	36	41	36	31	35	31	27	29	26	23
7	59	46	39	33	54	43	36	31	37	32	28	32	27	24	26	23	21
8	54	42	35	29	50	39	33	28	34	29	25	29	25	22	24	21	19
9	51	39	31	26	47	36	29	25	31	26	22	27	23	19	23	19	17
10	47	35	28	23	44	33	27	22	29	24	20	25	21	18	21	18	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6172	6172	6172
5°	6173	6018	6028
10°	6113	5867	5815
15°	6026	5654	5535
20°	5919	5399	5241
25°	5797	5149	4926
30°	5646	4876	4595
35°	5492	4597	4244
40°	5346	4311	3900
45°	5171	4002	3541
50°	4994	3675	3175
55°	4787	3352	2796
60°	4575	2983	2402
65°	4324	2571	1979
70°	4030	2093	1557
75°	3625	1574	1135
80°	3057	1020	765
85°	2287	548	431

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5171 cd/sqm

TEST NUMBER: P1027243

CATALOG NUMBER: S125RDIP-B610D610UB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.7	2.0
10°-20°	253.4	5.6
20°-30°	367.4	8.1
30°-40°	418.6	9.2
40°-50°	408.0	9.0
50°-60°	343.3	7.5
60°-70°	240.6	5.3
70°-80°	123.3	2.7
80°-90°	31.9	0.7
90°-100°	25.2	0.6
100°-110°	167.3	3.7
110°-120°	301.4	6.6
120°-130°	386.9	8.5
130°-140°	416.1	9.1
140°-150°	390.5	8.6
150°-160°	315.9	6.9
160°-170°	204.3	4.5
170°-180°	70.4	1.5
0°-30°	711.4	15.6
0°-40°	1130.0	24.8
0°-60°	1881.3	41.3
0°-90°	2277.1	50.0
90°-120°	493.9	10.8
90°-150°	1687.3	37.0
90°-180°	2278.0	50.0
0°-180°	4555.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	963	963	963	963	963	
5°	962	959	951	958	957	91
15°	915	910	895	894	888	258
25°	830	818	792	782	774	382
35°	714	697	664	643	633	447
45°	585	564	524	495	484	451
55°	444	420	380	347	335	397
65°	300	276	237	208	197	298
75°	160	138	108	92	87	169
85°	40	27	23	23	22	44
90°	0	5	9	12	13	4
95°	31	30	9	12	12	38
105°	162	164	164	164	163	171
115°	303	306	307	304	301	301
125°	432	435	435	433	432	385
135°	538	542	540	539	536	415
145°	624	625	625	626	622	390
155°	687	684	685	687	682	317
165°	725	722	722	726	721	205
175°	742	738	739	743	738	71
180°	742	742	742	742	742	

TEST NUMBER: P1027243

CATALOG NUMBER: S125RDIP-B610D610UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	963.3	963.3	963.3	963.3	963.3
2.5°	965.5	963.3	956.1	963.3	962.6
5°	961.9	959.0	951.0	958.2	956.8
7.5°	954.6	951.7	942.2	948.0	946.6
10°	943.7	941.5	931.3	933.5	931.3
12.5°	931.3	928.4	913.9	915.3	911.7
15°	914.6	910.2	894.9	894.2	887.7
17.5°	897.1	890.6	872.4	868.7	863.6
20°	876.0	868.7	845.5	841.8	835.3
22.5°	852.7	845.5	820.7	812.7	807.6
25°	829.5	818.5	791.6	782.2	774.2
27.5°	803.3	790.2	761.8	749.4	741.4
30°	774.2	760.3	729.8	713.0	706.5
32.5°	745.8	729.0	697.8	678.8	670.1
35°	714.5	697.0	664.3	643.2	633.0
37.5°	684.7	663.6	630.1	605.4	595.2
40°	652.6	630.8	595.9	568.2	559.5
42.5°	619.2	596.6	560.2	534.1	520.2
45°	585.0	563.9	523.9	494.8	483.8
47.5°	549.3	527.5	487.5	457.7	445.3
50°	515.9	491.8	450.4	419.8	408.9
52.5°	479.5	454.7	416.2	382.7	371.8
55°	443.8	420.5	379.8	347.1	335.4
57.5°	407.4	382.7	343.4	311.4	301.2
60°	372.5	347.1	307.8	275.8	264.8
62.5°	335.4	311.4	271.4	242.3	231.4
65°	300.5	275.8	237.2	208.1	197.2
67.5°	265.6	240.8	203.7	176.1	167.3
70°	229.9	205.2	168.8	146.2	137.5
72.5°	195.0	171.0	137.5	117.1	112.0
75°	160.1	138.2	107.7	91.7	86.6
77.5°	124.4	107.0	81.5	69.1	64.8
80°	94.6	77.1	56.8	50.2	48.7
82.5°	65.5	50.2	37.8	35.7	34.9
85°	40.0	26.9	23.3	22.6	21.8
87.5°	16.7	11.6	10.9	10.9	10.2
90°	0.5	4.9	8.8	11.5	13.2
92.5°	10.4	5.5	8.8	11.5	12.1
95°	31.3	29.7	8.8	11.5	11.5
97.5°	58.8	62.1	9.9	11.0	11.5
100°	91.8	93.5	95.6	13.7	11.5
102.5°	125.3	127.5	128.6	129.7	83.6
105°	161.6	163.8	163.8	163.8	163.3
107.5°	199.0	199.0	200.1	200.6	198.4
110°	235.3	235.3	236.4	234.7	235.3



TEST NUMBER: P1027243

CATALOG NUMBER: S125RDIP-B610D610UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	269.4	271.0	271.6	269.4	268.3
115°	303.4	306.2	306.7	304.5	301.2
117.5°	339.2	339.2	341.4	338.1	337.0
120°	372.2	371.6	373.3	372.2	369.4
122.5°	401.3	404.0	404.6	403.5	400.2
125°	431.5	435.4	435.4	433.2	431.5
127.5°	460.7	463.4	462.9	461.8	457.4
130°	487.0	489.8	490.3	488.7	485.9
132.5°	513.4	516.7	515.1	515.1	512.3
135°	538.2	541.5	540.4	539.3	536.0
137.5°	561.3	564.5	563.4	563.4	560.7
140°	583.8	584.9	584.3	585.4	582.1
142.5°	604.1	604.7	605.8	605.8	602.5
145°	623.9	625.0	625.0	625.6	622.3
147.5°	641.5	641.5	642.1	642.6	638.8
150°	658.0	656.9	658.0	659.1	654.7
152.5°	673.9	671.2	672.3	673.4	669.5
155°	687.1	683.8	684.9	686.6	682.2
157.5°	697.6	695.9	695.9	697.6	693.2
160°	708.6	705.3	705.8	708.0	703.6
162.5°	717.4	714.1	714.6	717.9	713.0
165°	725.1	721.8	722.3	725.6	721.2
167.5°	731.1	727.8	728.4	732.2	727.3
170°	736.1	732.2	732.8	737.2	732.2
172.5°	739.4	735.5	736.6	740.5	735.5
175°	741.6	738.3	738.8	743.2	738.3
177.5°	743.2	739.9	740.5	744.3	739.9
180°	741.6	741.6	741.6	741.6	741.6

(END OF REPORT)