

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026969

Luminaire Tested: S125DIP-B610D850UB2750-4F0-XX-W2A-D_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026969
REPORT IS A COMBINATION OF REPORTS P1002373 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B610D850UB2750-4F0-XX-W2A-D_2700K
Description: Define 5 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5509.2 lumens
Efficiency: N/A
Efficacy: 122.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.21 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 45.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026969

CATALOG NUMBER: S125DIP-B610D850UB2750-4F0-XX-W2A-D_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1026969

CATALOG NUMBER: S125DIP-B610D850UB2750-4F0-XX-W2A-D_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47
1	95	91	86	83	86	82	79	76	67	65	63	54	52	50	41	40	39
2	86	79	72	67	78	72	66	62	59	55	51	47	44	42	36	34	32
3	79	69	61	56	71	63	56	51	52	47	43	41	38	35	31	29	27
4	72	61	53	47	65	56	49	43	46	40	36	36	33	30	28	25	23
5	66	54	46	40	59	49	42	37	41	35	31	33	29	26	25	22	20
6	60	48	40	34	55	44	37	32	37	31	27	29	25	22	23	20	18
7	56	44	36	30	51	40	33	28	33	28	24	27	23	20	21	18	16
8	52	39	32	26	47	36	29	25	30	25	21	24	20	17	19	16	14
9	48	36	28	23	44	33	26	22	28	22	19	22	18	16	17	15	13
10	45	33	26	21	41	30	24	20	25	20	17	21	17	14	16	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4902	4902	4902
5°	4910	4799	4811
10°	4873	4701	4688
15°	4814	4588	4537
20°	4733	4450	4386
25°	4639	4303	4205
30°	4524	4144	4039
35°	4416	3996	3887
40°	4307	3842	3733
45°	4184	3708	3596
50°	4065	3561	3471
55°	3924	3423	3326
60°	3768	3264	3178
65°	3604	3097	3011
70°	3418	2874	2837
75°	3125	2652	2625
80°	2740	2384	2391
85°	2361	2170	2268

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4184 cd/sqm

TEST NUMBER: P1026969

CATALOG NUMBER: S125DIP-B610D850UB2750-4F0-XX-W2A-D_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.4	1.3
10°-20°	205.5	3.7
20°-30°	305.6	5.5
30°-40°	361.9	6.6
40°-50°	374.2	6.8
50°-60°	344.7	6.3
60°-70°	278.7	5.1
70°-80°	186.5	3.4
80°-90°	97.9	1.8
90°-100°	89.0	1.6
100°-110°	270.6	4.9
110°-120°	441.9	8.0
120°-130°	548.0	9.9
130°-140°	579.7	10.5
140°-150°	539.2	9.8
150°-160°	435.1	7.9
160°-170°	281.4	5.1
170°-180°	97.0	1.8
0°-30°	583.5	10.6
0°-40°	945.4	17.2
0°-60°	1664.3	30.2
0°-90°	2227.3	40.4
90°-120°	801.5	14.5
90°-150°	2468.4	44.8
90°-180°	3282.0	59.6
0°-180°	5509.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	765	765	765	765	765	
5°	765	764	758	764	764	73
15°	731	731	726	731	728	206
25°	664	666	662	664	661	306
35°	574	580	578	580	580	360
45°	473	482	485	490	491	365
55°	364	376	388	396	399	325
65°	250	268	286	297	300	249
75°	138	158	182	196	200	146
85°	41	66	92	109	115	43
90°	13	43	74	95	102	11
95°	53	70	67	87	92	61
105°	229	244	267	282	286	243
115°	422	432	452	462	462	419
125°	597	602	617	626	627	533
135°	743	747	750	759	758	573
145°	860	861	861	865	864	538
155°	946	942	943	946	940	436
165°	999	994	995	999	993	282
175°	1021	1017	1018	1024	1017	97
180°	1021	1021	1021	1021	1021	

TEST NUMBER: P1026969

CATALOG NUMBER: S125DIP-B610D850UB2750-4F0-XX-W2A-D_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	765.1	765.1	765.1	765.1	765.1
2.5°	767.3	765.8	760.6	765.8	765.1
5°	765.1	763.6	758.3	764.3	763.6
7.5°	759.8	759.1	753.8	759.1	758.3
10°	752.3	752.3	746.3	751.6	750.8
12.5°	741.8	742.6	738.1	741.8	739.6
15°	730.6	731.3	726.1	730.6	727.6
17.5°	716.3	717.8	712.5	716.3	714.0
20°	700.5	702.0	696.8	699.0	699.0
22.5°	682.5	685.5	679.5	682.5	680.3
25°	663.8	666.0	661.5	664.5	660.8
27.5°	643.5	646.5	641.3	643.5	642.0
30°	620.3	624.8	620.3	621.8	621.0
32.5°	599.3	603.0	600.0	601.5	600.8
35°	574.5	579.8	577.5	579.8	579.8
37.5°	550.5	555.0	554.3	557.3	556.5
40°	525.8	531.8	531.0	534.0	535.5
42.5°	498.8	507.0	509.3	513.0	513.0
45°	473.3	481.5	485.3	490.5	491.3
47.5°	447.0	454.5	460.5	468.0	469.5
50°	420.0	428.3	436.5	444.8	447.0
52.5°	391.5	402.0	412.5	421.5	423.0
55°	363.8	375.8	387.8	396.0	399.0
57.5°	335.3	349.5	363.0	372.0	374.3
60°	306.8	321.8	336.8	348.0	350.3
62.5°	279.0	294.0	310.5	323.3	326.3
65°	250.5	267.8	285.8	297.0	300.0
67.5°	224.3	240.8	258.8	272.3	276.0
70°	195.0	212.3	231.8	246.0	250.5
72.5°	166.5	184.5	206.3	222.0	225.0
75°	138.0	157.5	181.5	196.5	200.3
77.5°	110.3	132.8	155.3	171.8	174.8
80°	84.8	107.3	132.8	149.3	152.3
82.5°	61.5	85.5	111.8	127.5	133.5
85°	41.3	66.0	92.3	108.8	114.8
87.5°	26.3	50.3	75.8	93.0	98.3
90°	12.8	42.8	73.6	94.7	102.2
92.5°	24.9	39.9	70.6	90.9	97.0
95°	53.0	70.2	66.9	87.2	92.4
97.5°	90.0	112.6	65.4	82.6	88.7
100°	134.7	152.7	179.7	82.7	84.2
102.5°	180.1	197.5	222.2	238.7	179.6
105°	229.4	244.4	266.9	281.9	286.4
107.5°	280.1	290.6	313.9	329.7	331.1
110°	329.4	338.4	360.9	372.8	378.9

TEST NUMBER: P1026969

CATALOG NUMBER: S125DIP-B610D850UB2750-4F0-XX-W2A-D_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	376.3	385.3	406.3	416.8	420.5
115°	422.4	431.5	451.8	462.3	462.2
117.5°	471.0	474.7	496.5	504.6	508.4
120°	516.4	517.8	537.4	548.6	549.3
122.5°	555.7	560.3	577.6	588.0	588.0
125°	597.4	602.0	617.0	625.9	627.4
127.5°	636.8	639.8	651.8	661.5	659.9
130°	673.1	676.1	687.4	695.6	695.6
132.5°	708.7	713.2	718.4	728.9	728.2
135°	742.7	746.6	750.3	758.6	757.7
137.5°	774.5	778.4	779.9	788.9	788.1
140°	804.9	806.4	806.3	816.2	814.6
142.5°	832.9	832.9	834.4	841.2	839.6
145°	860.2	860.9	860.9	865.4	863.9
147.5°	883.6	883.6	884.3	886.6	882.8
150°	906.3	904.8	906.3	907.8	902.6
152.5°	928.3	924.5	926.0	927.5	922.2
155°	946.4	941.9	943.4	945.7	939.6
157.5°	960.8	958.5	958.5	960.8	954.8
160°	976.0	971.4	972.2	975.2	969.1
162.5°	988.1	983.5	984.3	988.8	982.0
165°	998.7	994.1	994.9	999.4	993.4
167.5°	1007.0	1002.5	1003.2	1008.5	1001.7
170°	1013.8	1008.5	1009.3	1015.3	1008.5
172.5°	1018.4	1013.1	1014.6	1019.9	1013.1
175°	1021.4	1016.8	1017.6	1023.7	1016.8
177.5°	1023.7	1019.1	1019.9	1025.2	1019.1
180°	1021.4	1021.4	1021.4	1021.4	1021.4

(END OF REPORT)