

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027283

Luminaire Tested: S125RDIP-B850D375UB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027283
REPORT IS A COMBINATION OF REPORTS P1005814 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIP-B850D375UB2750-4F0-XX-W2A-F_5000K
Description: Define 5 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4558.0 lumens
Efficiency: N/A
Efficacy: 100.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 45.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027283

CATALOG NUMBER: S125RDIP-B850D375UB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1027283

CATALOG NUMBER: S125RDIP-B850D375UB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	112	112	112	112	105	105	105	105	94	94	94	83	83	83	73	73	73
1	102	98	94	91	97	93	89	86	83	80	78	74	72	70	66	64	63
2	93	86	80	75	88	81	76	71	73	69	65	65	62	59	58	56	53
3	85	76	68	63	80	72	65	60	65	59	55	58	54	50	52	48	46
4	78	67	59	53	74	64	57	51	58	52	47	52	47	43	46	43	40
5	72	60	52	46	68	57	50	44	52	46	41	47	42	38	42	38	35
6	67	54	46	40	63	52	44	39	47	41	36	42	37	33	38	34	31
7	62	49	41	35	58	47	40	34	43	36	32	39	33	30	35	31	27
8	57	45	37	32	54	43	36	31	39	33	29	35	30	27	32	28	25
9	54	41	33	28	51	39	32	27	36	30	26	33	28	24	30	25	22
10	50	38	30	26	47	36	29	25	33	27	23	30	25	22	28	23	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8515	8515	8515
5°	8516	8303	8316
10°	8433	8094	8023
15°	8314	7801	7636
20°	8166	7448	7231
25°	7996	7104	6796
30°	7789	6726	6340
35°	7577	6342	5855
40°	7376	5948	5381
45°	7134	5521	4885
50°	6889	5069	4380
55°	6604	4625	3857
60°	6312	4115	3315
65°	5966	3546	2730
70°	5560	2887	2148
75°	4999	2171	1566
80°	4217	1406	1057
85°	3156	755	595

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 7134 cd/sqm

TEST NUMBER: P1027283

CATALOG NUMBER: S125RDIP-B850D375UB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	125.1	2.7
10°-20°	349.6	7.7
20°-30°	506.9	11.1
30°-40°	577.5	12.7
40°-50°	562.8	12.3
50°-60°	473.7	10.4
60°-70°	331.9	7.3
70°-80°	170.2	3.7
80°-90°	43.1	0.9
90°-100°	15.7	0.3
100°-110°	104.1	2.3
110°-120°	187.5	4.1
120°-130°	240.7	5.3
130°-140°	258.9	5.7
140°-150°	243.0	5.3
150°-160°	196.5	4.3
160°-170°	127.1	2.8
170°-180°	43.8	1.0
0°-30°	981.5	21.5
0°-40°	1559.0	34.2
0°-60°	2595.5	56.9
0°-90°	3140.7	68.9
90°-120°	307.3	6.7
90°-150°	1049.8	23.0
90°-180°	1417.0	31.1
0°-180°	4558.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1329	1329	1329	1329	1329	
5°	1327	1323	1312	1322	1320	126
15°	1262	1256	1235	1234	1225	356
25°	1144	1129	1092	1079	1068	527
35°	986	962	916	887	873	617
45°	807	778	723	683	668	622
55°	612	580	524	479	463	548
65°	415	380	327	287	272	411
75°	221	191	149	126	120	233
85°	55	37	32	31	30	60
90°	0	3	6	7	8	4
95°	20	18	6	7	7	24
105°	101	102	102	102	102	107
115°	189	190	191	190	187	187
125°	268	271	271	270	268	240
135°	335	337	336	336	334	258
145°	388	389	389	389	387	243
155°	428	426	426	427	424	197
165°	451	449	449	452	449	127
175°	461	459	460	462	459	44
180°	461	461	461	461	461	

TEST NUMBER: P1027283

CATALOG NUMBER: S125RDIP-B850D375UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1329.0	1329.0	1329.0	1329.0	1329.0
2.5°	1332.0	1329.0	1319.0	1329.0	1328.0
5°	1327.0	1323.0	1312.0	1322.0	1320.0
7.5°	1317.0	1313.0	1299.9	1307.9	1305.9
10°	1301.9	1298.9	1284.9	1287.9	1284.9
12.5°	1284.9	1280.8	1260.8	1262.8	1257.8
15°	1261.8	1255.7	1234.7	1233.7	1224.6
17.5°	1237.7	1228.6	1203.5	1198.5	1191.5
20°	1208.6	1198.5	1166.4	1161.4	1152.4
22.5°	1176.4	1166.4	1132.3	1121.2	1114.2
25°	1144.3	1129.3	1092.1	1079.1	1068.0
27.5°	1108.2	1090.1	1051.0	1033.9	1022.9
30°	1068.0	1049.0	1006.8	983.7	974.7
32.5°	1028.9	1005.8	962.6	936.5	924.5
35°	985.7	961.6	916.5	887.4	873.3
37.5°	944.6	915.5	869.3	835.2	821.1
40°	900.4	870.3	822.1	784.0	771.9
42.5°	854.2	823.1	772.9	736.8	717.7
45°	807.0	777.9	722.7	682.6	667.5
47.5°	757.9	727.7	672.5	631.4	614.3
50°	711.7	678.6	621.3	579.2	564.1
52.5°	661.5	627.4	574.2	528.0	512.9
55°	612.3	580.2	524.0	478.8	462.7
57.5°	562.1	528.0	473.8	429.6	415.6
60°	513.9	478.8	424.6	380.4	365.4
62.5°	462.7	429.6	374.4	334.3	319.2
65°	414.6	380.4	327.2	287.1	272.0
67.5°	366.4	332.3	281.1	242.9	230.9
70°	317.2	283.1	232.9	201.8	189.7
72.5°	269.0	235.9	189.7	161.6	154.6
75°	220.8	190.7	148.6	126.5	119.5
77.5°	171.6	147.6	112.4	95.4	89.3
80°	130.5	106.4	78.3	69.3	67.3
82.5°	90.3	69.3	52.2	49.2	48.2
85°	55.2	37.1	32.1	31.1	30.1
87.5°	23.1	16.1	15.1	15.1	14.1
90°	0.3	3.1	5.5	7.2	8.2
92.5°	6.5	3.4	5.5	7.2	7.5
95°	19.5	18.5	5.5	7.2	7.2
97.5°	36.6	38.6	6.2	6.8	7.2
100°	57.1	58.1	59.5	8.6	7.2
102.5°	78.0	79.4	80.0	80.7	52.0
105°	100.6	101.9	101.9	101.9	101.6
107.5°	123.8	123.8	124.5	124.8	123.5
110°	146.4	146.4	147.1	146.0	146.4



TEST NUMBER: P1027283

CATALOG NUMBER: S125RDIP-B850D375UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	167.6	168.6	169.0	167.6	166.9
115°	188.8	190.5	190.9	189.5	187.4
117.5°	211.0	211.0	212.4	210.3	209.7
120°	231.6	231.2	232.2	231.6	229.8
122.5°	249.7	251.4	251.7	251.0	249.0
125°	268.5	270.9	270.9	269.5	268.5
127.5°	286.6	288.3	288.0	287.3	284.6
130°	303.0	304.7	305.1	304.1	302.4
132.5°	319.5	321.5	320.5	320.5	318.8
135°	334.8	336.9	336.2	335.5	333.5
137.5°	349.2	351.3	350.6	350.6	348.9
140°	363.2	363.9	363.6	364.3	362.2
142.5°	375.9	376.2	376.9	376.9	374.9
145°	388.2	388.9	388.9	389.2	387.2
147.5°	399.1	399.1	399.5	399.8	397.4
150°	409.4	408.7	409.4	410.1	407.4
152.5°	419.3	417.6	418.3	419.0	416.6
155°	427.5	425.5	426.2	427.2	424.5
157.5°	434.0	433.0	433.0	434.0	431.3
160°	440.9	438.8	439.2	440.5	437.8
162.5°	446.3	444.3	444.6	446.7	443.6
165°	451.1	449.1	449.4	451.5	448.7
167.5°	454.9	452.8	453.2	455.6	452.5
170°	458.0	455.6	455.9	458.7	455.6
172.5°	460.0	457.6	458.3	460.7	457.6
175°	461.4	459.3	459.7	462.4	459.3
177.5°	462.4	460.4	460.7	463.1	460.4
180°	461.4	461.4	461.4	461.4	461.4

(END OF REPORT)