

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027290

Luminaire Tested: S125RDIP-B850D610UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027290
REPORT IS A COMBINATION OF REPORTS P1005851 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIP-B850D610UB2750-4F0-XX-W2A-F_3000K
Description: Define 5 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5636.0 lumens
Efficiency: N/A
Efficacy: 109.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 51.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027290

CATALOG NUMBER: S125RDIP-B850D610UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1027290

CATALOG NUMBER: S125RDIP-B850D610UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	63	63	63
1	100	96	92	88	93	89	86	83	77	75	73	67	65	63	57	55	54
2	91	84	78	73	85	78	73	68	68	64	61	59	56	53	50	48	46
3	83	74	67	61	77	69	63	57	60	55	51	52	48	45	45	42	39
4	76	66	58	52	71	61	54	49	54	48	44	47	42	39	40	37	34
5	70	59	50	44	65	55	48	42	48	42	38	42	37	34	36	33	30
6	65	53	45	39	60	49	42	37	44	38	33	38	33	30	33	29	26
7	60	48	40	34	56	45	38	33	40	34	29	35	30	26	30	26	24
8	56	43	36	30	52	41	34	29	36	30	26	32	27	24	28	24	21
9	52	40	32	27	48	37	31	26	33	28	24	29	25	21	26	22	19
10	49	36	29	24	45	34	28	23	31	25	21	27	23	19	24	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8857	8857	8857
5°	8858	8636	8650
10°	8772	8418	8344
15°	8647	8114	7943
20°	8494	7747	7521
25°	8317	7389	7069
30°	8102	6996	6594
35°	7882	6596	6089
40°	7672	6186	5597
45°	7420	5743	5081
50°	7165	5273	4556
55°	6869	4810	4012
60°	6566	4280	3448
65°	6205	3689	2839
70°	5783	3002	2234
75°	5201	2257	1628
80°	4385	1461	1099
85°	3282	785	618

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7420 cd/sqm

TEST NUMBER: P1027290

CATALOG NUMBER: S125RDIP-B850D610UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	130.1	2.3
10°-20°	363.6	6.5
20°-30°	527.2	9.4
30°-40°	600.6	10.7
40°-50°	585.4	10.4
50°-60°	492.7	8.7
60°-70°	345.2	6.1
70°-80°	177.0	3.1
80°-90°	45.3	0.8
90°-100°	26.2	0.5
100°-110°	174.1	3.1
110°-120°	313.4	5.6
120°-130°	402.3	7.1
130°-140°	432.7	7.7
140°-150°	406.1	7.2
150°-160°	328.5	5.8
160°-170°	212.4	3.8
170°-180°	73.3	1.3
0°-30°	1020.9	18.1
0°-40°	1621.5	28.8
0°-60°	2699.6	47.9
0°-90°	3267.1	58.0
90°-120°	513.6	9.1
90°-150°	1754.7	31.1
90°-180°	2369.0	42.0
0°-180°	5636.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1382	1382	1382	1382	1382	
5°	1380	1376	1365	1375	1373	131
15°	1312	1306	1284	1283	1274	370
25°	1190	1175	1136	1122	1111	548
35°	1025	1000	953	923	908	642
45°	839	809	752	710	694	647
55°	637	604	545	498	481	570
65°	431	396	340	299	283	427
75°	230	198	154	132	124	243
85°	57	39	33	32	31	63
90°	1	5	9	12	14	5
95°	33	31	9	12	12	40
105°	168	170	170	170	170	178
115°	316	318	319	317	313	313
125°	449	453	453	450	449	401
135°	560	563	562	561	557	431
145°	649	650	650	650	647	406
155°	715	711	712	714	709	329
165°	754	751	751	755	750	213
175°	771	768	768	773	768	73
180°	771	771	771	771	771	

TEST NUMBER: P1027290

CATALOG NUMBER: S125RDIP-B850D610UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1382.3	1382.3	1382.3	1382.3	1382.3
2.5°	1385.5	1382.3	1371.9	1382.3	1381.3
5°	1380.3	1376.1	1364.6	1375.0	1373.0
7.5°	1369.8	1365.6	1352.1	1360.4	1358.3
10°	1354.2	1351.0	1336.4	1339.5	1336.4
12.5°	1336.4	1332.2	1311.4	1313.4	1308.2
15°	1312.4	1306.1	1284.2	1283.2	1273.8
17.5°	1287.3	1277.9	1251.8	1246.6	1239.3
20°	1257.1	1246.6	1213.2	1208.0	1198.6
22.5°	1223.7	1213.2	1177.7	1166.2	1158.9
25°	1190.2	1174.6	1135.9	1122.4	1110.9
27.5°	1152.7	1133.9	1093.1	1075.4	1063.9
30°	1110.9	1091.1	1047.2	1023.2	1013.8
32.5°	1070.2	1046.2	1001.3	974.1	961.6
35°	1025.3	1000.2	953.2	923.0	908.3
37.5°	982.5	952.2	904.2	868.7	854.0
40°	936.5	905.2	855.1	815.4	802.9
42.5°	888.5	856.1	803.9	766.3	746.5
45°	839.4	809.2	751.7	710.0	694.3
47.5°	788.3	757.0	699.5	656.7	639.0
50°	740.2	705.8	646.3	602.4	586.8
52.5°	688.0	652.5	597.2	549.2	533.5
55°	636.9	603.5	545.0	498.0	481.3
57.5°	584.7	549.2	492.8	446.9	432.2
60°	534.6	498.0	441.6	395.7	380.0
62.5°	481.3	446.9	389.4	347.7	332.0
65°	431.2	395.7	340.4	298.6	282.9
67.5°	381.1	345.6	292.3	252.7	240.1
70°	329.9	294.4	242.2	209.9	197.3
72.5°	279.8	245.4	197.3	168.1	160.8
75°	229.7	198.4	154.5	131.6	124.2
77.5°	178.5	153.5	116.9	99.2	92.9
80°	135.7	110.7	81.4	72.0	70.0
82.5°	94.0	72.0	54.3	51.2	50.1
85°	57.4	38.6	33.4	32.4	31.3
87.5°	24.0	16.7	15.7	15.7	14.6
90°	0.6	5.1	9.1	12.0	13.7
92.5°	10.9	5.7	9.1	12.0	12.6
95°	32.6	30.9	9.1	12.0	12.0
97.5°	61.2	64.6	10.3	11.4	12.0
100°	95.5	97.2	99.5	14.3	12.0
102.5°	130.3	132.6	133.8	134.9	86.9
105°	168.1	170.4	170.4	170.4	169.8
107.5°	206.9	206.9	208.1	208.7	206.4
110°	244.7	244.7	245.8	244.1	244.7

TEST NUMBER: P1027290

CATALOG NUMBER: S125RDIP-B850D610UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	280.1	281.8	282.4	280.1	279.0
115°	315.6	318.4	319.0	316.7	313.3
117.5°	352.7	352.7	355.0	351.6	350.4
120°	387.0	386.4	388.2	387.0	384.2
122.5°	417.3	420.2	420.7	419.6	416.2
125°	448.8	452.8	452.8	450.5	448.8
127.5°	479.0	481.9	481.3	480.2	475.6
130°	506.5	509.3	509.9	508.2	505.3
132.5°	533.9	537.4	535.6	535.6	532.8
135°	559.7	563.1	561.9	560.8	557.4
137.5°	583.7	587.1	585.9	585.9	583.1
140°	607.1	608.2	607.7	608.8	605.4
142.5°	628.3	628.8	630.0	630.0	626.5
145°	648.8	650.0	650.0	650.5	647.1
147.5°	667.1	667.1	667.7	668.3	664.3
150°	684.3	683.1	684.3	685.4	680.8
152.5°	700.9	698.0	699.1	700.3	696.3
155°	714.6	711.1	712.3	714.0	709.4
157.5°	725.4	723.7	723.7	725.4	720.9
160°	736.9	733.4	734.0	736.3	731.7
162.5°	746.0	742.6	743.2	746.6	741.4
165°	754.0	750.6	751.2	754.6	750.0
167.5°	760.3	756.9	757.4	761.4	756.3
170°	765.4	761.4	762.0	766.6	761.4
172.5°	768.9	764.9	766.0	770.0	764.9
175°	771.2	767.7	768.3	772.9	767.7
177.5°	772.9	769.5	770.0	774.0	769.5
180°	771.2	771.2	771.2	771.2	771.2

(END OF REPORT)